

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999466

Luminaire Tested: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999466
REPORT IS A COMBINATION OF REPORTS P988017 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6803.9 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999466

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999466

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	52	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	25	21	26	21	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25830	25830	25830
5°	25872	24574	24392
10°	25617	23307	22538
15°	25266	21811	20425
20°	24800	20110	18215
25°	24322	18365	16192
30°	23681	16665	13984
35°	23054	14951	12087
40°	22417	13268	10134
45°	21674	11530	8430
50°	20905	9854	6862
55°	20107	8179	5449
60°	19178	6541	4123
65°	18112	4988	3351
70°	16820	3618	2664
75°	15199	2759	2035
80°	12854	1868	1367
85°	8970	857	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21674 cd/sqm

TEST NUMBER: P999466

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.9	2.2
10°-20°	419.8	6.2
20°-30°	589.4	8.7
30°-40°	642.5	9.4
40°-50°	590.5	8.7
50°-60°	463.8	6.8
60°-70°	301.9	4.4
70°-80°	155.4	2.3
80°-90°	42.9	0.6
90°-100°	200.3	2.9
100°-110°	677.1	10.0
110°-120°	711.8	10.5
120°-130°	585.3	8.6
130°-140°	470.3	6.9
140°-150°	355.3	5.2
150°-160°	249.8	3.7
160°-170°	147.1	2.2
170°-180°	47.8	0.7
0°-30°	1162.2	17.1
0°-40°	1804.7	26.5
0°-60°	2859.0	42.0
0°-90°	3359.1	49.4
90°-120°	1589.2	23.4
90°-150°	3000.1	44.1
90°-180°	3445.0	50.6
0°-180°	6803.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1632	1632	1632	1632	1632	
5°	1632	1624	1605	1618	1614	155
15°	1552	1536	1486	1458	1443	437
25°	1409	1362	1264	1204	1181	648
35°	1214	1139	1009	916	883	760
45°	992	893	738	634	598	766
55°	755	639	480	391	363	674
65°	510	390	257	207	202	505
75°	272	168	118	108	106	287
85°	64	32	28	28	28	73
90°	1	13	32	31	31	5
95°	33	82	372	141	108	34
105°	116	175	704	1258	1071	123
115°	204	258	589	1216	1409	203
125°	285	337	566	985	1143	253
135°	334	399	560	828	947	258
145°	382	439	557	691	756	240
155°	434	469	541	611	636	200
165°	473	487	518	549	558	133
175°	493	494	498	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P999466

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.8	1631.8	1631.8	1631.8	1631.8
2.5°	1639.2	1631.8	1615.6	1630.3	1627.4
5°	1631.8	1624.4	1605.2	1618.5	1614.1
7.5°	1618.5	1609.6	1589.0	1594.9	1587.5
10°	1600.8	1590.4	1560.9	1556.5	1547.6
12.5°	1578.6	1565.3	1525.5	1516.6	1500.4
15°	1552.1	1535.8	1485.6	1457.5	1442.8
17.5°	1521.0	1497.4	1435.4	1402.9	1379.3
20°	1485.6	1456.1	1382.2	1345.3	1312.8
22.5°	1447.2	1413.2	1327.6	1277.4	1255.2
25°	1408.8	1361.6	1264.1	1203.5	1181.4
27.5°	1363.0	1312.8	1205.0	1135.6	1101.6
30°	1314.3	1258.2	1140.0	1064.7	1024.9
32.5°	1267.0	1199.1	1078.0	989.4	952.5
35°	1213.9	1138.6	1008.6	915.6	883.1
37.5°	1162.2	1081.0	943.6	841.7	804.8
40°	1107.6	1019.0	875.7	770.9	732.5
42.5°	1051.4	956.9	807.8	698.5	661.6
45°	992.4	893.4	738.4	633.5	598.1
47.5°	936.3	831.4	671.9	567.1	534.6
50°	874.2	769.4	606.9	505.0	474.0
52.5°	813.7	702.9	544.9	447.5	419.4
55°	754.6	639.4	479.9	391.3	363.3
57.5°	694.1	575.9	422.3	339.7	316.0
60°	632.0	513.9	361.8	286.5	262.9
62.5°	571.5	453.4	310.1	239.2	227.4
65°	509.5	389.9	257.0	206.7	202.3
67.5°	450.4	330.8	206.7	181.6	177.2
70°	388.4	273.2	171.3	156.5	150.6
72.5°	329.3	220.0	143.2	131.4	128.5
75°	271.7	168.3	118.1	107.8	106.3
77.5°	214.1	119.6	93.0	87.1	84.2
80°	161.0	85.7	70.9	65.0	65.0
82.5°	112.2	57.6	48.7	45.8	45.8
85°	63.5	32.5	28.1	28.1	28.1
87.5°	23.6	11.8	11.8	10.3	10.3
90°	1.0	12.8	32.3	30.9	31.4
92.5°	14.3	45.2	146.3	67.5	58.0
95°	33.3	81.7	372.5	140.6	108.3
97.5°	49.4	107.8	607.2	282.2	181.5
100°	73.2	132.1	750.6	562.0	340.2
102.5°	95.0	153.9	755.4	950.2	663.2
105°	115.9	174.8	704.1	1258.5	1070.8
107.5°	138.7	195.7	656.6	1370.1	1345.4
110°	161.5	217.1	624.3	1352.0	1457.6

TEST NUMBER: P999466

CATALOG NUMBER: SA2XXRDIP-B1005D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.4	237.6	603.4	1290.8	1455.7
115°	204.3	258.0	589.1	1215.8	1409.1
117.5°	227.1	278.4	581.5	1144.0	1338.8
120°	248.0	298.4	574.8	1079.8	1271.3
122.5°	267.9	318.8	571.0	1030.0	1201.0
125°	285.0	337.3	566.3	984.8	1143.0
127.5°	299.3	354.9	563.4	946.4	1088.9
130°	311.7	370.6	561.5	907.4	1044.2
132.5°	323.1	385.8	560.6	867.0	997.7
135°	334.5	399.1	559.6	827.6	947.3
137.5°	344.9	410.4	559.6	787.6	898.9
140°	357.3	421.0	558.7	752.5	848.5
142.5°	369.6	429.5	558.7	718.8	798.1
145°	382.0	439.0	556.8	691.2	756.3
147.5°	395.3	446.6	553.9	667.0	719.3
150°	408.6	454.2	551.1	646.2	687.0
152.5°	421.9	461.8	546.3	628.6	659.4
155°	434.2	468.9	540.6	611.4	635.7
157.5°	444.7	474.6	534.9	595.3	614.8
160°	455.1	480.3	529.2	579.2	594.8
162.5°	465.6	484.6	524.5	563.9	575.8
165°	473.2	487.4	517.8	549.2	557.7
167.5°	479.8	490.3	512.1	535.9	540.6
170°	486.5	491.7	507.4	523.6	525.4
172.5°	490.3	493.2	501.7	512.6	513.1
175°	493.1	493.6	497.9	504.0	502.6
177.5°	495.0	494.1	494.1	497.9	495.0
180°	494.1	494.1	494.1	494.1	494.1

(END OF REPORT)