

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997628

Luminaire Tested: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P997628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2946.0 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	110	106	102	98		107	103	100	97		99	96	94		95	93	91		92	90	88		86			
2	101	94	87	82		98	92	86	81		88	83	79		85	81	78		82	79	76		74			
3	93	83	76	70		90	82	75	69		79	73	68		76	71	67		74	69	66		64			
4	86	75	66	60		83	73	66	60		71	64	59		69	63	58		66	62	58		55			
5	79	67	59	53		77	66	58	52		64	57	52		62	56	51		60	55	51		49			
6	74	61	53	47		72	60	52	46		58	51	46		57	51	46		55	50	45		43			
7	69	56	48	42		67	55	47	42		54	46	41		52	46	41		51	45	41		39			
8	64	51	43	38		63	51	43	38		49	42	37		48	42	37		47	41	37		35			
9	60	47	39	34		59	47	39	34		46	39	34		45	38	34		44	38	34		32			
10	56	44	36	31		55	43	36	31		42	36	31		41	35	31		41	35	31		29			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21233	23696	21315	18852
10°	21034	27155	21166	16315
15°	20570	30039	20857	14415
20°	20297	29582	20297	13139
25°	19700	26674	19790	12333
30°	18684	22042	19040	11744
35°	17790	16064	18087	11324
40°	16754	12830	16944	11092
45°	15462	11213	15715	10777
50°	14357	10540	14382	10565
55°	13087	9714	13170	10283
60°	11730	8902	11891	9846
65°	10532	8113	10723	9420
70°	9358	7363	9594	8789
75°	8036	6526	8348	7786
80°	6545	5615	7019	6272
85°	4849	5031	5213	3723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 155°

Vertical Angle: 45°

Luminance: 27593 cd/sqm

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	4.3
10°-20°	370.2	12.6
20°-30°	537.2	18.2
30°-40°	566.3	19.2
40°-50°	501.2	17.0
50°-60°	400.2	13.6
60°-70°	271.8	9.2
70°-80°	139.1	4.7
80°-90°	32.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.6	35.1
0°-40°	1600.9	54.3
0°-60°	2502.3	84.9
0°-90°	2946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2946.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	33
90°	0	0	0	0	0	

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P997628

CATALOG NUMBER: SA2XXDP-B675DB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.57	24.09	22.94	24.40	24.72	18.84	20.36	19.20	20.67	20.98
	3H	23.69	25.05	24.06	25.38	25.74	20.25	21.61	20.63	21.94	22.30
	4H	24.01	25.29	24.41	25.64	26.01	20.76	22.04	21.16	22.38	22.76
	6H	24.20	25.38	24.61	25.75	26.14	21.12	22.30	21.53	22.66	23.05
	8H	24.24	25.36	24.67	25.75	26.15	21.23	22.35	21.65	22.74	23.14
	12H	24.25	25.33	24.68	25.71	26.14	21.30	22.38	21.73	22.76	23.19
4H	2H	22.69	23.97	23.09	24.32	24.69	19.64	20.91	20.04	21.26	21.64
	3H	24.02	25.08	24.43	25.48	25.88	21.21	22.27	21.62	22.67	23.07
	4H	24.50	25.45	24.93	25.87	26.30	21.81	22.77	22.24	23.18	23.62
	6H	24.83	25.66	25.28	26.10	26.56	22.27	23.09	22.72	23.54	24.00
	8H	24.90	25.68	25.37	26.12	26.59	22.41	23.18	22.87	23.63	24.10
	12H	24.94	25.64	25.43	26.11	26.58	22.51	23.21	23.00	23.68	24.16
8H	4H	24.58	25.35	25.04	25.80	26.27	22.22	22.99	22.68	23.44	23.91
	6H	24.99	25.63	25.48	26.12	26.60	22.76	23.40	23.26	23.89	24.37
	8H	25.12	25.69	25.63	26.20	26.69	22.96	23.53	23.47	24.04	24.53
	12H	25.21	25.71	25.72	26.20	26.77	23.13	23.63	23.63	24.12	24.69
12H	4H	24.57	25.26	25.05	25.74	26.21	22.27	22.97	22.76	23.45	23.92
	6H	24.98	25.56	25.49	26.07	26.55	22.84	23.41	23.35	23.92	24.41
	8H	25.15	25.65	25.66	26.15	26.71	23.09	23.59	23.60	24.09	24.65

END OF REPORT