

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999568

Luminaire Tested: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P999568  
REPORT IS A COMBINATION OF REPORTS P988121 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1  
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}  
{m-EER=0.792}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3007.0 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 28.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

### Luminous Intensity Polar Plot



TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |    | 20 |    |    |    |    | 20 |    |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |    | 50 |    |    |    |    | 30 |    |    |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 104 | 104 | 104 | 104 | 94 | 94 | 94 | 94 | 76 | 76 | 76 | 59 | 59 | 59 | 44 | 44 | 44 | 44 | 44 | 37 |
| 1   | 95  | 91  | 88  | 84  | 86 | 83 | 80 | 77 | 67 | 65 | 63 | 53 | 52 | 50 | 40 | 39 | 38 | 38 | 38 | 32 |
| 2   | 87  | 80  | 75  | 70  | 79 | 73 | 68 | 64 | 60 | 56 | 53 | 47 | 45 | 43 | 36 | 34 | 33 | 33 | 33 | 28 |
| 3   | 80  | 71  | 64  | 59  | 72 | 65 | 59 | 54 | 53 | 49 | 46 | 42 | 39 | 37 | 32 | 30 | 29 | 29 | 29 | 24 |
| 4   | 73  | 63  | 56  | 50  | 67 | 58 | 52 | 47 | 48 | 43 | 39 | 38 | 35 | 32 | 29 | 27 | 25 | 25 | 25 | 21 |
| 5   | 68  | 57  | 49  | 44  | 61 | 52 | 45 | 40 | 43 | 38 | 34 | 34 | 31 | 28 | 27 | 24 | 23 | 23 | 23 | 19 |
| 6   | 62  | 51  | 44  | 38  | 57 | 47 | 40 | 35 | 39 | 34 | 30 | 31 | 28 | 25 | 24 | 22 | 20 | 20 | 20 | 17 |
| 7   | 58  | 46  | 39  | 34  | 53 | 43 | 36 | 31 | 35 | 31 | 27 | 29 | 25 | 23 | 22 | 20 | 18 | 18 | 18 | 16 |
| 8   | 54  | 42  | 35  | 30  | 49 | 39 | 32 | 28 | 32 | 28 | 24 | 26 | 23 | 20 | 21 | 18 | 17 | 17 | 17 | 14 |
| 9   | 50  | 39  | 32  | 27  | 46 | 36 | 29 | 25 | 30 | 25 | 22 | 24 | 21 | 18 | 19 | 17 | 15 | 15 | 15 | 13 |
| 10  | 47  | 35  | 29  | 24  | 43 | 33 | 27 | 23 | 28 | 23 | 20 | 23 | 19 | 17 | 18 | 16 | 14 | 14 | 14 | 12 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 10112 | 10112 | 10112 | 10112 |
| 5°  | 10136 | 10742 | 10171 | 8581  |
| 10° | 10024 | 11353 | 10096 | 7086  |
| 15° | 9806  | 11356 | 9972  | 5323  |
| 20° | 9545  | 9388  | 9752  | 4391  |
| 25° | 9228  | 5866  | 9428  | 3736  |
| 30° | 8823  | 3755  | 9063  | 3216  |
| 35° | 8330  | 2887  | 8599  | 2752  |
| 40° | 7782  | 2427  | 8114  | 2407  |
| 45° | 7194  | 2065  | 7495  | 2021  |
| 50° | 6593  | 1755  | 6901  | 1749  |
| 55° | 5926  | 1525  | 6246  | 1504  |
| 60° | 5335  | 1162  | 5617  | 1149  |
| 65° | 4781  | 874   | 5066  | 992   |
| 70° | 4170  | 699   | 4500  | 808   |
| 75° | 3524  | 536   | 3849  | 612   |
| 80° | 2802  | 364   | 3010  | 402   |
| 85° | 1949  | 188   | 2133  | 198   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9250 cd/sqm

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 60.6   | 2.0       |
| 10°-20°   | 169.1  | 5.6       |
| 20°-30°   | 217.7  | 7.2       |
| 30°-40°   | 206.5  | 6.9       |
| 40°-50°   | 177.0  | 5.9       |
| 50°-60°   | 134.8  | 4.5       |
| 60°-70°   | 85.0   | 2.8       |
| 70°-80°   | 42.4   | 1.4       |
| 80°-90°   | 12.8   | 0.4       |
| 90°-100°  | 42.1   | 1.4       |
| 100°-110° | 133.7  | 4.4       |
| 110°-120° | 228.8  | 7.6       |
| 120°-130° | 300.9  | 10.0      |
| 130°-140° | 337.8  | 11.2      |
| 140°-150° | 331.2  | 11.0      |
| 150°-160° | 277.9  | 9.2       |
| 160°-170° | 184.3  | 6.1       |
| 170°-180° | 64.4   | 2.1       |
| 0°-30°    | 447.4  | 14.9      |
| 0°-40°    | 653.9  | 21.7      |
| 0°-60°    | 965.7  | 32.1      |
| 0°-90°    | 1105.9 | 36.8      |
| 90°-120°  | 404.6  | 13.5      |
| 90°-150°  | 1374.5 | 45.7      |
| 90°-180°  | 1901.0 | 63.2      |
| 0°-180°   | 3007.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°  | 90° | 180° | 270° | 360° | Flux |
|------|-----|-----|------|------|------|------|
| 0°   | 639 | 639 | 639  | 639  | 639  |      |
| 5°   | 639 | 711 | 642  | 568  | 639  | 61   |
| 15°  | 602 | 802 | 613  | 376  | 602  | 169  |
| 25°  | 534 | 428 | 546  | 273  | 534  | 245  |
| 35°  | 439 | 211 | 453  | 201  | 439  | 274  |
| 45°  | 329 | 146 | 343  | 143  | 329  | 254  |
| 55°  | 222 | 102 | 234  | 100  | 222  | 200  |
| 65°  | 134 | 53  | 142  | 60   | 134  | 133  |
| 75°  | 63  | 28  | 69   | 32   | 63   | 68   |
| 85°  | 14  | 8   | 15   | 8    | 14   | 16   |
| 90°  | 1   | 20  | 1    | 20   | 1    | 3    |
| 95°  | 30  | 36  | 30   | 36   | 30   | 33   |
| 105° | 123 | 127 | 123  | 127  | 123  | 130  |
| 115° | 230 | 230 | 230  | 230  | 230  | 227  |
| 125° | 334 | 335 | 334  | 335  | 334  | 298  |
| 135° | 432 | 437 | 432  | 437  | 432  | 334  |
| 145° | 524 | 530 | 524  | 530  | 524  | 328  |
| 155° | 600 | 604 | 600  | 604  | 600  | 276  |
| 165° | 652 | 653 | 652  | 653  | 652  | 184  |
| 175° | 679 | 676 | 679  | 676  | 679  | 64   |
| 180° | 680 | 680 | 680  | 680  | 680  |      |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 5°    | 10°   | 15°   | 20°   | 22.5° | 25°   | 30°   | 35°   | 40°   | 45°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 642.8 | 645.5 | 646.8 | 648.6 | 652.6 | 655.3 | 659.3 | 660.2 | 659.7 | 661.5 | 656.6 |
| 5°     | 639.3 | 645.1 | 650.4 | 654.8 | 661.9 | 666.4 | 671.3 | 677.0 | 678.4 | 685.0 | 681.0 |
| 7.5°   | 634.4 | 642.8 | 650.4 | 659.3 | 669.9 | 675.7 | 683.2 | 692.1 | 696.1 | 704.1 | 706.3 |
| 10°    | 626.4 | 638.4 | 651.3 | 660.6 | 675.2 | 685.5 | 692.6 | 706.8 | 716.1 | 728.1 | 726.3 |
| 12.5°  | 613.5 | 629.1 | 646.4 | 661.9 | 681.0 | 687.7 | 701.0 | 715.6 | 727.6 | 738.7 | 748.5 |
| 15°    | 602.4 | 620.2 | 639.3 | 658.4 | 680.1 | 692.6 | 705.9 | 725.0 | 737.8 | 757.4 | 765.8 |
| 17.5°  | 587.3 | 610.0 | 632.6 | 653.9 | 679.7 | 693.9 | 710.3 | 729.0 | 748.1 | 766.7 | 773.4 |
| 20°    | 571.8 | 596.2 | 620.6 | 649.5 | 678.8 | 692.6 | 709.4 | 732.5 | 751.2 | 765.8 | 765.8 |
| 22.5°  | 553.2 | 582.9 | 610.9 | 638.4 | 670.4 | 690.3 | 707.7 | 734.7 | 748.1 | 751.2 | 739.2 |
| 25°    | 534.5 | 564.3 | 594.9 | 629.1 | 665.5 | 683.2 | 702.8 | 728.1 | 732.5 | 720.1 | 689.0 |
| 27.5°  | 512.3 | 545.6 | 580.2 | 617.1 | 655.3 | 677.5 | 695.2 | 712.1 | 703.7 | 670.4 | 622.0 |
| 30°    | 489.7 | 525.6 | 564.7 | 599.8 | 645.9 | 666.4 | 681.5 | 686.3 | 659.7 | 605.5 | 542.9 |
| 32.5°  | 466.1 | 501.2 | 542.5 | 584.7 | 631.3 | 650.8 | 660.6 | 647.7 | 598.9 | 530.5 | 454.2 |
| 35°    | 438.6 | 478.1 | 521.2 | 565.1 | 611.3 | 626.0 | 631.7 | 600.2 | 537.6 | 449.3 | 373.4 |
| 37.5°  | 413.8 | 453.3 | 499.4 | 544.3 | 589.1 | 597.1 | 591.3 | 542.1 | 462.6 | 375.1 | 301.0 |
| 40°    | 384.5 | 426.6 | 471.9 | 522.1 | 558.9 | 561.2 | 546.9 | 483.0 | 384.5 | 302.3 | 256.6 |
| 42.5°  | 357.4 | 400.0 | 445.3 | 496.3 | 524.3 | 516.8 | 497.7 | 413.8 | 321.0 | 260.6 | 223.8 |
| 45°    | 329.4 | 369.8 | 418.6 | 463.9 | 483.9 | 466.1 | 437.3 | 348.1 | 269.5 | 224.2 | 195.8 |
| 47.5°  | 302.3 | 340.1 | 388.5 | 432.0 | 435.5 | 415.5 | 381.4 | 291.7 | 233.5 | 197.1 | 174.0 |
| 50°    | 275.7 | 313.4 | 358.7 | 394.7 | 391.1 | 363.6 | 325.0 | 253.5 | 202.9 | 174.0 | 154.9 |
| 52.5°  | 249.1 | 283.2 | 327.2 | 355.6 | 340.5 | 313.9 | 275.7 | 214.9 | 177.1 | 151.8 | 137.2 |
| 55°    | 222.4 | 254.4 | 292.1 | 315.6 | 291.7 | 261.0 | 234.0 | 184.2 | 153.6 | 133.2 | 122.1 |
| 57.5°  | 200.2 | 225.5 | 260.2 | 274.4 | 245.5 | 221.5 | 198.0 | 158.5 | 133.2 | 118.5 | 105.7 |
| 60°    | 175.8 | 198.9 | 227.3 | 235.7 | 206.0 | 186.5 | 166.5 | 134.1 | 114.1 | 101.2 | 92.8  |
| 62.5°  | 154.9 | 174.0 | 195.8 | 195.8 | 169.6 | 154.9 | 139.8 | 112.3 | 95.9  | 85.7  | 81.7  |
| 65°    | 134.5 | 148.3 | 163.8 | 162.0 | 139.8 | 127.0 | 115.0 | 92.8  | 80.4  | 73.3  | 69.3  |
| 67.5°  | 114.5 | 125.2 | 135.4 | 129.2 | 113.2 | 102.1 | 91.0  | 75.0  | 66.6  | 61.7  | 56.4  |
| 70°    | 96.3  | 104.8 | 110.1 | 104.3 | 88.3  | 79.0  | 71.0  | 60.4  | 53.7  | 47.5  | 44.4  |
| 72.5°  | 80.8  | 84.4  | 86.1  | 79.0  | 65.7  | 60.4  | 54.6  | 47.1  | 41.3  | 38.2  | 37.3  |
| 75°    | 63.0  | 66.1  | 64.8  | 59.5  | 48.4  | 44.4  | 40.0  | 34.6  | 33.3  | 31.5  | 30.6  |
| 77.5°  | 49.3  | 49.3  | 47.1  | 42.2  | 34.6  | 31.5  | 29.7  | 27.1  | 25.7  | 25.3  | 24.4  |
| 80°    | 35.1  | 34.6  | 33.3  | 28.0  | 23.5  | 21.8  | 21.8  | 20.0  | 19.5  | 18.6  | 18.6  |
| 82.5°  | 23.1  | 23.1  | 21.3  | 16.9  | 15.5  | 15.1  | 14.7  | 13.8  | 13.8  | 13.3  | 13.3  |
| 85°    | 13.8  | 12.9  | 10.7  | 9.3   | 8.9   | 8.9   | 8.4   | 8.0   | 8.4   | 8.0   | 8.0   |
| 87.5°  | 6.2   | 4.9   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   |
| 90°    | 0.6   | 2.1   | 3.7   | 5.2   | 6.7   | 7.5   | 8.9   | 11.7  | 14.5  | 17.3  | 20.1  |
| 92.5°  | 12.6  | 13.6  | 14.6  | 15.7  | 16.7  | 17.2  | 17.3  | 17.4  | 17.5  | 17.7  | 17.8  |
| 95°    | 29.8  | 31.1  | 32.4  | 33.7  | 35.0  | 35.6  | 35.7  | 36.0  | 36.2  | 36.5  | 36.7  |
| 97.5°  | 49.9  | 51.1  | 52.2  | 53.4  | 54.5  | 55.1  | 55.4  | 55.9  | 56.4  | 56.9  | 57.4  |
| 100°   | 72.9  | 73.9  | 74.9  | 76.0  | 77.0  | 77.5  | 77.7  | 78.1  | 78.4  | 78.8  | 79.2  |
| 102.5° | 97.0  | 97.8  | 98.5  | 99.3  | 100.0 | 100.4 | 100.7 | 101.2 | 101.7 | 102.2 | 102.7 |
| 105°   | 123.4 | 123.8 | 124.2 | 124.5 | 124.9 | 125.1 | 125.2 | 125.5 | 125.7 | 126.0 | 126.2 |
| 107.5° | 149.8 | 150.3 | 150.8 | 151.3 | 151.8 | 152.1 | 152.1 | 152.1 | 152.1 | 152.1 | 152.1 |
| 110°   | 175.0 | 175.8 | 176.6 | 177.3 | 178.1 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 5°    | 10°   | 15°   | 20°   | 22.5° | 25°   | 30°   | 35°   | 40°   | 45°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 202.6 | 203.4 | 204.1 | 204.9 | 205.6 | 206.0 | 205.9 | 205.8 | 205.7 | 205.5 | 205.4 |
| 115°   | 229.5 | 230.3 | 231.1 | 231.8 | 232.6 | 233.0 | 232.9 | 232.6 | 232.3 | 232.1 | 231.8 |
| 117.5° | 256.5 | 257.5 | 258.5 | 259.6 | 260.6 | 261.1 | 260.8 | 260.1 | 259.5 | 258.8 | 258.2 |
| 120°   | 283.5 | 284.5 | 285.5 | 286.6 | 287.6 | 288.1 | 287.6 | 286.6 | 285.5 | 284.5 | 283.5 |
| 122.5° | 308.1 | 309.4 | 310.7 | 312.0 | 313.3 | 313.9 | 313.6 | 312.9 | 312.3 | 311.6 | 311.0 |
| 125°   | 334.0 | 335.1 | 336.3 | 337.4 | 338.5 | 339.1 | 338.9 | 338.5 | 338.2 | 337.8 | 337.4 |
| 127.5° | 359.2 | 360.6 | 362.0 | 363.4 | 364.8 | 365.5 | 365.2 | 364.7 | 364.2 | 363.7 | 363.2 |
| 130°   | 382.7 | 384.4 | 386.0 | 387.7 | 389.4 | 390.2 | 390.1 | 389.8 | 389.5 | 389.3 | 389.0 |
| 132.5° | 409.1 | 410.4 | 411.7 | 413.0 | 414.3 | 414.9 | 415.0 | 415.1 | 415.2 | 415.3 | 415.4 |
| 135°   | 432.1 | 433.5 | 434.9 | 436.3 | 437.7 | 438.4 | 438.5 | 438.8 | 439.0 | 439.3 | 439.5 |
| 137.5° | 457.3 | 458.5 | 459.6 | 460.8 | 461.9 | 462.5 | 462.6 | 462.9 | 463.1 | 463.4 | 463.6 |
| 140°   | 479.7 | 480.9 | 482.0 | 483.2 | 484.3 | 484.9 | 485.2 | 485.8 | 486.5 | 487.1 | 487.7 |
| 142.5° | 502.7 | 503.8 | 505.0 | 506.1 | 507.2 | 507.8 | 508.0 | 508.4 | 508.7 | 509.1 | 509.5 |
| 145°   | 524.5 | 525.4 | 526.3 | 527.2 | 528.1 | 528.5 | 528.9 | 529.6 | 530.4 | 531.1 | 531.9 |
| 147.5° | 544.0 | 545.1 | 546.3 | 547.4 | 548.5 | 549.1 | 549.4 | 549.9 | 550.4 | 550.9 | 551.4 |
| 150°   | 564.1 | 564.9 | 565.6 | 566.4 | 567.1 | 567.5 | 567.8 | 568.3 | 568.8 | 569.3 | 569.8 |
| 152.5° | 581.8 | 582.6 | 583.4 | 584.1 | 584.9 | 585.3 | 585.6 | 586.3 | 586.9 | 587.6 | 588.2 |
| 155°   | 599.6 | 600.0 | 600.4 | 600.8 | 601.2 | 601.4 | 601.6 | 602.0 | 602.3 | 602.7 | 603.1 |
| 157.5° | 615.1 | 615.4 | 615.6 | 615.9 | 616.2 | 616.3 | 616.4 | 616.7 | 616.9 | 617.2 | 617.4 |
| 160°   | 628.9 | 629.1 | 629.4 | 629.6 | 629.9 | 630.0 | 630.1 | 630.2 | 630.3 | 630.5 | 630.6 |
| 162.5° | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 | 641.6 | 641.7 | 641.8 | 642.0 | 642.1 |
| 165°   | 652.4 | 652.3 | 652.2 | 652.1 | 652.0 | 651.9 | 651.9 | 651.9 | 651.9 | 651.9 | 651.9 |
| 167.5° | 662.2 | 661.8 | 661.4 | 661.1 | 660.7 | 660.5 | 660.5 | 660.5 | 660.5 | 660.5 | 660.5 |
| 170°   | 669.6 | 669.2 | 668.8 | 668.5 | 668.1 | 667.9 | 667.8 | 667.7 | 667.6 | 667.4 | 667.3 |
| 172.5° | 674.8 | 674.4 | 674.0 | 673.7 | 673.3 | 673.1 | 673.0 | 672.9 | 672.8 | 672.6 | 672.5 |
| 175°   | 678.8 | 678.4 | 678.0 | 677.7 | 677.3 | 677.1 | 677.0 | 676.7 | 676.5 | 676.2 | 676.0 |
| 177.5° | 681.1 | 680.7 | 680.3 | 680.0 | 679.6 | 679.4 | 679.3 | 679.0 | 678.7 | 678.5 | 678.2 |
| 180°   | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 50°   | 55°   | 60°   | 65°   | 67.5° | 70°   | 75°   | 80°   | 85°   | 90°   | 95°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 661.5 | 662.4 | 663.7 | 669.9 | 670.8 | 672.6 | 671.7 | 671.7 | 672.1 | 671.3 | 671.7 |
| 5°     | 689.9 | 691.2 | 697.9 | 705.4 | 707.2 | 705.4 | 707.7 | 710.8 | 710.8 | 710.8 | 709.9 |
| 7.5°   | 716.5 | 721.4 | 729.0 | 740.1 | 742.3 | 744.5 | 748.5 | 745.8 | 746.7 | 750.7 | 749.4 |
| 10°    | 742.3 | 749.4 | 757.8 | 767.1 | 772.0 | 775.1 | 776.9 | 780.9 | 790.2 | 779.6 | 783.6 |
| 12.5°  | 766.7 | 776.9 | 785.8 | 796.0 | 799.6 | 803.5 | 804.9 | 808.4 | 808.4 | 808.0 | 811.1 |
| 15°    | 782.7 | 792.0 | 800.0 | 806.7 | 807.5 | 806.7 | 805.8 | 806.2 | 807.5 | 802.2 | 805.3 |
| 17.5°  | 786.2 | 787.1 | 789.8 | 787.1 | 787.6 | 778.2 | 772.9 | 771.6 | 759.2 | 759.6 | 769.8 |
| 20°    | 768.9 | 753.8 | 749.8 | 735.2 | 726.3 | 702.3 | 701.4 | 694.8 | 668.6 | 676.6 | 674.8 |
| 22.5°  | 721.4 | 695.7 | 661.5 | 644.6 | 636.2 | 610.9 | 591.3 | 577.6 | 568.3 | 558.9 | 554.9 |
| 25°    | 658.8 | 617.1 | 568.7 | 535.4 | 530.5 | 507.0 | 471.0 | 454.2 | 434.2 | 428.0 | 438.6 |
| 27.5°  | 578.0 | 523.9 | 469.3 | 418.2 | 408.9 | 387.6 | 369.4 | 357.4 | 334.3 | 333.0 | 333.8 |
| 30°    | 468.4 | 413.8 | 368.0 | 334.7 | 311.7 | 301.9 | 289.9 | 281.0 | 271.7 | 275.2 | 276.1 |
| 32.5°  | 384.9 | 333.0 | 290.3 | 272.6 | 261.9 | 255.7 | 245.5 | 239.7 | 235.7 | 234.4 | 234.0 |
| 35°    | 305.9 | 271.3 | 252.2 | 234.8 | 228.6 | 224.2 | 216.6 | 214.0 | 210.4 | 210.9 | 210.9 |
| 37.5°  | 261.9 | 233.1 | 218.9 | 210.0 | 204.2 | 202.0 | 197.1 | 194.4 | 192.2 | 191.3 | 192.7 |
| 40°    | 226.0 | 206.0 | 197.1 | 189.1 | 184.2 | 183.4 | 180.7 | 177.6 | 174.9 | 175.4 | 176.7 |
| 42.5°  | 199.8 | 188.2 | 177.6 | 171.4 | 167.8 | 166.5 | 164.3 | 162.0 | 162.0 | 160.7 | 160.3 |
| 45°    | 178.9 | 169.6 | 160.7 | 154.9 | 152.7 | 150.9 | 148.3 | 147.8 | 146.1 | 146.5 | 146.9 |
| 47.5°  | 160.3 | 152.7 | 146.1 | 140.3 | 138.1 | 137.6 | 135.0 | 133.2 | 133.2 | 132.7 | 132.3 |
| 50°    | 143.4 | 135.8 | 130.1 | 127.0 | 123.9 | 123.0 | 122.5 | 122.1 | 121.2 | 121.2 | 121.6 |
| 52.5°  | 129.6 | 122.1 | 117.6 | 115.0 | 113.2 | 112.3 | 112.3 | 111.9 | 111.9 | 111.9 | 111.4 |
| 55°    | 114.5 | 108.3 | 104.8 | 103.9 | 103.0 | 102.6 | 102.1 | 101.2 | 100.8 | 101.7 | 100.8 |
| 57.5°  | 100.3 | 98.1  | 95.0  | 94.1  | 91.9  | 91.9  | 90.6  | 89.7  | 88.8  | 89.7  | 89.7  |
| 60°    | 89.2  | 86.1  | 84.4  | 81.7  | 79.9  | 78.1  | 75.9  | 75.5  | 74.6  | 74.1  | 73.7  |
| 62.5°  | 77.7  | 75.0  | 70.6  | 66.6  | 63.9  | 62.2  | 61.3  | 60.8  | 60.8  | 60.4  | 60.4  |
| 65°    | 64.8  | 58.6  | 56.4  | 55.0  | 54.6  | 54.2  | 53.3  | 52.8  | 53.3  | 52.8  | 53.3  |
| 67.5°  | 50.6  | 49.7  | 48.4  | 47.5  | 47.1  | 46.6  | 46.6  | 46.2  | 46.2  | 46.2  | 46.2  |
| 70°    | 44.0  | 41.7  | 41.3  | 40.4  | 40.4  | 40.0  | 40.0  | 40.0  | 40.0  | 39.5  | 40.4  |
| 72.5°  | 36.4  | 35.1  | 34.6  | 34.2  | 34.2  | 34.2  | 33.7  | 33.7  | 33.7  | 33.3  | 33.7  |
| 75°    | 29.7  | 29.3  | 28.4  | 28.4  | 28.0  | 28.4  | 28.0  | 28.0  | 27.5  | 28.0  | 28.0  |
| 77.5°  | 24.0  | 23.5  | 23.1  | 23.1  | 22.6  | 22.6  | 22.6  | 22.6  | 22.6  | 22.6  | 23.1  |
| 80°    | 18.2  | 17.8  | 17.3  | 17.8  | 17.3  | 17.8  | 17.3  | 17.3  | 17.8  | 17.3  | 17.3  |
| 82.5°  | 13.3  | 12.9  | 12.9  | 12.4  | 12.4  | 12.4  | 12.4  | 12.4  | 12.4  | 12.4  | 12.4  |
| 85°    | 8.0   | 7.5   | 7.5   | 8.0   | 7.5   | 8.0   | 7.5   | 7.5   | 7.5   | 8.0   | 8.0   |
| 87.5°  | 3.6   | 4.0   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 3.6   | 4.0   |
| 90°    | 19.8  | 19.6  | 19.3  | 19.0  | 18.9  | 19.0  | 19.1  | 19.2  | 19.4  | 19.5  | 19.4  |
| 92.5°  | 17.9  | 18.1  | 18.2  | 18.3  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  |
| 95°    | 36.7  | 36.7  | 36.7  | 36.7  | 36.7  | 36.6  | 36.3  | 36.1  | 35.8  | 35.6  | 35.8  |
| 97.5°  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  |
| 100°   | 79.2  | 79.2  | 79.2  | 79.2  | 79.2  | 79.1  | 79.0  | 78.9  | 78.7  | 78.6  | 78.7  |
| 102.5° | 102.8 | 103.0 | 103.1 | 103.2 | 103.3 | 103.2 | 103.1 | 103.0 | 102.8 | 102.7 | 102.8 |
| 105°   | 126.5 | 126.7 | 127.0 | 127.3 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 |
| 107.5° | 152.2 | 152.3 | 152.4 | 152.5 | 152.6 | 152.3 | 151.7 | 151.0 | 150.4 | 149.8 | 150.4 |
| 110°   | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.3 | 177.9 | 177.5 | 177.1 | 176.7 | 177.1 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 50°   | 55°   | 60°   | 65°   | 67.5° | 70°   | 75°   | 80°   | 85°   | 90°   | 95°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 205.0 | 204.6 | 204.3 | 203.9 | 203.7 | 203.6 | 203.3 | 203.1 | 202.8 | 202.6 | 202.8 |
| 115°   | 231.7 | 231.5 | 231.4 | 231.3 | 231.2 | 231.0 | 230.6 | 230.3 | 229.9 | 229.5 | 229.9 |
| 117.5° | 257.8 | 257.4 | 257.1 | 256.7 | 256.5 | 256.3 | 255.9 | 255.6 | 255.2 | 254.8 | 255.2 |
| 120°   | 283.5 | 283.5 | 283.5 | 283.5 | 283.5 | 283.3 | 282.9 | 282.5 | 282.1 | 281.7 | 282.1 |
| 122.5° | 310.6 | 310.2 | 309.9 | 309.5 | 309.3 | 309.2 | 308.9 | 308.6 | 308.4 | 308.1 | 308.4 |
| 125°   | 337.0 | 336.6 | 336.3 | 335.9 | 335.7 | 335.6 | 335.5 | 335.4 | 335.2 | 335.1 | 335.2 |
| 127.5° | 362.7 | 362.2 | 361.7 | 361.2 | 360.9 | 360.7 | 360.3 | 360.0 | 359.6 | 359.2 | 359.6 |
| 130°   | 388.8 | 388.5 | 388.3 | 388.0 | 387.9 | 387.6 | 387.1 | 386.6 | 386.1 | 385.6 | 386.1 |
| 132.5° | 414.8 | 414.2 | 413.5 | 412.9 | 412.6 | 412.4 | 412.0 | 411.7 | 411.3 | 410.9 | 411.3 |
| 135°   | 439.4 | 439.3 | 439.2 | 439.1 | 439.0 | 438.8 | 438.4 | 438.0 | 437.6 | 437.2 | 437.6 |
| 137.5° | 463.5 | 463.4 | 463.3 | 463.2 | 463.1 | 462.8 | 462.3 | 461.8 | 461.3 | 460.8 | 461.3 |
| 140°   | 487.7 | 487.7 | 487.7 | 487.7 | 487.7 | 487.4 | 486.9 | 486.4 | 485.9 | 485.4 | 485.9 |
| 142.5° | 509.6 | 509.8 | 509.9 | 510.0 | 510.1 | 509.8 | 509.3 | 508.8 | 508.3 | 507.8 | 508.3 |
| 145°   | 532.0 | 532.2 | 532.3 | 532.4 | 532.5 | 532.2 | 531.7 | 531.2 | 530.7 | 530.2 | 530.7 |
| 147.5° | 551.7 | 551.9 | 552.2 | 552.5 | 552.6 | 552.3 | 551.8 | 551.3 | 550.8 | 550.3 | 550.8 |
| 150°   | 570.2 | 570.6 | 570.9 | 571.3 | 571.5 | 571.3 | 570.9 | 570.6 | 570.2 | 569.8 | 570.2 |
| 152.5° | 588.7 | 589.2 | 589.7 | 590.2 | 590.5 | 590.2 | 589.7 | 589.2 | 588.7 | 588.2 | 588.7 |
| 155°   | 603.7 | 604.3 | 605.0 | 605.6 | 605.9 | 605.7 | 605.3 | 605.0 | 604.6 | 604.2 | 604.6 |
| 157.5° | 618.3 | 619.2 | 620.1 | 621.0 | 621.4 | 621.1 | 620.5 | 619.8 | 619.2 | 618.6 | 619.2 |
| 160°   | 631.4 | 632.2 | 632.9 | 633.7 | 634.1 | 633.8 | 633.3 | 632.8 | 632.3 | 631.8 | 632.3 |
| 162.5° | 643.0 | 643.9 | 644.8 | 645.7 | 646.1 | 645.8 | 645.1 | 644.5 | 643.8 | 643.2 | 643.8 |
| 165°   | 652.8 | 653.7 | 654.6 | 655.5 | 655.9 | 655.6 | 654.9 | 654.3 | 653.6 | 653.0 | 653.6 |
| 167.5° | 661.4 | 662.3 | 663.2 | 664.1 | 664.5 | 664.2 | 663.5 | 662.9 | 662.2 | 661.6 | 662.2 |
| 170°   | 668.2 | 669.1 | 670.0 | 670.9 | 671.4 | 671.0 | 670.2 | 669.5 | 668.7 | 667.9 | 668.7 |
| 172.5° | 673.4 | 674.3 | 675.2 | 676.1 | 676.5 | 676.1 | 675.4 | 674.6 | 673.9 | 673.1 | 673.9 |
| 175°   | 676.9 | 677.8 | 678.7 | 679.6 | 680.0 | 679.6 | 678.8 | 678.1 | 677.3 | 676.5 | 677.3 |
| 177.5° | 679.0 | 679.8 | 680.5 | 681.3 | 681.7 | 681.3 | 680.5 | 679.8 | 679.0 | 678.2 | 679.0 |
| 180°   | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 100°  | 105°  | 110°  | 112.5° | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  |
|--------|-------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8 | 638.8 | 638.8  | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 673.5 | 670.4 | 669.5 | 670.4  | 669.5 | 669.9 | 666.8 | 655.3 | 658.4 | 653.5 | 656.2 |
| 5°     | 711.7 | 709.0 | 703.2 | 702.3  | 701.4 | 700.6 | 696.1 | 685.9 | 681.9 | 675.2 | 674.8 |
| 7.5°   | 748.1 | 748.1 | 743.6 | 740.5  | 736.5 | 733.4 | 727.6 | 712.5 | 706.3 | 698.3 | 693.9 |
| 10°    | 784.0 | 772.5 | 777.4 | 774.2  | 764.5 | 762.7 | 752.1 | 743.2 | 731.2 | 723.2 | 716.1 |
| 12.5°  | 809.8 | 806.2 | 801.8 | 799.1  | 796.4 | 790.7 | 783.6 | 760.9 | 754.7 | 738.7 | 730.7 |
| 15°    | 808.9 | 806.7 | 808.0 | 808.0  | 807.1 | 805.8 | 800.0 | 783.6 | 772.9 | 757.4 | 743.6 |
| 17.5°  | 765.4 | 771.1 | 776.9 | 780.9  | 789.8 | 793.8 | 799.1 | 789.3 | 782.7 | 769.4 | 754.7 |
| 20°    | 689.5 | 703.7 | 720.5 | 724.1  | 732.1 | 755.6 | 766.3 | 774.7 | 777.4 | 772.9 | 760.9 |
| 22.5°  | 583.8 | 595.8 | 636.6 | 635.7  | 647.3 | 675.2 | 706.3 | 731.6 | 751.6 | 762.7 | 758.3 |
| 25°    | 457.3 | 474.1 | 495.9 | 512.3  | 550.1 | 591.8 | 630.4 | 670.8 | 705.4 | 736.1 | 743.6 |
| 27.5°  | 345.8 | 368.0 | 385.3 | 407.1  | 426.2 | 475.5 | 525.2 | 588.2 | 628.6 | 686.8 | 717.0 |
| 30°    | 279.7 | 289.9 | 307.2 | 317.4  | 326.7 | 364.5 | 420.9 | 483.0 | 554.0 | 621.1 | 673.0 |
| 32.5°  | 238.8 | 245.9 | 258.8 | 263.3  | 273.0 | 298.3 | 333.8 | 390.7 | 463.9 | 545.2 | 613.5 |
| 35°    | 214.4 | 222.0 | 224.6 | 228.6  | 236.6 | 252.6 | 277.0 | 318.3 | 384.5 | 463.9 | 545.6 |
| 37.5°  | 193.6 | 197.6 | 205.1 | 207.8  | 210.4 | 222.4 | 238.8 | 267.7 | 311.7 | 376.9 | 467.5 |
| 40°    | 178.9 | 181.1 | 185.1 | 187.3  | 189.1 | 197.6 | 212.2 | 231.7 | 264.1 | 313.9 | 397.3 |
| 42.5°  | 163.4 | 166.0 | 168.7 | 171.4  | 173.6 | 180.2 | 189.1 | 207.8 | 229.5 | 267.3 | 327.6 |
| 45°    | 148.3 | 150.1 | 153.2 | 154.9  | 158.0 | 163.4 | 171.4 | 184.2 | 203.8 | 227.7 | 276.6 |
| 47.5°  | 134.5 | 136.7 | 138.1 | 140.3  | 142.5 | 148.3 | 155.8 | 164.3 | 180.2 | 203.8 | 239.3 |
| 50°    | 122.1 | 124.7 | 126.5 | 127.0  | 128.7 | 134.1 | 140.3 | 149.6 | 159.8 | 178.0 | 209.1 |
| 52.5°  | 113.2 | 113.7 | 115.0 | 116.8  | 116.3 | 119.4 | 125.2 | 132.3 | 143.0 | 157.6 | 180.2 |
| 55°    | 103.0 | 104.3 | 105.2 | 105.7  | 105.7 | 108.3 | 111.4 | 118.1 | 126.5 | 138.5 | 157.6 |
| 57.5°  | 90.1  | 91.5  | 94.1  | 95.0   | 96.3  | 97.7  | 99.0  | 103.4 | 110.5 | 122.1 | 137.6 |
| 60°    | 76.8  | 77.7  | 80.4  | 82.1   | 83.0  | 86.6  | 88.3  | 91.9  | 95.9  | 104.3 | 119.0 |
| 62.5°  | 61.7  | 62.6  | 63.9  | 65.7   | 67.5  | 72.8  | 77.2  | 80.8  | 83.9  | 89.7  | 101.7 |
| 65°    | 53.7  | 54.2  | 55.0  | 55.5   | 55.9  | 58.2  | 62.2  | 67.0  | 72.8  | 77.2  | 84.4  |
| 67.5°  | 46.6  | 47.1  | 47.5  | 48.4   | 48.8  | 49.3  | 51.1  | 52.4  | 58.2  | 64.4  | 69.7  |
| 70°    | 40.0  | 40.8  | 41.3  | 41.3   | 41.7  | 42.6  | 43.5  | 45.3  | 47.1  | 50.2  | 56.8  |
| 72.5°  | 33.7  | 34.2  | 35.1  | 35.1   | 35.1  | 36.0  | 36.8  | 37.7  | 38.6  | 40.4  | 43.1  |
| 75°    | 28.0  | 28.9  | 28.9  | 28.9   | 29.3  | 29.3  | 30.2  | 31.1  | 32.0  | 33.3  | 34.2  |
| 77.5°  | 23.1  | 23.1  | 23.1  | 23.1   | 23.5  | 23.5  | 24.0  | 24.9  | 25.3  | 25.7  | 26.6  |
| 80°    | 17.3  | 17.8  | 17.8  | 17.8   | 18.2  | 18.2  | 18.2  | 19.1  | 19.5  | 19.5  | 20.4  |
| 82.5°  | 12.9  | 12.9  | 12.9  | 13.3   | 12.9  | 13.3  | 13.3  | 13.8  | 13.3  | 13.8  | 14.2  |
| 85°    | 8.0   | 8.0   | 8.0   | 8.4    | 8.4   | 8.4   | 8.4   | 8.4   | 8.4   | 8.4   | 8.9   |
| 87.5°  | 4.0   | 4.0   | 4.0   | 4.0    | 4.0   | 4.0   | 4.0   | 4.0   | 4.4   | 4.0   | 4.0   |
| 90°    | 19.2  | 19.1  | 19.0  | 18.9   | 19.0  | 19.3  | 19.6  | 19.8  | 20.1  | 17.3  | 14.5  |
| 92.5°  | 18.4  | 18.4  | 18.4  | 18.4   | 18.3  | 18.2  | 18.1  | 17.9  | 17.8  | 17.7  | 17.5  |
| 95°    | 36.1  | 36.3  | 36.6  | 36.7   | 36.7  | 36.7  | 36.7  | 36.7  | 36.7  | 36.5  | 36.2  |
| 97.5°  | 57.4  | 57.4  | 57.4  | 57.4   | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 56.9  | 56.4  |
| 100°   | 78.9  | 79.0  | 79.1  | 79.2   | 79.2  | 79.2  | 79.2  | 79.2  | 79.2  | 78.8  | 78.4  |
| 102.5° | 103.0 | 103.1 | 103.2 | 103.3  | 103.2 | 103.1 | 103.0 | 102.8 | 102.7 | 102.2 | 101.7 |
| 105°   | 127.4 | 127.4 | 127.4 | 127.4  | 127.3 | 127.0 | 126.7 | 126.5 | 126.2 | 126.0 | 125.7 |
| 107.5° | 151.0 | 151.7 | 152.3 | 152.6  | 152.5 | 152.4 | 152.3 | 152.2 | 152.1 | 152.1 | 152.1 |
| 110°   | 177.5 | 177.9 | 178.3 | 178.5  | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 100°  | 105°  | 110°  | 112.5° | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  |
|--------|-------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 203.1 | 203.3 | 203.6 | 203.7  | 203.9 | 204.3 | 204.6 | 205.0 | 205.4 | 205.5 | 205.7 |
| 115°   | 230.3 | 230.6 | 231.0 | 231.2  | 231.3 | 231.4 | 231.5 | 231.7 | 231.8 | 232.1 | 232.3 |
| 117.5° | 255.6 | 255.9 | 256.3 | 256.5  | 256.7 | 257.1 | 257.4 | 257.8 | 258.2 | 258.8 | 259.5 |
| 120°   | 282.5 | 282.9 | 283.3 | 283.5  | 283.5 | 283.5 | 283.5 | 283.5 | 283.5 | 284.5 | 285.5 |
| 122.5° | 308.6 | 308.9 | 309.2 | 309.3  | 309.5 | 309.9 | 310.2 | 310.6 | 311.0 | 311.6 | 312.3 |
| 125°   | 335.4 | 335.5 | 335.6 | 335.7  | 335.9 | 336.3 | 336.6 | 337.0 | 337.4 | 337.8 | 338.2 |
| 127.5° | 360.0 | 360.3 | 360.7 | 360.9  | 361.2 | 361.7 | 362.2 | 362.7 | 363.2 | 363.7 | 364.2 |
| 130°   | 386.6 | 387.1 | 387.6 | 387.9  | 388.0 | 388.3 | 388.5 | 388.8 | 389.0 | 389.3 | 389.5 |
| 132.5° | 411.7 | 412.0 | 412.4 | 412.6  | 412.9 | 413.5 | 414.2 | 414.8 | 415.4 | 415.3 | 415.2 |
| 135°   | 438.0 | 438.4 | 438.8 | 439.0  | 439.1 | 439.2 | 439.3 | 439.4 | 439.5 | 439.3 | 439.0 |
| 137.5° | 461.8 | 462.3 | 462.8 | 463.1  | 463.2 | 463.3 | 463.4 | 463.5 | 463.6 | 463.4 | 463.1 |
| 140°   | 486.4 | 486.9 | 487.4 | 487.7  | 487.7 | 487.7 | 487.7 | 487.7 | 487.7 | 487.1 | 486.5 |
| 142.5° | 508.8 | 509.3 | 509.8 | 510.1  | 510.0 | 509.9 | 509.8 | 509.6 | 509.5 | 509.1 | 508.7 |
| 145°   | 531.2 | 531.7 | 532.2 | 532.5  | 532.4 | 532.3 | 532.2 | 532.0 | 531.9 | 531.1 | 530.4 |
| 147.5° | 551.3 | 551.8 | 552.3 | 552.6  | 552.5 | 552.2 | 551.9 | 551.7 | 551.4 | 550.9 | 550.4 |
| 150°   | 570.6 | 570.9 | 571.3 | 571.5  | 571.3 | 570.9 | 570.6 | 570.2 | 569.8 | 569.3 | 568.8 |
| 152.5° | 589.2 | 589.7 | 590.2 | 590.5  | 590.2 | 589.7 | 589.2 | 588.7 | 588.2 | 587.6 | 586.9 |
| 155°   | 605.0 | 605.3 | 605.7 | 605.9  | 605.6 | 605.0 | 604.3 | 603.7 | 603.1 | 602.7 | 602.3 |
| 157.5° | 619.8 | 620.5 | 621.1 | 621.4  | 621.0 | 620.1 | 619.2 | 618.3 | 617.4 | 617.2 | 616.9 |
| 160°   | 632.8 | 633.3 | 633.8 | 634.1  | 633.7 | 632.9 | 632.2 | 631.4 | 630.6 | 630.5 | 630.3 |
| 162.5° | 644.5 | 645.1 | 645.8 | 646.1  | 645.7 | 644.8 | 643.9 | 643.0 | 642.1 | 642.0 | 641.8 |
| 165°   | 654.3 | 654.9 | 655.6 | 655.9  | 655.5 | 654.6 | 653.7 | 652.8 | 651.9 | 651.9 | 651.9 |
| 167.5° | 662.9 | 663.5 | 664.2 | 664.5  | 664.1 | 663.2 | 662.3 | 661.4 | 660.5 | 660.5 | 660.5 |
| 170°   | 669.5 | 670.2 | 671.0 | 671.4  | 670.9 | 670.0 | 669.1 | 668.2 | 667.3 | 667.4 | 667.6 |
| 172.5° | 674.6 | 675.4 | 676.1 | 676.5  | 676.1 | 675.2 | 674.3 | 673.4 | 672.5 | 672.6 | 672.8 |
| 175°   | 678.1 | 678.8 | 679.6 | 680.0  | 679.6 | 678.7 | 677.8 | 676.9 | 676.0 | 676.2 | 676.5 |
| 177.5° | 679.8 | 680.5 | 681.3 | 681.7  | 681.3 | 680.5 | 679.8 | 679.0 | 678.2 | 678.5 | 678.7 |
| 180°   | 680.0 | 680.0 | 680.0 | 680.0  | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 150°  | 155°  | 157.5° | 160°  | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|--------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8 | 638.8  | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 652.2 | 649.9 | 649.9  | 648.6 | 648.6 | 641.5 | 641.5 | 643.7 | 641.1 | 638.0 | 633.5 |
| 5°     | 669.0 | 664.1 | 662.8  | 661.0 | 655.3 | 646.4 | 642.8 | 641.5 | 636.2 | 629.5 | 622.0 |
| 7.5°   | 685.0 | 677.0 | 673.0  | 669.0 | 661.5 | 649.1 | 642.0 | 637.1 | 629.1 | 618.9 | 609.1 |
| 10°    | 700.6 | 690.3 | 680.1  | 675.2 | 664.6 | 649.1 | 638.8 | 630.9 | 619.3 | 605.5 | 591.8 |
| 12.5°  | 714.8 | 693.4 | 691.7  | 681.9 | 666.4 | 648.6 | 633.1 | 621.5 | 606.9 | 590.9 | 574.9 |
| 15°    | 727.2 | 705.4 | 694.8  | 685.9 | 665.5 | 643.3 | 626.9 | 612.6 | 593.1 | 574.9 | 555.4 |
| 17.5°  | 733.4 | 709.9 | 702.8  | 688.1 | 667.3 | 638.4 | 616.2 | 598.9 | 577.6 | 555.8 | 533.6 |
| 20°    | 739.6 | 712.1 | 700.6  | 690.3 | 661.9 | 629.1 | 604.2 | 584.2 | 560.7 | 535.0 | 510.5 |
| 22.5°  | 742.7 | 712.1 | 698.3  | 684.1 | 656.6 | 618.9 | 589.6 | 566.0 | 538.5 | 512.3 | 483.0 |
| 25°    | 737.4 | 709.4 | 693.0  | 678.4 | 647.3 | 606.4 | 572.7 | 546.1 | 516.8 | 487.0 | 457.3 |
| 27.5°  | 724.1 | 703.2 | 684.1  | 669.0 | 634.4 | 590.5 | 554.9 | 524.7 | 494.6 | 461.3 | 431.1 |
| 30°    | 699.2 | 689.9 | 674.8  | 657.9 | 620.2 | 576.2 | 534.1 | 503.0 | 469.7 | 436.4 | 404.9 |
| 32.5°  | 660.6 | 668.6 | 658.8  | 644.2 | 603.3 | 556.7 | 511.9 | 480.4 | 443.9 | 408.0 | 379.1 |
| 35°    | 613.5 | 642.0 | 636.6  | 626.4 | 585.6 | 535.8 | 491.0 | 452.8 | 416.4 | 380.0 | 351.2 |
| 37.5°  | 562.0 | 605.1 | 609.5  | 603.3 | 565.1 | 514.5 | 465.3 | 428.0 | 390.7 | 353.8 | 324.5 |
| 40°    | 491.5 | 557.6 | 571.8  | 574.5 | 543.8 | 488.8 | 437.3 | 400.9 | 364.0 | 328.1 | 292.6 |
| 42.5°  | 426.6 | 510.1 | 527.9  | 539.0 | 516.8 | 463.5 | 411.5 | 371.1 | 334.7 | 302.3 | 266.8 |
| 45°    | 365.8 | 452.8 | 481.7  | 495.9 | 486.1 | 434.6 | 380.9 | 343.2 | 309.9 | 280.1 | 245.9 |
| 47.5°  | 303.2 | 390.7 | 431.1  | 453.7 | 453.7 | 405.3 | 351.6 | 314.3 | 282.4 | 257.0 | 226.9 |
| 50°    | 261.5 | 334.3 | 376.0  | 405.8 | 413.8 | 375.6 | 325.0 | 288.6 | 258.4 | 230.9 | 207.8 |
| 52.5°  | 222.9 | 288.1 | 322.8  | 353.8 | 376.9 | 343.6 | 295.2 | 262.4 | 232.6 | 206.9 | 188.7 |
| 55°    | 192.7 | 241.5 | 273.0  | 307.2 | 333.0 | 311.2 | 266.4 | 234.4 | 208.7 | 187.3 | 171.8 |
| 57.5°  | 163.8 | 206.4 | 232.2  | 262.4 | 289.9 | 273.5 | 237.5 | 210.0 | 187.3 | 168.7 | 154.9 |
| 60°    | 139.4 | 174.0 | 194.0  | 217.5 | 251.7 | 240.2 | 210.4 | 185.1 | 166.9 | 150.1 | 138.5 |
| 62.5°  | 118.5 | 146.1 | 162.9  | 179.8 | 210.9 | 205.5 | 182.5 | 162.9 | 147.4 | 133.2 | 123.4 |
| 65°    | 97.2  | 119.9 | 133.2  | 147.8 | 172.7 | 174.9 | 156.3 | 142.5 | 128.3 | 115.9 | 107.0 |
| 67.5°  | 78.6  | 96.3  | 108.3  | 120.8 | 140.7 | 146.9 | 134.1 | 122.5 | 110.5 | 100.3 | 92.3  |
| 70°    | 63.5  | 75.9  | 84.8   | 94.6  | 111.0 | 118.5 | 111.9 | 103.9 | 94.1  | 85.7  | 78.6  |
| 72.5°  | 50.2  | 58.2  | 63.5   | 71.0  | 84.4  | 91.9  | 91.5  | 84.4  | 77.2  | 71.5  | 65.7  |
| 75°    | 36.8  | 43.1  | 47.5   | 52.4  | 63.0  | 70.1  | 71.9  | 68.8  | 61.7  | 57.3  | 52.8  |
| 77.5°  | 28.0  | 31.5  | 33.7   | 37.3  | 44.8  | 51.1  | 53.7  | 52.8  | 47.9  | 44.4  | 41.3  |
| 80°    | 21.3  | 22.2  | 23.1   | 24.4  | 30.6  | 36.4  | 38.2  | 37.7  | 35.1  | 33.7  | 30.2  |
| 82.5°  | 15.1  | 15.5  | 16.0   | 16.4  | 18.6  | 23.5  | 25.3  | 26.2  | 24.0  | 22.6  | 19.5  |
| 85°    | 8.9   | 9.3   | 9.3    | 10.2  | 10.7  | 12.0  | 15.1  | 15.1  | 14.7  | 12.9  | 12.4  |
| 87.5°  | 4.4   | 4.4   | 4.0    | 4.0   | 4.4   | 4.9   | 5.8   | 6.7   | 5.8   | 5.3   | 4.9   |
| 90°    | 11.7  | 8.9   | 7.5    | 6.7   | 5.2   | 3.7   | 2.1   | 0.6   | 2.1   | 3.7   | 5.2   |
| 92.5°  | 17.4  | 17.3  | 17.2   | 16.7  | 15.7  | 14.6  | 13.6  | 12.6  | 13.6  | 14.6  | 15.7  |
| 95°    | 36.0  | 35.7  | 35.6   | 35.0  | 33.7  | 32.4  | 31.1  | 29.8  | 31.1  | 32.4  | 33.7  |
| 97.5°  | 55.9  | 55.4  | 55.1   | 54.5  | 53.4  | 52.2  | 51.1  | 49.9  | 51.1  | 52.2  | 53.4  |
| 100°   | 78.1  | 77.7  | 77.5   | 77.0  | 76.0  | 74.9  | 73.9  | 72.9  | 73.9  | 74.9  | 76.0  |
| 102.5° | 101.2 | 100.7 | 100.4  | 100.0 | 99.3  | 98.5  | 97.8  | 97.0  | 97.8  | 98.5  | 99.3  |
| 105°   | 125.5 | 125.2 | 125.1  | 124.9 | 124.5 | 124.2 | 123.8 | 123.4 | 123.8 | 124.2 | 124.5 |
| 107.5° | 152.1 | 152.1 | 152.1  | 151.8 | 151.3 | 150.8 | 150.3 | 149.8 | 150.3 | 150.8 | 151.3 |
| 110°   | 178.5 | 178.5 | 178.5  | 178.1 | 177.3 | 176.6 | 175.8 | 175.0 | 175.8 | 176.6 | 177.3 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 150°  | 155°  | 157.5° | 160°  | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|--------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 205.8 | 205.9 | 206.0  | 205.6 | 204.9 | 204.1 | 203.4 | 202.6 | 203.4 | 204.1 | 204.9 |
| 115°   | 232.6 | 232.9 | 233.0  | 232.6 | 231.8 | 231.1 | 230.3 | 229.5 | 230.3 | 231.1 | 231.8 |
| 117.5° | 260.1 | 260.8 | 261.1  | 260.6 | 259.6 | 258.5 | 257.5 | 256.5 | 257.5 | 258.5 | 259.6 |
| 120°   | 286.6 | 287.6 | 288.1  | 287.6 | 286.6 | 285.5 | 284.5 | 283.5 | 284.5 | 285.5 | 286.6 |
| 122.5° | 312.9 | 313.6 | 313.9  | 313.3 | 312.0 | 310.7 | 309.4 | 308.1 | 309.4 | 310.7 | 312.0 |
| 125°   | 338.5 | 338.9 | 339.1  | 338.5 | 337.4 | 336.3 | 335.1 | 334.0 | 335.1 | 336.3 | 337.4 |
| 127.5° | 364.7 | 365.2 | 365.5  | 364.8 | 363.4 | 362.0 | 360.6 | 359.2 | 360.6 | 362.0 | 363.4 |
| 130°   | 389.8 | 390.1 | 390.2  | 389.4 | 387.7 | 386.0 | 384.4 | 382.7 | 384.4 | 386.0 | 387.7 |
| 132.5° | 415.1 | 415.0 | 414.9  | 414.3 | 413.0 | 411.7 | 410.4 | 409.1 | 410.4 | 411.7 | 413.0 |
| 135°   | 438.8 | 438.5 | 438.4  | 437.7 | 436.3 | 434.9 | 433.5 | 432.1 | 433.5 | 434.9 | 436.3 |
| 137.5° | 462.9 | 462.6 | 462.5  | 461.9 | 460.8 | 459.6 | 458.5 | 457.3 | 458.5 | 459.6 | 460.8 |
| 140°   | 485.8 | 485.2 | 484.9  | 484.3 | 483.2 | 482.0 | 480.9 | 479.7 | 480.9 | 482.0 | 483.2 |
| 142.5° | 508.4 | 508.0 | 507.8  | 507.2 | 506.1 | 505.0 | 503.8 | 502.7 | 503.8 | 505.0 | 506.1 |
| 145°   | 529.6 | 528.9 | 528.5  | 528.1 | 527.2 | 526.3 | 525.4 | 524.5 | 525.4 | 526.3 | 527.2 |
| 147.5° | 549.9 | 549.4 | 549.1  | 548.5 | 547.4 | 546.3 | 545.1 | 544.0 | 545.1 | 546.3 | 547.4 |
| 150°   | 568.3 | 567.8 | 567.5  | 567.1 | 566.4 | 565.6 | 564.9 | 564.1 | 564.9 | 565.6 | 566.4 |
| 152.5° | 586.3 | 585.6 | 585.3  | 584.9 | 584.1 | 583.4 | 582.6 | 581.8 | 582.6 | 583.4 | 584.1 |
| 155°   | 602.0 | 601.6 | 601.4  | 601.2 | 600.8 | 600.4 | 600.0 | 599.6 | 600.0 | 600.4 | 600.8 |
| 157.5° | 616.7 | 616.4 | 616.3  | 616.2 | 615.9 | 615.6 | 615.4 | 615.1 | 615.4 | 615.6 | 615.9 |
| 160°   | 630.2 | 630.1 | 630.0  | 629.9 | 629.6 | 629.4 | 629.1 | 628.9 | 629.1 | 629.4 | 629.6 |
| 162.5° | 641.7 | 641.6 | 641.5  | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 | 641.5 |
| 165°   | 651.9 | 651.9 | 651.9  | 652.0 | 652.1 | 652.2 | 652.3 | 652.4 | 652.3 | 652.2 | 652.1 |
| 167.5° | 660.5 | 660.5 | 660.5  | 660.7 | 661.1 | 661.4 | 661.8 | 662.2 | 661.8 | 661.4 | 661.1 |
| 170°   | 667.7 | 667.8 | 667.9  | 668.1 | 668.5 | 668.8 | 669.2 | 669.6 | 669.2 | 668.8 | 668.5 |
| 172.5° | 672.9 | 673.0 | 673.1  | 673.3 | 673.7 | 674.0 | 674.4 | 674.8 | 674.4 | 674.0 | 673.7 |
| 175°   | 676.7 | 677.0 | 677.1  | 677.3 | 677.7 | 678.0 | 678.4 | 678.8 | 678.4 | 678.0 | 677.7 |
| 177.5° | 679.0 | 679.3 | 679.4  | 679.6 | 680.0 | 680.3 | 680.7 | 681.1 | 680.7 | 680.3 | 680.0 |
| 180°   | 680.0 | 680.0 | 680.0  | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°  | 245°  |
|--------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8  | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 631.7 | 632.2  | 633.5 | 629.5 | 623.3 | 620.6 | 612.6 | 611.3 | 610.0 | 610.0 | 611.3 |
| 5°     | 617.5 | 615.8  | 616.2 | 608.7 | 599.8 | 594.4 | 583.3 | 585.1 | 579.4 | 575.8 | 576.7 |
| 7.5°   | 602.0 | 597.1  | 596.7 | 586.9 | 575.8 | 566.0 | 554.5 | 551.8 | 546.5 | 540.3 | 537.6 |
| 10°    | 582.5 | 578.9  | 572.3 | 561.2 | 546.9 | 539.0 | 523.4 | 514.1 | 512.8 | 503.4 | 499.9 |
| 12.5°  | 562.5 | 556.3  | 549.6 | 534.1 | 518.1 | 505.2 | 493.7 | 483.5 | 476.4 | 468.4 | 463.0 |
| 15°    | 539.4 | 531.9  | 524.3 | 507.9 | 489.2 | 476.4 | 459.0 | 443.9 | 423.1 | 406.7 | 397.3 |
| 17.5°  | 514.1 | 505.7  | 495.4 | 477.2 | 459.0 | 441.3 | 409.3 | 391.6 | 376.9 | 367.1 | 361.4 |
| 20°    | 487.9 | 478.6  | 468.4 | 450.2 | 418.6 | 387.6 | 369.8 | 356.0 | 347.2 | 337.4 | 330.3 |
| 22.5°  | 460.4 | 450.6  | 439.5 | 411.1 | 377.8 | 356.0 | 342.3 | 329.4 | 316.5 | 311.2 | 307.7 |
| 25°    | 434.6 | 425.7  | 411.5 | 372.9 | 346.7 | 326.7 | 311.2 | 302.8 | 296.1 | 289.0 | 282.4 |
| 27.5°  | 408.0 | 391.6  | 371.6 | 339.2 | 322.8 | 302.3 | 291.2 | 285.0 | 273.5 | 268.6 | 265.5 |
| 30°    | 376.0 | 357.8  | 338.7 | 315.6 | 296.6 | 282.4 | 272.1 | 261.9 | 255.3 | 250.4 | 245.1 |
| 32.5°  | 343.6 | 326.3  | 314.3 | 290.3 | 276.1 | 261.5 | 251.7 | 245.5 | 235.7 | 232.6 | 230.4 |
| 35°    | 315.6 | 301.0  | 290.3 | 270.8 | 257.5 | 244.2 | 237.1 | 227.7 | 221.5 | 215.8 | 212.2 |
| 37.5°  | 288.1 | 280.1  | 269.0 | 252.6 | 238.4 | 227.7 | 218.0 | 214.9 | 206.4 | 203.3 | 199.8 |
| 40°    | 269.0 | 257.0  | 247.7 | 233.5 | 221.5 | 210.0 | 203.8 | 196.7 | 190.9 | 186.0 | 184.7 |
| 42.5°  | 245.9 | 237.1  | 231.7 | 216.2 | 203.8 | 197.1 | 189.6 | 181.6 | 177.1 | 173.1 | 168.3 |
| 45°    | 228.6 | 220.6  | 213.1 | 200.7 | 189.6 | 181.1 | 174.5 | 169.1 | 161.6 | 159.8 | 152.3 |
| 47.5°  | 210.4 | 202.4  | 196.7 | 184.2 | 174.0 | 166.0 | 161.2 | 154.1 | 147.8 | 143.8 | 140.3 |
| 50°    | 192.2 | 185.6  | 180.2 | 169.6 | 160.7 | 152.3 | 145.6 | 138.5 | 135.8 | 129.2 | 127.0 |
| 52.5°  | 174.9 | 170.5  | 164.7 | 154.5 | 145.6 | 138.5 | 131.4 | 125.6 | 121.6 | 118.1 | 115.4 |
| 55°    | 160.3 | 153.2  | 150.5 | 139.4 | 131.9 | 124.3 | 118.1 | 114.5 | 109.7 | 107.4 | 105.2 |
| 57.5°  | 143.8 | 139.8  | 135.4 | 127.0 | 118.5 | 111.4 | 107.0 | 101.7 | 99.0  | 96.3  | 94.6  |
| 60°    | 129.6 | 123.9  | 120.3 | 113.2 | 105.7 | 99.0  | 95.0  | 91.0  | 87.5  | 85.2  | 81.7  |
| 62.5°  | 113.2 | 108.8  | 106.5 | 99.0  | 92.8  | 86.6  | 83.0  | 79.0  | 76.4  | 72.4  | 67.9  |
| 65°    | 99.0  | 95.4   | 92.8  | 86.6  | 80.8  | 75.0  | 71.5  | 66.6  | 63.0  | 60.8  | 60.4  |
| 67.5°  | 86.6  | 83.9   | 79.9  | 74.1  | 68.4  | 63.9  | 59.9  | 55.9  | 55.5  | 54.6  | 54.6  |
| 70°    | 72.8  | 70.1   | 67.9  | 61.7  | 56.8  | 51.9  | 51.1  | 49.7  | 48.4  | 47.9  | 47.1  |
| 72.5°  | 60.8  | 58.6   | 55.9  | 50.6  | 45.7  | 44.4  | 43.5  | 42.6  | 41.3  | 40.8  | 40.4  |
| 75°    | 49.3  | 46.2   | 44.4  | 39.5  | 38.2  | 37.3  | 36.4  | 35.1  | 34.2  | 33.7  | 32.9  |
| 77.5°  | 37.7  | 34.6   | 34.6  | 32.0  | 31.1  | 29.7  | 28.9  | 28.0  | 27.5  | 26.6  | 26.6  |
| 80°    | 26.6  | 26.6   | 25.7  | 24.4  | 23.1  | 22.6  | 21.3  | 20.9  | 20.4  | 20.9  | 20.0  |
| 82.5°  | 19.5  | 17.8   | 17.8  | 16.9  | 16.0  | 15.5  | 14.7  | 14.7  | 14.2  | 14.2  | 14.2  |
| 85°    | 11.1  | 11.1   | 10.7  | 9.8   | 9.3   | 9.3   | 8.9   | 8.9   | 8.4   | 8.4   | 8.0   |
| 87.5°  | 4.4   | 4.0    | 4.4   | 4.0   | 4.0   | 3.6   | 3.6   | 3.6   | 3.1   | 3.6   | 3.1   |
| 90°    | 6.7   | 7.5    | 8.9   | 11.7  | 14.5  | 17.3  | 20.1  | 19.8  | 19.6  | 19.3  | 19.0  |
| 92.5°  | 16.7  | 17.2   | 17.3  | 17.4  | 17.5  | 17.7  | 17.8  | 17.9  | 18.1  | 18.2  | 18.3  |
| 95°    | 35.0  | 35.6   | 35.7  | 36.0  | 36.2  | 36.5  | 36.7  | 36.7  | 36.7  | 36.7  | 36.7  |
| 97.5°  | 54.5  | 55.1   | 55.4  | 55.9  | 56.4  | 56.9  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  |
| 100°   | 77.0  | 77.5   | 77.7  | 78.1  | 78.4  | 78.8  | 79.2  | 79.2  | 79.2  | 79.2  | 79.2  |
| 102.5° | 100.0 | 100.4  | 100.7 | 101.2 | 101.7 | 102.2 | 102.7 | 102.8 | 103.0 | 103.1 | 103.2 |
| 105°   | 124.9 | 125.1  | 125.2 | 125.5 | 125.7 | 126.0 | 126.2 | 126.5 | 126.7 | 127.0 | 127.3 |
| 107.5° | 151.8 | 152.1  | 152.1 | 152.1 | 152.1 | 152.1 | 152.1 | 152.2 | 152.3 | 152.4 | 152.5 |
| 110°   | 178.1 | 178.5  | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°  | 245°  |
|--------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 205.6 | 206.0  | 205.9 | 205.8 | 205.7 | 205.5 | 205.4 | 205.0 | 204.6 | 204.3 | 203.9 |
| 115°   | 232.6 | 233.0  | 232.9 | 232.6 | 232.3 | 232.1 | 231.8 | 231.7 | 231.5 | 231.4 | 231.3 |
| 117.5° | 260.6 | 261.1  | 260.8 | 260.1 | 259.5 | 258.8 | 258.2 | 257.8 | 257.4 | 257.1 | 256.7 |
| 120°   | 287.6 | 288.1  | 287.6 | 286.6 | 285.5 | 284.5 | 283.5 | 283.5 | 283.5 | 283.5 | 283.5 |
| 122.5° | 313.3 | 313.9  | 313.6 | 312.9 | 312.3 | 311.6 | 311.0 | 310.6 | 310.2 | 309.9 | 309.5 |
| 125°   | 338.5 | 339.1  | 338.9 | 338.5 | 338.2 | 337.8 | 337.4 | 337.0 | 336.6 | 336.3 | 335.9 |
| 127.5° | 364.8 | 365.5  | 365.2 | 364.7 | 364.2 | 363.7 | 363.2 | 362.7 | 362.2 | 361.7 | 361.2 |
| 130°   | 389.4 | 390.2  | 390.1 | 389.8 | 389.5 | 389.3 | 389.0 | 388.8 | 388.5 | 388.3 | 388.0 |
| 132.5° | 414.3 | 414.9  | 415.0 | 415.1 | 415.2 | 415.3 | 415.4 | 414.8 | 414.2 | 413.5 | 412.9 |
| 135°   | 437.7 | 438.4  | 438.5 | 438.8 | 439.0 | 439.3 | 439.5 | 439.4 | 439.3 | 439.2 | 439.1 |
| 137.5° | 461.9 | 462.5  | 462.6 | 462.9 | 463.1 | 463.4 | 463.6 | 463.5 | 463.4 | 463.3 | 463.2 |
| 140°   | 484.3 | 484.9  | 485.2 | 485.8 | 486.5 | 487.1 | 487.7 | 487.7 | 487.7 | 487.7 | 487.7 |
| 142.5° | 507.2 | 507.8  | 508.0 | 508.4 | 508.7 | 509.1 | 509.5 | 509.6 | 509.8 | 509.9 | 510.0 |
| 145°   | 528.1 | 528.5  | 528.9 | 529.6 | 530.4 | 531.1 | 531.9 | 532.0 | 532.2 | 532.3 | 532.4 |
| 147.5° | 548.5 | 549.1  | 549.4 | 549.9 | 550.4 | 550.9 | 551.4 | 551.7 | 551.9 | 552.2 | 552.5 |
| 150°   | 567.1 | 567.5  | 567.8 | 568.3 | 568.8 | 569.3 | 569.8 | 570.2 | 570.6 | 570.9 | 571.3 |
| 152.5° | 584.9 | 585.3  | 585.6 | 586.3 | 586.9 | 587.6 | 588.2 | 588.7 | 589.2 | 589.7 | 590.2 |
| 155°   | 601.2 | 601.4  | 601.6 | 602.0 | 602.3 | 602.7 | 603.1 | 603.7 | 604.3 | 605.0 | 605.6 |
| 157.5° | 616.2 | 616.3  | 616.4 | 616.7 | 616.9 | 617.2 | 617.4 | 618.3 | 619.2 | 620.1 | 621.0 |
| 160°   | 629.9 | 630.0  | 630.1 | 630.2 | 630.3 | 630.5 | 630.6 | 631.4 | 632.2 | 632.9 | 633.7 |
| 162.5° | 641.5 | 641.5  | 641.6 | 641.7 | 641.8 | 642.0 | 642.1 | 643.0 | 643.9 | 644.8 | 645.7 |
| 165°   | 652.0 | 651.9  | 651.9 | 651.9 | 651.9 | 651.9 | 651.9 | 652.8 | 653.7 | 654.6 | 655.5 |
| 167.5° | 660.7 | 660.5  | 660.5 | 660.5 | 660.5 | 660.5 | 660.5 | 661.4 | 662.3 | 663.2 | 664.1 |
| 170°   | 668.1 | 667.9  | 667.8 | 667.7 | 667.6 | 667.4 | 667.3 | 668.2 | 669.1 | 670.0 | 670.9 |
| 172.5° | 673.3 | 673.1  | 673.0 | 672.9 | 672.8 | 672.6 | 672.5 | 673.4 | 674.3 | 675.2 | 676.1 |
| 175°   | 677.3 | 677.1  | 677.0 | 676.7 | 676.5 | 676.2 | 676.0 | 676.9 | 677.8 | 678.7 | 679.6 |
| 177.5° | 679.6 | 679.4  | 679.3 | 679.0 | 678.7 | 678.5 | 678.2 | 679.0 | 679.8 | 680.5 | 681.3 |
| 180°   | 680.0 | 680.0  | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 255°  | 260°  | 265°  | 270°  | 275°  | 280°  | 285°  | 290°  | 292.5° |
|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0°     | 638.8  | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8  |
| 2.5°   | 611.3  | 610.4 | 607.8 | 608.7 | 607.3 | 607.3 | 606.4 | 606.4 | 606.4 | 608.7 | 607.3  |
| 5°     | 578.0  | 574.9 | 571.8 | 570.5 | 569.1 | 567.8 | 567.8 | 567.4 | 571.4 | 570.5 | 574.0  |
| 7.5°   | 536.7  | 535.8 | 529.6 | 529.6 | 527.4 | 526.5 | 528.7 | 529.2 | 529.6 | 530.5 | 532.7  |
| 10°    | 499.9  | 497.7 | 488.8 | 489.7 | 488.3 | 486.6 | 487.9 | 487.0 | 490.1 | 491.0 | 490.1  |
| 12.5°  | 456.4  | 452.4 | 442.6 | 437.7 | 432.4 | 428.4 | 433.3 | 429.7 | 442.2 | 445.7 | 455.5  |
| 15°    | 398.7  | 391.1 | 384.5 | 384.5 | 379.6 | 376.0 | 378.2 | 382.2 | 384.9 | 388.9 | 390.7  |
| 17.5°  | 360.0  | 356.9 | 351.6 | 348.5 | 347.2 | 345.8 | 345.8 | 347.6 | 353.4 | 352.9 | 356.5  |
| 20°    | 327.2  | 325.4 | 322.8 | 318.8 | 317.4 | 316.5 | 316.5 | 316.5 | 320.5 | 324.1 | 326.3  |
| 22.5°  | 304.5  | 303.2 | 301.4 | 296.1 | 293.5 | 292.6 | 294.8 | 296.1 | 299.2 | 301.9 | 304.1  |
| 25°    | 281.9  | 278.8 | 275.7 | 273.9 | 272.6 | 272.6 | 273.5 | 273.9 | 275.2 | 276.6 | 279.2  |
| 27.5°  | 263.3  | 261.0 | 256.6 | 251.7 | 251.7 | 250.4 | 251.3 | 252.2 | 255.3 | 259.7 | 261.9  |
| 30°    | 242.4  | 242.0 | 240.2 | 238.4 | 236.6 | 235.7 | 237.5 | 238.8 | 239.3 | 241.5 | 241.5  |
| 32.5°  | 227.3  | 224.2 | 221.1 | 219.3 | 218.4 | 218.0 | 218.4 | 220.2 | 220.2 | 222.9 | 226.0  |
| 35°    | 212.2  | 210.4 | 207.3 | 204.2 | 203.3 | 201.1 | 202.9 | 204.7 | 207.8 | 209.1 | 210.4  |
| 37.5°  | 195.8  | 193.6 | 192.2 | 191.3 | 189.6 | 190.0 | 188.7 | 191.3 | 194.0 | 193.6 | 194.4  |
| 40°    | 183.4  | 179.4 | 175.4 | 174.9 | 174.5 | 174.0 | 174.0 | 174.5 | 176.2 | 178.0 | 180.7  |
| 42.5°  | 167.4  | 166.0 | 162.5 | 158.9 | 158.0 | 157.2 | 156.3 | 158.0 | 161.6 | 164.7 | 166.0  |
| 45°    | 150.9  | 149.2 | 148.3 | 145.6 | 143.8 | 143.4 | 142.5 | 144.7 | 147.8 | 149.2 | 150.1  |
| 47.5°  | 135.8  | 135.4 | 132.7 | 133.2 | 131.9 | 132.3 | 131.9 | 133.2 | 133.2 | 134.5 | 135.4  |
| 50°    | 125.6  | 124.3 | 123.0 | 122.1 | 120.8 | 120.8 | 120.3 | 120.8 | 122.5 | 124.3 | 123.9  |
| 52.5°  | 115.4  | 113.2 | 112.8 | 112.3 | 111.4 | 112.3 | 111.0 | 111.4 | 113.2 | 114.1 | 113.7  |
| 55°    | 103.4  | 103.0 | 102.1 | 101.2 | 100.8 | 100.3 | 100.3 | 100.3 | 102.1 | 103.4 | 103.9  |
| 57.5°  | 94.1   | 91.9  | 90.1  | 90.1  | 88.3  | 87.9  | 88.8  | 89.2  | 90.6  | 91.5  | 92.3   |
| 60°    | 81.2   | 80.4  | 77.7  | 76.4  | 73.7  | 73.3  | 73.3  | 75.0  | 77.2  | 80.4  | 81.2   |
| 62.5°  | 67.5   | 66.1  | 65.7  | 65.7  | 65.7  | 65.7  | 65.7  | 65.7  | 65.7  | 66.1  | 66.1   |
| 65°    | 59.9   | 60.4  | 59.9  | 59.5  | 59.9  | 59.9  | 59.5  | 59.5  | 59.5  | 59.9  | 60.4   |
| 67.5°  | 53.7   | 53.3  | 53.7  | 53.3  | 52.8  | 52.8  | 52.4  | 52.8  | 53.3  | 53.7  | 53.7   |
| 70°    | 46.6   | 46.6  | 46.2  | 46.6  | 46.2  | 45.7  | 45.3  | 45.3  | 46.2  | 46.6  | 46.6   |
| 72.5°  | 40.0   | 40.0  | 39.5  | 39.5  | 38.6  | 38.6  | 39.1  | 38.6  | 38.6  | 40.0  | 40.0   |
| 75°    | 33.3   | 32.9  | 32.4  | 32.4  | 32.0  | 32.0  | 32.0  | 31.5  | 32.4  | 32.4  | 32.9   |
| 77.5°  | 26.2   | 26.2  | 26.2  | 25.7  | 25.7  | 25.3  | 25.3  | 25.7  | 25.7  | 25.7  | 26.2   |
| 80°    | 20.0   | 20.0  | 20.0  | 19.5  | 19.1  | 19.1  | 19.1  | 19.1  | 19.1  | 19.5  | 19.1   |
| 82.5°  | 13.8   | 13.8  | 13.8  | 13.8  | 13.8  | 13.3  | 13.3  | 13.3  | 13.8  | 13.8  | 13.3   |
| 85°    | 8.4    | 8.0   | 8.4   | 8.4   | 8.0   | 8.4   | 8.0   | 8.0   | 7.5   | 7.5   | 8.0    |
| 87.5°  | 3.6    | 3.1   | 2.7   | 2.7   | 3.1   | 2.7   | 2.7   | 2.7   | 3.1   | 2.7   | 2.7    |
| 90°    | 18.9   | 19.0  | 19.1  | 19.2  | 19.4  | 19.5  | 19.4  | 19.2  | 19.1  | 19.0  | 18.9   |
| 92.5°  | 18.4   | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4  | 18.4   |
| 95°    | 36.7   | 36.6  | 36.3  | 36.1  | 35.8  | 35.6  | 35.8  | 36.1  | 36.3  | 36.6  | 36.7   |
| 97.5°  | 57.4   | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4   |
| 100°   | 79.2   | 79.1  | 79.0  | 78.9  | 78.7  | 78.6  | 78.7  | 78.9  | 79.0  | 79.1  | 79.2   |
| 102.5° | 103.3  | 103.2 | 103.1 | 103.0 | 102.8 | 102.7 | 102.8 | 103.0 | 103.1 | 103.2 | 103.3  |
| 105°   | 127.4  | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4 | 127.4  |
| 107.5° | 152.6  | 152.3 | 151.7 | 151.0 | 150.4 | 149.8 | 150.4 | 151.0 | 151.7 | 152.3 | 152.6  |
| 110°   | 178.5  | 178.3 | 177.9 | 177.5 | 177.1 | 176.7 | 177.1 | 177.5 | 177.9 | 178.3 | 178.5  |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 255°  | 260°  | 265°  | 270°  | 275°  | 280°  | 285°  | 290°  | 292.5° |
|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 112.5° | 203.7  | 203.6 | 203.3 | 203.1 | 202.8 | 202.6 | 202.8 | 203.1 | 203.3 | 203.6 | 203.7  |
| 115°   | 231.2  | 231.0 | 230.6 | 230.3 | 229.9 | 229.5 | 229.9 | 230.3 | 230.6 | 231.0 | 231.2  |
| 117.5° | 256.5  | 256.3 | 255.9 | 255.6 | 255.2 | 254.8 | 255.2 | 255.6 | 255.9 | 256.3 | 256.5  |
| 120°   | 283.5  | 283.3 | 282.9 | 282.5 | 282.1 | 281.7 | 282.1 | 282.5 | 282.9 | 283.3 | 283.5  |
| 122.5° | 309.3  | 309.2 | 308.9 | 308.6 | 308.4 | 308.1 | 308.4 | 308.6 | 308.9 | 309.2 | 309.3  |
| 125°   | 335.7  | 335.6 | 335.5 | 335.4 | 335.2 | 335.1 | 335.2 | 335.4 | 335.5 | 335.6 | 335.7  |
| 127.5° | 360.9  | 360.7 | 360.3 | 360.0 | 359.6 | 359.2 | 359.6 | 360.0 | 360.3 | 360.7 | 360.9  |
| 130°   | 387.9  | 387.6 | 387.1 | 386.6 | 386.1 | 385.6 | 386.1 | 386.6 | 387.1 | 387.6 | 387.9  |
| 132.5° | 412.6  | 412.4 | 412.0 | 411.7 | 411.3 | 410.9 | 411.3 | 411.7 | 412.0 | 412.4 | 412.6  |
| 135°   | 439.0  | 438.8 | 438.4 | 438.0 | 437.6 | 437.2 | 437.6 | 438.0 | 438.4 | 438.8 | 439.0  |
| 137.5° | 463.1  | 462.8 | 462.3 | 461.8 | 461.3 | 460.8 | 461.3 | 461.8 | 462.3 | 462.8 | 463.1  |
| 140°   | 487.7  | 487.4 | 486.9 | 486.4 | 485.9 | 485.4 | 485.9 | 486.4 | 486.9 | 487.4 | 487.7  |
| 142.5° | 510.1  | 509.8 | 509.3 | 508.8 | 508.3 | 507.8 | 508.3 | 508.8 | 509.3 | 509.8 | 510.1  |
| 145°   | 532.5  | 532.2 | 531.7 | 531.2 | 530.7 | 530.2 | 530.7 | 531.2 | 531.7 | 532.2 | 532.5  |
| 147.5° | 552.6  | 552.3 | 551.8 | 551.3 | 550.8 | 550.3 | 550.8 | 551.3 | 551.8 | 552.3 | 552.6  |
| 150°   | 571.5  | 571.3 | 570.9 | 570.6 | 570.2 | 569.8 | 570.2 | 570.6 | 570.9 | 571.3 | 571.5  |
| 152.5° | 590.5  | 590.2 | 589.7 | 589.2 | 588.7 | 588.2 | 588.7 | 589.2 | 589.7 | 590.2 | 590.5  |
| 155°   | 605.9  | 605.7 | 605.3 | 605.0 | 604.6 | 604.2 | 604.6 | 605.0 | 605.3 | 605.7 | 605.9  |
| 157.5° | 621.4  | 621.1 | 620.5 | 619.8 | 619.2 | 618.6 | 619.2 | 619.8 | 620.5 | 621.1 | 621.4  |
| 160°   | 634.1  | 633.8 | 633.3 | 632.8 | 632.3 | 631.8 | 632.3 | 632.8 | 633.3 | 633.8 | 634.1  |
| 162.5° | 646.1  | 645.8 | 645.1 | 644.5 | 643.8 | 643.2 | 643.8 | 644.5 | 645.1 | 645.8 | 646.1  |
| 165°   | 655.9  | 655.6 | 654.9 | 654.3 | 653.6 | 653.0 | 653.6 | 654.3 | 654.9 | 655.6 | 655.9  |
| 167.5° | 664.5  | 664.2 | 663.5 | 662.9 | 662.2 | 661.6 | 662.2 | 662.9 | 663.5 | 664.2 | 664.5  |
| 170°   | 671.4  | 671.0 | 670.2 | 669.5 | 668.7 | 667.9 | 668.7 | 669.5 | 670.2 | 671.0 | 671.4  |
| 172.5° | 676.5  | 676.1 | 675.4 | 674.6 | 673.9 | 673.1 | 673.9 | 674.6 | 675.4 | 676.1 | 676.5  |
| 175°   | 680.0  | 679.6 | 678.8 | 678.1 | 677.3 | 676.5 | 677.3 | 678.1 | 678.8 | 679.6 | 680.0  |
| 177.5° | 681.7  | 681.3 | 680.5 | 679.8 | 679.0 | 678.2 | 679.0 | 679.8 | 680.5 | 681.3 | 681.7  |
| 180°   | 680.0  | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0  |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 295°  | 300°  | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0°     | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8 | 638.8  | 638.8 |
| 2.5°   | 608.7 | 610.9 | 610.0 | 605.1 | 610.0 | 611.3 | 614.0 | 616.6 | 618.4 | 621.1  | 623.3 |
| 5°     | 570.5 | 574.9 | 577.6 | 574.9 | 583.8 | 585.1 | 591.3 | 594.9 | 600.2 | 604.7  | 608.2 |
| 7.5°   | 534.5 | 538.1 | 543.4 | 544.3 | 549.6 | 555.8 | 564.7 | 573.6 | 582.0 | 586.5  | 590.5 |
| 10°    | 495.9 | 502.1 | 510.1 | 508.3 | 516.3 | 526.1 | 535.4 | 549.6 | 556.7 | 564.7  | 571.8 |
| 12.5°  | 457.3 | 461.3 | 471.9 | 475.5 | 487.0 | 494.6 | 507.4 | 516.3 | 534.1 | 543.4  | 549.6 |
| 15°    | 389.8 | 406.2 | 419.5 | 435.5 | 450.6 | 464.8 | 476.4 | 492.3 | 507.9 | 515.0  | 525.2 |
| 17.5°  | 359.2 | 366.7 | 374.7 | 382.7 | 402.2 | 427.5 | 447.9 | 465.3 | 478.6 | 487.9  | 499.9 |
| 20°    | 327.2 | 334.7 | 343.6 | 351.2 | 363.2 | 381.4 | 406.7 | 436.4 | 452.4 | 462.2  | 473.7 |
| 22.5°  | 304.5 | 311.7 | 317.4 | 324.1 | 333.4 | 346.7 | 365.8 | 402.7 | 424.0 | 436.0  | 446.2 |
| 25°    | 280.1 | 289.0 | 295.2 | 300.1 | 307.7 | 322.3 | 337.8 | 358.7 | 396.9 | 406.2  | 420.4 |
| 27.5°  | 263.3 | 265.9 | 273.0 | 280.6 | 288.1 | 296.1 | 312.1 | 329.9 | 355.6 | 376.0  | 393.3 |
| 30°    | 243.3 | 249.9 | 256.6 | 259.7 | 266.4 | 277.9 | 287.7 | 306.8 | 326.7 | 342.7  | 363.6 |
| 32.5°  | 228.2 | 232.2 | 236.6 | 244.2 | 250.4 | 258.4 | 268.1 | 284.1 | 301.0 | 311.2  | 327.2 |
| 35°    | 211.3 | 214.0 | 223.3 | 226.4 | 232.6 | 240.6 | 250.4 | 262.8 | 281.0 | 289.0  | 300.6 |
| 37.5°  | 195.3 | 201.6 | 204.2 | 211.3 | 217.1 | 225.1 | 232.2 | 246.4 | 258.4 | 267.7  | 278.4 |
| 40°    | 182.9 | 185.6 | 190.5 | 196.7 | 201.6 | 207.8 | 216.6 | 226.9 | 239.7 | 247.3  | 256.6 |
| 42.5°  | 167.8 | 170.0 | 176.2 | 179.8 | 187.8 | 193.6 | 198.9 | 211.3 | 222.9 | 228.6  | 238.0 |
| 45°    | 151.4 | 156.7 | 160.7 | 167.8 | 172.3 | 179.4 | 186.0 | 194.9 | 205.5 | 212.2  | 217.5 |
| 47.5°  | 137.2 | 142.5 | 146.5 | 153.2 | 160.3 | 163.4 | 170.5 | 179.8 | 189.6 | 194.9  | 202.4 |
| 50°    | 125.6 | 127.4 | 135.0 | 138.1 | 145.6 | 151.8 | 156.7 | 164.7 | 175.4 | 178.5  | 184.7 |
| 52.5°  | 114.5 | 115.9 | 120.8 | 124.7 | 131.4 | 136.7 | 143.0 | 150.5 | 159.4 | 164.3  | 169.1 |
| 55°    | 104.8 | 105.7 | 107.9 | 112.3 | 116.8 | 123.4 | 129.2 | 136.3 | 143.8 | 149.2  | 153.6 |
| 57.5°  | 93.7  | 95.4  | 97.2  | 99.9  | 104.3 | 110.5 | 116.8 | 123.4 | 129.6 | 133.2  | 139.0 |
| 60°    | 80.8  | 83.5  | 86.6  | 89.7  | 92.8  | 97.2  | 104.3 | 110.5 | 116.3 | 119.4  | 123.9 |
| 62.5°  | 67.0  | 72.4  | 75.0  | 78.6  | 81.2  | 85.2  | 90.6  | 97.7  | 101.7 | 105.7  | 109.2 |
| 65°    | 60.4  | 60.8  | 61.3  | 64.8  | 69.7  | 73.7  | 78.6  | 83.9  | 90.1  | 92.8   | 95.4  |
| 67.5°  | 53.7  | 54.2  | 55.0  | 55.5  | 57.3  | 61.7  | 67.0  | 72.8  | 77.7  | 79.5   | 82.1  |
| 70°    | 47.1  | 47.1  | 48.8  | 49.3  | 49.7  | 50.2  | 54.6  | 60.4  | 64.8  | 67.0   | 70.1  |
| 72.5°  | 40.0  | 40.4  | 41.3  | 41.7  | 42.6  | 43.5  | 44.8  | 47.9  | 53.3  | 55.5   | 59.0  |
| 75°    | 32.9  | 33.3  | 33.7  | 34.2  | 35.5  | 36.0  | 37.3  | 39.1  | 41.3  | 44.0   | 46.2  |
| 77.5°  | 26.2  | 26.2  | 26.6  | 27.5  | 28.4  | 28.9  | 30.2  | 31.1  | 32.0  | 33.3   | 35.1  |
| 80°    | 19.5  | 20.0  | 20.0  | 20.9  | 20.9  | 21.3  | 21.8  | 23.1  | 24.0  | 24.9   | 25.7  |
| 82.5°  | 13.3  | 14.2  | 14.2  | 14.2  | 14.7  | 15.1  | 15.5  | 15.5  | 16.4  | 16.9   | 18.2  |
| 85°    | 8.0   | 8.4   | 8.4   | 8.4   | 8.0   | 8.9   | 8.9   | 9.3   | 9.3   | 9.3    | 9.8   |
| 87.5°  | 3.1   | 2.7   | 3.1   | 3.1   | 3.1   | 3.6   | 3.1   | 3.1   | 3.6   | 4.0    | 4.0   |
| 90°    | 19.0  | 19.3  | 19.6  | 19.8  | 20.1  | 17.3  | 14.5  | 11.7  | 8.9   | 7.5    | 6.7   |
| 92.5°  | 18.3  | 18.2  | 18.1  | 17.9  | 17.8  | 17.7  | 17.5  | 17.4  | 17.3  | 17.2   | 16.7  |
| 95°    | 36.7  | 36.7  | 36.7  | 36.7  | 36.7  | 36.5  | 36.2  | 36.0  | 35.7  | 35.6   | 35.0  |
| 97.5°  | 57.4  | 57.4  | 57.4  | 57.4  | 57.4  | 56.9  | 56.4  | 55.9  | 55.4  | 55.1   | 54.5  |
| 100°   | 79.2  | 79.2  | 79.2  | 79.2  | 79.2  | 78.8  | 78.4  | 78.1  | 77.7  | 77.5   | 77.0  |
| 102.5° | 103.2 | 103.1 | 103.0 | 102.8 | 102.7 | 102.2 | 101.7 | 101.2 | 100.7 | 100.4  | 100.0 |
| 105°   | 127.3 | 127.0 | 126.7 | 126.5 | 126.2 | 126.0 | 125.7 | 125.5 | 125.2 | 125.1  | 124.9 |
| 107.5° | 152.5 | 152.4 | 152.3 | 152.2 | 152.1 | 152.1 | 152.1 | 152.1 | 152.1 | 152.1  | 151.8 |
| 110°   | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5 | 178.5  | 178.1 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 295°  | 300°  | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 112.5° | 203.9 | 204.3 | 204.6 | 205.0 | 205.4 | 205.5 | 205.7 | 205.8 | 205.9 | 206.0  | 205.6 |
| 115°   | 231.3 | 231.4 | 231.5 | 231.7 | 231.8 | 232.1 | 232.3 | 232.6 | 232.9 | 233.0  | 232.6 |
| 117.5° | 256.7 | 257.1 | 257.4 | 257.8 | 258.2 | 258.8 | 259.5 | 260.1 | 260.8 | 261.1  | 260.6 |
| 120°   | 283.5 | 283.5 | 283.5 | 283.5 | 283.5 | 284.5 | 285.5 | 286.6 | 287.6 | 288.1  | 287.6 |
| 122.5° | 309.5 | 309.9 | 310.2 | 310.6 | 311.0 | 311.6 | 312.3 | 312.9 | 313.6 | 313.9  | 313.3 |
| 125°   | 335.9 | 336.3 | 336.6 | 337.0 | 337.4 | 337.8 | 338.2 | 338.5 | 338.9 | 339.1  | 338.5 |
| 127.5° | 361.2 | 361.7 | 362.2 | 362.7 | 363.2 | 363.7 | 364.2 | 364.7 | 365.2 | 365.5  | 364.8 |
| 130°   | 388.0 | 388.3 | 388.5 | 388.8 | 389.0 | 389.3 | 389.5 | 389.8 | 390.1 | 390.2  | 389.4 |
| 132.5° | 412.9 | 413.5 | 414.2 | 414.8 | 415.4 | 415.3 | 415.2 | 415.1 | 415.0 | 414.9  | 414.3 |
| 135°   | 439.1 | 439.2 | 439.3 | 439.4 | 439.5 | 439.3 | 439.0 | 438.8 | 438.5 | 438.4  | 437.7 |
| 137.5° | 463.2 | 463.3 | 463.4 | 463.5 | 463.6 | 463.4 | 463.1 | 462.9 | 462.6 | 462.5  | 461.9 |
| 140°   | 487.7 | 487.7 | 487.7 | 487.7 | 487.7 | 487.1 | 486.5 | 485.8 | 485.2 | 484.9  | 484.3 |
| 142.5° | 510.0 | 509.9 | 509.8 | 509.6 | 509.5 | 509.1 | 508.7 | 508.4 | 508.0 | 507.8  | 507.2 |
| 145°   | 532.4 | 532.3 | 532.2 | 532.0 | 531.9 | 531.1 | 530.4 | 529.6 | 528.9 | 528.5  | 528.1 |
| 147.5° | 552.5 | 552.2 | 551.9 | 551.7 | 551.4 | 550.9 | 550.4 | 549.9 | 549.4 | 549.1  | 548.5 |
| 150°   | 571.3 | 570.9 | 570.6 | 570.2 | 569.8 | 569.3 | 568.8 | 568.3 | 567.8 | 567.5  | 567.1 |
| 152.5° | 590.2 | 589.7 | 589.2 | 588.7 | 588.2 | 587.6 | 586.9 | 586.3 | 585.6 | 585.3  | 584.9 |
| 155°   | 605.6 | 605.0 | 604.3 | 603.7 | 603.1 | 602.7 | 602.3 | 602.0 | 601.6 | 601.4  | 601.2 |
| 157.5° | 621.0 | 620.1 | 619.2 | 618.3 | 617.4 | 617.2 | 616.9 | 616.7 | 616.4 | 616.3  | 616.2 |
| 160°   | 633.7 | 632.9 | 632.2 | 631.4 | 630.6 | 630.5 | 630.3 | 630.2 | 630.1 | 630.0  | 629.9 |
| 162.5° | 645.7 | 644.8 | 643.9 | 643.0 | 642.1 | 642.0 | 641.8 | 641.7 | 641.6 | 641.5  | 641.5 |
| 165°   | 655.5 | 654.6 | 653.7 | 652.8 | 651.9 | 651.9 | 651.9 | 651.9 | 651.9 | 651.9  | 652.0 |
| 167.5° | 664.1 | 663.2 | 662.3 | 661.4 | 660.5 | 660.5 | 660.5 | 660.5 | 660.5 | 660.5  | 660.7 |
| 170°   | 670.9 | 670.0 | 669.1 | 668.2 | 667.3 | 667.4 | 667.6 | 667.7 | 667.8 | 667.9  | 668.1 |
| 172.5° | 676.1 | 675.2 | 674.3 | 673.4 | 672.5 | 672.6 | 672.8 | 672.9 | 673.0 | 673.1  | 673.3 |
| 175°   | 679.6 | 678.7 | 677.8 | 676.9 | 676.0 | 676.2 | 676.5 | 676.7 | 677.0 | 677.1  | 677.3 |
| 177.5° | 681.3 | 680.5 | 679.8 | 679.0 | 678.2 | 678.5 | 678.7 | 679.0 | 679.3 | 679.4  | 679.6 |
| 180°   | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0 | 680.0  | 680.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 345°  | 350°  | 355°  | 360°  |
|--------|-------|-------|-------|-------|
| 0°     | 638.8 | 638.8 | 638.8 | 638.8 |
| 2.5°   | 627.3 | 626.0 | 634.0 | 642.8 |
| 5°     | 614.4 | 616.6 | 626.9 | 639.3 |
| 7.5°   | 601.1 | 606.0 | 618.0 | 634.4 |
| 10°    | 582.5 | 591.3 | 609.5 | 626.4 |
| 12.5°  | 564.3 | 576.2 | 593.6 | 613.5 |
| 15°    | 543.8 | 557.2 | 578.5 | 602.4 |
| 17.5°  | 521.2 | 536.3 | 561.2 | 587.3 |
| 20°    | 497.2 | 517.2 | 543.4 | 571.8 |
| 22.5°  | 470.6 | 494.6 | 521.6 | 553.2 |
| 25°    | 444.8 | 471.0 | 498.1 | 534.5 |
| 27.5°  | 419.5 | 445.3 | 475.5 | 512.3 |
| 30°    | 394.2 | 417.8 | 450.2 | 489.7 |
| 32.5°  | 367.1 | 391.6 | 425.7 | 466.1 |
| 35°    | 342.3 | 366.7 | 398.7 | 438.6 |
| 37.5°  | 315.6 | 341.8 | 372.5 | 413.8 |
| 40°    | 284.6 | 315.2 | 344.9 | 384.5 |
| 42.5°  | 258.8 | 291.2 | 320.1 | 357.4 |
| 45°    | 238.4 | 269.0 | 293.0 | 329.4 |
| 47.5°  | 219.3 | 244.2 | 268.6 | 302.3 |
| 50°    | 201.1 | 220.2 | 245.5 | 275.7 |
| 52.5°  | 182.5 | 198.9 | 220.6 | 249.1 |
| 55°    | 165.6 | 181.1 | 200.7 | 222.4 |
| 57.5°  | 150.1 | 161.2 | 180.7 | 200.2 |
| 60°    | 132.7 | 144.3 | 159.4 | 175.8 |
| 62.5°  | 118.1 | 127.0 | 141.2 | 154.9 |
| 65°    | 102.6 | 111.0 | 121.6 | 134.5 |
| 67.5°  | 88.3  | 95.9  | 104.3 | 114.5 |
| 70°    | 75.5  | 81.2  | 87.5  | 96.3  |
| 72.5°  | 61.7  | 67.9  | 73.7  | 80.8  |
| 75°    | 50.6  | 53.3  | 58.2  | 63.0  |
| 77.5°  | 39.1  | 42.6  | 45.3  | 49.3  |
| 80°    | 28.0  | 31.1  | 32.0  | 35.1  |
| 82.5°  | 18.6  | 20.4  | 22.2  | 23.1  |
| 85°    | 10.7  | 11.5  | 13.3  | 13.8  |
| 87.5°  | 4.0   | 4.4   | 5.3   | 6.2   |
| 90°    | 5.2   | 3.7   | 2.1   | 0.6   |
| 92.5°  | 15.7  | 14.6  | 13.6  | 12.6  |
| 95°    | 33.7  | 32.4  | 31.1  | 29.8  |
| 97.5°  | 53.4  | 52.2  | 51.1  | 49.9  |
| 100°   | 76.0  | 74.9  | 73.9  | 72.9  |
| 102.5° | 99.3  | 98.5  | 97.8  | 97.0  |
| 105°   | 124.5 | 124.2 | 123.8 | 123.4 |
| 107.5° | 151.3 | 150.8 | 150.3 | 149.8 |
| 110°   | 177.3 | 176.6 | 175.8 | 175.0 |

TEST NUMBER: P999568

CATALOG NUMBER: SA2XXRDIP-B290D530UB35-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 345°  | 350°  | 355°  | 360°  |
|--------|-------|-------|-------|-------|
| 112.5° | 204.9 | 204.1 | 203.4 | 202.6 |
| 115°   | 231.8 | 231.1 | 230.3 | 229.5 |
| 117.5° | 259.6 | 258.5 | 257.5 | 256.5 |
| 120°   | 286.6 | 285.5 | 284.5 | 283.5 |
| 122.5° | 312.0 | 310.7 | 309.4 | 308.1 |
| 125°   | 337.4 | 336.3 | 335.1 | 334.0 |
| 127.5° | 363.4 | 362.0 | 360.6 | 359.2 |
| 130°   | 387.7 | 386.0 | 384.4 | 382.7 |
| 132.5° | 413.0 | 411.7 | 410.4 | 409.1 |
| 135°   | 436.3 | 434.9 | 433.5 | 432.1 |
| 137.5° | 460.8 | 459.6 | 458.5 | 457.3 |
| 140°   | 483.2 | 482.0 | 480.9 | 479.7 |
| 142.5° | 506.1 | 505.0 | 503.8 | 502.7 |
| 145°   | 527.2 | 526.3 | 525.4 | 524.5 |
| 147.5° | 547.4 | 546.3 | 545.1 | 544.0 |
| 150°   | 566.4 | 565.6 | 564.9 | 564.1 |
| 152.5° | 584.1 | 583.4 | 582.6 | 581.8 |
| 155°   | 600.8 | 600.4 | 600.0 | 599.6 |
| 157.5° | 615.9 | 615.6 | 615.4 | 615.1 |
| 160°   | 629.6 | 629.4 | 629.1 | 628.9 |
| 162.5° | 641.5 | 641.5 | 641.5 | 641.5 |
| 165°   | 652.1 | 652.2 | 652.3 | 652.4 |
| 167.5° | 661.1 | 661.4 | 661.8 | 662.2 |
| 170°   | 668.5 | 668.8 | 669.2 | 669.6 |
| 172.5° | 673.7 | 674.0 | 674.4 | 674.8 |
| 175°   | 677.7 | 678.0 | 678.4 | 678.8 |
| 177.5° | 680.0 | 680.3 | 680.7 | 681.1 |
| 180°   | 680.0 | 680.0 | 680.0 | 680.0 |

(END OF REPORT)