

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999583

Luminaire Tested: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999583
REPORT IS A COMBINATION OF REPORTS P988136 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2788.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999583

CATALOG NUMBER: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999583

CATALOG NUMBER: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	16	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7435	7435	7435
5°	7447	7073	7021
10°	7374	6709	6488
15°	7272	6278	5879
20°	7138	5789	5243
25°	7001	5287	4661
30°	6816	4798	4025
35°	6636	4303	3479
40°	6452	3820	2916
45°	6238	3318	2427
50°	6017	2836	1975
55°	5788	2354	1569
60°	5520	1882	1187
65°	5212	1436	964
70°	4842	1041	768
75°	4375	794	586
80°	3696	538	393
85°	2585	247	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6238 cd/sqm

TEST NUMBER: P999583

CATALOG NUMBER: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.6
10°-20°	120.8	4.3
20°-30°	169.7	6.1
30°-40°	184.9	6.6
40°-50°	170.0	6.1
50°-60°	133.5	4.8
60°-70°	86.9	3.1
70°-80°	44.7	1.6
80°-90°	13.3	0.5
90°-100°	40.3	1.4
100°-110°	128.0	4.6
110°-120°	219.1	7.9
120°-130°	288.1	10.3
130°-140°	323.4	11.6
140°-150°	317.1	11.4
150°-160°	266.0	9.5
160°-170°	176.4	6.3
170°-180°	61.7	2.2
0°-30°	334.5	12.0
0°-40°	519.5	18.6
0°-60°	823.0	29.5
0°-90°	967.9	34.7
90°-120°	387.4	13.9
90°-150°	1316.0	47.2
90°-180°	1820.0	65.3
0°-180°	2788.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	470	470	470	470	470	
5°	470	468	462	466	465	45
15°	447	442	428	420	415	126
25°	406	392	364	346	340	186
35°	349	328	290	264	254	219
45°	286	257	212	182	172	221
55°	217	184	138	113	105	194
65°	147	112	74	60	58	145
75°	78	48	34	31	31	83
85°	18	9	8	8	8	21
90°	0	7	19	18	19	3
95°	29	34	35	35	34	32
105°	118	120	121	122	122	125
115°	220	223	222	221	220	217
125°	320	325	323	321	321	286
135°	414	420	421	420	419	320
145°	502	506	509	510	508	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P999583

CATALOG NUMBER: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	469.7	469.7	469.7	469.7	469.7
2.5°	471.8	469.7	465.0	469.3	468.4
5°	469.7	467.6	462.0	465.9	464.6
7.5°	465.9	463.3	457.4	459.1	456.9
10°	460.8	457.8	449.3	448.0	445.5
12.5°	454.4	450.6	439.1	436.5	431.9
15°	446.7	442.1	427.6	419.5	415.3
17.5°	437.8	431.0	413.2	403.8	397.0
20°	427.6	419.1	397.9	387.2	377.9
22.5°	416.6	406.8	382.1	367.7	361.3
25°	405.5	391.9	363.9	346.4	340.1
27.5°	392.3	377.9	346.9	326.9	317.1
30°	378.3	362.2	328.2	306.5	295.0
32.5°	364.7	345.2	310.3	284.8	274.2
35°	349.4	327.7	290.3	263.5	254.2
37.5°	334.5	311.2	271.6	242.3	231.7
40°	318.8	293.3	252.1	221.9	210.8
42.5°	302.6	275.4	232.5	201.1	190.4
45°	285.6	257.2	212.5	182.4	172.2
47.5°	269.5	239.3	193.4	163.2	153.9
50°	251.6	221.5	174.7	145.4	136.4
52.5°	234.2	202.3	156.9	128.8	120.7
55°	217.2	184.1	138.1	112.6	104.6
57.5°	199.8	165.8	121.6	97.8	91.0
60°	181.9	147.9	104.1	82.5	75.7
62.5°	164.5	130.5	89.3	68.9	65.5
65°	146.6	112.2	74.0	59.5	58.2
67.5°	129.6	95.2	59.5	52.3	51.0
70°	111.8	78.6	49.3	45.1	43.4
72.5°	94.8	63.3	41.2	37.8	37.0
75°	78.2	48.5	34.0	31.0	30.6
77.5°	61.6	34.4	26.8	25.1	24.2
80°	46.3	24.7	20.4	18.7	18.7
82.5°	32.3	16.6	14.0	13.2	13.2
85°	18.3	9.4	8.1	8.1	8.1
87.5°	6.8	3.4	3.4	3.0	3.0
90°	0.5	7.1	19.2	18.1	18.7
92.5°	12.1	16.5	17.0	17.6	17.6
95°	28.6	34.1	35.2	35.2	34.1
97.5°	47.8	52.7	54.9	54.9	54.9
100°	69.8	74.2	75.8	75.8	75.3
102.5°	92.8	96.1	98.3	98.9	98.3
105°	118.1	119.8	120.9	122.0	122.0
107.5°	143.4	145.6	145.6	146.1	143.4
110°	167.6	170.9	170.9	170.9	169.2

TEST NUMBER: P999583

CATALOG NUMBER: SA2XXRDIP-B290D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.9	197.2	196.7	195.0	193.9
115°	219.8	223.1	222.0	221.4	219.8
117.5°	245.6	250.0	247.2	245.6	243.9
120°	271.4	275.8	271.4	271.4	269.8
122.5°	295.0	300.5	297.8	296.1	295.0
125°	319.7	324.7	323.0	321.4	320.8
127.5°	343.9	350.0	347.8	345.6	343.9
130°	366.4	373.6	372.5	371.4	369.2
132.5°	391.7	397.2	397.8	395.0	393.4
135°	413.7	419.7	420.8	420.3	418.6
137.5°	437.9	442.8	443.9	443.4	441.2
140°	459.3	464.2	467.0	467.0	464.8
142.5°	481.3	486.2	487.9	488.4	486.2
145°	502.1	506.0	509.3	509.8	507.6
147.5°	520.8	525.8	528.0	529.1	526.9
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)