

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999608

Luminaire Tested: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999608
REPORT IS A COMBINATION OF REPORTS P988161 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3647.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33
2	86	79	73	69	77	71	66	62	57	53	51	43	41	39	31	30	29
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22
5	66	55	48	42	59	50	44	39	41	36	32	31	28	26	23	21	19
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	14	13
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10112	10112	10112	10112
5°	10136	10742	10171	8581
10°	10024	11353	10096	7086
15°	9806	11356	9972	5323
20°	9545	9388	9752	4391
25°	9228	5866	9428	3736
30°	8823	3755	9063	3216
35°	8330	2887	8599	2752
40°	7782	2427	8114	2407
45°	7194	2065	7495	2021
50°	6593	1755	6901	1749
55°	5926	1525	6246	1504
60°	5335	1162	5617	1149
65°	4781	874	5066	992
70°	4170	699	4500	808
75°	3524	536	3849	612
80°	2802	364	3010	402
85°	1949	188	2133	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9250 cd/sqm

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	1.7
10°-20°	169.1	4.6
20°-30°	217.7	6.0
30°-40°	206.5	5.7
40°-50°	177.0	4.9
50°-60°	134.8	3.7
60°-70°	85.0	2.3
70°-80°	42.4	1.2
80°-90°	13.5	0.4
90°-100°	56.2	1.5
100°-110°	178.7	4.9
110°-120°	305.8	8.4
120°-130°	402.1	11.0
130°-140°	451.4	12.4
140°-150°	442.6	12.1
150°-160°	371.3	10.2
160°-170°	246.2	6.8
170°-180°	86.1	2.4
0°-30°	447.4	12.3
0°-40°	653.9	17.9
0°-60°	965.7	26.5
0°-90°	1106.6	30.3
90°-120°	540.7	14.8
90°-150°	1836.8	50.4
90°-180°	2540.0	69.6
0°-180°	3647.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	639	639	639	639	639	
5°	639	711	642	568	639	61
15°	602	802	613	376	602	169
25°	534	428	546	273	534	245
35°	439	211	453	201	439	274
45°	329	146	343	143	329	254
55°	222	102	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	26	1	26	1	3
95°	40	48	40	48	40	45
105°	165	170	165	170	165	174
115°	307	307	307	307	307	303
125°	446	448	446	448	446	399
135°	577	584	577	584	577	446
145°	701	708	701	708	701	438
155°	801	807	801	807	801	369
165°	872	873	872	873	872	246
175°	907	904	907	904	907	86
180°	909	909	909	909	909	

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	642.8	645.5	646.8	648.6	652.6	655.3	659.3	660.2	659.7	661.5	656.6
5°	639.3	645.1	650.4	654.8	661.9	666.4	671.3	677.0	678.4	685.0	681.0
7.5°	634.4	642.8	650.4	659.3	669.9	675.7	683.2	692.1	696.1	704.1	706.3
10°	626.4	638.4	651.3	660.6	675.2	685.5	692.6	706.8	716.1	728.1	726.3
12.5°	613.5	629.1	646.4	661.9	681.0	687.7	701.0	715.6	727.6	738.7	748.5
15°	602.4	620.2	639.3	658.4	680.1	692.6	705.9	725.0	737.8	757.4	765.8
17.5°	587.3	610.0	632.6	653.9	679.7	693.9	710.3	729.0	748.1	766.7	773.4
20°	571.8	596.2	620.6	649.5	678.8	692.6	709.4	732.5	751.2	765.8	765.8
22.5°	553.2	582.9	610.9	638.4	670.4	690.3	707.7	734.7	748.1	751.2	739.2
25°	534.5	564.3	594.9	629.1	665.5	683.2	702.8	728.1	732.5	720.1	689.0
27.5°	512.3	545.6	580.2	617.1	655.3	677.5	695.2	712.1	703.7	670.4	622.0
30°	489.7	525.6	564.7	599.8	645.9	666.4	681.5	686.3	659.7	605.5	542.9
32.5°	466.1	501.2	542.5	584.7	631.3	650.8	660.6	647.7	598.9	530.5	454.2
35°	438.6	478.1	521.2	565.1	611.3	626.0	631.7	600.2	537.6	449.3	373.4
37.5°	413.8	453.3	499.4	544.3	589.1	597.1	591.3	542.1	462.6	375.1	301.0
40°	384.5	426.6	471.9	522.1	558.9	561.2	546.9	483.0	384.5	302.3	256.6
42.5°	357.4	400.0	445.3	496.3	524.3	516.8	497.7	413.8	321.0	260.6	223.8
45°	329.4	369.8	418.6	463.9	483.9	466.1	437.3	348.1	269.5	224.2	195.8
47.5°	302.3	340.1	388.5	432.0	435.5	415.5	381.4	291.7	233.5	197.1	174.0
50°	275.7	313.4	358.7	394.7	391.1	363.6	325.0	253.5	202.9	174.0	154.9
52.5°	249.1	283.2	327.2	355.6	340.5	313.9	275.7	214.9	177.1	151.8	137.2
55°	222.4	254.4	292.1	315.6	291.7	261.0	234.0	184.2	153.6	133.2	122.1
57.5°	200.2	225.5	260.2	274.4	245.5	221.5	198.0	158.5	133.2	118.5	105.7
60°	175.8	198.9	227.3	235.7	206.0	186.5	166.5	134.1	114.1	101.2	92.8
62.5°	154.9	174.0	195.8	195.8	169.6	154.9	139.8	112.3	95.9	85.7	81.7
65°	134.5	148.3	163.8	162.0	139.8	127.0	115.0	92.8	80.4	73.3	69.3
67.5°	114.5	125.2	135.4	129.2	113.2	102.1	91.0	75.0	66.6	61.7	56.4
70°	96.3	104.8	110.1	104.3	88.3	79.0	71.0	60.4	53.7	47.5	44.4
72.5°	80.8	84.4	86.1	79.0	65.7	60.4	54.6	47.1	41.3	38.2	37.3
75°	63.0	66.1	64.8	59.5	48.4	44.4	40.0	34.6	33.3	31.5	30.6
77.5°	49.3	49.3	47.1	42.2	34.6	31.5	29.7	27.1	25.7	25.3	24.4
80°	35.1	34.6	33.3	28.0	23.5	21.8	21.8	20.0	19.5	18.6	18.6
82.5°	23.1	23.1	21.3	16.9	15.5	15.1	14.7	13.8	13.8	13.3	13.3
85°	13.8	12.9	10.7	9.3	8.9	8.9	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.8	2.8	4.9	6.9	9.0	10.0	11.9	15.6	19.3	23.1	26.8
92.5°	16.9	18.3	19.6	21.0	22.3	23.0	23.1	23.3	23.4	23.6	23.8
95°	39.9	41.6	43.3	45.0	46.7	47.5	47.7	48.0	48.4	48.7	49.1
97.5°	66.7	68.2	69.8	71.3	72.8	73.6	73.9	74.6	75.3	76.0	76.7
100°	97.4	98.8	100.1	101.5	102.8	103.5	103.8	104.3	104.8	105.3	105.8
102.5°	129.6	130.6	131.6	132.7	133.7	134.2	134.5	135.2	135.9	136.6	137.3
105°	164.9	165.4	165.9	166.4	166.9	167.2	167.4	167.7	168.0	168.4	168.7
107.5°	200.1	200.8	201.5	202.2	202.9	203.2	203.2	203.2	203.2	203.2	203.2
110°	233.9	234.9	235.9	237.0	238.0	238.5	238.5	238.5	238.5	238.5	238.5



TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	270.7	271.7	272.7	273.8	274.8	275.3	275.2	275.0	274.9	274.7	274.5
115°	306.7	307.7	308.7	309.8	310.8	311.3	311.1	310.8	310.5	310.1	309.8
117.5°	342.8	344.2	345.5	346.9	348.2	348.9	348.5	347.6	346.8	345.9	345.1
120°	378.8	380.2	381.5	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8
122.5°	411.8	413.5	415.2	416.9	418.6	419.4	419.0	418.1	417.3	416.4	415.6
125°	446.3	447.8	449.4	450.9	452.4	453.2	452.9	452.4	451.9	451.4	450.9
127.5°	480.0	481.9	483.7	485.6	487.5	488.4	488.1	487.4	486.7	486.1	485.4
130°	511.5	513.7	515.9	518.1	520.3	521.4	521.2	520.9	520.6	520.2	519.9
132.5°	546.7	548.4	550.1	551.8	553.5	554.4	554.5	554.7	554.8	555.0	555.2
135°	577.4	579.3	581.1	583.0	584.9	585.8	586.0	586.3	586.7	587.0	587.4
137.5°	611.1	612.6	614.2	615.7	617.2	618.0	618.2	618.5	618.9	619.2	619.6
140°	641.0	642.5	644.1	645.6	647.1	647.9	648.3	649.2	650.1	650.9	651.8
142.5°	671.7	673.2	674.8	676.3	677.8	678.6	678.9	679.4	679.9	680.4	680.9
145°	700.8	702.0	703.2	704.4	705.6	706.2	706.7	707.7	708.8	709.8	710.8
147.5°	726.9	728.4	730.0	731.5	733.0	733.8	734.1	734.8	735.5	736.2	736.9
150°	753.8	754.8	755.8	756.9	757.9	758.4	758.7	759.4	760.1	760.7	761.4
152.5°	777.5	778.5	779.5	780.6	781.6	782.1	782.5	783.4	784.3	785.1	786.0
155°	801.3	801.8	802.3	802.8	803.3	803.6	803.9	804.4	804.9	805.4	805.9
157.5°	822.0	822.3	822.7	823.0	823.3	823.5	823.7	824.0	824.4	824.7	825.1
160°	840.4	840.7	841.1	841.4	841.7	841.9	842.0	842.2	842.3	842.5	842.7
162.5°	857.3	857.3	857.3	857.3	857.3	857.3	857.4	857.5	857.7	857.8	858.0
165°	871.8	871.6	871.5	871.3	871.2	871.1	871.1	871.1	871.1	871.1	871.1
167.5°	884.9	884.4	883.9	883.4	882.9	882.6	882.6	882.6	882.6	882.6	882.6
170°	894.8	894.3	893.8	893.3	892.8	892.5	892.4	892.3	892.1	892.0	891.8
172.5°	901.7	901.2	900.7	900.2	899.7	899.4	899.3	899.2	899.0	898.9	898.7
175°	907.1	906.6	906.1	905.6	905.1	904.8	904.6	904.3	904.0	903.6	903.3
177.5°	910.2	909.7	909.2	908.7	908.2	907.9	907.7	907.4	907.0	906.7	906.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	661.5	662.4	663.7	669.9	670.8	672.6	671.7	671.7	672.1	671.3	671.7
5°	689.9	691.2	697.9	705.4	707.2	705.4	707.7	710.8	710.8	710.8	709.9
7.5°	716.5	721.4	729.0	740.1	742.3	744.5	748.5	745.8	746.7	750.7	749.4
10°	742.3	749.4	757.8	767.1	772.0	775.1	776.9	780.9	790.2	779.6	783.6
12.5°	766.7	776.9	785.8	796.0	799.6	803.5	804.9	808.4	808.4	808.0	811.1
15°	782.7	792.0	800.0	806.7	807.5	806.7	805.8	806.2	807.5	802.2	805.3
17.5°	786.2	787.1	789.8	787.1	787.6	778.2	772.9	771.6	759.2	759.6	769.8
20°	768.9	753.8	749.8	735.2	726.3	702.3	701.4	694.8	668.6	676.6	674.8
22.5°	721.4	695.7	661.5	644.6	636.2	610.9	591.3	577.6	568.3	558.9	554.9
25°	658.8	617.1	568.7	535.4	530.5	507.0	471.0	454.2	434.2	428.0	438.6
27.5°	578.0	523.9	469.3	418.2	408.9	387.6	369.4	357.4	334.3	333.0	333.8
30°	468.4	413.8	368.0	334.7	311.7	301.9	289.9	281.0	271.7	275.2	276.1
32.5°	384.9	333.0	290.3	272.6	261.9	255.7	245.5	239.7	235.7	234.4	234.0
35°	305.9	271.3	252.2	234.8	228.6	224.2	216.6	214.0	210.4	210.9	210.9
37.5°	261.9	233.1	218.9	210.0	204.2	202.0	197.1	194.4	192.2	191.3	192.7
40°	226.0	206.0	197.1	189.1	184.2	183.4	180.7	177.6	174.9	175.4	176.7
42.5°	199.8	188.2	177.6	171.4	167.8	166.5	164.3	162.0	162.0	160.7	160.3
45°	178.9	169.6	160.7	154.9	152.7	150.9	148.3	147.8	146.1	146.5	146.9
47.5°	160.3	152.7	146.1	140.3	138.1	137.6	135.0	133.2	133.2	132.7	132.3
50°	143.4	135.8	130.1	127.0	123.9	123.0	122.5	122.1	121.2	121.2	121.6
52.5°	129.6	122.1	117.6	115.0	113.2	112.3	112.3	111.9	111.9	111.9	111.4
55°	114.5	108.3	104.8	103.9	103.0	102.6	102.1	101.2	100.8	101.7	100.8
57.5°	100.3	98.1	95.0	94.1	91.9	91.9	90.6	89.7	88.8	89.7	89.7
60°	89.2	86.1	84.4	81.7	79.9	78.1	75.9	75.5	74.6	74.1	73.7
62.5°	77.7	75.0	70.6	66.6	63.9	62.2	61.3	60.8	60.8	60.4	60.4
65°	64.8	58.6	56.4	55.0	54.6	54.2	53.3	52.8	53.3	52.8	53.3
67.5°	50.6	49.7	48.4	47.5	47.1	46.6	46.6	46.2	46.2	46.2	46.2
70°	44.0	41.7	41.3	40.4	40.4	40.0	40.0	40.0	40.0	39.5	40.4
72.5°	36.4	35.1	34.6	34.2	34.2	34.2	33.7	33.7	33.7	33.3	33.7
75°	29.7	29.3	28.4	28.4	28.0	28.4	28.0	28.0	27.5	28.0	28.0
77.5°	24.0	23.5	23.1	23.1	22.6	22.6	22.6	22.6	22.6	22.6	23.1
80°	18.2	17.8	17.3	17.8	17.3	17.8	17.3	17.3	17.8	17.3	17.3
82.5°	13.3	12.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.6	4.0	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.0
90°	26.5	26.1	25.8	25.5	25.3	25.4	25.6	25.7	25.9	26.1	25.9
92.5°	24.0	24.1	24.3	24.4	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	49.1	49.1	49.1	49.1	48.9	48.6	48.2	47.9	47.5	47.9
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.8	105.8	105.8	105.8	105.7	105.6	105.4	105.3	105.1	105.3
102.5°	137.5	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	137.5
105°	169.0	169.4	169.7	170.0	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	203.4	203.6	203.7	203.9	204.0	203.6	202.7	201.8	201.0	200.1	201.0
110°	238.5	238.5	238.5	238.5	238.5	238.2	237.7	237.2	236.7	236.2	236.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	274.0	273.5	273.0	272.5	272.2	272.0	271.7	271.4	271.0	270.7	271.0
115°	309.6	309.4	309.3	309.1	309.0	308.7	308.2	307.7	307.2	306.7	307.2
117.5°	344.6	344.1	343.6	343.1	342.8	342.5	342.0	341.5	341.0	340.5	341.0
120°	378.8	378.8	378.8	378.8	378.8	378.5	378.0	377.5	377.0	376.5	377.0
122.5°	415.1	414.6	414.1	413.6	413.3	413.1	412.8	412.5	412.1	411.8	412.1
125°	450.4	449.9	449.4	448.9	448.6	448.5	448.3	448.2	448.0	447.8	448.0
127.5°	484.7	484.0	483.3	482.6	482.3	482.0	481.5	481.0	480.5	480.0	480.5
130°	519.6	519.2	518.9	518.6	518.4	518.1	517.4	516.7	516.0	515.3	516.0
132.5°	554.3	553.5	552.6	551.7	551.3	551.0	550.5	550.0	549.5	549.0	549.5
135°	587.2	587.0	586.9	586.7	586.6	586.3	585.8	585.3	584.8	584.3	584.8
137.5°	619.4	619.2	619.1	618.9	618.8	618.5	617.8	617.1	616.4	615.7	616.4
140°	651.8	651.8	651.8	651.8	651.8	651.5	650.8	650.1	649.4	648.7	649.4
142.5°	681.1	681.3	681.4	681.6	681.7	681.4	680.7	680.0	679.3	678.6	679.3
145°	711.0	711.2	711.3	711.5	711.6	711.3	710.6	709.9	709.2	708.5	709.2
147.5°	737.2	737.6	737.9	738.2	738.4	738.1	737.4	736.7	736.1	735.4	736.1
150°	761.9	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	761.9
152.5°	786.7	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	786.7
155°	806.7	807.6	808.4	809.3	809.7	809.4	808.9	808.4	807.9	807.4	807.9
157.5°	826.3	827.5	828.6	829.8	830.4	830.0	829.1	828.3	827.4	826.6	827.4
160°	843.7	844.7	845.8	846.8	847.3	847.0	846.3	845.6	844.9	844.2	844.9
162.5°	859.2	860.4	861.6	862.8	863.4	863.0	862.1	861.3	860.4	859.6	860.4
165°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
167.5°	883.8	885.0	886.1	887.3	887.9	887.5	886.6	885.8	884.9	884.1	884.9
170°	893.0	894.2	895.3	896.5	897.1	896.6	895.6	894.5	893.5	892.5	893.5
172.5°	899.9	901.1	902.2	903.4	904.0	903.5	902.5	901.4	900.4	899.4	900.4
175°	904.5	905.7	906.9	908.1	908.7	908.2	907.1	906.1	905.0	904.0	905.0
177.5°	907.3	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	907.3
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	673.5	670.4	669.5	670.4	669.5	669.9	666.8	655.3	658.4	653.5	656.2
5°	711.7	709.0	703.2	702.3	701.4	700.6	696.1	685.9	681.9	675.2	674.8
7.5°	748.1	748.1	743.6	740.5	736.5	733.4	727.6	712.5	706.3	698.3	693.9
10°	784.0	772.5	777.4	774.2	764.5	762.7	752.1	743.2	731.2	723.2	716.1
12.5°	809.8	806.2	801.8	799.1	796.4	790.7	783.6	760.9	754.7	738.7	730.7
15°	808.9	806.7	808.0	808.0	807.1	805.8	800.0	783.6	772.9	757.4	743.6
17.5°	765.4	771.1	776.9	780.9	789.8	793.8	799.1	789.3	782.7	769.4	754.7
20°	689.5	703.7	720.5	724.1	732.1	755.6	766.3	774.7	777.4	772.9	760.9
22.5°	583.8	595.8	636.6	635.7	647.3	675.2	706.3	731.6	751.6	762.7	758.3
25°	457.3	474.1	495.9	512.3	550.1	591.8	630.4	670.8	705.4	736.1	743.6
27.5°	345.8	368.0	385.3	407.1	426.2	475.5	525.2	588.2	628.6	686.8	717.0
30°	279.7	289.9	307.2	317.4	326.7	364.5	420.9	483.0	554.0	621.1	673.0
32.5°	238.8	245.9	258.8	263.3	273.0	298.3	333.8	390.7	463.9	545.2	613.5
35°	214.4	222.0	224.6	228.6	236.6	252.6	277.0	318.3	384.5	463.9	545.6
37.5°	193.6	197.6	205.1	207.8	210.4	222.4	238.8	267.7	311.7	376.9	467.5
40°	178.9	181.1	185.1	187.3	189.1	197.6	212.2	231.7	264.1	313.9	397.3
42.5°	163.4	166.0	168.7	171.4	173.6	180.2	189.1	207.8	229.5	267.3	327.6
45°	148.3	150.1	153.2	154.9	158.0	163.4	171.4	184.2	203.8	227.7	276.6
47.5°	134.5	136.7	138.1	140.3	142.5	148.3	155.8	164.3	180.2	203.8	239.3
50°	122.1	124.7	126.5	127.0	128.7	134.1	140.3	149.6	159.8	178.0	209.1
52.5°	113.2	113.7	115.0	116.8	116.3	119.4	125.2	132.3	143.0	157.6	180.2
55°	103.0	104.3	105.2	105.7	105.7	108.3	111.4	118.1	126.5	138.5	157.6
57.5°	90.1	91.5	94.1	95.0	96.3	97.7	99.0	103.4	110.5	122.1	137.6
60°	76.8	77.7	80.4	82.1	83.0	86.6	88.3	91.9	95.9	104.3	119.0
62.5°	61.7	62.6	63.9	65.7	67.5	72.8	77.2	80.8	83.9	89.7	101.7
65°	53.7	54.2	55.0	55.5	55.9	58.2	62.2	67.0	72.8	77.2	84.4
67.5°	46.6	47.1	47.5	48.4	48.8	49.3	51.1	52.4	58.2	64.4	69.7
70°	40.0	40.8	41.3	41.3	41.7	42.6	43.5	45.3	47.1	50.2	56.8
72.5°	33.7	34.2	35.1	35.1	35.1	36.0	36.8	37.7	38.6	40.4	43.1
75°	28.0	28.9	28.9	28.9	29.3	29.3	30.2	31.1	32.0	33.3	34.2
77.5°	23.1	23.1	23.1	23.1	23.5	23.5	24.0	24.9	25.3	25.7	26.6
80°	17.3	17.8	17.8	17.8	18.2	18.2	18.2	19.1	19.5	19.5	20.4
82.5°	12.9	12.9	12.9	13.3	12.9	13.3	13.3	13.8	13.3	13.8	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.9
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	25.7	25.6	25.4	25.3	25.5	25.8	26.1	26.5	26.8	23.1	19.3
92.5°	24.5	24.5	24.5	24.5	24.4	24.3	24.1	24.0	23.8	23.6	23.4
95°	48.2	48.6	48.9	49.1	49.1	49.1	49.1	49.1	49.1	48.7	48.4
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.0	75.3
100°	105.4	105.6	105.7	105.8	105.8	105.8	105.8	105.8	105.8	105.3	104.8
102.5°	137.6	137.8	137.9	138.0	137.9	137.8	137.6	137.5	137.3	136.6	135.9
105°	170.2	170.2	170.2	170.2	170.0	169.7	169.4	169.0	168.7	168.4	168.0
107.5°	201.8	202.7	203.6	204.0	203.9	203.7	203.6	203.4	203.2	203.2	203.2
110°	237.2	237.7	238.2	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	271.4	271.7	272.0	272.2	272.5	273.0	273.5	274.0	274.5	274.7	274.9
115°	307.7	308.2	308.7	309.0	309.1	309.3	309.4	309.6	309.8	310.1	310.5
117.5°	341.5	342.0	342.5	342.8	343.1	343.6	344.1	344.6	345.1	345.9	346.8
120°	377.5	378.0	378.5	378.8	378.8	378.8	378.8	378.8	378.8	380.2	381.5
122.5°	412.5	412.8	413.1	413.3	413.6	414.1	414.6	415.1	415.6	416.4	417.3
125°	448.2	448.3	448.5	448.6	448.9	449.4	449.9	450.4	450.9	451.4	451.9
127.5°	481.0	481.5	482.0	482.3	482.6	483.3	484.0	484.7	485.4	486.1	486.7
130°	516.7	517.4	518.1	518.4	518.6	518.9	519.2	519.6	519.9	520.2	520.6
132.5°	550.0	550.5	551.0	551.3	551.7	552.6	553.5	554.3	555.2	555.0	554.8
135°	585.3	585.8	586.3	586.6	586.7	586.9	587.0	587.2	587.4	587.0	586.7
137.5°	617.1	617.8	618.5	618.8	618.9	619.1	619.2	619.4	619.6	619.2	618.9
140°	650.1	650.8	651.5	651.8	651.8	651.8	651.8	651.8	651.8	650.9	650.1
142.5°	680.0	680.7	681.4	681.7	681.6	681.4	681.3	681.1	680.9	680.4	679.9
145°	709.9	710.6	711.3	711.6	711.5	711.3	711.2	711.0	710.8	709.8	708.8
147.5°	736.7	737.4	738.1	738.4	738.2	737.9	737.6	737.2	736.9	736.2	735.5
150°	762.4	762.9	763.4	763.7	763.4	762.9	762.4	761.9	761.4	760.7	760.1
152.5°	787.3	788.0	788.7	789.0	788.7	788.0	787.3	786.7	786.0	785.1	784.3
155°	808.4	808.9	809.4	809.7	809.3	808.4	807.6	806.7	805.9	805.4	804.9
157.5°	828.3	829.1	830.0	830.4	829.8	828.6	827.5	826.3	825.1	824.7	824.4
160°	845.6	846.3	847.0	847.3	846.8	845.8	844.7	843.7	842.7	842.5	842.3
162.5°	861.3	862.1	863.0	863.4	862.8	861.6	860.4	859.2	858.0	857.8	857.7
165°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
167.5°	885.8	886.6	887.5	887.9	887.3	886.1	885.0	883.8	882.6	882.6	882.6
170°	894.5	895.6	896.6	897.1	896.5	895.3	894.2	893.0	891.8	892.0	892.1
172.5°	901.4	902.5	903.5	904.0	903.4	902.2	901.1	899.9	898.7	898.9	899.0
175°	906.1	907.1	908.2	908.7	908.1	906.9	905.7	904.5	903.3	903.6	904.0
177.5°	908.4	909.4	910.5	911.0	910.5	909.4	908.4	907.3	906.3	906.7	907.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	652.2	649.9	649.9	648.6	648.6	641.5	641.5	643.7	641.1	638.0	633.5
5°	669.0	664.1	662.8	661.0	655.3	646.4	642.8	641.5	636.2	629.5	622.0
7.5°	685.0	677.0	673.0	669.0	661.5	649.1	642.0	637.1	629.1	618.9	609.1
10°	700.6	690.3	680.1	675.2	664.6	649.1	638.8	630.9	619.3	605.5	591.8
12.5°	714.8	693.4	691.7	681.9	666.4	648.6	633.1	621.5	606.9	590.9	574.9
15°	727.2	705.4	694.8	685.9	665.5	643.3	626.9	612.6	593.1	574.9	555.4
17.5°	733.4	709.9	702.8	688.1	667.3	638.4	616.2	598.9	577.6	555.8	533.6
20°	739.6	712.1	700.6	690.3	661.9	629.1	604.2	584.2	560.7	535.0	510.5
22.5°	742.7	712.1	698.3	684.1	656.6	618.9	589.6	566.0	538.5	512.3	483.0
25°	737.4	709.4	693.0	678.4	647.3	606.4	572.7	546.1	516.8	487.0	457.3
27.5°	724.1	703.2	684.1	669.0	634.4	590.5	554.9	524.7	494.6	461.3	431.1
30°	699.2	689.9	674.8	657.9	620.2	576.2	534.1	503.0	469.7	436.4	404.9
32.5°	660.6	668.6	658.8	644.2	603.3	556.7	511.9	480.4	443.9	408.0	379.1
35°	613.5	642.0	636.6	626.4	585.6	535.8	491.0	452.8	416.4	380.0	351.2
37.5°	562.0	605.1	609.5	603.3	565.1	514.5	465.3	428.0	390.7	353.8	324.5
40°	491.5	557.6	571.8	574.5	543.8	488.8	437.3	400.9	364.0	328.1	292.6
42.5°	426.6	510.1	527.9	539.0	516.8	463.5	411.5	371.1	334.7	302.3	266.8
45°	365.8	452.8	481.7	495.9	486.1	434.6	380.9	343.2	309.9	280.1	245.9
47.5°	303.2	390.7	431.1	453.7	453.7	405.3	351.6	314.3	282.4	257.0	226.9
50°	261.5	334.3	376.0	405.8	413.8	375.6	325.0	288.6	258.4	230.9	207.8
52.5°	222.9	288.1	322.8	353.8	376.9	343.6	295.2	262.4	232.6	206.9	188.7
55°	192.7	241.5	273.0	307.2	333.0	311.2	266.4	234.4	208.7	187.3	171.8
57.5°	163.8	206.4	232.2	262.4	289.9	273.5	237.5	210.0	187.3	168.7	154.9
60°	139.4	174.0	194.0	217.5	251.7	240.2	210.4	185.1	166.9	150.1	138.5
62.5°	118.5	146.1	162.9	179.8	210.9	205.5	182.5	162.9	147.4	133.2	123.4
65°	97.2	119.9	133.2	147.8	172.7	174.9	156.3	142.5	128.3	115.9	107.0
67.5°	78.6	96.3	108.3	120.8	140.7	146.9	134.1	122.5	110.5	100.3	92.3
70°	63.5	75.9	84.8	94.6	111.0	118.5	111.9	103.9	94.1	85.7	78.6
72.5°	50.2	58.2	63.5	71.0	84.4	91.9	91.5	84.4	77.2	71.5	65.7
75°	36.8	43.1	47.5	52.4	63.0	70.1	71.9	68.8	61.7	57.3	52.8
77.5°	28.0	31.5	33.7	37.3	44.8	51.1	53.7	52.8	47.9	44.4	41.3
80°	21.3	22.2	23.1	24.4	30.6	36.4	38.2	37.7	35.1	33.7	30.2
82.5°	15.1	15.5	16.0	16.4	18.6	23.5	25.3	26.2	24.0	22.6	19.5
85°	8.9	9.3	9.3	10.2	10.7	12.0	15.1	15.1	14.7	12.9	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.7	5.8	5.3	4.9
90°	15.6	11.9	10.0	9.0	6.9	4.9	2.8	0.8	2.8	4.9	6.9
92.5°	23.3	23.1	23.0	22.3	21.0	19.6	18.3	16.9	18.3	19.6	21.0
95°	48.0	47.7	47.5	46.7	45.0	43.3	41.6	39.9	41.6	43.3	45.0
97.5°	74.6	73.9	73.6	72.8	71.3	69.8	68.2	66.7	68.2	69.8	71.3
100°	104.3	103.8	103.5	102.8	101.5	100.1	98.8	97.4	98.8	100.1	101.5
102.5°	135.2	134.5	134.2	133.7	132.7	131.6	130.6	129.6	130.6	131.6	132.7
105°	167.7	167.4	167.2	166.9	166.4	165.9	165.4	164.9	165.4	165.9	166.4
107.5°	203.2	203.2	203.2	202.9	202.2	201.5	200.8	200.1	200.8	201.5	202.2
110°	238.5	238.5	238.5	238.0	237.0	235.9	234.9	233.9	234.9	235.9	237.0

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	275.0	275.2	275.3	274.8	273.8	272.7	271.7	270.7	271.7	272.7	273.8
115°	310.8	311.1	311.3	310.8	309.8	308.7	307.7	306.7	307.7	308.7	309.8
117.5°	347.6	348.5	348.9	348.2	346.9	345.5	344.2	342.8	344.2	345.5	346.9
120°	382.9	384.2	384.9	384.2	382.9	381.5	380.2	378.8	380.2	381.5	382.9
122.5°	418.1	419.0	419.4	418.6	416.9	415.2	413.5	411.8	413.5	415.2	416.9
125°	452.4	452.9	453.2	452.4	450.9	449.4	447.8	446.3	447.8	449.4	450.9
127.5°	487.4	488.1	488.4	487.5	485.6	483.7	481.9	480.0	481.9	483.7	485.6
130°	520.9	521.2	521.4	520.3	518.1	515.9	513.7	511.5	513.7	515.9	518.1
132.5°	554.7	554.5	554.4	553.5	551.8	550.1	548.4	546.7	548.4	550.1	551.8
135°	586.3	586.0	585.8	584.9	583.0	581.1	579.3	577.4	579.3	581.1	583.0
137.5°	618.5	618.2	618.0	617.2	615.7	614.2	612.6	611.1	612.6	614.2	615.7
140°	649.2	648.3	647.9	647.1	645.6	644.1	642.5	641.0	642.5	644.1	645.6
142.5°	679.4	678.9	678.6	677.8	676.3	674.8	673.2	671.7	673.2	674.8	676.3
145°	707.7	706.7	706.2	705.6	704.4	703.2	702.0	700.8	702.0	703.2	704.4
147.5°	734.8	734.1	733.8	733.0	731.5	730.0	728.4	726.9	728.4	730.0	731.5
150°	759.4	758.7	758.4	757.9	756.9	755.8	754.8	753.8	754.8	755.8	756.9
152.5°	783.4	782.5	782.1	781.6	780.6	779.5	778.5	777.5	778.5	779.5	780.6
155°	804.4	803.9	803.6	803.3	802.8	802.3	801.8	801.3	801.8	802.3	802.8
157.5°	824.0	823.7	823.5	823.3	823.0	822.7	822.3	822.0	822.3	822.7	823.0
160°	842.2	842.0	841.9	841.7	841.4	841.1	840.7	840.4	840.7	841.1	841.4
162.5°	857.5	857.4	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3	857.3
165°	871.1	871.1	871.1	871.2	871.3	871.5	871.6	871.8	871.6	871.5	871.3
167.5°	882.6	882.6	882.6	882.9	883.4	883.9	884.4	884.9	884.4	883.9	883.4
170°	892.3	892.4	892.5	892.8	893.3	893.8	894.3	894.8	894.3	893.8	893.3
172.5°	899.2	899.3	899.4	899.7	900.2	900.7	901.2	901.7	901.2	900.7	900.2
175°	904.3	904.6	904.8	905.1	905.6	906.1	906.6	907.1	906.6	906.1	905.6
177.5°	907.4	907.7	907.9	908.2	908.7	909.2	909.7	910.2	909.7	909.2	908.7
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	631.7	632.2	633.5	629.5	623.3	620.6	612.6	611.3	610.0	610.0	611.3
5°	617.5	615.8	616.2	608.7	599.8	594.4	583.3	585.1	579.4	575.8	576.7
7.5°	602.0	597.1	596.7	586.9	575.8	566.0	554.5	551.8	546.5	540.3	537.6
10°	582.5	578.9	572.3	561.2	546.9	539.0	523.4	514.1	512.8	503.4	499.9
12.5°	562.5	556.3	549.6	534.1	518.1	505.2	493.7	483.5	476.4	468.4	463.0
15°	539.4	531.9	524.3	507.9	489.2	476.4	459.0	443.9	423.1	406.7	397.3
17.5°	514.1	505.7	495.4	477.2	459.0	441.3	409.3	391.6	376.9	367.1	361.4
20°	487.9	478.6	468.4	450.2	418.6	387.6	369.8	356.0	347.2	337.4	330.3
22.5°	460.4	450.6	439.5	411.1	377.8	356.0	342.3	329.4	316.5	311.2	307.7
25°	434.6	425.7	411.5	372.9	346.7	326.7	311.2	302.8	296.1	289.0	282.4
27.5°	408.0	391.6	371.6	339.2	322.8	302.3	291.2	285.0	273.5	268.6	265.5
30°	376.0	357.8	338.7	315.6	296.6	282.4	272.1	261.9	255.3	250.4	245.1
32.5°	343.6	326.3	314.3	290.3	276.1	261.5	251.7	245.5	235.7	232.6	230.4
35°	315.6	301.0	290.3	270.8	257.5	244.2	237.1	227.7	221.5	215.8	212.2
37.5°	288.1	280.1	269.0	252.6	238.4	227.7	218.0	214.9	206.4	203.3	199.8
40°	269.0	257.0	247.7	233.5	221.5	210.0	203.8	196.7	190.9	186.0	184.7
42.5°	245.9	237.1	231.7	216.2	203.8	197.1	189.6	181.6	177.1	173.1	168.3
45°	228.6	220.6	213.1	200.7	189.6	181.1	174.5	169.1	161.6	159.8	152.3
47.5°	210.4	202.4	196.7	184.2	174.0	166.0	161.2	154.1	147.8	143.8	140.3
50°	192.2	185.6	180.2	169.6	160.7	152.3	145.6	138.5	135.8	129.2	127.0
52.5°	174.9	170.5	164.7	154.5	145.6	138.5	131.4	125.6	121.6	118.1	115.4
55°	160.3	153.2	150.5	139.4	131.9	124.3	118.1	114.5	109.7	107.4	105.2
57.5°	143.8	139.8	135.4	127.0	118.5	111.4	107.0	101.7	99.0	96.3	94.6
60°	129.6	123.9	120.3	113.2	105.7	99.0	95.0	91.0	87.5	85.2	81.7
62.5°	113.2	108.8	106.5	99.0	92.8	86.6	83.0	79.0	76.4	72.4	67.9
65°	99.0	95.4	92.8	86.6	80.8	75.0	71.5	66.6	63.0	60.8	60.4
67.5°	86.6	83.9	79.9	74.1	68.4	63.9	59.9	55.9	55.5	54.6	54.6
70°	72.8	70.1	67.9	61.7	56.8	51.9	51.1	49.7	48.4	47.9	47.1
72.5°	60.8	58.6	55.9	50.6	45.7	44.4	43.5	42.6	41.3	40.8	40.4
75°	49.3	46.2	44.4	39.5	38.2	37.3	36.4	35.1	34.2	33.7	32.9
77.5°	37.7	34.6	34.6	32.0	31.1	29.7	28.9	28.0	27.5	26.6	26.6
80°	26.6	26.6	25.7	24.4	23.1	22.6	21.3	20.9	20.4	20.9	20.0
82.5°	19.5	17.8	17.8	16.9	16.0	15.5	14.7	14.7	14.2	14.2	14.2
85°	11.1	11.1	10.7	9.8	9.3	9.3	8.9	8.9	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.6	3.6	3.6	3.1	3.6	3.1
90°	9.0	10.0	11.9	15.6	19.3	23.1	26.8	26.5	26.1	25.8	25.5
92.5°	22.3	23.0	23.1	23.3	23.4	23.6	23.8	24.0	24.1	24.3	24.4
95°	46.7	47.5	47.7	48.0	48.4	48.7	49.1	49.1	49.1	49.1	49.1
97.5°	72.8	73.6	73.9	74.6	75.3	76.0	76.7	76.7	76.7	76.7	76.7
100°	102.8	103.5	103.8	104.3	104.8	105.3	105.8	105.8	105.8	105.8	105.8
102.5°	133.7	134.2	134.5	135.2	135.9	136.6	137.3	137.5	137.6	137.8	137.9
105°	166.9	167.2	167.4	167.7	168.0	168.4	168.7	169.0	169.4	169.7	170.0
107.5°	202.9	203.2	203.2	203.2	203.2	203.2	203.2	203.4	203.6	203.7	203.9
110°	238.0	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.8	275.3	275.2	275.0	274.9	274.7	274.5	274.0	273.5	273.0	272.5
115°	310.8	311.3	311.1	310.8	310.5	310.1	309.8	309.6	309.4	309.3	309.1
117.5°	348.2	348.9	348.5	347.6	346.8	345.9	345.1	344.6	344.1	343.6	343.1
120°	384.2	384.9	384.2	382.9	381.5	380.2	378.8	378.8	378.8	378.8	378.8
122.5°	418.6	419.4	419.0	418.1	417.3	416.4	415.6	415.1	414.6	414.1	413.6
125°	452.4	453.2	452.9	452.4	451.9	451.4	450.9	450.4	449.9	449.4	448.9
127.5°	487.5	488.4	488.1	487.4	486.7	486.1	485.4	484.7	484.0	483.3	482.6
130°	520.3	521.4	521.2	520.9	520.6	520.2	519.9	519.6	519.2	518.9	518.6
132.5°	553.5	554.4	554.5	554.7	554.8	555.0	555.2	554.3	553.5	552.6	551.7
135°	584.9	585.8	586.0	586.3	586.7	587.0	587.4	587.2	587.0	586.9	586.7
137.5°	617.2	618.0	618.2	618.5	618.9	619.2	619.6	619.4	619.2	619.1	618.9
140°	647.1	647.9	648.3	649.2	650.1	650.9	651.8	651.8	651.8	651.8	651.8
142.5°	677.8	678.6	678.9	679.4	679.9	680.4	680.9	681.1	681.3	681.4	681.6
145°	705.6	706.2	706.7	707.7	708.8	709.8	710.8	711.0	711.2	711.3	711.5
147.5°	733.0	733.8	734.1	734.8	735.5	736.2	736.9	737.2	737.6	737.9	738.2
150°	757.9	758.4	758.7	759.4	760.1	760.7	761.4	761.9	762.4	762.9	763.4
152.5°	781.6	782.1	782.5	783.4	784.3	785.1	786.0	786.7	787.3	788.0	788.7
155°	803.3	803.6	803.9	804.4	804.9	805.4	805.9	806.7	807.6	808.4	809.3
157.5°	823.3	823.5	823.7	824.0	824.4	824.7	825.1	826.3	827.5	828.6	829.8
160°	841.7	841.9	842.0	842.2	842.3	842.5	842.7	843.7	844.7	845.8	846.8
162.5°	857.3	857.3	857.4	857.5	857.7	857.8	858.0	859.2	860.4	861.6	862.8
165°	871.2	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
167.5°	882.9	882.6	882.6	882.6	882.6	882.6	882.6	883.8	885.0	886.1	887.3
170°	892.8	892.5	892.4	892.3	892.1	892.0	891.8	893.0	894.2	895.3	896.5
172.5°	899.7	899.4	899.3	899.2	899.0	898.9	898.7	899.9	901.1	902.2	903.4
175°	905.1	904.8	904.6	904.3	904.0	903.6	903.3	904.5	905.7	906.9	908.1
177.5°	908.2	907.9	907.7	907.4	907.0	906.7	906.3	907.3	908.4	909.4	910.5
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	611.3	610.4	607.8	608.7	607.3	607.3	606.4	606.4	606.4	608.7	607.3
5°	578.0	574.9	571.8	570.5	569.1	567.8	567.8	567.4	571.4	570.5	574.0
7.5°	536.7	535.8	529.6	529.6	527.4	526.5	528.7	529.2	529.6	530.5	532.7
10°	499.9	497.7	488.8	489.7	488.3	486.6	487.9	487.0	490.1	491.0	490.1
12.5°	456.4	452.4	442.6	437.7	432.4	428.4	433.3	429.7	442.2	445.7	455.5
15°	398.7	391.1	384.5	384.5	379.6	376.0	378.2	382.2	384.9	388.9	390.7
17.5°	360.0	356.9	351.6	348.5	347.2	345.8	345.8	347.6	353.4	352.9	356.5
20°	327.2	325.4	322.8	318.8	317.4	316.5	316.5	316.5	320.5	324.1	326.3
22.5°	304.5	303.2	301.4	296.1	293.5	292.6	294.8	296.1	299.2	301.9	304.1
25°	281.9	278.8	275.7	273.9	272.6	272.6	273.5	273.9	275.2	276.6	279.2
27.5°	263.3	261.0	256.6	251.7	251.7	250.4	251.3	252.2	255.3	259.7	261.9
30°	242.4	242.0	240.2	238.4	236.6	235.7	237.5	238.8	239.3	241.5	241.5
32.5°	227.3	224.2	221.1	219.3	218.4	218.0	218.4	220.2	220.2	222.9	226.0
35°	212.2	210.4	207.3	204.2	203.3	201.1	202.9	204.7	207.8	209.1	210.4
37.5°	195.8	193.6	192.2	191.3	189.6	190.0	188.7	191.3	194.0	193.6	194.4
40°	183.4	179.4	175.4	174.9	174.5	174.0	174.0	174.5	176.2	178.0	180.7
42.5°	167.4	166.0	162.5	158.9	158.0	157.2	156.3	158.0	161.6	164.7	166.0
45°	150.9	149.2	148.3	145.6	143.8	143.4	142.5	144.7	147.8	149.2	150.1
47.5°	135.8	135.4	132.7	133.2	131.9	132.3	131.9	133.2	133.2	134.5	135.4
50°	125.6	124.3	123.0	122.1	120.8	120.8	120.3	120.8	122.5	124.3	123.9
52.5°	115.4	113.2	112.8	112.3	111.4	112.3	111.0	111.4	113.2	114.1	113.7
55°	103.4	103.0	102.1	101.2	100.8	100.3	100.3	100.3	102.1	103.4	103.9
57.5°	94.1	91.9	90.1	90.1	88.3	87.9	88.8	89.2	90.6	91.5	92.3
60°	81.2	80.4	77.7	76.4	73.7	73.3	73.3	75.0	77.2	80.4	81.2
62.5°	67.5	66.1	65.7	65.7	65.7	65.7	65.7	65.7	65.7	66.1	66.1
65°	59.9	60.4	59.9	59.5	59.9	59.9	59.5	59.5	59.5	59.9	60.4
67.5°	53.7	53.3	53.7	53.3	52.8	52.8	52.4	52.8	53.3	53.7	53.7
70°	46.6	46.6	46.2	46.6	46.2	45.7	45.3	45.3	46.2	46.6	46.6
72.5°	40.0	40.0	39.5	39.5	38.6	38.6	39.1	38.6	38.6	40.0	40.0
75°	33.3	32.9	32.4	32.4	32.0	32.0	32.0	31.5	32.4	32.4	32.9
77.5°	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.7	25.7	25.7	26.2
80°	20.0	20.0	20.0	19.5	19.1	19.1	19.1	19.1	19.1	19.5	19.1
82.5°	13.8	13.8	13.8	13.8	13.8	13.3	13.3	13.3	13.8	13.8	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.6	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	25.3	25.4	25.6	25.7	25.9	26.1	25.9	25.7	25.6	25.4	25.3
92.5°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5
95°	49.1	48.9	48.6	48.2	47.9	47.5	47.9	48.2	48.6	48.9	49.1
97.5°	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7	76.7
100°	105.8	105.7	105.6	105.4	105.3	105.1	105.3	105.4	105.6	105.7	105.8
102.5°	138.0	137.9	137.8	137.6	137.5	137.3	137.5	137.6	137.8	137.9	138.0
105°	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2	170.2
107.5°	204.0	203.6	202.7	201.8	201.0	200.1	201.0	201.8	202.7	203.6	204.0
110°	238.5	238.2	237.7	237.2	236.7	236.2	236.7	237.2	237.7	238.2	238.5

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	272.2	272.0	271.7	271.4	271.0	270.7	271.0	271.4	271.7	272.0	272.2
115°	309.0	308.7	308.2	307.7	307.2	306.7	307.2	307.7	308.2	308.7	309.0
117.5°	342.8	342.5	342.0	341.5	341.0	340.5	341.0	341.5	342.0	342.5	342.8
120°	378.8	378.5	378.0	377.5	377.0	376.5	377.0	377.5	378.0	378.5	378.8
122.5°	413.3	413.1	412.8	412.5	412.1	411.8	412.1	412.5	412.8	413.1	413.3
125°	448.6	448.5	448.3	448.2	448.0	447.8	448.0	448.2	448.3	448.5	448.6
127.5°	482.3	482.0	481.5	481.0	480.5	480.0	480.5	481.0	481.5	482.0	482.3
130°	518.4	518.1	517.4	516.7	516.0	515.3	516.0	516.7	517.4	518.1	518.4
132.5°	551.3	551.0	550.5	550.0	549.5	549.0	549.5	550.0	550.5	551.0	551.3
135°	586.6	586.3	585.8	585.3	584.8	584.3	584.8	585.3	585.8	586.3	586.6
137.5°	618.8	618.5	617.8	617.1	616.4	615.7	616.4	617.1	617.8	618.5	618.8
140°	651.8	651.5	650.8	650.1	649.4	648.7	649.4	650.1	650.8	651.5	651.8
142.5°	681.7	681.4	680.7	680.0	679.3	678.6	679.3	680.0	680.7	681.4	681.7
145°	711.6	711.3	710.6	709.9	709.2	708.5	709.2	709.9	710.6	711.3	711.6
147.5°	738.4	738.1	737.4	736.7	736.1	735.4	736.1	736.7	737.4	738.1	738.4
150°	763.7	763.4	762.9	762.4	761.9	761.4	761.9	762.4	762.9	763.4	763.7
152.5°	789.0	788.7	788.0	787.3	786.7	786.0	786.7	787.3	788.0	788.7	789.0
155°	809.7	809.4	808.9	808.4	807.9	807.4	807.9	808.4	808.9	809.4	809.7
157.5°	830.4	830.0	829.1	828.3	827.4	826.6	827.4	828.3	829.1	830.0	830.4
160°	847.3	847.0	846.3	845.6	844.9	844.2	844.9	845.6	846.3	847.0	847.3
162.5°	863.4	863.0	862.1	861.3	860.4	859.6	860.4	861.3	862.1	863.0	863.4
165°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
167.5°	887.9	887.5	886.6	885.8	884.9	884.1	884.9	885.8	886.6	887.5	887.9
170°	897.1	896.6	895.6	894.5	893.5	892.5	893.5	894.5	895.6	896.6	897.1
172.5°	904.0	903.5	902.5	901.4	900.4	899.4	900.4	901.4	902.5	903.5	904.0
175°	908.7	908.2	907.1	906.1	905.0	904.0	905.0	906.1	907.1	908.2	908.7
177.5°	911.0	910.5	909.4	908.4	907.3	906.3	907.3	908.4	909.4	910.5	911.0
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	608.7	610.9	610.0	605.1	610.0	611.3	614.0	616.6	618.4	621.1	623.3
5°	570.5	574.9	577.6	574.9	583.8	585.1	591.3	594.9	600.2	604.7	608.2
7.5°	534.5	538.1	543.4	544.3	549.6	555.8	564.7	573.6	582.0	586.5	590.5
10°	495.9	502.1	510.1	508.3	516.3	526.1	535.4	549.6	556.7	564.7	571.8
12.5°	457.3	461.3	471.9	475.5	487.0	494.6	507.4	516.3	534.1	543.4	549.6
15°	389.8	406.2	419.5	435.5	450.6	464.8	476.4	492.3	507.9	515.0	525.2
17.5°	359.2	366.7	374.7	382.7	402.2	427.5	447.9	465.3	478.6	487.9	499.9
20°	327.2	334.7	343.6	351.2	363.2	381.4	406.7	436.4	452.4	462.2	473.7
22.5°	304.5	311.7	317.4	324.1	333.4	346.7	365.8	402.7	424.0	436.0	446.2
25°	280.1	289.0	295.2	300.1	307.7	322.3	337.8	358.7	396.9	406.2	420.4
27.5°	263.3	265.9	273.0	280.6	288.1	296.1	312.1	329.9	355.6	376.0	393.3
30°	243.3	249.9	256.6	259.7	266.4	277.9	287.7	306.8	326.7	342.7	363.6
32.5°	228.2	232.2	236.6	244.2	250.4	258.4	268.1	284.1	301.0	311.2	327.2
35°	211.3	214.0	223.3	226.4	232.6	240.6	250.4	262.8	281.0	289.0	300.6
37.5°	195.3	201.6	204.2	211.3	217.1	225.1	232.2	246.4	258.4	267.7	278.4
40°	182.9	185.6	190.5	196.7	201.6	207.8	216.6	226.9	239.7	247.3	256.6
42.5°	167.8	170.0	176.2	179.8	187.8	193.6	198.9	211.3	222.9	228.6	238.0
45°	151.4	156.7	160.7	167.8	172.3	179.4	186.0	194.9	205.5	212.2	217.5
47.5°	137.2	142.5	146.5	153.2	160.3	163.4	170.5	179.8	189.6	194.9	202.4
50°	125.6	127.4	135.0	138.1	145.6	151.8	156.7	164.7	175.4	178.5	184.7
52.5°	114.5	115.9	120.8	124.7	131.4	136.7	143.0	150.5	159.4	164.3	169.1
55°	104.8	105.7	107.9	112.3	116.8	123.4	129.2	136.3	143.8	149.2	153.6
57.5°	93.7	95.4	97.2	99.9	104.3	110.5	116.8	123.4	129.6	133.2	139.0
60°	80.8	83.5	86.6	89.7	92.8	97.2	104.3	110.5	116.3	119.4	123.9
62.5°	67.0	72.4	75.0	78.6	81.2	85.2	90.6	97.7	101.7	105.7	109.2
65°	60.4	60.8	61.3	64.8	69.7	73.7	78.6	83.9	90.1	92.8	95.4
67.5°	53.7	54.2	55.0	55.5	57.3	61.7	67.0	72.8	77.7	79.5	82.1
70°	47.1	47.1	48.8	49.3	49.7	50.2	54.6	60.4	64.8	67.0	70.1
72.5°	40.0	40.4	41.3	41.7	42.6	43.5	44.8	47.9	53.3	55.5	59.0
75°	32.9	33.3	33.7	34.2	35.5	36.0	37.3	39.1	41.3	44.0	46.2
77.5°	26.2	26.2	26.6	27.5	28.4	28.9	30.2	31.1	32.0	33.3	35.1
80°	19.5	20.0	20.0	20.9	20.9	21.3	21.8	23.1	24.0	24.9	25.7
82.5°	13.3	14.2	14.2	14.2	14.7	15.1	15.5	15.5	16.4	16.9	18.2
85°	8.0	8.4	8.4	8.4	8.0	8.9	8.9	9.3	9.3	9.3	9.8
87.5°	3.1	2.7	3.1	3.1	3.1	3.6	3.1	3.1	3.6	4.0	4.0
90°	25.5	25.8	26.1	26.5	26.8	23.1	19.3	15.6	11.9	10.0	9.0
92.5°	24.4	24.3	24.1	24.0	23.8	23.6	23.4	23.3	23.1	23.0	22.3
95°	49.1	49.1	49.1	49.1	49.1	48.7	48.4	48.0	47.7	47.5	46.7
97.5°	76.7	76.7	76.7	76.7	76.7	76.0	75.3	74.6	73.9	73.6	72.8
100°	105.8	105.8	105.8	105.8	105.8	105.3	104.8	104.3	103.8	103.5	102.8
102.5°	137.9	137.8	137.6	137.5	137.3	136.6	135.9	135.2	134.5	134.2	133.7
105°	170.0	169.7	169.4	169.0	168.7	168.4	168.0	167.7	167.4	167.2	166.9
107.5°	203.9	203.7	203.6	203.4	203.2	203.2	203.2	203.2	203.2	203.2	202.9
110°	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.5	238.0

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	272.5	273.0	273.5	274.0	274.5	274.7	274.9	275.0	275.2	275.3	274.8
115°	309.1	309.3	309.4	309.6	309.8	310.1	310.5	310.8	311.1	311.3	310.8
117.5°	343.1	343.6	344.1	344.6	345.1	345.9	346.8	347.6	348.5	348.9	348.2
120°	378.8	378.8	378.8	378.8	378.8	380.2	381.5	382.9	384.2	384.9	384.2
122.5°	413.6	414.1	414.6	415.1	415.6	416.4	417.3	418.1	419.0	419.4	418.6
125°	448.9	449.4	449.9	450.4	450.9	451.4	451.9	452.4	452.9	453.2	452.4
127.5°	482.6	483.3	484.0	484.7	485.4	486.1	486.7	487.4	488.1	488.4	487.5
130°	518.6	518.9	519.2	519.6	519.9	520.2	520.6	520.9	521.2	521.4	520.3
132.5°	551.7	552.6	553.5	554.3	555.2	555.0	554.8	554.7	554.5	554.4	553.5
135°	586.7	586.9	587.0	587.2	587.4	587.0	586.7	586.3	586.0	585.8	584.9
137.5°	618.9	619.1	619.2	619.4	619.6	619.2	618.9	618.5	618.2	618.0	617.2
140°	651.8	651.8	651.8	651.8	651.8	650.9	650.1	649.2	648.3	647.9	647.1
142.5°	681.6	681.4	681.3	681.1	680.9	680.4	679.9	679.4	678.9	678.6	677.8
145°	711.5	711.3	711.2	711.0	710.8	709.8	708.8	707.7	706.7	706.2	705.6
147.5°	738.2	737.9	737.6	737.2	736.9	736.2	735.5	734.8	734.1	733.8	733.0
150°	763.4	762.9	762.4	761.9	761.4	760.7	760.1	759.4	758.7	758.4	757.9
152.5°	788.7	788.0	787.3	786.7	786.0	785.1	784.3	783.4	782.5	782.1	781.6
155°	809.3	808.4	807.6	806.7	805.9	805.4	804.9	804.4	803.9	803.6	803.3
157.5°	829.8	828.6	827.5	826.3	825.1	824.7	824.4	824.0	823.7	823.5	823.3
160°	846.8	845.8	844.7	843.7	842.7	842.5	842.3	842.2	842.0	841.9	841.7
162.5°	862.8	861.6	860.4	859.2	858.0	857.8	857.7	857.5	857.4	857.3	857.3
165°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.2
167.5°	887.3	886.1	885.0	883.8	882.6	882.6	882.6	882.6	882.6	882.6	882.9
170°	896.5	895.3	894.2	893.0	891.8	892.0	892.1	892.3	892.4	892.5	892.8
172.5°	903.4	902.2	901.1	899.9	898.7	898.9	899.0	899.2	899.3	899.4	899.7
175°	908.1	906.9	905.7	904.5	903.3	903.6	904.0	904.3	904.6	904.8	905.1
177.5°	910.5	909.4	908.4	907.3	906.3	906.7	907.0	907.4	907.7	907.9	908.2
180°	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7	908.7

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	638.8	638.8	638.8	638.8
2.5°	627.3	626.0	634.0	642.8
5°	614.4	616.6	626.9	639.3
7.5°	601.1	606.0	618.0	634.4
10°	582.5	591.3	609.5	626.4
12.5°	564.3	576.2	593.6	613.5
15°	543.8	557.2	578.5	602.4
17.5°	521.2	536.3	561.2	587.3
20°	497.2	517.2	543.4	571.8
22.5°	470.6	494.6	521.6	553.2
25°	444.8	471.0	498.1	534.5
27.5°	419.5	445.3	475.5	512.3
30°	394.2	417.8	450.2	489.7
32.5°	367.1	391.6	425.7	466.1
35°	342.3	366.7	398.7	438.6
37.5°	315.6	341.8	372.5	413.8
40°	284.6	315.2	344.9	384.5
42.5°	258.8	291.2	320.1	357.4
45°	238.4	269.0	293.0	329.4
47.5°	219.3	244.2	268.6	302.3
50°	201.1	220.2	245.5	275.7
52.5°	182.5	198.9	220.6	249.1
55°	165.6	181.1	200.7	222.4
57.5°	150.1	161.2	180.7	200.2
60°	132.7	144.3	159.4	175.8
62.5°	118.1	127.0	141.2	154.9
65°	102.6	111.0	121.6	134.5
67.5°	88.3	95.9	104.3	114.5
70°	75.5	81.2	87.5	96.3
72.5°	61.7	67.9	73.7	80.8
75°	50.6	53.3	58.2	63.0
77.5°	39.1	42.6	45.3	49.3
80°	28.0	31.1	32.0	35.1
82.5°	18.6	20.4	22.2	23.1
85°	10.7	11.5	13.3	13.8
87.5°	4.0	4.4	5.3	6.2
90°	6.9	4.9	2.8	0.8
92.5°	21.0	19.6	18.3	16.9
95°	45.0	43.3	41.6	39.9
97.5°	71.3	69.8	68.2	66.7
100°	101.5	100.1	98.8	97.4
102.5°	132.7	131.6	130.6	129.6
105°	166.4	165.9	165.4	164.9
107.5°	202.2	201.5	200.8	200.1
110°	237.0	235.9	234.9	233.9

TEST NUMBER: P999608

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	273.8	272.7	271.7	270.7
115°	309.8	308.7	307.7	306.7
117.5°	346.9	345.5	344.2	342.8
120°	382.9	381.5	380.2	378.8
122.5°	416.9	415.2	413.5	411.8
125°	450.9	449.4	447.8	446.3
127.5°	485.6	483.7	481.9	480.0
130°	518.1	515.9	513.7	511.5
132.5°	551.8	550.1	548.4	546.7
135°	583.0	581.1	579.3	577.4
137.5°	615.7	614.2	612.6	611.1
140°	645.6	644.1	642.5	641.0
142.5°	676.3	674.8	673.2	671.7
145°	704.4	703.2	702.0	700.8
147.5°	731.5	730.0	728.4	726.9
150°	756.9	755.8	754.8	753.8
152.5°	780.6	779.5	778.5	777.5
155°	802.8	802.3	801.8	801.3
157.5°	823.0	822.7	822.3	822.0
160°	841.4	841.1	840.7	840.4
162.5°	857.3	857.3	857.3	857.3
165°	871.3	871.5	871.6	871.8
167.5°	883.4	883.9	884.4	884.9
170°	893.3	893.8	894.3	894.8
172.5°	900.2	900.7	901.2	901.7
175°	905.6	906.1	906.6	907.1
177.5°	908.7	909.2	909.7	910.2
180°	908.7	908.7	908.7	908.7

(END OF REPORT)