

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999612

Luminaire Tested: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999612
REPORT IS A COMBINATION OF REPORTS P988165 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3791.2 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999612

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999612

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	41	38	37	28	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	55	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7778	7388	7334
10°	7702	7007	6776
15°	7596	6558	6141
20°	7457	6047	5476
25°	7313	5522	4868
30°	7121	5011	4204
35°	6932	4494	3634
40°	6740	3989	3046
45°	6517	3467	2534
50°	6284	2963	2063
55°	6046	2459	1638
60°	5765	1967	1239
65°	5446	1500	1007
70°	5058	1088	801
75°	4570	829	612
80°	3864	561	410
85°	2698	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6517 cd/sqm

TEST NUMBER: P999612

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.2
10°-20°	126.2	3.3
20°-30°	177.2	4.7
30°-40°	193.2	5.1
40°-50°	177.6	4.7
50°-60°	139.4	3.7
60°-70°	90.8	2.4
70°-80°	46.7	1.2
80°-90°	14.5	0.4
90°-100°	161.6	4.3
100°-110°	546.4	14.4
110°-120°	574.3	15.1
120°-130°	472.3	12.5
130°-140°	379.5	10.0
140°-150°	286.7	7.6
150°-160°	201.6	5.3
160°-170°	118.7	3.1
170°-180°	38.6	1.0
0°-30°	349.4	9.2
0°-40°	542.6	14.3
0°-60°	859.6	22.7
0°-90°	1011.6	26.7
90°-120°	1282.3	33.8
90°-150°	2420.8	63.9
90°-180°	2780.0	73.3
0°-180°	3791.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	22
90°	1	10	26	25	25	3
95°	27	66	300	113	87	28
105°	94	141	568	1015	864	99
115°	165	208	475	981	1137	163
125°	230	272	457	795	922	204
135°	270	322	452	668	764	208
145°	308	354	449	558	610	193
155°	350	378	436	493	513	161
165°	382	393	418	443	450	108
175°	398	398	402	407	406	38
180°	399	399	399	399	399	

TEST NUMBER: P999612

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	0.8	10.4	26.1	24.9	25.3
92.5°	11.5	36.4	118.1	54.4	46.8
95°	26.8	65.9	300.5	113.4	87.4
97.5°	39.9	87.1	489.9	227.7	146.4
100°	59.0	106.6	605.7	453.5	274.5
102.5°	76.7	124.2	609.5	766.7	535.2
105°	93.5	141.0	568.1	1015.4	864.1
107.5°	111.9	158.0	529.8	1105.6	1085.6
110°	130.3	175.2	503.7	1091.0	1176.1

TEST NUMBER: P999612

CATALOG NUMBER: SA2XXRDIP-B290D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	147.2	191.7	486.9	1041.6	1174.6
115°	164.8	208.2	475.4	981.0	1137.0
117.5°	183.2	224.6	469.2	923.1	1080.3
120°	200.1	240.8	463.9	871.4	1025.8
122.5°	216.2	257.2	460.8	831.1	969.1
125°	230.0	272.2	457.0	794.6	922.3
127.5°	241.5	286.4	454.7	763.6	878.6
130°	251.5	299.0	453.1	732.2	842.6
132.5°	260.7	311.2	452.4	699.6	805.0
135°	269.9	322.0	451.6	667.8	764.4
137.5°	278.3	331.2	451.6	635.6	725.3
140°	288.3	339.6	450.8	607.2	684.7
142.5°	298.2	346.5	450.8	580.0	644.0
145°	308.2	354.2	449.3	557.8	610.3
147.5°	318.9	360.4	447.0	538.2	580.4
150°	329.7	366.5	444.7	521.4	554.3
152.5°	340.4	372.6	440.9	507.2	532.1
155°	350.4	378.4	436.3	493.4	512.9
157.5°	358.8	383.0	431.7	480.4	496.1
160°	367.2	387.6	427.1	467.3	480.0
162.5°	375.7	391.0	423.2	455.0	464.6
165°	381.8	393.3	417.9	443.2	450.1
167.5°	387.2	395.6	413.3	432.4	436.3
170°	392.5	396.8	409.4	422.4	424.0
172.5°	395.6	397.9	404.8	413.6	414.0
175°	397.9	398.3	401.7	406.7	405.6
177.5°	399.4	398.7	398.7	401.7	399.4
180°	398.7	398.7	398.7	398.7	398.7

(END OF REPORT)