

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999617

Luminaire Tested: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999617
REPORT IS A COMBINATION OF REPORTS P988170 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3516.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999617

CATALOG NUMBER: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999617

CATALOG NUMBER: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20
5	65	54	47	41	58	49	42	38	39	34	31	30	27	24	21	19	18
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	18	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7688	7688	7688
5°	7701	7315	7261
10°	7625	6937	6709
15°	7521	6492	6080
20°	7382	5987	5422
25°	7241	5467	4820
30°	7049	4961	4163
35°	6862	4450	3598
40°	6673	3950	3016
45°	6452	3432	2509
50°	6222	2934	2043
55°	5985	2435	1621
60°	5708	1947	1226
65°	5393	1485	997
70°	5006	1077	793
75°	4526	822	607
80°	3824	556	406
85°	2670	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6452 cd/sqm

TEST NUMBER: P999617

CATALOG NUMBER: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.3
10°-20°	125.0	3.6
20°-30°	175.5	5.0
30°-40°	191.3	5.4
40°-50°	175.8	5.0
50°-60°	138.0	3.9
60°-70°	89.9	2.6
70°-80°	46.3	1.3
80°-90°	14.4	0.4
90°-100°	55.6	1.6
100°-110°	176.9	5.0
110°-120°	302.6	8.6
120°-130°	398.0	11.3
130°-140°	446.8	12.7
140°-150°	438.1	12.5
150°-160°	367.5	10.5
160°-170°	243.7	6.9
170°-180°	85.2	2.4
0°-30°	346.0	9.8
0°-40°	537.2	15.3
0°-60°	851.1	24.2
0°-90°	1001.5	28.5
90°-120°	535.2	15.2
90°-150°	1818.0	51.7
90°-180°	2514.0	71.5
0°-180°	3516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	486	484	478	482	480	46
15°	462	457	442	434	430	130
25°	419	405	376	358	352	193
35°	361	339	300	272	263	226
45°	295	266	220	189	178	228
55°	225	190	143	116	108	201
65°	152	116	76	62	60	150
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	10	27	25	26	3
95°	40	47	49	49	47	44
105°	163	166	167	168	168	172
115°	304	308	307	306	304	300
125°	442	448	446	444	443	395
135°	572	580	581	581	578	442
145°	694	699	704	704	701	433
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P999617

CATALOG NUMBER: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.7	485.7	485.7	485.7	485.7
2.5°	487.9	485.7	480.9	485.3	484.4
5°	485.7	483.5	477.8	481.8	480.5
7.5°	481.8	479.2	473.0	474.8	472.6
10°	476.5	473.4	464.6	463.3	460.7
12.5°	469.9	466.0	454.1	451.5	446.6
15°	462.0	457.2	442.2	433.9	429.5
17.5°	452.8	445.7	427.3	417.6	410.6
20°	442.2	433.4	411.5	400.5	390.8
22.5°	430.8	420.7	395.2	380.2	373.7
25°	419.4	405.3	376.3	358.3	351.7
27.5°	405.7	390.8	358.7	338.0	327.9
30°	391.2	374.5	339.4	316.9	305.1
32.5°	377.2	356.9	320.9	294.5	283.5
35°	361.3	338.9	300.2	272.5	262.9
37.5°	346.0	321.8	280.9	250.6	239.6
40°	329.7	303.3	260.7	229.5	218.0
42.5°	313.0	284.9	240.5	207.9	196.9
45°	295.4	266.0	219.8	188.6	178.0
47.5°	278.7	247.5	200.0	168.8	159.1
50°	260.2	229.0	180.7	150.3	141.1
52.5°	242.2	209.2	162.2	133.2	124.8
55°	224.6	190.3	142.9	116.5	108.1
57.5°	206.6	171.4	125.7	101.1	94.1
60°	188.1	153.0	107.7	85.3	78.2
62.5°	170.1	135.0	92.3	71.2	67.7
65°	151.7	116.1	76.5	61.5	60.2
67.5°	134.1	98.5	61.5	54.1	52.8
70°	115.6	81.3	51.0	46.6	44.8
72.5°	98.0	65.5	42.6	39.1	38.2
75°	80.9	50.1	35.2	32.1	31.7
77.5°	63.7	35.6	27.7	25.9	25.1
80°	47.9	25.5	21.1	19.3	19.3
82.5°	33.4	17.1	14.5	13.6	13.6
85°	18.9	9.7	8.4	8.4	8.4
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.8	9.9	26.6	25.0	25.8
92.5°	16.7	22.8	23.5	24.3	24.3
95°	39.5	47.1	48.6	48.6	47.1
97.5°	66.0	72.9	75.9	75.9	75.9
100°	96.4	102.5	104.7	104.7	104.0
102.5°	128.3	132.8	135.9	136.6	135.9
105°	163.2	165.5	167.0	168.5	168.5
107.5°	198.1	201.1	201.1	201.9	198.1
110°	231.5	236.0	236.0	236.0	233.8

TEST NUMBER: P999617

CATALOG NUMBER: SA2XXRDIP-B290D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.9	272.5	271.7	269.4	267.9
115°	303.6	308.1	306.6	305.9	303.6
117.5°	339.3	345.3	341.5	339.3	337.0
120°	374.9	381.0	374.9	374.9	372.6
122.5°	407.6	415.1	411.4	409.1	407.6
125°	441.7	448.5	446.3	444.0	443.2
127.5°	475.1	483.5	480.4	477.4	475.1
130°	506.2	516.1	514.6	513.1	510.0
132.5°	541.1	548.7	549.5	545.7	543.4
135°	571.5	579.8	581.4	580.6	578.3
137.5°	604.9	611.7	613.2	612.5	609.4
140°	634.5	641.3	645.1	645.1	642.1
142.5°	664.8	671.7	674.0	674.7	671.7
145°	693.7	699.0	703.6	704.3	701.3
147.5°	719.5	726.3	729.4	730.9	727.8
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

(END OF REPORT)