

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999629

Luminaire Tested: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999629
REPORT IS A COMBINATION OF REPORTS P988182 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4244.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999629

CATALOG NUMBER: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999629

CATALOG NUMBER: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	18	17	15
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	14
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7666	7666	7666
5°	7679	7293	7239
10°	7603	6918	6689
15°	7498	6473	6062
20°	7360	5968	5406
25°	7218	5451	4805
30°	7029	4945	4151
35°	6843	4437	3587
40°	6653	3938	3008
45°	6432	3421	2502
50°	6206	2924	2037
55°	5969	2427	1617
60°	5693	1942	1223
65°	5375	1481	994
70°	4993	1073	791
75°	4509	820	605
80°	3816	553	406
85°	2656	253	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6432 cd/sqm

TEST NUMBER: P999629

CATALOG NUMBER: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.1
10°-20°	124.6	2.9
20°-30°	174.9	4.1
30°-40°	190.7	4.5
40°-50°	175.3	4.1
50°-60°	137.6	3.2
60°-70°	89.6	2.1
70°-80°	46.1	1.1
80°-90°	15.1	0.4
90°-100°	71.8	1.7
100°-110°	228.2	5.4
110°-120°	390.5	9.2
120°-130°	513.6	12.1
130°-140°	576.5	13.6
140°-150°	565.4	13.3
150°-160°	474.2	11.2
160°-170°	314.5	7.4
170°-180°	109.9	2.6
0°-30°	344.9	8.1
0°-40°	535.6	12.6
0°-60°	848.5	20.0
0°-90°	999.3	23.5
90°-120°	690.5	16.3
90°-150°	2346.0	55.3
90°-180°	3245.0	76.5
0°-180°	4244.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	484	484	484	484	484	
5°	484	482	476	480	479	46
15°	461	456	441	433	428	130
25°	418	404	375	357	351	192
35°	360	338	299	272	262	225
45°	294	265	219	188	178	227
55°	224	190	142	116	108	200
65°	151	116	76	61	60	150
75°	81	50	35	32	32	85
85°	19	10	8	8	8	22
90°	1	13	34	32	33	4
95°	51	61	63	63	61	57
105°	211	214	216	217	217	222
115°	392	398	396	395	392	388
125°	570	579	576	573	572	509
135°	738	748	750	749	746	570
145°	895	902	908	909	905	559
155°	1023	1026	1029	1034	1031	471
165°	1114	1113	1113	1119	1114	314
175°	1159	1156	1154	1161	1155	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P999629

CATALOG NUMBER: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	484.3	484.3	484.3	484.3	484.3
2.5°	486.5	484.3	479.5	483.8	483.0
5°	484.3	482.1	476.4	480.3	479.0
7.5°	480.3	477.7	471.6	473.3	471.1
10°	475.1	472.0	463.3	461.9	459.3
12.5°	468.5	464.6	452.7	450.1	445.3
15°	460.6	455.8	440.9	432.6	428.2
17.5°	451.4	444.4	426.0	416.4	409.3
20°	440.9	432.1	410.2	399.3	389.6
22.5°	429.5	419.4	394.0	379.1	372.5
25°	418.1	404.1	375.2	357.2	350.6
27.5°	404.5	389.6	357.6	337.0	326.9
30°	390.1	373.4	338.3	316.0	304.2
32.5°	376.0	355.9	319.9	293.6	282.7
35°	360.3	337.9	299.3	271.7	262.1
37.5°	344.9	320.8	280.1	249.8	238.9
40°	328.7	302.4	259.9	228.8	217.4
42.5°	312.0	284.0	239.7	207.3	196.3
45°	294.5	265.2	219.1	188.0	177.5
47.5°	277.9	246.7	199.4	168.3	158.7
50°	259.5	228.3	180.1	149.9	140.7
52.5°	241.5	208.6	161.7	132.8	124.5
55°	224.0	189.8	142.4	116.1	107.8
57.5°	206.0	170.9	125.3	100.8	93.8
60°	187.6	152.5	107.4	85.0	78.0
62.5°	169.6	134.5	92.0	71.0	67.5
65°	151.2	115.7	76.3	61.4	60.0
67.5°	133.7	98.2	61.4	53.9	52.6
70°	115.3	81.1	50.8	46.5	44.7
72.5°	97.7	65.3	42.5	39.0	38.1
75°	80.6	50.0	35.1	32.0	31.6
77.5°	63.5	35.5	27.6	25.9	25.0
80°	47.8	25.4	21.0	19.3	19.3
82.5°	33.3	17.1	14.5	13.6	13.6
85°	18.8	9.6	8.3	8.3	8.3
87.5°	7.0	3.5	3.5	3.1	3.1
90°	1.0	12.7	34.3	32.3	33.3
92.5°	21.5	29.4	30.4	31.3	31.3
95°	50.9	60.7	62.7	62.7	60.7
97.5°	85.2	94.0	97.9	97.9	97.9
100°	124.4	132.2	135.2	135.2	134.2
102.5°	165.5	171.4	175.3	176.3	175.3
105°	210.6	213.5	215.5	217.4	217.4
107.5°	255.6	259.5	259.5	260.5	255.6
110°	298.7	304.6	304.6	304.6	301.6

TEST NUMBER: P999629

CATALOG NUMBER: SA2XXRDIP-B290D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	345.7	351.6	350.6	347.7	345.7
115°	391.7	397.6	395.7	394.7	391.7
117.5°	437.8	445.6	440.7	437.8	434.8
120°	483.8	491.6	483.8	483.8	480.9
122.5°	525.9	535.7	530.8	527.9	525.9
125°	570.0	578.8	575.9	572.9	572.0
127.5°	613.1	623.9	619.9	616.0	613.1
130°	653.2	666.0	664.0	662.1	658.1
132.5°	698.3	708.1	709.1	704.2	701.2
135°	737.5	748.2	750.2	749.2	746.3
137.5°	780.6	789.4	791.3	790.4	786.4
140°	818.8	827.6	832.5	832.5	828.5
142.5°	857.9	866.7	869.7	870.7	866.7
145°	895.1	902.0	907.9	908.9	904.9
147.5°	928.4	937.3	941.2	943.1	939.2
150°	962.7	968.6	972.5	975.5	972.5
152.5°	993.1	999.0	1003.9	1007.8	1003.9
155°	1023.4	1026.4	1029.3	1034.2	1031.3
157.5°	1049.9	1051.8	1053.8	1060.7	1055.8
160°	1073.4	1075.4	1076.3	1082.2	1078.3
162.5°	1094.9	1094.9	1095.9	1102.8	1097.9
165°	1113.5	1112.6	1112.6	1119.4	1114.5
167.5°	1130.2	1127.3	1127.3	1134.1	1129.2
170°	1142.9	1140.0	1139.0	1145.9	1140.0
172.5°	1151.7	1148.8	1147.8	1154.7	1148.8
175°	1158.6	1155.7	1153.7	1160.6	1154.7
177.5°	1162.5	1159.6	1157.6	1163.5	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6

(END OF REPORT)