

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999646

Luminaire Tested: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999646
REPORT IS A COMBINATION OF REPORTS P988199 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4590.1 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999646

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999646

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	26	26	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	22	22	16
3	76	68	61	55	67	60	54	50	46	42	39	33	31	29	22	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17	17	17	12
5	64	53	46	40	57	47	41	36	37	32	29	27	24	22	17	16	15	15	15	11
6	59	48	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	13	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	11	11	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	10	10	8
9	47	35	28	23	41	32	26	21	25	20	17	18	15	13	12	11	9	9	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6491 cd/sqm

TEST NUMBER: P999646

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.0
10°-20°	125.7	2.7
20°-30°	176.5	3.8
30°-40°	192.4	4.2
40°-50°	176.8	3.9
50°-60°	138.9	3.0
60°-70°	90.4	2.0
70°-80°	46.5	1.0
80°-90°	15.2	0.3
90°-100°	208.3	4.5
100°-110°	704.1	15.3
110°-120°	740.1	16.1
120°-130°	608.6	13.3
130°-140°	489.0	10.7
140°-150°	369.4	8.0
150°-160°	259.7	5.7
160°-170°	152.9	3.3
170°-180°	49.7	1.1
0°-30°	348.0	7.6
0°-40°	540.4	11.8
0°-60°	856.2	18.7
0°-90°	1008.3	22.0
90°-120°	1652.4	36.0
90°-150°	3119.5	68.0
90°-180°	3582.0	78.0
0°-180°	4590.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	13	34	32	33	3
95°	35	85	387	146	113	36
105°	120	182	732	1309	1113	128
115°	212	268	612	1264	1465	211
125°	296	351	589	1024	1188	263
135°	348	415	582	861	985	269
145°	397	456	579	719	786	249
155°	452	488	562	636	661	208
165°	492	507	538	571	580	139
175°	513	513	518	524	523	49
180°	514	514	514	514	514	

TEST NUMBER: P999646

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	1.0	13.4	33.6	32.1	32.6
92.5°	14.8	47.0	152.1	70.2	60.3
95°	34.6	84.9	387.3	146.2	112.6
97.5°	51.4	112.2	631.3	293.5	188.7
100°	76.1	137.4	780.5	584.4	353.7
102.5°	98.8	160.0	785.4	988.0	689.6
105°	120.5	181.8	732.1	1308.6	1113.4
107.5°	144.2	203.6	682.7	1424.6	1399.0
110°	168.0	225.8	649.1	1405.9	1515.5

TEST NUMBER: P999646

CATALOG NUMBER: SA2XXRDIP-B290D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.7	247.0	627.4	1342.2	1513.6
115°	212.4	268.2	612.5	1264.1	1465.1
117.5°	236.1	289.5	604.6	1189.5	1392.0
120°	257.9	310.2	597.7	1122.8	1321.9
122.5°	278.6	331.5	593.8	1071.0	1248.8
125°	296.4	350.8	588.8	1024.0	1188.5
127.5°	311.2	369.0	585.9	984.0	1132.2
130°	324.1	385.3	583.9	943.5	1085.8
132.5°	335.9	401.1	582.9	901.5	1037.4
135°	347.8	415.0	581.9	860.6	985.0
137.5°	358.6	426.8	581.9	819.0	934.6
140°	371.5	437.6	580.9	782.4	882.2
142.5°	384.3	446.6	580.9	747.4	829.9
145°	397.2	456.4	578.9	718.8	786.4
147.5°	411.0	464.4	576.0	693.6	747.9
150°	424.8	472.2	573.0	671.8	714.3
152.5°	438.7	480.2	568.1	653.5	685.6
155°	451.5	487.6	562.2	635.8	660.9
157.5°	462.4	493.5	556.2	619.0	639.2
160°	473.2	499.4	550.3	602.2	618.5
162.5°	484.1	503.8	545.4	586.3	598.7
165°	492.0	506.8	538.4	571.0	579.9
167.5°	498.9	509.8	532.5	557.2	562.2
170°	505.8	511.3	527.6	544.4	546.3
172.5°	509.8	512.8	521.6	533.0	533.5
175°	512.8	513.2	517.7	524.1	522.6
177.5°	514.7	513.7	513.7	517.7	514.7
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)