

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999651

Luminaire Tested: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999651
REPORT IS A COMBINATION OF REPORTS P988204 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4300.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999651

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999651

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	42	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	18	17	15
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	14
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7778	7388	7334
10°	7702	7007	6776
15°	7596	6558	6141
20°	7457	6047	5476
25°	7313	5522	4868
30°	7121	5011	4204
35°	6932	4494	3634
40°	6740	3989	3046
45°	6517	3467	2534
50°	6284	2963	2063
55°	6046	2459	1638
60°	5765	1967	1239
65°	5446	1500	1007
70°	5058	1088	801
75°	4570	829	612
80°	3864	561	410
85°	2698	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6517 cd/sqm

TEST NUMBER: P999651

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.1
10°-20°	126.2	2.9
20°-30°	177.2	4.1
30°-40°	193.2	4.5
40°-50°	177.6	4.1
50°-60°	139.4	3.2
60°-70°	90.8	2.1
70°-80°	46.7	1.1
80°-90°	15.3	0.4
90°-100°	72.7	1.7
100°-110°	231.3	5.4
110°-120°	395.7	9.2
120°-130°	520.4	12.1
130°-140°	584.1	13.6
140°-150°	572.8	13.3
150°-160°	480.5	11.2
160°-170°	318.7	7.4
170°-180°	111.4	2.6
0°-30°	349.4	8.1
0°-40°	542.6	12.6
0°-60°	859.6	20.0
0°-90°	1012.4	23.5
90°-120°	699.7	16.3
90°-150°	2377.1	55.3
90°-180°	3288.0	76.5
0°-180°	4300.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	22
90°	1	13	35	33	34	4
95°	52	62	64	64	62	58
105°	213	216	218	220	220	225
115°	397	403	401	400	397	393
125°	578	586	584	580	580	516
135°	747	758	760	759	756	577
145°	907	914	920	921	917	567
155°	1037	1040	1043	1048	1045	477
165°	1128	1127	1127	1134	1129	318
175°	1174	1171	1169	1176	1170	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P999651

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	1.0	12.9	34.7	32.7	33.7
92.5°	21.8	29.8	30.8	31.8	31.8
95°	51.6	61.5	63.5	63.5	61.5
97.5°	86.3	95.3	99.2	99.2	99.2
100°	126.0	134.0	136.9	136.9	136.0
102.5°	167.7	173.7	177.6	178.6	177.6
105°	213.4	216.3	218.3	220.3	220.3
107.5°	259.0	263.0	263.0	264.0	259.0
110°	302.7	308.6	308.6	308.6	305.6

TEST NUMBER: P999651

CATALOG NUMBER: SA2XXRDIP-B290D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.3	356.2	355.3	352.3	350.3
115°	396.9	402.9	400.9	399.9	396.9
117.5°	443.6	451.5	446.6	443.6	440.6
120°	490.2	498.2	490.2	490.2	487.2
122.5°	532.9	542.8	537.8	534.9	532.9
125°	577.5	586.5	583.5	580.5	579.5
127.5°	621.2	632.1	628.2	624.2	621.2
130°	661.9	674.8	672.8	670.8	666.9
132.5°	707.5	717.5	718.5	713.5	710.5
135°	747.2	758.1	760.1	759.1	756.2
137.5°	790.9	799.8	801.8	800.8	796.8
140°	829.6	838.5	843.5	843.5	839.5
142.5°	869.3	878.2	881.2	882.2	878.2
145°	907.0	913.9	919.9	920.9	916.9
147.5°	940.7	949.7	953.6	955.6	951.7
150°	975.5	981.4	985.4	988.4	985.4
152.5°	1006.2	1012.2	1017.1	1021.1	1017.1
155°	1037.0	1040.0	1042.9	1047.9	1044.9
157.5°	1063.8	1065.8	1067.8	1074.7	1069.7
160°	1087.6	1089.6	1090.6	1096.5	1092.6
162.5°	1109.4	1109.4	1110.4	1117.4	1112.4
165°	1128.3	1127.3	1127.3	1134.2	1129.3
167.5°	1145.2	1142.2	1142.2	1149.1	1144.2
170°	1158.1	1155.1	1154.1	1161.0	1155.1
172.5°	1167.0	1164.0	1163.0	1170.0	1164.0
175°	1173.9	1171.0	1169.0	1175.9	1170.0
177.5°	1177.9	1174.9	1172.9	1178.9	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)