

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999696

Luminaire Tested: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999696
REPORT IS A COMBINATION OF REPORTS P988251 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5869.8 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999696

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999696

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12939	12939	12939
5°	12960	12308	12218
10°	12831	11675	11289
15°	12655	10925	10231
20°	12421	10072	9124
25°	12184	9199	8111
30°	11861	8347	7004
35°	11547	7489	6054
40°	11229	6645	5076
45°	10857	5774	4223
50°	10472	4936	3437
55°	10072	4097	2730
60°	9607	3276	2065
65°	9072	2498	1678
70°	8423	1812	1334
75°	7613	1383	1020
80°	6435	936	683
85°	4492	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10857 cd/sqm

TEST NUMBER: P999696

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	1.3
10°-20°	210.3	3.6
20°-30°	295.2	5.0
30°-40°	321.8	5.5
40°-50°	295.8	5.0
50°-60°	232.3	4.0
60°-70°	151.2	2.6
70°-80°	77.8	1.3
80°-90°	23.7	0.4
90°-100°	243.3	4.1
100°-110°	822.6	14.0
110°-120°	864.7	14.7
120°-130°	711.0	12.1
130°-140°	571.4	9.7
140°-150°	431.6	7.4
150°-160°	303.4	5.2
160°-170°	178.7	3.0
170°-180°	58.1	1.0
0°-30°	582.1	9.9
0°-40°	904.0	15.4
0°-60°	1432.1	24.4
0°-90°	1684.8	28.7
90°-120°	1930.6	32.9
90°-150°	3644.7	62.1
90°-180°	4185.0	71.3
0°-180°	5869.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	817	814	804	811	808	78
15°	777	769	744	730	723	219
25°	706	682	633	603	592	325
35°	608	570	505	459	442	381
45°	497	448	370	317	300	384
55°	378	320	240	196	182	338
65°	255	195	129	104	101	253
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	16	39	38	38	4
95°	40	99	452	171	132	42
105°	141	212	855	1529	1301	150
115°	248	313	716	1477	1712	246
125°	346	410	688	1196	1389	308
135°	406	485	680	1005	1151	314
145°	464	533	676	840	919	291
155°	528	570	657	743	772	243
165°	575	592	629	667	678	162
175°	599	600	605	612	611	57
180°	600	600	600	600	600	

TEST NUMBER: P999696

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	817.4	817.4	817.4	817.4	817.4
2.5°	821.1	817.4	809.2	816.6	815.1
5°	817.4	813.7	804.0	810.7	808.5
7.5°	810.7	806.3	795.9	798.9	795.2
10°	801.8	796.6	781.9	779.6	775.2
12.5°	790.7	784.1	764.1	759.7	751.5
15°	777.4	769.3	744.1	730.1	722.7
17.5°	761.9	750.0	719.0	702.7	690.9
20°	744.1	729.3	692.3	673.9	657.6
22.5°	724.9	707.9	665.0	639.8	628.7
25°	705.7	682.0	633.2	602.8	591.8
27.5°	682.7	657.6	603.6	568.8	551.8
30°	658.3	630.2	571.0	533.3	513.3
32.5°	634.7	600.6	540.0	495.6	477.1
35°	608.0	570.3	505.2	458.6	442.3
37.5°	582.1	541.5	472.7	421.6	403.1
40°	554.8	510.4	438.6	386.1	366.9
42.5°	526.7	479.3	404.6	349.9	331.4
45°	497.1	447.5	369.8	317.3	299.6
47.5°	469.0	416.4	336.6	284.0	267.8
50°	437.9	385.4	304.0	253.0	237.4
52.5°	407.6	352.1	272.9	224.1	210.1
55°	378.0	320.3	240.4	196.0	182.0
57.5°	347.7	288.5	211.6	170.1	158.3
60°	316.6	257.4	181.2	143.5	131.7
62.5°	286.3	227.1	155.3	119.8	113.9
65°	255.2	195.3	128.7	103.6	101.3
67.5°	225.6	165.7	103.6	91.0	88.8
70°	194.5	136.8	85.8	78.4	75.4
72.5°	165.0	110.2	71.7	65.8	64.4
75°	136.1	84.3	59.2	54.0	53.3
77.5°	107.3	59.9	46.6	43.6	42.2
80°	80.6	42.9	35.5	32.5	32.5
82.5°	56.2	28.8	24.4	22.9	22.9
85°	31.8	16.3	14.1	14.1	14.1
87.5°	11.8	5.9	5.9	5.2	5.2
90°	1.2	15.6	39.2	37.5	38.1
92.5°	17.3	54.8	177.8	81.9	70.4
95°	40.4	99.2	452.5	170.8	131.6
97.5°	60.0	131.0	737.6	342.8	220.5
100°	88.9	160.4	911.9	682.8	413.2
102.5°	115.4	187.0	917.7	1154.4	805.7
105°	140.8	212.4	855.4	1528.9	1300.9
107.5°	168.5	237.8	797.6	1664.5	1634.5
110°	196.2	263.8	758.4	1642.6	1770.7

TEST NUMBER: P999696

CATALOG NUMBER: SA2XXRDIP-B485D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.6	288.6	733.0	1568.2	1768.4
115°	248.2	313.4	715.7	1477.0	1711.9
117.5°	275.9	338.2	706.4	1389.8	1626.4
120°	301.3	362.5	698.4	1311.9	1544.5
122.5°	325.5	387.2	693.7	1251.3	1459.1
125°	346.3	409.8	688.0	1196.4	1388.7
127.5°	363.6	431.2	684.5	1149.7	1322.9
130°	378.6	450.2	682.2	1102.4	1268.6
132.5°	392.5	468.6	681.1	1053.3	1212.0
135°	406.3	484.8	679.9	1005.4	1150.9
137.5°	419.0	498.7	679.9	957.0	1092.0
140°	434.0	511.4	678.7	914.2	1030.8
142.5°	449.0	521.8	678.7	873.2	969.6
145°	464.0	533.3	676.4	839.8	918.8
147.5°	480.2	542.6	673.0	810.3	873.8
150°	496.4	551.8	669.5	785.0	834.6
152.5°	512.5	561.0	663.7	763.6	801.1
155°	527.5	569.6	656.8	742.8	772.2
157.5°	540.2	576.6	649.9	723.2	746.8
160°	552.9	583.6	643.0	703.6	722.6
162.5°	565.6	588.7	637.2	685.1	699.5
165°	574.9	592.2	629.1	667.2	677.6
167.5°	582.9	595.6	622.2	651.0	656.8
170°	591.0	597.4	616.4	636.0	638.3
172.5°	595.6	599.0	609.5	622.8	623.3
175°	599.1	599.7	604.9	612.3	610.6
177.5°	601.4	600.2	600.2	604.9	601.4
180°	600.2	600.2	600.2	600.2	600.2

(END OF REPORT)