

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999764

Luminaire Tested: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999764
REPORT IS A COMBINATION OF REPORTS P988319 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3763.4 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999764

CATALOG NUMBER: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999764

CATALOG NUMBER: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	37	35	33
4	74	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	27	25	22
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P999764

CATALOG NUMBER: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	2.0
10°-20°	211.4	5.6
20°-30°	296.8	7.9
30°-40°	323.6	8.6
40°-50°	297.4	7.9
50°-60°	233.5	6.2
60°-70°	152.0	4.0
70°-80°	78.3	2.1
80°-90°	21.9	0.6
90°-100°	120.5	3.2
100°-110°	407.2	10.8
110°-120°	428.0	11.4
120°-130°	352.0	9.4
130°-140°	282.8	7.5
140°-150°	213.7	5.7
150°-160°	150.2	4.0
160°-170°	88.4	2.3
170°-180°	28.8	0.8
0°-30°	585.3	15.6
0°-40°	908.8	24.1
0°-60°	1439.7	38.3
0°-90°	1691.9	45.0
90°-120°	955.6	25.4
90°-150°	1804.1	47.9
90°-180°	2071.0	55.0
0°-180°	3763.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	8	19	19	19	3
95°	20	49	224	85	65	21
105°	70	105	423	757	644	74
115°	123	155	354	731	847	122
125°	171	203	340	592	687	152
135°	201	240	336	498	570	155
145°	230	264	335	416	455	144
155°	261	282	325	368	382	120
165°	284	293	311	330	335	80
175°	296	297	299	303	302	28
180°	297	297	297	297	297	

TEST NUMBER: P999764

CATALOG NUMBER: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.6	7.8	19.4	18.6	18.9
92.5°	8.6	27.2	88.0	40.6	34.9
95°	20.0	49.2	224.0	84.6	65.1
97.5°	29.7	64.8	365.1	169.7	109.1
100°	44.0	79.4	451.4	338.0	204.5
102.5°	57.1	92.6	454.2	571.4	398.8
105°	69.7	105.1	423.4	756.8	643.9
107.5°	83.4	117.7	394.8	823.9	809.1
110°	97.1	130.6	375.4	813.0	876.5

TEST NUMBER: P999764

CATALOG NUMBER: SA2XXRDIP-B485D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.7	142.9	362.8	776.2	875.3
115°	122.8	155.1	354.2	731.0	847.3
117.5°	136.6	167.4	349.7	687.9	805.1
120°	149.1	179.4	345.7	649.4	764.5
122.5°	161.1	191.7	343.4	619.4	722.2
125°	171.4	202.8	340.5	592.2	687.4
127.5°	180.0	213.4	338.8	569.1	654.8
130°	187.4	222.8	337.7	545.6	627.9
132.5°	194.3	232.0	337.1	521.3	599.9
135°	201.1	240.0	336.5	497.7	569.7
137.5°	207.4	246.8	336.5	473.6	540.5
140°	214.8	253.1	336.0	452.6	510.2
142.5°	222.3	258.2	336.0	432.2	479.9
145°	229.7	264.0	334.8	415.7	454.8
147.5°	237.7	268.6	333.1	401.1	432.5
150°	245.7	273.2	331.4	388.5	413.1
152.5°	253.7	277.7	328.5	378.0	396.5
155°	261.1	282.0	325.1	367.6	382.2
157.5°	267.4	285.4	321.7	358.0	369.7
160°	273.7	288.8	318.3	348.2	357.7
162.5°	280.0	291.4	315.4	339.1	346.2
165°	284.5	293.1	311.4	330.2	335.4
167.5°	288.5	294.8	308.0	322.2	325.1
170°	292.5	295.6	305.1	314.8	316.0
172.5°	294.8	296.6	301.7	308.2	308.5
175°	296.5	296.8	299.4	303.1	302.3
177.5°	297.7	297.1	297.1	299.4	297.7
180°	297.1	297.1	297.1	297.1	297.1

(END OF REPORT)