

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999781

Luminaire Tested: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999781
REPORT IS A COMBINATION OF REPORTS P988336 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3447.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999781

CATALOG NUMBER: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999781

CATALOG NUMBER: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12527	11900	11810
10°	12404	11285	10913
15°	12233	10561	9890
20°	12007	9738	8820
25°	11778	8893	7840
30°	11467	8069	6770
35°	11163	7240	5852
40°	10854	6424	4907
45°	10494	5582	4082
50°	10123	4772	3322
55°	9737	3961	2638
60°	9285	3168	1996
65°	8770	2414	1623
70°	8146	1751	1290
75°	7362	1336	986
80°	6219	904	662
85°	4337	415	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10494 cd/sqm

TEST NUMBER: P999781

CATALOG NUMBER: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	2.1
10°-20°	203.3	5.9
20°-30°	285.4	8.3
30°-40°	311.1	9.0
40°-50°	285.9	8.3
50°-60°	224.6	6.5
60°-70°	146.2	4.2
70°-80°	75.2	2.2
80°-90°	21.1	0.6
90°-100°	40.3	1.2
100°-110°	128.0	3.7
110°-120°	219.1	6.4
120°-130°	288.1	8.4
130°-140°	323.4	9.4
140°-150°	317.1	9.2
150°-160°	266.0	7.7
160°-170°	176.4	5.1
170°-180°	61.7	1.8
0°-30°	562.8	16.3
0°-40°	873.9	25.4
0°-60°	1384.4	40.2
0°-90°	1626.9	47.2
90°-120°	387.4	11.2
90°-150°	1316.0	38.2
90°-180°	1820.0	52.8
0°-180°	3447.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	35
90°	0	7	19	18	19	3
95°	29	34	35	35	34	32
105°	118	120	121	122	122	125
115°	220	223	222	221	220	217
125°	320	325	323	321	321	286
135°	414	420	421	420	419	320
145°	502	506	509	510	508	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P999781

CATALOG NUMBER: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.5	7.1	19.2	18.1	18.7
92.5°	12.1	16.5	17.0	17.6	17.6
95°	28.6	34.1	35.2	35.2	34.1
97.5°	47.8	52.7	54.9	54.9	54.9
100°	69.8	74.2	75.8	75.8	75.3
102.5°	92.8	96.1	98.3	98.9	98.3
105°	118.1	119.8	120.9	122.0	122.0
107.5°	143.4	145.6	145.6	146.1	143.4
110°	167.6	170.9	170.9	170.9	169.2



TEST NUMBER: P999781

CATALOG NUMBER: SA2XXRDIP-B485D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.9	197.2	196.7	195.0	193.9
115°	219.8	223.1	222.0	221.4	219.8
117.5°	245.6	250.0	247.2	245.6	243.9
120°	271.4	275.8	271.4	271.4	269.8
122.5°	295.0	300.5	297.8	296.1	295.0
125°	319.7	324.7	323.0	321.4	320.8
127.5°	343.9	350.0	347.8	345.6	343.9
130°	366.4	373.6	372.5	371.4	369.2
132.5°	391.7	397.2	397.8	395.0	393.4
135°	413.7	419.7	420.8	420.3	418.6
137.5°	437.9	442.8	443.9	443.4	441.2
140°	459.3	464.2	467.0	467.0	464.8
142.5°	481.3	486.2	487.9	488.4	486.2
145°	502.1	506.0	509.3	509.8	507.6
147.5°	520.8	525.8	528.0	529.1	526.9
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)