

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999803

Luminaire Tested: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999803
REPORT IS A COMBINATION OF REPORTS P988358 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4222.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999803

CATALOG NUMBER: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999803

CATALOG NUMBER: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P999803

CATALOG NUMBER: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.8
10°-20°	211.4	5.0
20°-30°	296.8	7.0
30°-40°	323.6	7.7
40°-50°	297.4	7.0
50°-60°	233.5	5.5
60°-70°	152.0	3.6
70°-80°	78.3	1.9
80°-90°	22.6	0.5
90°-100°	56.0	1.3
100°-110°	177.9	4.2
110°-120°	304.4	7.2
120°-130°	400.4	9.5
130°-140°	449.4	10.6
140°-150°	440.7	10.4
150°-160°	369.7	8.8
160°-170°	245.2	5.8
170°-180°	85.7	2.0
0°-30°	585.3	13.9
0°-40°	908.8	21.5
0°-60°	1439.7	34.1
0°-90°	1692.6	40.1
90°-120°	538.3	12.8
90°-150°	1828.9	43.3
90°-180°	2529.0	59.9
0°-180°	4222.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	10	27	25	26	4
95°	40	47	49	49	47	44
105°	164	166	168	170	170	173
115°	305	310	308	308	305	302
125°	444	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	703	708	708	706	436
155°	798	800	802	806	804	367
165°	868	867	867	873	869	245
175°	903	901	899	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P999803

CATALOG NUMBER: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.8	9.9	26.7	25.2	26.0
92.5°	16.8	22.9	23.7	24.4	24.4
95°	39.7	47.3	48.9	48.9	47.3
97.5°	66.4	73.3	76.3	76.3	76.3
100°	97.0	103.1	105.4	105.4	104.6
102.5°	129.0	133.6	136.7	137.4	136.7
105°	164.1	166.4	168.0	169.5	169.5
107.5°	199.3	202.3	202.3	203.1	199.3
110°	232.9	237.4	237.4	237.4	235.2

TEST NUMBER: P999803

CATALOG NUMBER: SA2XXRDIP-B485D725UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.5	274.1	273.3	271.0	269.5
115°	305.4	310.0	308.4	307.7	305.4
117.5°	341.3	347.4	343.6	341.3	339.0
120°	377.2	383.3	377.2	377.2	374.9
122.5°	410.0	417.6	413.8	411.5	410.0
125°	444.3	451.2	448.9	446.6	445.9
127.5°	477.9	486.3	483.3	480.2	477.9
130°	509.2	519.2	517.6	516.1	513.1
132.5°	544.4	552.0	552.8	548.9	546.6
135°	574.9	583.3	584.8	584.1	581.8
137.5°	608.5	615.4	616.9	616.1	613.1
140°	638.3	645.1	649.0	649.0	645.9
142.5°	668.8	675.7	678.0	678.7	675.7
145°	697.8	703.2	707.7	708.5	705.5
147.5°	723.8	730.6	733.7	735.2	732.2
150°	750.5	755.1	758.1	760.4	758.1
152.5°	774.2	778.7	782.6	785.6	782.6
155°	797.8	800.1	802.4	806.2	803.9
157.5°	818.4	820.0	821.5	826.8	823.0
160°	836.8	838.3	839.1	843.6	840.6
162.5°	853.6	853.6	854.3	859.7	855.9
165°	868.1	867.3	867.3	872.7	868.8
167.5°	881.1	878.8	878.8	884.1	880.3
170°	891.0	888.7	887.9	893.3	888.7
172.5°	897.8	895.6	894.8	900.1	895.6
175°	903.2	900.9	899.4	904.7	900.1
177.5°	906.2	904.0	902.4	907.0	902.4
180°	904.7	904.7	904.7	904.7	904.7

(END OF REPORT)