

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000707

Luminaire Tested: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000707
REPORT IS A COMBINATION OF REPORTS P995320 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6798.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000707

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000707

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33		
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25		
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14045	14045	14045
5°	14058	13642	13658
10°	13938	13262	13170
15°	13739	12812	12620
20°	13483	12326	12049
25°	13196	11811	11436
30°	12849	11254	10762
35°	12491	10685	10110
40°	12116	10073	9418
45°	11723	9457	8771
50°	11289	8861	8053
55°	10818	8165	7341
60°	10334	7403	6598
65°	9781	6615	5762
70°	9145	5668	4866
75°	8193	4568	3897
80°	6984	3304	2741
85°	5421	1840	1476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11723 cd/sqm

TEST NUMBER: P1000707

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.4
10°-20°	457.4	6.7
20°-30°	673.1	9.9
30°-40°	782.5	11.5
40°-50°	782.4	11.5
50°-60°	684.3	10.1
60°-70°	508.0	7.5
70°-80°	288.3	4.2
80°-90°	84.1	1.2
90°-100°	25.5	0.4
100°-110°	167.8	2.5
110°-120°	320.5	4.7
120°-130°	406.8	6.0
130°-140°	435.2	6.4
140°-150°	406.9	6.0
150°-160°	328.2	4.8
160°-170°	211.6	3.1
170°-180°	72.9	1.1
0°-30°	1292.9	19.0
0°-40°	2075.4	30.5
0°-60°	3542.1	52.1
0°-90°	4422.6	65.1
90°-120°	513.8	7.6
90°-150°	1762.7	25.9
90°-180°	2375.0	34.9
0°-180°	6798.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1722	1722	1722	1722	1722	
5°	1721	1716	1700	1716	1713	163
15°	1638	1633	1612	1620	1616	462
25°	1484	1474	1455	1456	1451	683
35°	1277	1267	1248	1238	1231	798
45°	1042	1032	1010	995	991	803
55°	788	784	765	748	740	706
65°	534	527	513	500	493	529
75°	284	277	270	265	264	302
85°	74	74	72	72	70	80
90°	2	8	13	16	17	7
95°	32	12	13	16	17	39
105°	173	176	179	184	164	181
115°	323	324	324	325	325	318
125°	454	456	455	456	457	405
135°	563	562	564	566	567	434
145°	649	650	650	651	652	405
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1000707

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1722.4	1722.4	1722.4	1722.4	1722.4
2.5°	1728.0	1723.8	1708.6	1722.4	1721.1
5°	1721.1	1715.5	1700.4	1715.5	1712.8
7.5°	1708.6	1703.1	1686.6	1699.0	1697.6
10°	1690.7	1685.2	1667.2	1678.3	1675.5
12.5°	1667.2	1661.7	1642.4	1654.8	1650.7
15°	1638.3	1632.7	1612.0	1620.3	1616.2
17.5°	1605.1	1598.2	1578.9	1584.4	1581.7
20°	1567.9	1561.0	1540.3	1544.4	1541.6
22.5°	1527.8	1518.2	1497.5	1505.8	1500.2
25°	1483.7	1474.0	1454.7	1456.1	1450.6
27.5°	1434.0	1424.3	1406.4	1403.6	1396.7
30°	1384.3	1373.3	1355.3	1349.8	1342.9
32.5°	1331.9	1322.2	1302.9	1296.0	1289.1
35°	1276.7	1267.0	1247.7	1238.0	1231.1
37.5°	1218.7	1210.4	1189.7	1180.0	1170.4
40°	1162.1	1151.1	1130.4	1116.6	1109.7
42.5°	1101.4	1095.9	1072.4	1055.8	1051.7
45°	1042.0	1032.4	1010.3	995.1	991.0
47.5°	979.9	973.0	952.3	935.8	924.7
50°	916.4	910.9	891.6	872.3	864.0
52.5°	854.3	847.4	826.7	810.2	799.1
55°	788.1	783.9	764.6	748.1	739.8
57.5°	726.0	721.8	702.5	685.9	677.7
60°	661.1	654.2	636.3	623.8	616.9
62.5°	597.6	592.1	572.8	561.7	554.8
65°	534.1	527.2	513.4	499.6	492.7
67.5°	469.3	463.7	449.9	436.1	434.8
70°	409.9	400.2	389.2	378.2	374.0
72.5°	346.4	336.8	328.5	320.2	316.1
75°	284.3	277.4	270.5	265.0	263.6
77.5°	223.6	220.8	213.9	212.5	208.4
80°	169.8	165.6	162.9	160.1	158.7
82.5°	117.3	115.9	115.9	114.6	113.2
85°	74.5	74.5	71.8	71.8	70.4
87.5°	35.9	34.5	33.1	33.1	33.1
90°	1.7	8.0	12.6	16.1	17.2
92.5°	8.6	7.5	12.1	15.5	15.5
95°	31.6	12.1	12.6	16.1	16.7
97.5°	60.3	72.9	12.6	15.5	16.1
100°	94.2	104.5	25.3	15.5	16.1
102.5°	132.1	138.9	145.8	16.7	16.7
105°	172.8	176.3	179.1	184.3	163.6
107.5°	210.1	211.9	215.9	218.8	221.1
110°	248.0	249.8	253.2	254.4	256.1



TEST NUMBER: P1000707

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.8	288.2	289.4	288.8	291.1
115°	322.7	324.4	323.8	325.0	325.0
117.5°	356.6	358.9	360.6	360.0	360.0
120°	391.0	393.3	392.7	393.9	392.7
122.5°	423.2	424.3	425.5	426.0	424.9
125°	453.6	455.9	454.7	456.5	457.0
127.5°	482.9	483.4	486.3	485.7	485.2
130°	511.0	511.6	513.3	513.9	513.9
132.5°	536.8	538.0	540.3	540.9	540.3
135°	562.7	562.1	564.4	565.6	566.7
137.5°	585.7	585.7	588.5	589.7	589.1
140°	608.0	609.2	610.3	612.1	612.6
142.5°	628.1	630.4	631.0	632.2	632.2
145°	648.8	650.5	650.5	651.1	652.3
147.5°	664.9	668.3	667.8	668.3	668.9
150°	682.7	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)