

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000708

Luminaire Tested: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000708
REPORT IS A COMBINATION OF REPORTS P995321 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6730.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000708

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000708

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33		
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25		
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	23		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13917	13506	13522
10°	13800	13130	13039
15°	13602	12685	12494
20°	13349	12203	11929
25°	13064	11693	11321
30°	12721	11142	10654
35°	12365	10579	10010
40°	11995	9972	9324
45°	11608	9363	8683
50°	11177	8773	7973
55°	10710	8084	7267
60°	10231	7329	6533
65°	9684	6550	5705
70°	9053	5611	4818
75°	8112	4522	3859
80°	6914	3269	2714
85°	5370	1822	1461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11608 cd/sqm

TEST NUMBER: P1000708

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	2.4
10°-20°	452.8	6.7
20°-30°	666.4	9.9
30°-40°	774.7	11.5
40°-50°	774.6	11.5
50°-60°	677.5	10.1
60°-70°	503.0	7.5
70°-80°	285.4	4.2
80°-90°	83.3	1.2
90°-100°	25.2	0.4
100°-110°	166.1	2.5
110°-120°	317.2	4.7
120°-130°	402.7	6.0
130°-140°	430.8	6.4
140°-150°	402.8	6.0
150°-160°	324.8	4.8
160°-170°	209.5	3.1
170°-180°	72.2	1.1
0°-30°	1280.0	19.0
0°-40°	2054.7	30.5
0°-60°	3506.8	52.1
0°-90°	4378.6	65.1
90°-120°	508.5	7.6
90°-150°	1744.9	25.9
90°-180°	2351.0	34.9
0°-180°	6730.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	79
90°	2	8	12	16	17	6
95°	31	12	12	16	16	39
105°	171	174	177	182	162	179
115°	319	321	321	322	322	314
125°	449	451	450	452	452	401
135°	557	556	559	560	561	429
145°	642	644	644	644	646	401
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1000708

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	1.7	8.0	12.5	15.9	17.1
92.5°	8.5	7.4	11.9	15.3	15.3
95°	31.3	11.9	12.5	15.9	16.5
97.5°	59.7	72.2	12.5	15.3	15.9
100°	93.2	103.4	25.0	15.3	15.9
102.5°	130.7	137.5	144.4	16.5	16.5
105°	171.1	174.5	177.3	182.4	162.0
107.5°	208.0	209.7	213.7	216.5	218.8
110°	245.5	247.2	250.7	251.8	253.5



TEST NUMBER: P1000708

CATALOG NUMBER: SA4XXDIP-B1020D590UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	285.3	286.5	285.9	288.2
115°	319.4	321.1	320.6	321.7	321.7
117.5°	353.0	355.2	356.9	356.4	356.4
120°	387.1	389.3	388.8	389.9	388.8
122.5°	418.9	420.0	421.2	421.7	420.6
125°	449.0	451.3	450.1	451.9	452.4
127.5°	478.0	478.6	481.4	480.8	480.3
130°	505.8	506.4	508.1	508.7	508.7
132.5°	531.4	532.6	534.8	535.4	534.8
135°	557.0	556.4	558.7	559.8	561.0
137.5°	579.7	579.7	582.6	583.7	583.1
140°	601.9	603.0	604.2	605.9	606.5
142.5°	621.8	624.1	624.6	625.8	625.8
145°	642.3	644.0	644.0	644.5	645.7
147.5°	658.2	661.6	661.0	661.6	662.2
150°	675.8	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)