

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999822

Luminaire Tested: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999822
REPORT IS A COMBINATION OF REPORTS P988377 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4289.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999822

CATALOG NUMBER: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999822

CATALOG NUMBER: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	87	83	80	77	68	65	64	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	43	61	51	45	39	42	37	34	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12527	11900	11810
10°	12404	11285	10913
15°	12233	10561	9890
20°	12007	9738	8820
25°	11778	8893	7840
30°	11467	8069	6770
35°	11163	7240	5852
40°	10854	6424	4907
45°	10494	5582	4082
50°	10123	4772	3322
55°	9737	3961	2638
60°	9285	3168	1996
65°	8770	2414	1623
70°	8146	1751	1290
75°	7362	1336	986
80°	6219	904	662
85°	4337	415	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10494 cd/sqm

TEST NUMBER: P999822

CATALOG NUMBER: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	1.7
10°-20°	203.3	4.7
20°-30°	285.4	6.7
30°-40°	311.1	7.3
40°-50°	285.9	6.7
50°-60°	224.6	5.2
60°-70°	146.2	3.4
70°-80°	75.2	1.8
80°-90°	21.7	0.5
90°-100°	154.7	3.6
100°-110°	523.2	12.2
110°-120°	549.9	12.8
120°-130°	452.2	10.5
130°-140°	363.4	8.5
140°-150°	274.5	6.4
150°-160°	193.0	4.5
160°-170°	113.6	2.6
170°-180°	37.0	0.9
0°-30°	562.8	13.1
0°-40°	873.9	20.4
0°-60°	1384.4	32.3
0°-90°	1627.4	37.9
90°-120°	1227.9	28.6
90°-150°	2318.0	54.0
90°-180°	2662.0	62.1
0°-180°	4289.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	35
90°	1	10	25	24	24	3
95°	26	63	288	109	84	27
105°	90	135	544	972	827	95
115°	158	199	455	939	1089	157
125°	220	261	438	761	883	196
135°	258	308	432	639	732	200
145°	295	339	430	534	584	185
155°	336	362	418	472	491	154
165°	366	377	400	424	431	103
175°	381	381	385	390	388	36
180°	382	382	382	382	382	

TEST NUMBER: P999822

CATALOG NUMBER: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.7	9.9	25.0	23.8	24.2
92.5°	11.0	34.8	113.1	52.2	44.8
95°	25.7	63.1	287.8	108.6	83.7
97.5°	38.2	83.3	469.1	218.0	140.2
100°	56.5	102.0	580.0	434.2	262.8
102.5°	73.4	119.0	583.6	734.2	512.4
105°	89.6	135.1	544.0	972.4	827.4
107.5°	107.2	151.2	507.3	1058.6	1039.5
110°	124.8	167.8	482.3	1044.7	1126.2

TEST NUMBER: P999822

CATALOG NUMBER: SA2XXRDIP-B485D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.0	183.5	466.2	997.3	1124.7
115°	157.8	199.3	455.2	939.3	1088.7
117.5°	175.5	215.1	449.3	883.9	1034.4
120°	191.6	230.5	444.2	834.4	982.3
122.5°	207.0	246.3	441.2	795.8	928.0
125°	220.2	260.6	437.5	761.0	883.2
127.5°	231.3	274.2	435.3	731.2	841.3
130°	240.8	286.3	433.9	701.1	806.8
132.5°	249.6	298.0	433.1	669.9	770.8
135°	258.4	308.4	432.4	639.4	731.9
137.5°	266.5	317.2	432.4	608.6	694.5
140°	276.0	325.2	431.7	581.4	655.6
142.5°	285.6	331.8	431.7	555.4	616.7
145°	295.1	339.2	430.2	534.0	584.4
147.5°	305.4	345.0	428.0	515.4	555.7
150°	315.7	350.9	425.8	499.2	530.8
152.5°	326.0	356.8	422.1	485.6	509.5
155°	335.5	362.3	417.7	472.4	491.1
157.5°	343.6	366.7	413.3	459.9	475.0
160°	351.7	371.1	408.9	447.4	459.6
162.5°	359.7	374.4	405.2	435.7	444.9
165°	365.6	376.6	400.1	424.4	430.9
167.5°	370.7	378.8	395.7	414.0	417.7
170°	375.9	379.9	392.0	404.5	406.0
172.5°	378.8	381.0	387.6	396.0	396.4
175°	381.0	381.4	384.7	389.5	388.4
177.5°	382.5	381.8	381.8	384.7	382.5
180°	381.8	381.8	381.8	381.8	381.8

(END OF REPORT)