

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000824

Luminaire Tested: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000824
REPORT IS A COMBINATION OF REPORTS P995437 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8619.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000824

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000824

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	58	56	48	47	46
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	32
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	41	34	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11205	11205	11205
5°	11236	10913	10933
10°	11163	10699	10668
15°	11059	10457	10369
20°	10904	10196	10078
25°	10729	9908	9765
30°	10541	9622	9446
35°	10327	9330	9162
40°	10156	9050	8867
45°	9903	8787	8607
50°	9686	8488	8332
55°	9463	8201	8017
60°	9117	7842	7719
65°	8735	7456	7361
70°	8272	7013	6947
75°	7628	6522	6553
80°	6897	6023	6141
85°	5938	5520	5806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9903 cd/sqm

TEST NUMBER: P1000824

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.5
10°-20°	373.1	4.3
20°-30°	564.1	6.5
30°-40°	682.4	7.9
40°-50°	721.4	8.4
50°-60°	678.9	7.9
60°-70°	563.4	6.5
70°-80°	395.4	4.6
80°-90°	225.5	2.6
90°-100°	174.9	2.0
100°-110°	376.0	4.4
110°-120°	596.3	6.9
120°-130°	710.4	8.2
130°-140°	736.3	8.5
140°-150°	676.7	7.9
150°-160°	543.1	6.3
160°-170°	350.3	4.1
170°-180°	120.7	1.4
0°-30°	1067.3	12.4
0°-40°	1749.7	20.3
0°-60°	3150.1	36.5
0°-90°	4334.3	50.3
90°-120°	1147.2	13.3
90°-150°	3270.5	37.9
90°-180°	4285.0	49.7
0°-180°	8619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1376	1371	1360	1373	1371	131
15°	1319	1320	1316	1330	1328	372
25°	1206	1216	1220	1237	1239	556
35°	1056	1074	1090	1111	1116	661
45°	880	909	939	965	972	680
55°	689	722	768	799	808	614
65°	477	526	579	617	629	473
75°	265	322	386	429	443	281
85°	82	146	215	262	277	85
90°	28	100	173	224	238	20
95°	72	91	155	202	217	80
105°	300	336	398	445	423	315
115°	543	560	608	644	655	535
125°	757	759	796	828	838	676
135°	934	933	948	974	986	720
145°	1075	1077	1077	1087	1095	672
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P1000824

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.1	1374.1	1374.1	1374.1	1374.1
2.5°	1380.3	1375.7	1363.4	1374.1	1372.6
5°	1375.7	1371.1	1360.3	1372.6	1371.1
7.5°	1366.4	1363.4	1354.1	1368.0	1366.4
10°	1354.1	1352.6	1344.9	1358.8	1357.2
12.5°	1337.2	1337.2	1332.6	1344.9	1344.9
15°	1318.7	1320.3	1315.7	1329.5	1328.0
17.5°	1294.1	1298.7	1297.2	1311.0	1309.5
20°	1268.0	1272.6	1274.1	1289.5	1289.5
22.5°	1238.7	1244.9	1248.0	1263.3	1266.4
25°	1206.4	1215.6	1220.3	1237.2	1238.7
27.5°	1171.0	1184.9	1191.0	1206.4	1207.9
30°	1135.6	1147.9	1158.7	1175.6	1178.7
32.5°	1097.2	1112.5	1124.9	1144.9	1147.9
35°	1055.6	1074.1	1089.5	1111.0	1115.6
37.5°	1014.1	1035.6	1054.1	1075.6	1080.2
40°	974.1	994.1	1015.6	1038.7	1044.8
42.5°	927.9	951.0	977.1	1003.3	1007.9
45°	880.2	909.4	938.7	964.8	972.5
47.5°	835.6	864.8	898.7	924.8	934.0
50°	786.3	820.2	854.0	884.8	894.0
52.5°	737.1	770.9	810.9	841.7	850.9
55°	689.4	721.7	767.9	798.6	807.9
57.5°	635.5	675.5	720.2	757.1	764.8
60°	583.2	623.2	674.0	709.4	721.7
62.5°	532.4	577.0	627.8	663.2	675.5
65°	477.0	526.3	578.6	617.1	629.4
67.5°	424.7	477.0	532.4	570.9	583.2
70°	370.8	423.2	481.6	523.2	534.0
72.5°	318.5	372.4	435.5	475.5	487.8
75°	264.7	321.6	386.2	429.3	443.2
77.5°	213.9	273.9	341.6	384.7	400.1
80°	167.7	229.3	297.0	343.1	355.5
82.5°	121.6	186.2	253.9	301.6	315.5
85°	81.6	146.2	215.4	261.6	277.0
87.5°	50.8	113.9	181.6	226.2	240.1
90°	27.5	99.5	173.2	223.6	237.8
92.5°	37.4	89.3	163.1	211.9	224.2
95°	72.3	90.8	154.8	202.0	216.9
97.5°	118.3	183.8	147.1	191.9	206.6
100°	172.7	229.8	158.7	184.2	195.9
102.5°	235.5	280.8	350.7	176.9	189.2
105°	299.8	336.3	398.1	445.0	423.1
107.5°	361.6	390.6	451.2	494.3	509.0
110°	422.8	447.3	506.8	544.1	559.2



TEST NUMBER: P1000824

CATALOG NUMBER: SA4XXDIP-B1195D1035UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	482.1	506.2	558.9	591.9	608.0
115°	543.2	560.0	608.2	644.0	654.7
117.5°	599.3	612.4	661.4	692.7	705.1
120°	654.8	663.2	706.9	739.6	750.0
122.5°	708.0	709.9	753.3	785.1	794.0
125°	756.9	759.1	795.7	827.8	838.0
127.5°	805.4	804.7	840.3	867.0	876.9
130°	850.3	849.8	877.2	905.9	915.1
132.5°	893.1	893.5	915.7	942.8	951.1
135°	934.4	933.4	947.9	974.5	985.6
137.5°	972.4	970.8	981.7	1006.7	1013.5
140°	1009.4	1009.7	1013.2	1036.1	1044.7
142.5°	1041.1	1044.9	1044.3	1063.1	1069.3
145°	1075.3	1076.6	1076.6	1086.8	1094.9
147.5°	1101.9	1106.1	1105.2	1107.6	1114.8
150°	1131.4	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)