

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000939

Luminaire Tested: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000939
REPORT IS A COMBINATION OF REPORTS P995553 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6290.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000939

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000939

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	101	96	91	87	95	91	87	83	81	78	75	73	70	68	64	63	61
2	91	83	76	70	86	79	72	67	70	65	61	63	59	56	56	53	50
3	83	73	64	58	78	69	61	55	62	56	51	55	50	46	49	45	42
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	39	36
5	70	57	48	41	65	54	46	40	49	42	37	44	38	34	39	35	31
6	64	51	42	36	60	49	40	35	44	37	32	39	34	30	35	31	27
7	59	46	37	31	56	44	36	30	40	33	28	36	30	26	32	28	24
8	55	42	34	28	52	40	32	27	36	30	25	33	27	23	30	25	21
9	51	38	30	25	48	37	29	24	33	27	22	30	25	21	27	23	19
10	48	35	27	22	45	34	26	22	31	24	20	28	23	19	25	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11555	11555	11555
5°	11586	11254	11274
10°	11511	11032	11000
15°	11403	10783	10692
20°	11244	10513	10393
25°	11064	10216	10070
30°	10869	9922	9740
35°	10649	9621	9447
40°	10472	9331	9144
45°	10211	9060	8875
50°	9988	8752	8592
55°	9758	8456	8266
60°	9401	8086	7959
65°	9008	7688	7590
70°	8531	7233	7163
75°	7864	6726	6757
80°	7115	6210	6331
85°	6120	5691	5986

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10211 cd/sqm

TEST NUMBER: P1000939

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	2.1
10°-20°	384.7	6.1
20°-30°	581.6	9.2
30°-40°	703.7	11.2
40°-50°	743.9	11.8
50°-60°	700.1	11.1
60°-70°	581.0	9.2
70°-80°	407.7	6.5
80°-90°	230.8	3.7
90°-100°	152.5	2.4
100°-110°	204.3	3.2
110°-120°	264.7	4.2
120°-130°	288.0	4.6
130°-140°	283.7	4.5
140°-150°	253.1	4.0
150°-160°	201.4	3.2
160°-170°	129.9	2.1
170°-180°	44.8	0.7
0°-30°	1100.6	17.5
0°-40°	1804.2	28.7
0°-60°	3248.2	51.6
0°-90°	4467.7	71.0
90°-120°	621.5	9.9
90°-150°	1446.2	23.0
90°-180°	1822.0	29.0
0°-180°	6290.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1417	1417	1417	1417	1417	
5°	1418	1414	1403	1415	1414	135
15°	1360	1361	1357	1371	1369	383
25°	1244	1254	1258	1276	1277	573
35°	1088	1108	1123	1146	1150	682
45°	908	938	968	995	1003	701
55°	711	744	792	824	833	633
65°	492	543	597	636	649	488
75°	273	332	398	443	457	290
85°	84	151	222	270	286	88
90°	26	94	165	213	226	18
95°	40	80	146	191	205	40
105°	120	154	215	258	258	127
115°	208	223	273	309	320	205
125°	285	285	324	355	365	255
135°	349	348	361	387	397	269
145°	400	399	399	409	416	250
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1000939

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1423.3	1418.5	1405.9	1417.0	1415.4
5°	1418.5	1413.8	1402.7	1415.4	1413.8
7.5°	1409.0	1405.9	1396.3	1410.6	1409.0
10°	1396.3	1394.7	1386.8	1401.1	1399.5
12.5°	1378.9	1378.9	1374.1	1386.8	1386.8
15°	1359.8	1361.4	1356.7	1370.9	1369.4
17.5°	1334.5	1339.2	1337.6	1351.9	1350.3
20°	1307.5	1312.2	1313.8	1329.7	1329.7
22.5°	1277.3	1283.7	1286.8	1302.7	1305.9
25°	1244.0	1253.5	1258.3	1275.7	1277.3
27.5°	1207.5	1221.8	1228.1	1244.0	1245.6
30°	1171.0	1183.7	1194.8	1212.3	1215.4
32.5°	1131.3	1147.2	1159.9	1180.5	1183.7
35°	1088.5	1107.5	1123.4	1145.6	1150.4
37.5°	1045.7	1067.9	1086.9	1109.1	1113.9
40°	1004.4	1025.0	1047.2	1071.1	1077.4
42.5°	956.8	980.6	1007.6	1034.6	1039.3
45°	907.6	937.8	967.9	994.9	1002.8
47.5°	861.6	891.7	926.7	953.6	963.2
50°	810.8	845.7	880.6	912.4	921.9
52.5°	760.0	795.0	836.2	867.9	877.5
55°	710.9	744.2	791.8	823.5	833.0
57.5°	655.3	696.6	742.6	780.7	788.6
60°	601.4	642.6	695.0	731.5	744.2
62.5°	549.0	595.0	647.4	683.9	696.6
65°	491.9	542.7	596.6	636.3	649.0
67.5°	437.9	491.9	549.0	588.7	601.4
70°	382.4	436.4	496.7	539.5	550.6
72.5°	328.5	384.0	449.0	490.3	503.0
75°	272.9	331.6	398.3	442.7	457.0
77.5°	220.6	282.4	352.3	396.7	412.6
80°	173.0	236.4	306.2	353.8	366.5
82.5°	125.4	192.0	261.8	311.0	325.3
85°	84.1	150.7	222.1	269.7	285.6
87.5°	52.4	117.4	187.2	233.3	247.5
90°	26.5	93.8	164.9	213.0	226.4
92.5°	29.1	83.9	155.0	201.5	214.2
95°	40.0	80.4	145.8	190.8	205.4
97.5°	56.0	109.9	137.9	180.9	195.5
100°	75.3	122.8	136.1	172.9	184.4
102.5°	98.6	137.7	202.2	164.1	176.8
105°	120.4	154.2	214.7	257.5	257.5
107.5°	143.3	171.3	229.3	270.8	283.3
110°	164.9	188.2	245.8	283.0	296.8

TEST NUMBER: P1000939

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	185.9	207.0	260.1	294.7	308.8
115°	207.6	222.9	273.4	309.0	320.1
117.5°	228.4	239.3	287.9	321.0	333.7
120°	247.9	254.1	299.8	332.2	344.2
122.5°	267.6	268.3	311.9	344.0	354.4
125°	284.7	284.6	323.5	354.8	364.6
127.5°	302.7	301.5	335.0	363.2	374.0
130°	318.5	317.2	343.7	372.5	382.0
132.5°	334.3	333.4	353.8	381.2	390.3
135°	348.6	348.2	360.7	386.8	397.0
137.5°	362.7	361.1	369.1	393.6	401.3
140°	376.4	375.5	377.8	399.5	407.7
142.5°	387.2	388.6	387.3	405.5	411.8
145°	399.8	399.3	399.3	409.1	416.3
147.5°	409.7	410.2	409.9	411.8	418.5
150°	420.6	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)