

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000941

Luminaire Tested: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000941
REPORT IS A COMBINATION OF REPORTS P995555 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6371.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000941

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000941

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71		
1	101	96	91	87	95	91	87	83	81	78	75	73	70	68	64	63	61	57		
2	91	83	76	70	86	79	72	67	70	65	61	63	59	56	56	53	50	46		
3	83	73	64	58	78	69	61	55	62	56	51	55	50	46	49	45	42	39		
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	39	36	33		
5	70	57	48	41	65	54	46	40	49	42	37	44	38	34	39	35	31	28		
6	64	51	42	36	60	49	40	35	44	37	32	39	34	30	35	31	27	24		
7	59	46	37	31	56	44	36	30	40	33	28	36	30	26	32	28	24	22		
8	55	42	34	28	52	40	32	27	36	30	25	33	27	23	30	25	21	19		
9	51	38	30	25	48	37	29	24	33	27	22	30	25	21	27	23	19	17		
10	48	35	27	22	45	34	26	22	31	24	20	28	23	19	25	21	17	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11702	11702	11702
5°	11735	11398	11418
10°	11659	11173	11142
15°	11550	10922	10829
20°	11388	10649	10526
25°	11206	10347	10199
30°	11008	10049	9865
35°	10786	9744	9569
40°	10607	9452	9261
45°	10343	9176	8989
50°	10116	8864	8702
55°	9883	8564	8372
60°	9521	8190	8061
65°	9124	7787	7687
70°	8641	7325	7256
75°	7965	6812	6843
80°	7206	6291	6412
85°	6200	5766	6064

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10343 cd/sqm

TEST NUMBER: P1000941

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	2.1
10°-20°	389.6	6.1
20°-30°	589.1	9.2
30°-40°	712.7	11.2
40°-50°	753.4	11.8
50°-60°	709.1	11.1
60°-70°	588.4	9.2
70°-80°	412.9	6.5
80°-90°	233.8	3.7
90°-100°	154.4	2.4
100°-110°	207.0	3.2
110°-120°	268.1	4.2
120°-130°	291.7	4.6
130°-140°	287.4	4.5
140°-150°	256.4	4.0
150°-160°	204.1	3.2
160°-170°	131.6	2.1
170°-180°	45.4	0.7
0°-30°	1114.7	17.5
0°-40°	1827.4	28.7
0°-60°	3289.9	51.6
0°-90°	4525.0	71.0
90°-120°	629.5	9.9
90°-150°	1465.0	23.0
90°-180°	1846.0	29.0
0°-180°	6371.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1435	1435	1435	1435	1435	
5°	1437	1432	1421	1434	1432	136
15°	1377	1379	1374	1388	1387	388
25°	1260	1270	1274	1292	1294	580
35°	1102	1122	1138	1160	1165	690
45°	919	950	980	1008	1016	710
55°	720	754	802	834	844	642
65°	498	550	604	644	657	494
75°	276	336	403	448	463	294
85°	85	153	225	273	289	89
90°	27	95	167	216	229	19
95°	40	81	148	193	208	41
105°	122	156	218	261	261	129
115°	210	226	277	313	324	208
125°	288	288	328	359	369	258
135°	353	353	365	392	402	273
145°	405	404	404	414	422	253
155°	442	443	442	443	442	204
165°	467	465	465	468	464	132
175°	477	475	476	479	474	45
180°	477	477	477	477	477	

TEST NUMBER: P1000941

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1441.6	1436.8	1423.9	1435.1	1433.5
5°	1436.8	1431.9	1420.7	1433.5	1431.9
7.5°	1427.1	1423.9	1414.3	1428.7	1427.1
10°	1414.3	1412.6	1404.6	1419.1	1417.5
12.5°	1396.6	1396.6	1391.8	1404.6	1404.6
15°	1377.3	1378.9	1374.1	1388.5	1386.9
17.5°	1351.6	1356.4	1354.8	1369.3	1367.6
20°	1324.3	1329.1	1330.7	1346.8	1346.8
22.5°	1293.7	1300.1	1303.4	1319.4	1322.6
25°	1260.0	1269.6	1274.4	1292.1	1293.7
27.5°	1223.0	1237.5	1243.9	1260.0	1261.6
30°	1186.0	1198.9	1210.2	1227.8	1231.0
32.5°	1145.9	1161.9	1174.8	1195.7	1198.9
35°	1102.5	1121.8	1137.8	1160.3	1165.2
37.5°	1059.1	1081.6	1100.9	1123.4	1128.2
40°	1017.3	1038.2	1060.7	1084.8	1091.2
42.5°	969.1	993.2	1020.5	1047.8	1052.7
45°	919.3	949.8	980.3	1007.7	1015.7
47.5°	872.7	903.2	938.5	965.9	975.5
50°	821.2	856.6	891.9	924.1	933.7
52.5°	769.8	805.2	846.9	879.1	888.7
55°	720.0	753.7	801.9	834.1	843.7
57.5°	663.7	705.5	752.1	790.7	798.7
60°	609.1	650.9	703.9	740.9	753.7
62.5°	556.1	602.7	655.7	692.7	705.5
65°	498.2	549.6	604.3	644.4	657.3
67.5°	443.6	498.2	556.1	596.2	609.1
70°	387.3	442.0	503.0	546.4	557.7
72.5°	332.7	388.9	454.8	496.6	509.5
75°	276.4	335.9	403.4	448.4	462.8
77.5°	223.4	286.1	356.8	401.8	417.8
80°	175.2	239.5	310.2	358.4	371.2
82.5°	127.0	194.5	265.2	315.0	329.5
85°	85.2	152.7	225.0	273.2	289.3
87.5°	53.0	118.9	189.6	236.2	250.7
90°	26.8	95.0	167.0	215.7	229.3
92.5°	29.5	85.0	157.0	204.1	216.9
95°	40.5	81.4	147.7	193.2	208.1
97.5°	56.8	111.2	139.7	183.2	198.0
100°	76.3	124.5	137.8	175.1	186.8
102.5°	99.8	139.4	204.8	166.3	179.1
105°	122.0	156.2	217.5	260.8	260.8
107.5°	145.2	173.5	232.2	274.2	286.9
110°	167.1	190.7	249.0	286.8	300.6

TEST NUMBER: P1000941

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.3	209.7	263.5	298.5	312.8
115°	210.2	225.8	276.9	313.0	324.2
117.5°	231.3	242.4	291.7	325.0	337.9
120°	251.1	257.5	303.7	336.5	348.7
122.5°	271.1	271.8	315.9	348.5	359.0
125°	288.4	288.3	327.8	359.3	369.4
127.5°	306.6	305.4	339.4	367.9	378.8
130°	322.5	321.3	348.1	377.4	387.0
132.5°	338.6	337.7	358.4	386.1	395.4
135°	353.1	352.7	365.4	391.9	402.2
137.5°	367.4	365.8	373.9	398.8	406.5
140°	381.3	380.4	382.7	404.7	413.0
142.5°	392.2	393.6	392.4	410.8	417.2
145°	405.0	404.5	404.5	414.5	421.7
147.5°	415.0	415.6	415.2	417.2	423.9
150°	426.1	425.9	425.6	425.6	425.9
152.5°	433.8	434.8	434.1	434.8	434.5
155°	442.3	442.7	441.6	443.1	442.0
157.5°	449.8	449.8	448.4	450.2	448.4
160°	456.3	455.2	454.8	457.0	454.8
162.5°	462.0	460.5	460.2	462.3	459.8
165°	466.6	464.8	464.8	467.7	464.5
167.5°	470.5	468.8	468.4	471.6	468.0
170°	473.8	471.6	472.0	474.8	471.3
172.5°	475.9	473.8	474.1	477.0	473.0
175°	477.3	475.2	475.5	478.8	474.5
177.5°	478.4	475.9	476.6	479.5	475.2
180°	477.3	477.3	477.3	477.3	477.3

(END OF REPORT)