

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000943

Luminaire Tested: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000943
REPORT IS A COMBINATION OF REPORTS P995558 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6541.0 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000943

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000943

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49
4	79	68	59	53	75	65	57	52	60	53	48	55	50	45	50	46	43
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1000943

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.9
10°-20°	525.8	8.0
20°-30°	773.8	11.8
30°-40°	899.5	13.8
40°-50°	899.4	13.8
50°-60°	786.6	12.0
60°-70°	584.0	8.9
70°-80°	331.4	5.1
80°-90°	95.9	1.5
90°-100°	15.7	0.2
100°-110°	103.0	1.6
110°-120°	196.7	3.0
120°-130°	249.7	3.8
130°-140°	267.1	4.1
140°-150°	249.8	3.8
150°-160°	201.4	3.1
160°-170°	129.9	2.0
170°-180°	44.8	0.7
0°-30°	1486.2	22.7
0°-40°	2385.7	36.5
0°-60°	4071.7	62.2
0°-90°	5083.0	77.7
90°-120°	315.4	4.8
90°-150°	1081.9	16.5
90°-180°	1458.0	22.3
0°-180°	6541.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	1	5	8	10	11	7
95°	19	7	8	10	10	24
105°	106	108	110	113	100	111
115°	198	199	199	200	200	195
125°	278	280	279	280	280	249
135°	345	345	346	347	348	266
145°	398	399	399	400	400	249
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1000943

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	1.1	4.9	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.2
97.5°	37.0	44.8	7.8	9.5	9.9
100°	57.8	64.1	15.5	9.5	9.9
102.5°	81.1	85.3	89.5	10.2	10.2
105°	106.1	108.2	110.0	113.1	100.4
107.5°	129.0	130.0	132.5	134.3	135.7
110°	152.2	153.3	155.4	156.1	157.2



TEST NUMBER: P1000943

CATALOG NUMBER: SA4XXDIP-B1195D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	176.9	177.6	177.3	178.7
115°	198.1	199.1	198.8	199.5	199.5
117.5°	218.9	220.3	221.3	221.0	221.0
120°	240.0	241.4	241.1	241.8	241.1
122.5°	259.7	260.4	261.1	261.5	260.8
125°	278.4	279.8	279.1	280.2	280.5
127.5°	296.4	296.7	298.5	298.1	297.8
130°	313.7	314.0	315.1	315.4	315.4
132.5°	329.5	330.2	331.6	332.0	331.6
135°	345.4	345.0	346.4	347.1	347.8
137.5°	359.5	359.5	361.2	361.9	361.6
140°	373.2	373.9	374.6	375.7	376.0
142.5°	385.6	387.0	387.3	388.0	388.0
145°	398.2	399.3	399.3	399.6	400.4
147.5°	408.1	410.2	409.9	410.2	410.6
150°	419.0	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)