

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999862

Luminaire Tested: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999862
REPORT IS A COMBINATION OF REPORTS P988417 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5073.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999862

CATALOG NUMBER: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999862

CATALOG NUMBER: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	62	54	48	65	56	49	45	45	40	37	35	32	29	25	23	22
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	48	37	30	25	44	34	27	23	28	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12527	11900	11810
10°	12404	11285	10913
15°	12233	10561	9890
20°	12007	9738	8820
25°	11778	8893	7840
30°	11467	8069	6770
35°	11163	7240	5852
40°	10854	6424	4907
45°	10494	5582	4082
50°	10123	4772	3322
55°	9737	3961	2638
60°	9285	3168	1996
65°	8770	2414	1623
70°	8146	1751	1290
75°	7362	1336	986
80°	6219	904	662
85°	4337	415	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10494 cd/sqm

TEST NUMBER: P999862

CATALOG NUMBER: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	1.5
10°-20°	203.3	4.0
20°-30°	285.4	5.6
30°-40°	311.1	6.1
40°-50°	285.9	5.6
50°-60°	224.6	4.4
60°-70°	146.2	2.9
70°-80°	75.2	1.5
80°-90°	22.4	0.4
90°-100°	200.3	3.9
100°-110°	677.1	13.3
110°-120°	711.8	14.0
120°-130°	585.3	11.5
130°-140°	470.3	9.3
140°-150°	355.3	7.0
150°-160°	249.8	4.9
160°-170°	147.1	2.9
170°-180°	47.8	0.9
0°-30°	562.8	11.1
0°-40°	873.9	17.2
0°-60°	1384.4	27.3
0°-90°	1628.2	32.1
90°-120°	1589.2	31.3
90°-150°	3000.1	59.1
90°-180°	3445.0	67.9
0°-180°	5073.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	35
90°	1	13	32	31	31	4
95°	33	82	372	141	108	34
105°	116	175	704	1258	1071	123
115°	204	258	589	1216	1409	203
125°	285	337	566	985	1143	253
135°	334	399	560	828	947	258
145°	382	439	557	691	756	240
155°	434	469	541	611	636	200
165°	473	487	518	549	558	133
175°	493	494	498	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P999862

CATALOG NUMBER: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	1.0	12.8	32.3	30.9	31.4
92.5°	14.3	45.2	146.3	67.5	58.0
95°	33.3	81.7	372.5	140.6	108.3
97.5°	49.4	107.8	607.2	282.2	181.5
100°	73.2	132.1	750.6	562.0	340.2
102.5°	95.0	153.9	755.4	950.2	663.2
105°	115.9	174.8	704.1	1258.5	1070.8
107.5°	138.7	195.7	656.6	1370.1	1345.4
110°	161.5	217.1	624.3	1352.0	1457.6

TEST NUMBER: P999862

CATALOG NUMBER: SA2XXRDIP-B485D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.4	237.6	603.4	1290.8	1455.7
115°	204.3	258.0	589.1	1215.8	1409.1
117.5°	227.1	278.4	581.5	1144.0	1338.8
120°	248.0	298.4	574.8	1079.8	1271.3
122.5°	267.9	318.8	571.0	1030.0	1201.0
125°	285.0	337.3	566.3	984.8	1143.0
127.5°	299.3	354.9	563.4	946.4	1088.9
130°	311.7	370.6	561.5	907.4	1044.2
132.5°	323.1	385.8	560.6	867.0	997.7
135°	334.5	399.1	559.6	827.6	947.3
137.5°	344.9	410.4	559.6	787.6	898.9
140°	357.3	421.0	558.7	752.5	848.5
142.5°	369.6	429.5	558.7	718.8	798.1
145°	382.0	439.0	556.8	691.2	756.3
147.5°	395.3	446.6	553.9	667.0	719.3
150°	408.6	454.2	551.1	646.2	687.0
152.5°	421.9	461.8	546.3	628.6	659.4
155°	434.2	468.9	540.6	611.4	635.7
157.5°	444.7	474.6	534.9	595.3	614.8
160°	455.1	480.3	529.2	579.2	594.8
162.5°	465.6	484.6	524.5	563.9	575.8
165°	473.2	487.4	517.8	549.2	557.7
167.5°	479.8	490.3	512.1	535.9	540.6
170°	486.5	491.7	507.4	523.6	525.4
172.5°	490.3	493.2	501.7	512.6	513.1
175°	493.1	493.6	497.9	504.0	502.6
177.5°	495.0	494.1	494.1	497.9	495.0
180°	494.1	494.1	494.1	494.1	494.1

(END OF REPORT)