

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999868

Luminaire Tested: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999868
REPORT IS A COMBINATION OF REPORTS P988423 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6488.8 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999868

CATALOG NUMBER: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999868

CATALOG NUMBER: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17795	17795	17795
5°	17824	16930	16805
10°	17648	16056	15527
15°	17405	15027	14070
20°	17086	13854	12548
25°	16757	12653	11155
30°	16314	11481	9633
35°	15883	10299	8327
40°	15442	9141	6981
45°	14932	7943	5807
50°	14403	6788	4728
55°	13853	5634	3754
60°	13212	4507	2840
65°	12478	3435	2309
70°	11589	2492	1836
75°	10472	1901	1401
80°	8854	1286	942
85°	6173	588	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14932 cd/sqm

TEST NUMBER: P999868

CATALOG NUMBER: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	1.6
10°-20°	289.2	4.5
20°-30°	406.1	6.3
30°-40°	442.6	6.8
40°-50°	406.8	6.3
50°-60°	319.5	4.9
60°-70°	208.0	3.2
70°-80°	107.1	1.6
80°-90°	31.2	0.5
90°-100°	242.6	3.7
100°-110°	820.3	12.6
110°-120°	862.2	13.3
120°-130°	709.0	10.9
130°-140°	569.7	8.8
140°-150°	430.4	6.6
150°-160°	302.6	4.7
160°-170°	178.2	2.7
170°-180°	58.0	0.9
0°-30°	800.7	12.3
0°-40°	1243.3	19.2
0°-60°	1969.7	30.4
0°-90°	2315.8	35.7
90°-120°	1925.1	29.7
90°-150°	3634.3	56.0
90°-180°	4173.0	64.3
0°-180°	6488.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1124	1119	1106	1115	1112	107
15°	1069	1058	1024	1004	994	301
25°	971	938	871	829	814	446
35°	836	784	695	631	608	523
45°	684	616	509	436	412	528
55°	520	440	331	270	250	465
65°	351	269	177	142	139	348
75°	187	116	81	74	73	198
85°	44	22	19	19	19	50
90°	1	16	39	37	38	5
95°	40	99	451	170	131	42
105°	140	212	853	1524	1297	149
115°	248	312	714	1473	1707	245
125°	345	409	686	1193	1385	307
135°	405	483	678	1003	1148	313
145°	463	532	674	837	916	290
155°	526	568	655	741	770	242
165°	573	590	627	665	676	162
175°	597	598	603	611	609	57
180°	598	598	598	598	598	

TEST NUMBER: P999868

CATALOG NUMBER: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1124.2	1124.2	1124.2	1124.2	1124.2
2.5°	1129.3	1124.2	1113.0	1123.2	1121.1
5°	1124.2	1119.1	1105.9	1115.0	1112.0
7.5°	1115.0	1108.9	1094.7	1098.7	1093.6
10°	1102.8	1095.7	1075.3	1072.3	1066.2
12.5°	1087.5	1078.4	1050.9	1044.8	1033.6
15°	1069.2	1058.0	1023.5	1004.1	993.9
17.5°	1047.9	1031.6	988.9	966.5	950.2
20°	1023.5	1003.1	952.2	926.8	904.4
22.5°	997.0	973.6	914.6	880.0	864.7
25°	970.6	938.0	870.9	829.1	813.9
27.5°	939.0	904.4	830.2	782.3	758.9
30°	905.4	866.8	785.4	733.5	706.0
32.5°	872.9	826.1	742.7	681.6	656.2
35°	836.3	784.4	694.8	630.8	608.4
37.5°	800.7	744.7	650.1	579.9	554.5
40°	763.0	702.0	603.3	531.1	504.6
42.5°	724.4	659.2	556.5	481.2	455.8
45°	683.7	615.5	508.7	436.4	412.0
47.5°	645.0	572.8	462.9	390.7	368.3
50°	602.3	530.0	418.1	347.9	326.6
52.5°	560.6	484.3	375.4	308.3	288.9
55°	519.9	440.5	330.6	269.6	250.3
57.5°	478.2	396.8	291.0	234.0	217.7
60°	435.4	354.0	249.3	197.4	181.1
62.5°	393.7	312.3	213.6	164.8	156.7
65°	351.0	268.6	177.0	142.4	139.4
67.5°	310.3	227.9	142.4	125.1	122.1
70°	267.6	188.2	118.0	107.8	103.8
72.5°	226.9	151.6	98.7	90.5	88.5
75°	187.2	116.0	81.4	74.3	73.2
77.5°	147.5	82.4	64.1	60.0	58.0
80°	110.9	59.0	48.8	44.8	44.8
82.5°	77.3	39.7	33.6	31.5	31.5
85°	43.7	22.4	19.3	19.3	19.3
87.5°	16.3	8.1	8.1	7.1	7.1
90°	1.2	15.6	39.1	37.4	38.0
92.5°	17.3	54.6	177.3	81.7	70.2
95°	40.3	99.0	451.2	170.4	131.2
97.5°	59.9	130.6	735.5	341.8	219.8
100°	88.6	160.0	909.3	680.8	412.1
102.5°	115.1	186.4	915.1	1151.0	803.4
105°	140.4	211.8	852.9	1524.5	1297.2
107.5°	168.0	237.1	795.3	1659.8	1629.8
110°	195.7	263.0	756.2	1637.9	1765.7

TEST NUMBER: P999868

CATALOG NUMBER: SA2XXRDIP-B675D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.0	287.8	730.9	1563.6	1763.4
115°	247.5	312.5	713.6	1472.7	1707.0
117.5°	275.1	337.2	704.4	1385.8	1621.8
120°	300.4	361.4	696.4	1308.2	1540.1
122.5°	324.6	386.2	691.8	1247.7	1454.9
125°	345.3	408.6	686.0	1193.1	1384.7
127.5°	362.6	429.9	682.6	1146.4	1319.1
130°	377.5	448.9	680.2	1099.2	1265.0
132.5°	391.3	467.3	679.1	1050.3	1208.6
135°	405.2	483.4	677.9	1002.6	1147.6
137.5°	417.8	497.2	677.9	954.2	1088.9
140°	432.8	509.9	676.8	911.6	1027.9
142.5°	447.7	520.2	676.8	870.8	966.9
145°	462.7	531.8	674.5	837.4	916.2
147.5°	478.8	541.0	671.0	808.0	871.3
150°	494.9	550.2	667.6	782.6	832.2
152.5°	511.0	559.4	661.8	761.4	798.8
155°	526.0	568.0	654.9	740.6	770.0
157.5°	538.7	574.9	648.0	721.1	744.7
160°	551.3	581.8	641.1	701.6	720.5
162.5°	564.0	587.0	635.4	683.1	697.5
165°	573.2	590.4	627.3	665.3	675.6
167.5°	581.3	593.9	620.4	649.2	654.9
170°	589.3	595.6	614.6	634.2	636.5
172.5°	593.9	597.4	607.7	621.0	621.5
175°	597.4	598.0	603.1	610.6	608.9
177.5°	599.7	598.5	598.5	603.1	599.7
180°	598.5	598.5	598.5	598.5	598.5

(END OF REPORT)