

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001000

Luminaire Tested: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001000
REPORT IS A COMBINATION OF REPORTS P995616 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7198.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001000

CATALOG NUMBER: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001000

CATALOG NUMBER: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	93	88	84	81	77	74	72	67	65	63	58	56	54
2	90	82	75	69	84	77	71	65	67	62	58	58	55	51	50	47	45
3	82	71	63	57	76	67	60	54	59	53	48	51	47	43	44	40	38
4	75	63	54	48	69	59	51	46	52	46	41	45	40	36	39	35	32
5	68	56	47	41	64	53	45	39	46	40	35	40	35	31	35	31	28
6	63	50	41	35	59	47	39	34	42	35	30	36	31	27	32	27	24
7	58	45	37	31	54	43	35	29	38	31	27	33	28	24	29	25	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	33	26	21	29	23	19	26	21	17	23	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11588	11588	11588
5°	11620	11286	11307
10°	11545	11064	11033
15°	11437	10814	10723
20°	11277	10544	10422
25°	11096	10246	10099
30°	10901	9951	9769
35°	10681	9649	9474
40°	10502	9359	9170
45°	10241	9087	8901
50°	10018	8778	8617
55°	9786	8480	8290
60°	9428	8109	7982
65°	9034	7709	7612
70°	8556	7253	7184
75°	7887	6745	6776
80°	7136	6228	6350
85°	6134	5709	6003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10241 cd/sqm

TEST NUMBER: P1001000

CATALOG NUMBER: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.9
10°-20°	385.8	5.4
20°-30°	583.3	8.1
30°-40°	705.7	9.8
40°-50°	746.0	10.4
50°-60°	702.1	9.8
60°-70°	582.6	8.1
70°-80°	408.9	5.7
80°-90°	232.1	3.2
90°-100°	162.4	2.3
100°-110°	267.7	3.7
110°-120°	385.4	5.4
120°-130°	441.1	6.1
130°-140°	447.4	6.2
140°-150°	406.1	5.6
150°-160°	324.9	4.5
160°-170°	209.5	2.9
170°-180°	72.2	1.0
0°-30°	1103.7	15.3
0°-40°	1809.5	25.1
0°-60°	3257.6	45.3
0°-90°	4481.2	62.3
90°-120°	815.6	11.3
90°-150°	2110.2	29.3
90°-180°	2717.0	37.7
0°-180°	7198.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1423	1418	1407	1420	1418	135
15°	1364	1365	1361	1375	1373	384
25°	1248	1257	1262	1279	1281	575
35°	1092	1111	1127	1149	1154	684
45°	910	940	971	998	1006	704
55°	713	746	794	826	836	635
65°	493	544	598	638	651	489
75°	274	333	399	444	458	291
85°	84	151	223	270	286	88
90°	27	97	170	220	234	19
95°	52	85	151	197	212	55
105°	185	221	282	327	320	195
115°	329	345	395	432	443	324
125°	455	456	495	527	537	407
135°	560	560	573	600	610	432
145°	644	644	644	654	662	402
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1001000

CATALOG NUMBER: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.1	1421.1	1421.1	1421.1	1421.1
2.5°	1427.4	1422.7	1409.9	1421.1	1419.5
5°	1422.7	1417.9	1406.7	1419.5	1417.9
7.5°	1413.1	1409.9	1400.4	1414.7	1413.1
10°	1400.4	1398.8	1390.8	1405.2	1403.6
12.5°	1382.9	1382.9	1378.1	1390.8	1390.8
15°	1363.8	1365.4	1360.6	1374.9	1373.3
17.5°	1338.3	1343.1	1341.5	1355.8	1354.2
20°	1311.3	1316.0	1317.6	1333.5	1333.5
22.5°	1281.0	1287.4	1290.6	1306.5	1309.7
25°	1247.6	1257.2	1261.9	1279.4	1281.0
27.5°	1211.0	1225.3	1231.7	1247.6	1249.2
30°	1174.4	1187.1	1198.3	1215.8	1219.0
32.5°	1134.6	1150.5	1163.3	1184.0	1187.1
35°	1091.7	1110.8	1126.7	1148.9	1153.7
37.5°	1048.7	1071.0	1090.1	1112.3	1117.1
40°	1007.3	1028.0	1050.3	1074.2	1080.5
42.5°	959.6	983.4	1010.5	1037.6	1042.3
45°	910.2	940.5	970.7	997.8	1005.7
47.5°	864.1	894.3	929.3	956.4	965.9
50°	813.2	848.2	883.2	915.0	924.6
52.5°	762.3	797.3	838.6	870.5	880.0
55°	712.9	746.3	794.1	825.9	835.5
57.5°	657.2	698.6	744.7	782.9	790.9
60°	603.1	644.5	697.0	733.6	746.3
62.5°	550.6	596.8	649.3	685.9	698.6
65°	493.3	544.2	598.3	638.1	650.9
67.5°	439.2	493.3	550.6	590.4	603.1
70°	383.5	437.6	498.1	541.1	552.2
72.5°	329.4	385.1	450.3	491.7	504.5
75°	273.7	332.6	399.4	444.0	458.3
77.5°	221.2	283.3	353.3	397.8	413.7
80°	173.5	237.1	307.1	354.9	367.6
82.5°	125.7	192.6	262.6	311.9	326.2
85°	84.3	151.2	222.8	270.5	286.4
87.5°	52.5	117.8	187.8	233.9	248.2
90°	27.2	97.1	170.0	219.6	233.5
92.5°	32.4	87.0	159.9	207.9	220.6
95°	52.0	85.1	150.9	197.3	212.2
97.5°	78.8	137.4	143.0	187.2	202.1
100°	110.7	162.3	145.9	179.2	190.9
102.5°	148.2	190.0	257.4	170.9	183.6
105°	185.4	220.6	282.3	327.2	319.5
107.5°	222.3	251.1	310.8	353.4	366.8
110°	258.2	282.2	341.4	379.1	393.5



TEST NUMBER: P1001000

CATALOG NUMBER: SA4XXDIP-B1195D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.0	315.5	369.2	403.7	418.7
115°	328.9	345.0	395.4	431.5	442.6
117.5°	362.5	374.3	423.7	456.7	469.4
120°	395.1	402.0	447.7	480.6	492.2
122.5°	426.9	428.0	472.1	504.4	514.5
125°	455.4	456.1	494.7	526.7	536.7
127.5°	484.4	483.4	518.0	546.0	556.7
130°	510.6	509.6	536.7	566.0	575.5
132.5°	536.2	535.8	557.1	584.7	593.7
135°	560.2	559.6	573.0	599.6	610.3
137.5°	582.9	581.3	590.6	615.5	622.9
140°	605.1	604.6	607.4	629.8	638.3
142.5°	623.4	625.7	624.6	643.3	649.7
145°	643.9	644.0	644.0	654.0	661.6
147.5°	659.8	661.6	661.0	663.2	670.2
150°	677.4	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)