

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999896

Luminaire Tested: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999896
REPORT IS A COMBINATION OF REPORTS P988453 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6156.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	35	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	31	31	26
4	74	64	57	51	67	59	52	47	49	44	41	40	36	34	31	29	27	27	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	24	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	22	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	22	20	20	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	18	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	16	16	14
10	48	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22478	22478	22478	22478
5°	22530	23875	22609	19073
10°	22282	25236	22441	15751
15°	21799	25244	22168	11832
20°	21217	20866	21680	9762
25°	20512	13039	20956	8305
30°	19613	8348	20146	7150
35°	18517	6415	19117	6118
40°	17296	5393	18035	5351
45°	15991	4591	16660	4492
50°	14654	3900	15338	3886
55°	13174	3390	13883	3345
60°	11859	2584	12487	2553
65°	10629	1944	11262	2206
70°	9272	1553	10000	1797
75°	7837	1191	8559	1361
80°	6227	809	6698	891
85°	4322	419	4746	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 20563 cd/sqm

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.7	2.2
10°-20°	376.0	6.1
20°-30°	483.9	7.9
30°-40°	459.0	7.5
40°-50°	393.4	6.4
50°-60°	299.6	4.9
60°-70°	188.9	3.1
70°-80°	94.3	1.5
80°-90°	28.0	0.5
90°-100°	81.8	1.3
100°-110°	260.1	4.2
110°-120°	445.1	7.2
120°-130°	585.4	9.5
130°-140°	657.1	10.7
140°-150°	644.4	10.5
150°-160°	540.5	8.8
160°-170°	358.5	5.8
170°-180°	125.3	2.0
0°-30°	994.5	16.2
0°-40°	1453.6	23.6
0°-60°	2146.6	34.9
0°-90°	2457.8	39.9
90°-120°	787.1	12.8
90°-150°	2673.9	43.4
90°-180°	3698.0	60.1
0°-180°	6156.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1420	1420	1420	1420	1420	
5°	1421	1580	1426	1262	1421	135
15°	1339	1783	1362	836	1339	377
25°	1188	951	1214	606	1188	546
35°	975	469	1007	447	975	610
45°	732	326	763	319	732	565
55°	494	226	521	223	494	446
65°	299	117	317	133	299	297
75°	140	62	153	71	140	152
85°	31	18	34	19	31	35
90°	1	38	1	38	1	6
95°	58	69	58	69	58	65
105°	240	248	240	248	240	253
115°	446	446	446	446	446	442
125°	650	652	650	652	650	581
135°	840	851	840	851	840	650
145°	1020	1031	1020	1031	1020	637
155°	1166	1175	1166	1175	1166	537
165°	1269	1270	1269	1270	1269	358
175°	1320	1316	1320	1316	1320	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1428.9	1434.8	1437.8	1441.7	1450.6	1456.5	1465.4	1467.4	1466.4	1470.4	1459.5
5°	1421.0	1433.9	1445.7	1455.6	1471.4	1481.2	1492.1	1504.9	1507.9	1522.7	1513.8
7.5°	1410.2	1428.9	1445.7	1465.4	1489.1	1501.9	1518.7	1538.5	1547.3	1565.1	1570.0
10°	1392.4	1419.1	1447.7	1468.4	1501.0	1523.7	1539.4	1571.0	1591.7	1618.4	1614.4
12.5°	1363.8	1398.3	1436.8	1471.4	1513.8	1528.6	1558.2	1590.8	1617.4	1642.1	1663.8
15°	1339.1	1378.6	1421.0	1463.5	1511.8	1539.4	1569.0	1611.5	1640.1	1683.5	1702.3
17.5°	1305.6	1355.9	1406.2	1453.6	1510.8	1542.4	1578.9	1620.4	1662.8	1704.2	1719.0
20°	1271.0	1325.3	1379.6	1443.7	1508.9	1539.4	1576.9	1628.3	1669.7	1702.3	1702.3
22.5°	1229.6	1295.7	1357.9	1419.1	1490.1	1534.5	1573.0	1633.2	1662.8	1669.7	1643.1
25°	1188.1	1254.3	1322.3	1398.3	1479.2	1518.7	1562.1	1618.4	1628.3	1600.6	1531.5
27.5°	1138.8	1212.8	1289.8	1371.7	1456.5	1505.9	1545.4	1582.9	1564.1	1490.1	1382.5
30°	1088.5	1168.4	1255.2	1333.2	1435.8	1481.2	1514.8	1525.6	1466.4	1346.0	1206.9
32.5°	1036.2	1114.1	1205.9	1299.6	1403.3	1446.7	1468.4	1439.8	1331.2	1179.3	1009.5
35°	975.0	1062.8	1158.5	1256.2	1358.9	1391.4	1404.2	1334.2	1195.0	998.7	829.9
37.5°	919.7	1007.5	1110.2	1209.8	1309.5	1327.3	1314.4	1204.9	1028.3	833.9	669.1
40°	854.6	948.3	1049.0	1160.5	1242.4	1247.3	1215.8	1073.7	854.6	672.0	570.4
42.5°	794.4	889.1	989.8	1103.3	1165.4	1148.7	1106.2	919.7	713.5	579.3	497.4
45°	732.2	822.0	930.6	1031.2	1075.6	1036.2	972.0	773.7	599.0	498.3	435.2
47.5°	672.0	755.9	863.5	960.2	968.1	923.7	847.7	648.3	519.1	438.1	386.8
50°	612.8	696.7	797.4	877.3	869.4	808.2	722.4	563.5	451.0	386.8	344.4
52.5°	553.6	629.6	727.3	790.4	756.9	697.7	612.8	477.6	393.7	337.5	304.9
55°	494.4	565.4	649.3	701.6	648.3	580.3	520.1	409.5	341.4	296.0	271.4
57.5°	445.1	501.3	578.3	609.9	545.7	492.4	440.1	352.3	296.0	263.5	234.9
60°	390.8	442.1	505.3	524.0	457.9	414.5	370.1	298.0	253.6	225.0	206.2
62.5°	344.4	386.8	435.2	435.2	377.0	344.4	310.8	249.7	213.2	190.5	181.6
65°	299.0	329.6	364.1	360.2	310.8	282.2	255.6	206.2	178.6	162.8	153.9
67.5°	254.6	278.3	301.0	287.2	251.6	227.0	202.3	166.8	148.0	137.2	125.3
70°	214.1	232.9	244.7	231.9	196.4	175.7	157.9	134.2	119.4	105.6	98.7
72.5°	179.6	187.5	191.4	175.7	146.0	134.2	121.4	104.6	91.8	84.9	82.9
75°	140.1	147.0	144.1	132.2	107.6	98.7	88.8	77.0	74.0	70.1	68.1
77.5°	109.5	109.5	104.6	93.7	77.0	70.1	66.1	60.2	57.2	56.2	54.3
80°	78.0	77.0	74.0	62.2	52.3	48.4	48.4	44.4	43.4	41.4	41.4
82.5°	51.3	51.3	47.4	37.5	34.5	33.6	32.6	30.6	30.6	29.6	29.6
85°	30.6	28.6	23.7	20.7	19.7	19.7	18.7	17.8	18.7	17.8	17.8
87.5°	13.8	10.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
90°	1.1	4.1	7.1	10.0	13.0	14.5	17.2	22.7	28.2	33.6	39.1
92.5°	24.6	26.6	28.6	30.5	32.5	33.5	33.6	33.9	34.1	34.4	34.6
95°	58.0	60.5	63.0	65.5	68.0	69.2	69.4	69.9	70.4	70.9	71.4
97.5°	97.1	99.3	101.6	103.8	106.1	107.2	107.7	108.7	109.6	110.6	111.6
100°	141.8	143.8	145.8	147.7	149.7	150.7	151.1	151.8	152.5	153.3	154.0
102.5°	188.6	190.1	191.6	193.1	194.6	195.3	195.8	196.8	197.8	198.8	199.8
105°	240.0	240.7	241.5	242.2	242.9	243.3	243.6	244.1	244.6	245.1	245.6
107.5°	291.3	292.3	293.3	294.3	295.3	295.8	295.8	295.8	295.8	295.8	295.8
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	394.0	395.5	397.0	398.5	400.0	400.7	400.6	400.3	400.1	399.8	399.6
115°	446.5	448.0	449.5	451.0	452.5	453.2	453.0	452.5	452.0	451.5	451.0
117.5°	499.0	501.0	503.0	504.9	506.9	507.9	507.3	506.0	504.8	503.5	502.3
120°	551.4	553.4	555.4	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4
122.5°	599.4	601.9	604.4	606.9	609.4	610.6	610.0	608.7	607.5	606.2	605.0
125°	649.7	651.9	654.1	656.4	658.6	659.7	659.3	658.6	657.9	657.1	656.4
127.5°	698.8	701.5	704.3	707.0	709.7	711.1	710.6	709.6	708.6	707.6	706.6
130°	744.6	747.8	751.0	754.3	757.5	759.1	758.8	758.3	757.8	757.3	756.8
132.5°	795.9	798.4	800.9	803.4	805.9	807.1	807.2	807.5	807.7	808.0	808.2
135°	840.5	843.2	846.0	848.7	851.4	852.8	853.1	853.6	854.1	854.6	855.1
137.5°	889.7	891.9	894.1	896.4	898.6	899.7	899.9	900.4	900.9	901.4	901.9
140°	933.2	935.4	937.6	939.9	942.1	943.2	943.8	945.1	946.3	947.6	948.8
142.5°	977.9	980.1	982.3	984.6	986.8	987.9	988.3	989.0	989.7	990.5	991.2
145°	1020.3	1022.0	1023.8	1025.5	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8
147.5°	1058.2	1060.4	1062.7	1064.9	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7
150°	1097.3	1098.8	1100.3	1101.8	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5
152.5°	1131.9	1133.4	1134.9	1136.4	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2
155°	1166.5	1167.2	1168.0	1168.7	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2
157.5°	1196.6	1197.1	1197.6	1198.1	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1
160°	1223.4	1223.9	1224.4	1224.9	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8
162.5°	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1
165°	1269.2	1269.0	1268.7	1268.5	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1
167.5°	1288.2	1287.4	1286.7	1285.9	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8
170°	1302.7	1301.9	1301.2	1300.4	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2
172.5°	1312.7	1312.0	1311.2	1310.5	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3
175°	1320.5	1319.8	1319.0	1318.3	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0
177.5°	1325.0	1324.3	1323.5	1322.8	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1470.4	1472.3	1475.3	1489.1	1491.1	1495.0	1493.1	1493.1	1494.0	1492.1	1493.1
5°	1533.5	1536.5	1551.3	1568.1	1572.0	1568.1	1573.0	1579.9	1579.9	1579.9	1577.9
7.5°	1592.7	1603.6	1620.4	1645.0	1650.0	1654.9	1663.8	1657.9	1659.8	1668.7	1665.8
10°	1650.0	1665.8	1684.5	1705.2	1716.1	1723.0	1726.9	1735.8	1756.5	1732.9	1741.7
12.5°	1704.2	1726.9	1746.7	1769.4	1777.3	1786.1	1789.1	1797.0	1797.0	1796.0	1802.9
15°	1739.8	1760.5	1778.3	1793.1	1795.0	1793.1	1791.1	1792.1	1795.0	1783.2	1790.1
17.5°	1747.7	1749.6	1755.6	1749.6	1750.6	1729.9	1718.1	1715.1	1687.5	1688.5	1711.1
20°	1709.2	1675.6	1666.7	1634.2	1614.4	1561.2	1559.2	1544.4	1486.2	1503.9	1500.0
22.5°	1603.6	1546.4	1470.4	1432.9	1414.1	1357.9	1314.4	1283.9	1263.1	1242.4	1233.5
25°	1464.4	1371.7	1264.1	1190.1	1179.3	1127.0	1047.0	1009.5	965.1	951.3	975.0
27.5°	1284.8	1164.4	1043.1	929.6	908.9	861.5	821.0	794.4	743.1	740.1	742.1
30°	1041.1	919.7	818.1	744.1	692.7	671.0	644.4	624.7	603.9	611.8	613.8
32.5°	855.6	740.1	645.4	605.9	582.2	568.4	545.7	532.9	524.0	521.0	520.1
35°	679.9	602.9	560.5	522.0	508.2	498.3	481.6	475.6	467.8	468.7	468.7
37.5°	582.2	518.1	486.5	466.8	453.9	449.0	438.1	432.2	427.3	425.3	428.3
40°	502.3	457.9	438.1	420.4	409.5	407.6	401.6	394.7	388.8	389.8	392.8
42.5°	444.1	418.4	394.7	380.9	373.0	370.1	365.1	360.2	360.2	357.2	356.2
45°	397.7	377.0	357.2	344.4	339.5	335.5	329.6	328.6	324.7	325.7	326.6
47.5°	356.2	339.5	324.7	311.8	306.9	305.9	300.0	296.0	296.0	295.1	294.1
50°	318.7	302.0	289.1	282.2	275.3	273.3	272.4	271.4	269.4	269.4	270.4
52.5°	288.2	271.4	261.5	255.6	251.6	249.7	249.7	248.7	248.7	248.7	247.7
55°	254.6	240.8	232.9	230.9	228.9	228.0	227.0	225.0	224.0	226.0	224.0
57.5°	223.0	218.1	211.2	209.2	204.3	204.3	201.3	199.3	197.4	199.3	199.3
60°	198.4	191.4	187.5	181.6	177.6	173.7	168.7	167.8	165.8	164.8	163.8
62.5°	172.7	166.8	156.9	148.0	142.1	138.2	136.2	135.2	135.2	134.2	134.2
65°	144.1	130.3	125.3	122.4	121.4	120.4	118.4	117.4	118.4	117.4	118.4
67.5°	112.5	110.5	107.6	105.6	104.6	103.6	103.6	102.6	102.6	102.6	102.6
70°	97.7	92.8	91.8	89.8	89.8	88.8	88.8	88.8	88.8	87.8	89.8
72.5°	80.9	78.0	77.0	76.0	76.0	76.0	75.0	75.0	75.0	74.0	75.0
75°	66.1	65.1	63.2	63.2	62.2	63.2	62.2	62.2	61.2	62.2	62.2
77.5°	53.3	52.3	51.3	51.3	50.3	50.3	50.3	50.3	50.3	50.3	51.3
80°	40.5	39.5	38.5	39.5	38.5	39.5	38.5	38.5	39.5	38.5	38.5
82.5°	29.6	28.6	28.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6
85°	17.8	16.8	16.8	17.8	16.8	17.8	16.8	16.8	16.8	17.8	17.8
87.5°	7.9	8.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.9
90°	38.6	38.1	37.6	37.1	36.8	36.9	37.2	37.5	37.7	38.0	37.7
92.5°	34.8	35.1	35.3	35.6	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.4	71.4	71.4	71.4	71.2	70.7	70.2	69.7	69.2	69.7
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	154.0	154.0	154.0	154.0	153.9	153.6	153.4	153.1	152.9	153.1
102.5°	200.0	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	200.0
105°	246.1	246.6	247.1	247.6	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.0	296.3	296.5	296.8	296.9	296.3	295.0	293.8	292.5	291.3	292.5
110°	347.2	347.2	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.8	344.6

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	398.9	398.1	397.4	396.7	396.3	396.0	395.5	395.0	394.5	394.0	394.5
115°	450.8	450.5	450.3	450.0	449.9	449.5	448.8	448.0	447.3	446.5	447.3
117.5°	501.6	500.8	500.1	499.4	499.0	498.6	497.9	497.1	496.4	495.6	496.4
120°	551.4	551.4	551.4	551.4	551.4	551.0	550.3	549.6	548.8	548.1	548.8
122.5°	604.3	603.5	602.8	602.1	601.7	601.4	600.9	600.4	599.9	599.4	599.9
125°	655.6	654.9	654.1	653.4	653.0	652.9	652.6	652.4	652.1	651.9	652.1
127.5°	705.6	704.6	703.6	702.6	702.1	701.7	701.0	700.3	699.5	698.8	699.5
130°	756.3	755.8	755.3	754.8	754.6	754.1	753.1	752.1	751.1	750.1	751.1
132.5°	807.0	805.7	804.5	803.2	802.6	802.2	801.5	800.7	800.0	799.2	800.0
135°	854.8	854.6	854.3	854.0	853.9	853.5	852.8	852.1	851.3	850.6	851.3
137.5°	901.7	901.4	901.2	900.9	900.8	900.3	899.3	898.4	897.4	896.4	897.4
140°	948.8	948.8	948.8	948.8	948.8	948.3	947.3	946.4	945.4	944.4	945.4
142.5°	991.5	991.7	992.0	992.3	992.4	991.9	990.9	989.9	988.9	987.9	988.9
145°	1035.0	1035.3	1035.5	1035.8	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4
147.5°	1073.2	1073.7	1074.2	1074.7	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5
150°	1109.2	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2
152.5°	1145.2	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2
155°	1174.4	1175.7	1176.9	1178.2	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2
157.5°	1202.8	1204.6	1206.3	1208.0	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5
160°	1228.3	1229.8	1231.3	1232.8	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0
162.5°	1250.8	1252.6	1254.3	1256.0	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5
165°	1269.8	1271.6	1273.3	1275.0	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5
167.5°	1286.5	1288.3	1290.0	1291.7	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3
170°	1299.9	1301.7	1303.4	1305.1	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8
172.5°	1310.0	1311.8	1313.5	1315.2	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9
175°	1316.7	1318.5	1320.2	1321.9	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6
177.5°	1320.9	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1497.0	1490.1	1488.1	1490.1	1488.1	1489.1	1482.2	1456.5	1463.5	1452.6	1458.5
5°	1581.9	1576.0	1563.1	1561.2	1559.2	1557.2	1547.3	1524.6	1515.8	1501.0	1500.0
7.5°	1662.8	1662.8	1652.9	1646.0	1637.1	1630.2	1617.4	1583.8	1570.0	1552.3	1542.4
10°	1742.7	1717.1	1727.9	1721.0	1699.3	1695.4	1671.7	1651.9	1625.3	1607.5	1591.7
12.5°	1800.0	1792.1	1782.2	1776.3	1770.4	1757.5	1741.7	1691.4	1677.6	1642.1	1624.3
15°	1798.0	1793.1	1796.0	1796.0	1794.0	1791.1	1778.3	1741.7	1718.1	1683.5	1652.9
17.5°	1701.3	1714.1	1726.9	1735.8	1755.6	1764.4	1776.3	1754.6	1739.8	1710.2	1677.6
20°	1532.5	1564.1	1601.6	1609.5	1627.3	1679.6	1703.3	1722.0	1727.9	1718.1	1691.4
22.5°	1297.7	1324.3	1415.1	1413.1	1438.8	1501.0	1570.0	1626.3	1670.7	1695.4	1685.5
25°	1016.4	1053.9	1102.3	1138.8	1222.7	1315.4	1401.3	1491.1	1568.1	1636.2	1652.9
27.5°	768.7	818.1	856.6	904.9	947.3	1056.9	1167.4	1307.5	1397.3	1526.6	1593.7
30°	621.7	644.4	682.9	705.6	726.3	810.2	935.5	1073.7	1231.6	1380.6	1496.0
32.5°	530.9	546.7	575.3	585.2	606.9	663.1	742.1	868.4	1031.2	1211.8	1363.8
35°	476.6	493.4	499.3	508.2	526.0	561.5	615.8	707.6	854.6	1031.2	1212.8
37.5°	430.3	439.1	455.9	461.8	467.8	494.4	530.9	595.1	692.7	837.8	1039.1
40°	397.7	402.6	411.5	416.4	420.4	439.1	471.7	515.1	587.2	697.7	883.2
42.5°	363.2	369.1	375.0	380.9	385.8	400.6	420.4	461.8	510.2	594.1	728.3
45°	329.6	333.5	340.5	344.4	351.3	363.2	380.9	409.5	453.0	506.2	614.8
47.5°	299.0	303.9	306.9	311.8	316.8	329.6	346.4	365.1	400.6	453.0	531.9
50°	271.4	277.3	281.2	282.2	286.2	298.0	311.8	332.6	355.3	395.7	464.8
52.5°	251.6	252.6	255.6	259.5	258.5	265.5	278.3	294.1	317.8	350.3	400.6
55°	228.9	231.9	233.9	234.9	234.9	240.8	247.7	262.5	281.2	307.9	350.3
57.5°	200.3	203.3	209.2	211.2	214.1	217.1	220.1	229.9	245.7	271.4	305.9
60°	170.7	172.7	178.6	182.6	184.5	192.4	196.4	204.3	213.2	231.9	264.5
62.5°	137.2	139.1	142.1	146.0	150.0	161.8	171.7	179.6	186.5	199.3	226.0
65°	119.4	120.4	122.4	123.4	124.3	129.3	138.2	149.0	161.8	171.7	187.5
67.5°	103.6	104.6	105.6	107.6	108.6	109.5	113.5	116.4	129.3	143.1	154.9
70°	88.8	90.8	91.8	91.8	92.8	94.7	96.7	100.7	104.6	111.5	126.3
72.5°	75.0	76.0	78.0	78.0	78.0	79.9	81.9	83.9	85.9	89.8	95.7
75°	62.2	64.1	64.1	64.1	65.1	65.1	67.1	69.1	71.1	74.0	76.0
77.5°	51.3	51.3	51.3	51.3	52.3	52.3	53.3	55.3	56.2	57.2	59.2
80°	38.5	39.5	39.5	39.5	40.5	40.5	40.5	42.4	43.4	43.4	45.4
82.5°	28.6	28.6	28.6	29.6	28.6	29.6	29.6	30.6	29.6	30.6	31.6
85°	17.8	17.8	17.8	18.7	18.7	18.7	18.7	18.7	18.7	18.7	19.7
87.5°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	9.9	8.9	8.9
90°	37.5	37.2	36.9	36.8	37.1	37.6	38.1	38.6	39.1	33.6	28.2
92.5°	35.7	35.7	35.7	35.7	35.6	35.3	35.1	34.8	34.6	34.4	34.1
95°	70.2	70.7	71.2	71.4	71.4	71.4	71.4	71.4	71.4	70.9	70.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	110.6	109.6
100°	153.4	153.6	153.9	154.0	154.0	154.0	154.0	154.0	154.0	153.3	152.5
102.5°	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	198.8	197.8
105°	247.8	247.8	247.8	247.8	247.6	247.1	246.6	246.1	245.6	245.1	244.6
107.5°	293.8	295.0	296.3	296.9	296.8	296.5	296.3	296.0	295.8	295.8	295.8
110°	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.0	395.5	396.0	396.3	396.7	397.4	398.1	398.9	399.6	399.8	400.1
115°	448.0	448.8	449.5	449.9	450.0	450.3	450.5	450.8	451.0	451.5	452.0
117.5°	497.1	497.9	498.6	499.0	499.4	500.1	500.8	501.6	502.3	503.5	504.8
120°	549.6	550.3	551.0	551.4	551.4	551.4	551.4	551.4	551.4	553.4	555.4
122.5°	600.4	600.9	601.4	601.7	602.1	602.8	603.5	604.3	605.0	606.2	607.5
125°	652.4	652.6	652.9	653.0	653.4	654.1	654.9	655.6	656.4	657.1	657.9
127.5°	700.3	701.0	701.7	702.1	702.6	703.6	704.6	705.6	706.6	707.6	708.6
130°	752.1	753.1	754.1	754.6	754.8	755.3	755.8	756.3	756.8	757.3	757.8
132.5°	800.7	801.5	802.2	802.6	803.2	804.5	805.7	807.0	808.2	808.0	807.7
135°	852.1	852.8	853.5	853.9	854.0	854.3	854.6	854.8	855.1	854.6	854.1
137.5°	898.4	899.3	900.3	900.8	900.9	901.2	901.4	901.7	901.9	901.4	900.9
140°	946.4	947.3	948.3	948.8	948.8	948.8	948.8	948.8	948.8	947.6	946.3
142.5°	989.9	990.9	991.9	992.4	992.3	992.0	991.7	991.5	991.2	990.5	989.7
145°	1033.4	1034.4	1035.4	1035.9	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8
147.5°	1072.5	1073.5	1074.5	1075.0	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7
150°	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5
152.5°	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7
155°	1176.9	1177.7	1178.4	1178.8	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7
157.5°	1205.8	1207.0	1208.3	1208.9	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1
160°	1231.0	1232.0	1233.0	1233.5	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3
162.5°	1253.8	1255.0	1256.3	1256.9	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6
165°	1272.8	1274.0	1275.3	1275.9	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1
167.5°	1289.5	1290.8	1292.0	1292.6	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8
170°	1302.3	1303.8	1305.3	1306.0	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7
172.5°	1312.4	1313.9	1315.4	1316.1	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8
175°	1319.1	1320.6	1322.1	1322.8	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0
177.5°	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1449.6	1444.7	1444.7	1441.7	1441.7	1426.0	1426.0	1430.9	1425.0	1418.1	1408.2
5°	1487.1	1476.3	1473.3	1469.4	1456.5	1436.8	1428.9	1426.0	1414.1	1399.3	1382.5
7.5°	1522.7	1504.9	1496.0	1487.1	1470.4	1442.7	1426.9	1416.1	1398.3	1375.6	1353.9
10°	1557.2	1534.5	1511.8	1501.0	1477.3	1442.7	1420.0	1402.3	1376.6	1346.0	1315.4
12.5°	1588.8	1541.4	1537.5	1515.8	1481.2	1441.7	1407.2	1381.6	1349.0	1313.5	1277.9
15°	1616.4	1568.1	1544.4	1524.6	1479.2	1429.9	1393.4	1361.8	1318.4	1277.9	1234.5
17.5°	1630.2	1577.9	1562.1	1529.6	1483.2	1419.1	1369.7	1331.2	1283.9	1235.5	1186.2
20°	1644.0	1582.9	1557.2	1534.5	1471.4	1398.3	1343.1	1298.7	1246.4	1189.1	1134.8
22.5°	1651.0	1582.9	1552.3	1520.7	1459.5	1375.6	1310.5	1258.2	1197.0	1138.8	1073.7
25°	1639.1	1576.9	1540.4	1507.9	1438.8	1348.0	1273.0	1213.8	1148.7	1082.5	1016.4
27.5°	1609.5	1563.1	1520.7	1487.1	1410.2	1312.5	1233.5	1166.4	1099.3	1025.3	958.2
30°	1554.2	1533.5	1500.0	1462.5	1378.6	1280.9	1187.1	1118.1	1044.1	970.0	900.0
32.5°	1468.4	1486.2	1464.4	1431.9	1341.1	1237.5	1137.8	1067.7	986.8	906.9	842.7
35°	1363.8	1426.9	1415.1	1392.4	1301.6	1191.1	1091.4	1006.6	925.6	844.7	780.6
37.5°	1249.3	1345.0	1354.9	1341.1	1256.2	1143.7	1034.2	951.3	868.4	786.5	721.4
40°	1092.4	1239.4	1271.0	1276.9	1208.9	1086.5	972.0	891.1	809.2	729.3	650.3
42.5°	948.3	1133.9	1173.3	1198.0	1148.7	1030.2	914.8	825.0	744.1	672.0	593.1
45°	813.1	1006.6	1070.7	1102.3	1080.6	966.1	846.7	762.8	688.8	622.7	546.7
47.5°	674.0	868.4	958.2	1008.5	1008.5	901.0	781.6	698.7	627.6	571.4	504.3
50°	581.2	743.1	835.8	902.0	919.7	834.9	722.4	641.4	574.3	513.1	461.8
52.5°	495.4	640.4	717.4	786.5	837.8	763.8	656.2	583.2	517.1	459.9	419.4
55°	428.3	536.8	606.9	682.9	740.1	691.8	592.1	521.0	463.8	416.4	381.9
57.5°	364.1	458.9	516.1	583.2	644.4	607.9	527.9	466.8	416.4	375.0	344.4
60°	309.9	386.8	431.2	483.5	559.5	533.9	467.8	411.5	371.0	333.5	307.9
62.5°	263.5	324.7	362.2	399.7	468.7	456.9	405.6	362.2	327.6	296.0	274.3
65°	216.1	266.4	296.0	328.6	383.9	388.8	347.4	316.8	285.2	257.6	237.8
67.5°	174.7	214.1	240.8	268.4	312.8	326.6	298.0	272.4	245.7	223.0	205.3
70°	141.1	168.7	188.5	210.2	246.7	263.5	248.7	230.9	209.2	190.5	174.7
72.5°	111.5	129.3	141.1	157.9	187.5	204.3	203.3	187.5	171.7	158.9	146.0
75°	81.9	95.7	105.6	116.4	140.1	155.9	159.9	153.0	137.2	127.3	117.4
77.5°	62.2	70.1	75.0	82.9	99.7	113.5	119.4	117.4	106.6	98.7	91.8
80°	47.4	49.3	51.3	54.3	68.1	80.9	84.9	83.9	78.0	75.0	67.1
82.5°	33.6	34.5	35.5	36.5	41.4	52.3	56.2	58.2	53.3	50.3	43.4
85°	19.7	20.7	20.7	22.7	23.7	26.6	33.6	33.6	32.6	28.6	27.6
87.5°	9.9	9.9	8.9	8.9	9.9	10.9	12.8	14.8	12.8	11.8	10.9
90°	22.7	17.2	14.5	13.0	10.0	7.1	4.1	1.1	4.1	7.1	10.0
92.5°	33.9	33.6	33.5	32.5	30.5	28.6	26.6	24.6	26.6	28.6	30.5
95°	69.9	69.4	69.2	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	108.7	107.7	107.2	106.1	103.8	101.6	99.3	97.1	99.3	101.6	103.8
100°	151.8	151.1	150.7	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	196.8	195.8	195.3	194.6	193.1	191.6	190.1	188.6	190.1	191.6	193.1
105°	244.1	243.6	243.3	242.9	242.2	241.5	240.7	240.0	240.7	241.5	242.2
107.5°	295.8	295.8	295.8	295.3	294.3	293.3	292.3	291.3	292.3	293.3	294.3
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	400.3	400.6	400.7	400.0	398.5	397.0	395.5	394.0	395.5	397.0	398.5
115°	452.5	453.0	453.2	452.5	451.0	449.5	448.0	446.5	448.0	449.5	451.0
117.5°	506.0	507.3	507.9	506.9	504.9	503.0	501.0	499.0	501.0	503.0	504.9
120°	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4	553.4	555.4	557.4
122.5°	608.7	610.0	610.6	609.4	606.9	604.4	601.9	599.4	601.9	604.4	606.9
125°	658.6	659.3	659.7	658.6	656.4	654.1	651.9	649.7	651.9	654.1	656.4
127.5°	709.6	710.6	711.1	709.7	707.0	704.3	701.5	698.8	701.5	704.3	707.0
130°	758.3	758.8	759.1	757.5	754.3	751.0	747.8	744.6	747.8	751.0	754.3
132.5°	807.5	807.2	807.1	805.9	803.4	800.9	798.4	795.9	798.4	800.9	803.4
135°	853.6	853.1	852.8	851.4	848.7	846.0	843.2	840.5	843.2	846.0	848.7
137.5°	900.4	899.9	899.7	898.6	896.4	894.1	891.9	889.7	891.9	894.1	896.4
140°	945.1	943.8	943.2	942.1	939.9	937.6	935.4	933.2	935.4	937.6	939.9
142.5°	989.0	988.3	987.9	986.8	984.6	982.3	980.1	977.9	980.1	982.3	984.6
145°	1030.3	1028.8	1028.1	1027.2	1025.5	1023.8	1022.0	1020.3	1022.0	1023.8	1025.5
147.5°	1069.8	1068.8	1068.3	1067.2	1064.9	1062.7	1060.4	1058.2	1060.4	1062.7	1064.9
150°	1105.5	1104.5	1104.0	1103.3	1101.8	1100.3	1098.8	1097.3	1098.8	1100.3	1101.8
152.5°	1140.5	1139.2	1138.6	1137.9	1136.4	1134.9	1133.4	1131.9	1133.4	1134.9	1136.4
155°	1170.9	1170.2	1169.8	1169.4	1168.7	1168.0	1167.2	1166.5	1167.2	1168.0	1168.7
157.5°	1199.6	1199.1	1198.9	1198.6	1198.1	1197.6	1197.1	1196.6	1197.1	1197.6	1198.1
160°	1226.1	1225.8	1225.7	1225.4	1224.9	1224.4	1223.9	1223.4	1223.9	1224.4	1224.9
162.5°	1248.4	1248.1	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0
165°	1268.1	1268.1	1268.1	1268.2	1268.5	1268.7	1269.0	1269.2	1269.0	1268.7	1268.5
167.5°	1284.8	1284.8	1284.8	1285.2	1285.9	1286.7	1287.4	1288.2	1287.4	1286.7	1285.9
170°	1298.9	1299.2	1299.3	1299.7	1300.4	1301.2	1301.9	1302.7	1301.9	1301.2	1300.4
172.5°	1309.0	1309.3	1309.4	1309.8	1310.5	1311.2	1312.0	1312.7	1312.0	1311.2	1310.5
175°	1316.5	1317.0	1317.2	1317.6	1318.3	1319.0	1319.8	1320.5	1319.8	1319.0	1318.3
177.5°	1320.9	1321.4	1321.7	1322.1	1322.8	1323.5	1324.3	1325.0	1324.3	1323.5	1322.8
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1404.2	1405.2	1408.2	1399.3	1385.5	1379.6	1361.8	1358.9	1355.9	1355.9	1358.9
5°	1372.7	1368.7	1369.7	1352.9	1333.2	1321.4	1296.7	1300.6	1287.8	1279.9	1281.9
7.5°	1338.1	1327.3	1326.3	1304.6	1279.9	1258.2	1232.5	1226.6	1214.8	1201.0	1195.0
10°	1294.7	1286.8	1272.0	1247.3	1215.8	1198.0	1163.5	1142.7	1139.8	1119.1	1111.2
12.5°	1250.3	1236.5	1221.7	1187.1	1151.6	1123.0	1097.3	1074.6	1058.9	1041.1	1029.3
15°	1199.0	1182.2	1165.4	1128.9	1087.5	1058.9	1020.4	986.8	940.4	903.9	883.2
17.5°	1142.7	1124.0	1101.3	1060.8	1020.4	980.9	909.8	870.4	837.8	816.1	803.3
20°	1084.5	1063.8	1041.1	1000.6	930.6	861.5	822.0	791.4	771.7	750.0	734.2
22.5°	1023.3	1001.6	977.0	913.8	839.8	791.4	760.8	732.2	703.6	691.8	683.9
25°	966.1	946.4	914.8	828.9	770.7	726.3	691.8	673.0	658.2	642.4	627.6
27.5°	906.9	870.4	826.0	753.9	717.4	672.0	647.4	633.5	607.9	597.0	590.1
30°	835.8	795.4	752.9	701.6	659.2	627.6	604.9	582.2	567.4	556.6	544.7
32.5°	763.8	725.3	698.7	645.4	613.8	581.2	559.5	545.7	524.0	517.1	512.2
35°	701.6	669.1	645.4	602.0	572.4	542.8	527.0	506.2	492.4	479.6	471.7
37.5°	640.4	622.7	598.0	561.5	529.9	506.2	484.5	477.6	458.9	452.0	444.1
40°	598.0	571.4	550.6	519.1	492.4	466.8	453.0	437.2	424.3	413.5	410.5
42.5°	546.7	527.0	515.1	480.6	453.0	438.1	421.4	403.6	393.7	384.9	374.0
45°	508.2	490.5	473.7	446.0	421.4	402.6	387.8	376.0	359.2	355.3	338.5
47.5°	467.8	450.0	437.2	409.5	386.8	369.1	358.2	342.4	328.6	319.7	311.8
50°	427.3	412.5	400.6	377.0	357.2	338.5	323.7	307.9	302.0	287.2	282.2
52.5°	388.8	378.9	366.1	343.4	323.7	307.9	292.1	279.3	270.4	262.5	256.6
55°	356.2	340.5	334.5	309.9	293.1	276.3	262.5	254.6	243.7	238.8	233.9
57.5°	319.7	310.8	301.0	282.2	263.5	247.7	237.8	226.0	220.1	214.1	210.2
60°	288.2	275.3	267.4	251.6	234.9	220.1	211.2	202.3	194.4	189.5	181.6
62.5°	251.6	241.8	236.8	220.1	206.2	192.4	184.5	175.7	169.7	160.9	151.0
65°	220.1	212.2	206.2	192.4	179.6	166.8	158.9	148.0	140.1	135.2	134.2
67.5°	192.4	186.5	177.6	164.8	152.0	142.1	133.2	124.3	123.4	121.4	121.4
70°	161.8	155.9	151.0	137.2	126.3	115.5	113.5	110.5	107.6	106.6	104.6
72.5°	135.2	130.3	124.3	112.5	101.6	98.7	96.7	94.7	91.8	90.8	89.8
75°	109.5	102.6	98.7	87.8	84.9	82.9	80.9	78.0	76.0	75.0	73.0
77.5°	83.9	77.0	77.0	71.1	69.1	66.1	64.1	62.2	61.2	59.2	59.2
80°	59.2	59.2	57.2	54.3	51.3	50.3	47.4	46.4	45.4	46.4	44.4
82.5°	43.4	39.5	39.5	37.5	35.5	34.5	32.6	32.6	31.6	31.6	31.6
85°	24.7	24.7	23.7	21.7	20.7	20.7	19.7	19.7	18.7	18.7	17.8
87.5°	9.9	8.9	9.9	8.9	8.9	7.9	7.9	7.9	6.9	7.9	6.9
90°	13.0	14.5	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1
92.5°	32.5	33.5	33.6	33.9	34.1	34.4	34.6	34.8	35.1	35.3	35.6
95°	68.0	69.2	69.4	69.9	70.4	70.9	71.4	71.4	71.4	71.4	71.4
97.5°	106.1	107.2	107.7	108.7	109.6	110.6	111.6	111.6	111.6	111.6	111.6
100°	149.7	150.7	151.1	151.8	152.5	153.3	154.0	154.0	154.0	154.0	154.0
102.5°	194.6	195.3	195.8	196.8	197.8	198.8	199.8	200.0	200.3	200.5	200.8
105°	242.9	243.3	243.6	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6
107.5°	295.3	295.8	295.8	295.8	295.8	295.8	295.8	296.0	296.3	296.5	296.8
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	400.0	400.7	400.6	400.3	400.1	399.8	399.6	398.9	398.1	397.4	396.7
115°	452.5	453.2	453.0	452.5	452.0	451.5	451.0	450.8	450.5	450.3	450.0
117.5°	506.9	507.9	507.3	506.0	504.8	503.5	502.3	501.6	500.8	500.1	499.4
120°	559.4	560.4	559.4	557.4	555.4	553.4	551.4	551.4	551.4	551.4	551.4
122.5°	609.4	610.6	610.0	608.7	607.5	606.2	605.0	604.3	603.5	602.8	602.1
125°	658.6	659.7	659.3	658.6	657.9	657.1	656.4	655.6	654.9	654.1	653.4
127.5°	709.7	711.1	710.6	709.6	708.6	707.6	706.6	705.6	704.6	703.6	702.6
130°	757.5	759.1	758.8	758.3	757.8	757.3	756.8	756.3	755.8	755.3	754.8
132.5°	805.9	807.1	807.2	807.5	807.7	808.0	808.2	807.0	805.7	804.5	803.2
135°	851.4	852.8	853.1	853.6	854.1	854.6	855.1	854.8	854.6	854.3	854.0
137.5°	898.6	899.7	899.9	900.4	900.9	901.4	901.9	901.7	901.4	901.2	900.9
140°	942.1	943.2	943.8	945.1	946.3	947.6	948.8	948.8	948.8	948.8	948.8
142.5°	986.8	987.9	988.3	989.0	989.7	990.5	991.2	991.5	991.7	992.0	992.3
145°	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8	1035.0	1035.3	1035.5	1035.8
147.5°	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7	1073.2	1073.7	1074.2	1074.7
150°	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5	1109.2	1110.0	1110.7	1111.4
152.5°	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2	1145.2	1146.2	1147.1	1148.1
155°	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2	1174.4	1175.7	1176.9	1178.2
157.5°	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1	1202.8	1204.6	1206.3	1208.0
160°	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8	1228.3	1229.8	1231.3	1232.8
162.5°	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1	1250.8	1252.6	1254.3	1256.0
165°	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1269.8	1271.6	1273.3	1275.0
167.5°	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1286.5	1288.3	1290.0	1291.7
170°	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2	1299.9	1301.7	1303.4	1305.1
172.5°	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3	1310.0	1311.8	1313.5	1315.2
175°	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0	1316.7	1318.5	1320.2	1321.9
177.5°	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4	1320.9	1322.4	1323.9	1325.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1358.9	1356.9	1351.0	1352.9	1350.0	1350.0	1348.0	1348.0	1348.0	1352.9	1350.0
5°	1284.8	1277.9	1271.0	1268.1	1265.1	1262.1	1262.1	1261.2	1270.0	1268.1	1276.0
7.5°	1193.1	1191.1	1177.3	1177.3	1172.3	1170.4	1175.3	1176.3	1177.3	1179.3	1184.2
10°	1111.2	1106.2	1086.5	1088.5	1085.5	1081.6	1084.5	1082.5	1089.5	1091.4	1089.5
12.5°	1014.5	1005.6	983.9	973.0	961.2	952.3	963.1	955.2	982.9	990.8	1012.5
15°	886.2	869.4	854.6	854.6	843.7	835.8	840.8	849.7	855.6	864.5	868.4
17.5°	800.3	793.4	781.6	774.7	771.7	768.7	768.7	772.7	785.5	784.5	792.4
20°	727.3	723.3	717.4	708.5	705.6	703.6	703.6	703.6	712.5	720.4	725.3
22.5°	677.0	674.0	670.1	658.2	652.3	650.3	655.2	658.2	665.1	671.0	676.0
25°	626.6	619.7	612.8	608.9	605.9	605.9	607.9	608.9	611.8	614.8	620.7
27.5°	585.2	580.3	570.4	559.5	559.5	556.6	558.5	560.5	567.4	577.3	582.2
30°	538.8	537.8	533.9	529.9	526.0	524.0	527.9	530.9	531.9	536.8	536.8
32.5°	505.3	498.3	491.4	487.5	485.5	484.5	485.5	489.5	489.5	495.4	502.3
35°	471.7	467.8	460.8	453.9	452.0	447.0	451.0	454.9	461.8	464.8	467.8
37.5°	435.2	430.3	427.3	425.3	421.4	422.4	419.4	425.3	431.2	430.3	432.2
40°	407.6	398.7	389.8	388.8	387.8	386.8	386.8	387.8	391.8	395.7	401.6
42.5°	372.0	369.1	361.2	353.3	351.3	349.3	347.4	351.3	359.2	366.1	369.1
45°	335.5	331.6	329.6	323.7	319.7	318.7	316.8	321.7	328.6	331.6	333.5
47.5°	302.0	301.0	295.1	296.0	293.1	294.1	293.1	296.0	296.0	299.0	301.0
50°	279.3	276.3	273.3	271.4	268.4	268.4	267.4	268.4	272.4	276.3	275.3
52.5°	256.6	251.6	250.7	249.7	247.7	249.7	246.7	247.7	251.6	253.6	252.6
55°	229.9	228.9	227.0	225.0	224.0	223.0	223.0	223.0	227.0	229.9	230.9
57.5°	209.2	204.3	200.3	200.3	196.4	195.4	197.4	198.4	201.3	203.3	205.3
60°	180.6	178.6	172.7	169.7	163.8	162.8	162.8	166.8	171.7	178.6	180.6
62.5°	150.0	147.0	146.0	146.0	146.0	146.0	146.0	146.0	146.0	147.0	147.0
65°	133.2	134.2	133.2	132.2	133.2	133.2	132.2	132.2	132.2	133.2	134.2
67.5°	119.4	118.4	119.4	118.4	117.4	117.4	116.4	117.4	118.4	119.4	119.4
70°	103.6	103.6	102.6	103.6	102.6	101.6	100.7	100.7	102.6	103.6	103.6
72.5°	88.8	88.8	87.8	87.8	85.9	85.9	86.8	85.9	85.9	88.8	88.8
75°	74.0	73.0	72.0	72.0	71.1	71.1	71.1	70.1	72.0	72.0	73.0
77.5°	58.2	58.2	58.2	57.2	57.2	56.2	56.2	57.2	57.2	57.2	58.2
80°	44.4	44.4	44.4	43.4	42.4	42.4	42.4	42.4	42.4	43.4	42.4
82.5°	30.6	30.6	30.6	30.6	30.6	29.6	29.6	29.6	30.6	30.6	29.6
85°	18.7	17.8	18.7	18.7	17.8	18.7	17.8	17.8	16.8	16.8	17.8
87.5°	7.9	6.9	5.9	5.9	6.9	5.9	5.9	5.9	6.9	5.9	5.9
90°	36.8	36.9	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	36.8
92.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.2	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	153.9	153.6	153.4	153.1	152.9	153.1	153.4	153.6	153.9	154.0
102.5°	200.9	200.8	200.5	200.3	200.0	199.8	200.0	200.3	200.5	200.8	200.9
105°	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.9	296.3	295.0	293.8	292.5	291.3	292.5	293.8	295.0	296.3	296.9
110°	347.2	346.8	346.1	345.3	344.6	343.8	344.6	345.3	346.1	346.8	347.2

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	396.3	396.0	395.5	395.0	394.5	394.0	394.5	395.0	395.5	396.0	396.3
115°	449.9	449.5	448.8	448.0	447.3	446.5	447.3	448.0	448.8	449.5	449.9
117.5°	499.0	498.6	497.9	497.1	496.4	495.6	496.4	497.1	497.9	498.6	499.0
120°	551.4	551.0	550.3	549.6	548.8	548.1	548.8	549.6	550.3	551.0	551.4
122.5°	601.7	601.4	600.9	600.4	599.9	599.4	599.9	600.4	600.9	601.4	601.7
125°	653.0	652.9	652.6	652.4	652.1	651.9	652.1	652.4	652.6	652.9	653.0
127.5°	702.1	701.7	701.0	700.3	699.5	698.8	699.5	700.3	701.0	701.7	702.1
130°	754.6	754.1	753.1	752.1	751.1	750.1	751.1	752.1	753.1	754.1	754.6
132.5°	802.6	802.2	801.5	800.7	800.0	799.2	800.0	800.7	801.5	802.2	802.6
135°	853.9	853.5	852.8	852.1	851.3	850.6	851.3	852.1	852.8	853.5	853.9
137.5°	900.8	900.3	899.3	898.4	897.4	896.4	897.4	898.4	899.3	900.3	900.8
140°	948.8	948.3	947.3	946.4	945.4	944.4	945.4	946.4	947.3	948.3	948.8
142.5°	992.4	991.9	990.9	989.9	988.9	987.9	988.9	989.9	990.9	991.9	992.4
145°	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4	1033.4	1034.4	1035.4	1035.9
147.5°	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5	1072.5	1073.5	1074.5	1075.0
150°	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2	1110.0	1110.7	1111.4	1111.8
152.5°	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2	1146.2	1147.1	1148.1	1148.6
155°	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2	1176.9	1177.7	1178.4	1178.8
157.5°	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5	1205.8	1207.0	1208.3	1208.9
160°	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0	1231.0	1232.0	1233.0	1233.5
162.5°	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5	1253.8	1255.0	1256.3	1256.9
165°	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5	1272.8	1274.0	1275.3	1275.9
167.5°	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3	1289.5	1290.8	1292.0	1292.6
170°	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8	1302.3	1303.8	1305.3	1306.0
172.5°	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9	1312.4	1313.9	1315.4	1316.1
175°	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6	1319.1	1320.6	1322.1	1322.8
177.5°	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9	1322.4	1323.9	1325.4	1326.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0	1420.0
2.5°	1352.9	1357.9	1355.9	1345.0	1355.9	1358.9	1364.8	1370.7	1374.6	1380.6	1385.5
5°	1268.1	1277.9	1283.9	1277.9	1297.7	1300.6	1314.4	1322.3	1334.2	1344.1	1351.9
7.5°	1188.1	1196.0	1207.9	1209.8	1221.7	1235.5	1255.2	1275.0	1293.7	1303.6	1312.5
10°	1102.3	1116.1	1133.9	1129.9	1147.7	1169.4	1190.1	1221.7	1237.5	1255.2	1271.0
12.5°	1016.4	1025.3	1049.0	1056.9	1082.5	1099.3	1127.9	1147.7	1187.1	1207.9	1221.7
15°	866.4	902.9	932.5	968.1	1001.6	1033.2	1058.9	1094.4	1128.9	1144.7	1167.4
17.5°	798.3	815.1	832.9	850.6	894.1	950.3	995.7	1034.2	1063.8	1084.5	1111.2
20°	727.3	744.1	763.8	780.6	807.2	847.7	903.9	970.0	1005.6	1027.3	1052.9
22.5°	677.0	692.7	705.6	720.4	741.1	770.7	813.1	895.0	942.4	969.1	991.8
25°	622.7	642.4	656.2	667.1	683.9	716.4	751.0	797.4	882.2	902.9	934.5
27.5°	585.2	591.1	606.9	623.7	640.4	658.2	693.7	733.2	790.4	835.8	874.3
30°	540.8	555.6	570.4	577.3	592.1	617.8	639.5	681.9	726.3	761.8	808.2
32.5°	507.2	516.1	526.0	542.8	556.6	574.3	596.0	631.6	669.1	691.8	727.3
35°	469.7	475.6	496.4	503.3	517.1	534.9	556.6	584.2	624.7	642.4	668.1
37.5°	434.2	448.0	453.9	469.7	482.6	500.3	516.1	547.7	574.3	595.1	618.7
40°	406.6	412.5	423.3	437.2	448.0	461.8	481.6	504.3	532.9	549.7	570.4
42.5°	373.0	378.0	391.8	399.7	417.4	430.3	442.1	469.7	495.4	508.2	528.9
45°	336.5	348.3	357.2	373.0	382.9	398.7	413.5	433.2	456.9	471.7	483.5
47.5°	304.9	316.8	325.7	340.5	356.2	363.2	378.9	399.7	421.4	433.2	450.0
50°	279.3	283.2	300.0	306.9	323.7	337.5	348.3	366.1	389.8	396.7	410.5
52.5°	254.6	257.6	268.4	277.3	292.1	303.9	317.8	334.5	354.3	365.1	376.0
55°	232.9	234.9	239.8	249.7	259.5	274.3	287.2	303.0	319.7	331.6	341.4
57.5°	208.2	212.2	216.1	222.0	231.9	245.7	259.5	274.3	288.2	296.0	308.9
60°	179.6	185.5	192.4	199.3	206.2	216.1	231.9	245.7	258.5	265.5	275.3
62.5°	149.0	160.9	166.8	174.7	180.6	189.5	201.3	217.1	226.0	234.9	242.8
65°	134.2	135.2	136.2	144.1	154.9	163.8	174.7	186.5	200.3	206.2	212.2
67.5°	119.4	120.4	122.4	123.4	127.3	137.2	149.0	161.8	172.7	176.6	182.6
70°	104.6	104.6	108.6	109.5	110.5	111.5	121.4	134.2	144.1	149.0	155.9
72.5°	88.8	89.8	91.8	92.8	94.7	96.7	99.7	106.6	118.4	123.4	131.2
75°	73.0	74.0	75.0	76.0	78.9	79.9	82.9	86.8	91.8	97.7	102.6
77.5°	58.2	58.2	59.2	61.2	63.2	64.1	67.1	69.1	71.1	74.0	78.0
80°	43.4	44.4	44.4	46.4	46.4	47.4	48.4	51.3	53.3	55.3	57.2
82.5°	29.6	31.6	31.6	31.6	32.6	33.6	34.5	34.5	36.5	37.5	40.5
85°	17.8	18.7	18.7	18.7	17.8	19.7	19.7	20.7	20.7	20.7	21.7
87.5°	6.9	5.9	6.9	6.9	6.9	7.9	6.9	6.9	7.9	8.9	8.9
90°	37.1	37.6	38.1	38.6	39.1	33.6	28.2	22.7	17.2	14.5	13.0
92.5°	35.6	35.3	35.1	34.8	34.6	34.4	34.1	33.9	33.6	33.5	32.5
95°	71.4	71.4	71.4	71.4	71.4	70.9	70.4	69.9	69.4	69.2	68.0
97.5°	111.6	111.6	111.6	111.6	111.6	110.6	109.6	108.7	107.7	107.2	106.1
100°	154.0	154.0	154.0	154.0	154.0	153.3	152.5	151.8	151.1	150.7	149.7
102.5°	200.8	200.5	200.3	200.0	199.8	198.8	197.8	196.8	195.8	195.3	194.6
105°	247.6	247.1	246.6	246.1	245.6	245.1	244.6	244.1	243.6	243.3	242.9
107.5°	296.8	296.5	296.3	296.0	295.8	295.8	295.8	295.8	295.8	295.8	295.3
110°	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.5

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	396.7	397.4	398.1	398.9	399.6	399.8	400.1	400.3	400.6	400.7	400.0
115°	450.0	450.3	450.5	450.8	451.0	451.5	452.0	452.5	453.0	453.2	452.5
117.5°	499.4	500.1	500.8	501.6	502.3	503.5	504.8	506.0	507.3	507.9	506.9
120°	551.4	551.4	551.4	551.4	551.4	553.4	555.4	557.4	559.4	560.4	559.4
122.5°	602.1	602.8	603.5	604.3	605.0	606.2	607.5	608.7	610.0	610.6	609.4
125°	653.4	654.1	654.9	655.6	656.4	657.1	657.9	658.6	659.3	659.7	658.6
127.5°	702.6	703.6	704.6	705.6	706.6	707.6	708.6	709.6	710.6	711.1	709.7
130°	754.8	755.3	755.8	756.3	756.8	757.3	757.8	758.3	758.8	759.1	757.5
132.5°	803.2	804.5	805.7	807.0	808.2	808.0	807.7	807.5	807.2	807.1	805.9
135°	854.0	854.3	854.6	854.8	855.1	854.6	854.1	853.6	853.1	852.8	851.4
137.5°	900.9	901.2	901.4	901.7	901.9	901.4	900.9	900.4	899.9	899.7	898.6
140°	948.8	948.8	948.8	948.8	948.8	947.6	946.3	945.1	943.8	943.2	942.1
142.5°	992.3	992.0	991.7	991.5	991.2	990.5	989.7	989.0	988.3	987.9	986.8
145°	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8	1030.3	1028.8	1028.1	1027.2
147.5°	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7	1069.8	1068.8	1068.3	1067.2
150°	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5	1105.5	1104.5	1104.0	1103.3
152.5°	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7	1140.5	1139.2	1138.6	1137.9
155°	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7	1170.9	1170.2	1169.8	1169.4
157.5°	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1	1199.6	1199.1	1198.9	1198.6
160°	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3	1226.1	1225.8	1225.7	1225.4
162.5°	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6	1248.4	1248.1	1248.0	1248.0
165°	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1268.2
167.5°	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1285.2
170°	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7	1298.9	1299.2	1299.3	1299.7
172.5°	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8	1309.0	1309.3	1309.4	1309.8
175°	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0	1316.5	1317.0	1317.2	1317.6
177.5°	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4	1320.9	1321.4	1321.7	1322.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1420.0	1420.0	1420.0	1420.0
2.5°	1394.4	1391.4	1409.2	1428.9
5°	1365.8	1370.7	1393.4	1421.0
7.5°	1336.2	1347.0	1373.7	1410.2
10°	1294.7	1314.4	1354.9	1392.4
12.5°	1254.3	1280.9	1319.4	1363.8
15°	1208.9	1238.5	1285.8	1339.1
17.5°	1158.5	1192.1	1247.3	1305.6
20°	1105.2	1149.6	1207.9	1271.0
22.5°	1046.0	1099.3	1159.5	1229.6
25°	988.8	1047.0	1107.2	1188.1
27.5°	932.5	989.8	1056.9	1138.8
30°	876.3	928.6	1000.6	1088.5
32.5°	816.1	870.4	946.4	1036.2
35°	760.8	815.1	886.2	975.0
37.5°	701.6	759.9	827.9	919.7
40°	632.6	700.6	766.8	854.6
42.5°	575.3	647.4	711.5	794.4
45°	529.9	598.0	651.3	732.2
47.5°	487.5	542.8	597.0	672.0
50°	447.0	489.5	545.7	612.8
52.5°	405.6	442.1	490.5	553.6
55°	368.1	402.6	446.0	494.4
57.5°	333.5	358.2	401.6	445.1
60°	295.1	320.7	354.3	390.8
62.5°	262.5	282.2	313.8	344.4
65°	228.0	246.7	270.4	299.0
67.5°	196.4	213.2	231.9	254.6
70°	167.8	180.6	194.4	214.1
72.5°	137.2	151.0	163.8	179.6
75°	112.5	118.4	129.3	140.1
77.5°	86.8	94.7	100.7	109.5
80°	62.2	69.1	71.1	78.0
82.5°	41.4	45.4	49.3	51.3
85°	23.7	25.7	29.6	30.6
87.5°	8.9	9.9	11.8	13.8
90°	10.0	7.1	4.1	1.1
92.5°	30.5	28.6	26.6	24.6
95°	65.5	63.0	60.5	58.0
97.5°	103.8	101.6	99.3	97.1
100°	147.7	145.8	143.8	141.8
102.5°	193.1	191.6	190.1	188.6
105°	242.2	241.5	240.7	240.0
107.5°	294.3	293.3	292.3	291.3
110°	345.0	343.5	342.0	340.5

TEST NUMBER: P999896

CATALOG NUMBER: SA2XXRDIP-B675D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	398.5	397.0	395.5	394.0
115°	451.0	449.5	448.0	446.5
117.5°	504.9	503.0	501.0	499.0
120°	557.4	555.4	553.4	551.4
122.5°	606.9	604.4	601.9	599.4
125°	656.4	654.1	651.9	649.7
127.5°	707.0	704.3	701.5	698.8
130°	754.3	751.0	747.8	744.6
132.5°	803.4	800.9	798.4	795.9
135°	848.7	846.0	843.2	840.5
137.5°	896.4	894.1	891.9	889.7
140°	939.9	937.6	935.4	933.2
142.5°	984.6	982.3	980.1	977.9
145°	1025.5	1023.8	1022.0	1020.3
147.5°	1064.9	1062.7	1060.4	1058.2
150°	1101.8	1100.3	1098.8	1097.3
152.5°	1136.4	1134.9	1133.4	1131.9
155°	1168.7	1168.0	1167.2	1166.5
157.5°	1198.1	1197.6	1197.1	1196.6
160°	1224.9	1224.4	1223.9	1223.4
162.5°	1248.0	1248.0	1248.0	1248.0
165°	1268.5	1268.7	1269.0	1269.2
167.5°	1285.9	1286.7	1287.4	1288.2
170°	1300.4	1301.2	1301.9	1302.7
172.5°	1310.5	1311.2	1312.0	1312.7
175°	1318.3	1319.0	1319.8	1320.5
177.5°	1322.8	1323.5	1324.3	1325.0
180°	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)