

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001066

Luminaire Tested: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001066
REPORT IS A COMBINATION OF REPORTS P995682 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7969.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001066

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001066

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	41
4	76	65	57	51	71	61	54	49	54	48	44	48	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1001066

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.3
10°-20°	509.9	6.4
20°-30°	750.5	9.4
30°-40°	872.4	10.9
40°-50°	872.3	10.9
50°-60°	763.0	9.6
60°-70°	566.4	7.1
70°-80°	321.4	4.0
80°-90°	94.1	1.2
90°-100°	32.6	0.4
100°-110°	214.6	2.7
110°-120°	409.8	5.1
120°-130°	520.3	6.5
130°-140°	556.6	7.0
140°-150°	520.4	6.5
150°-160°	419.7	5.3
160°-170°	270.7	3.4
170°-180°	93.3	1.2
0°-30°	1441.4	18.1
0°-40°	2313.8	29.0
0°-60°	3949.1	49.6
0°-90°	4931.0	61.9
90°-120°	657.0	8.2
90°-150°	2254.3	28.3
90°-180°	3038.0	38.1
0°-180°	7969.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	2	10	16	21	22	8
95°	40	15	16	21	21	50
105°	221	225	229	236	209	231
115°	413	415	414	416	416	406
125°	580	583	582	584	584	518
135°	720	719	722	723	725	554
145°	830	832	832	833	834	518
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001066

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	2.2	10.3	16.2	20.6	22.0
92.5°	11.0	9.5	15.4	19.8	19.8
95°	40.4	15.4	16.2	20.6	21.3
97.5°	77.1	93.3	16.2	19.8	20.6
100°	120.4	133.6	32.3	19.8	20.6
102.5°	168.9	177.7	186.5	21.3	21.3
105°	221.0	225.4	229.1	235.7	209.3
107.5°	268.8	271.0	276.1	279.8	282.7
110°	317.2	319.4	323.8	325.3	327.5



TEST NUMBER: P1001066

CATALOG NUMBER: SA4XXDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	368.6	370.1	369.4	372.3
115°	412.7	414.9	414.2	415.6	415.6
117.5°	456.0	458.9	461.2	460.4	460.4
120°	500.1	503.0	502.3	503.7	502.3
122.5°	541.2	542.7	544.1	544.9	543.4
125°	580.1	583.0	581.6	583.8	584.5
127.5°	617.6	618.3	622.0	621.2	620.5
130°	653.5	654.3	656.5	657.2	657.2
132.5°	686.6	688.1	691.0	691.7	691.0
135°	719.6	718.9	721.8	723.3	724.8
137.5°	749.0	749.0	752.7	754.1	753.4
140°	777.6	779.1	780.6	782.8	783.5
142.5°	803.3	806.3	807.0	808.5	808.5
145°	829.8	832.0	832.0	832.7	834.2
147.5°	850.3	854.7	854.0	854.7	855.5
150°	873.1	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)