

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999928

Luminaire Tested: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999928
REPORT IS A COMBINATION OF REPORTS P988485 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3637.5 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999928

CATALOG NUMBER: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999928

CATALOG NUMBER: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	31
7	62	50	42	36	58	47	40	35	43	37	32	38	34	30	34	30	27
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P999928

CATALOG NUMBER: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	2.9
10°-20°	293.0	8.1
20°-30°	411.3	11.3
30°-40°	448.4	12.3
40°-50°	412.1	11.3
50°-60°	323.6	8.9
60°-70°	210.7	5.8
70°-80°	108.4	3.0
80°-90°	28.9	0.8
90°-100°	75.3	2.1
100°-110°	254.4	7.0
110°-120°	267.4	7.4
120°-130°	219.9	6.0
130°-140°	176.7	4.9
140°-150°	133.5	3.7
150°-160°	93.9	2.6
160°-170°	55.3	1.5
170°-180°	18.0	0.5
0°-30°	811.1	22.3
0°-40°	1259.4	34.6
0°-60°	1995.2	54.9
0°-90°	2343.2	64.4
90°-120°	597.1	16.4
90°-150°	1127.2	31.0
90°-180°	1294.0	35.6
0°-180°	3637.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	0	5	12	12	12	3
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	430	95
135°	126	150	210	311	356	97
145°	144	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	195	206	210	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	

TEST NUMBER: P999928

CATALOG NUMBER: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	0.4	4.8	12.1	11.6	11.8
92.5°	5.4	17.0	55.0	25.4	21.8
95°	12.5	30.7	139.9	52.8	40.7
97.5°	18.6	40.5	228.1	106.0	68.2
100°	27.5	49.6	282.0	211.2	127.8
102.5°	35.7	57.8	283.8	357.0	249.2
105°	43.6	65.7	264.5	472.8	402.3
107.5°	52.1	73.5	246.7	514.8	505.5
110°	60.7	81.6	234.5	508.0	547.6



TEST NUMBER: P999928

CATALOG NUMBER: SA2XXRDIP-B675D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.5	89.2	226.7	485.0	546.9
115°	76.8	96.9	221.3	456.8	529.4
117.5°	85.3	104.6	218.5	429.8	503.0
120°	93.2	112.1	216.0	405.8	477.7
122.5°	100.7	119.8	214.6	387.0	451.2
125°	107.1	126.7	212.8	370.0	429.5
127.5°	112.5	133.4	211.7	355.6	409.1
130°	117.1	139.2	211.0	341.0	392.3
132.5°	121.4	144.9	210.6	325.8	374.9
135°	125.7	149.9	210.3	311.0	355.9
137.5°	129.6	154.2	210.3	296.0	337.7
140°	134.2	158.2	209.9	282.8	318.8
142.5°	138.9	161.4	209.9	270.0	299.9
145°	143.5	165.0	209.2	259.7	284.2
147.5°	148.5	167.8	208.1	250.6	270.3
150°	153.5	170.6	207.1	242.8	258.1
152.5°	158.5	173.5	205.3	236.2	247.8
155°	163.1	176.2	203.1	229.8	238.8
157.5°	167.1	178.3	201.0	223.7	231.0
160°	171.0	180.4	198.8	217.6	223.5
162.5°	174.9	182.0	197.1	211.9	216.3
165°	177.8	183.1	194.6	206.4	209.6
167.5°	180.3	184.2	192.4	201.4	203.1
170°	182.8	184.8	190.6	196.8	197.4
172.5°	184.2	185.2	188.5	192.6	192.8
175°	185.3	185.4	187.1	189.4	188.9
177.5°	186.0	185.6	185.6	187.1	186.0
180°	185.6	185.6	185.6	185.6	185.6

(END OF REPORT)