

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001120

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001120
REPORT IS A COMBINATION OF REPORTS P995736 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5463.0 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001120

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001120

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	91	87	83	80	81	77	74	71	59	57	55	43	41	40	27	27	26
2	83	76	70	65	73	67	62	58	52	48	45	37	35	33	24	23	21
3	76	66	59	53	67	59	53	48	45	41	38	33	30	28	21	19	18
4	69	58	51	45	61	52	45	40	40	35	32	29	26	23	19	17	15
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	30	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9
9	46	34	27	22	41	30	24	20	24	19	16	17	14	12	11	10	8
10	43	31	24	19	38	28	22	18	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3346	3249	3255
10°	3324	3186	3176
15°	3293	3114	3087
20°	3246	3036	3001
25°	3195	2950	2907
30°	3138	2865	2813
35°	3075	2778	2728
40°	3024	2695	2640
45°	2949	2616	2563
50°	2884	2527	2481
55°	2818	2441	2386
60°	2715	2335	2298
65°	2600	2220	2192
70°	2463	2088	2069
75°	2271	1942	1952
80°	2052	1793	1828
85°	1768	1643	1729

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3327 cd/sqm

TEST NUMBER: P1001120

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.8	0.7
10°-20°	111.1	2.0
20°-30°	168.0	3.1
30°-40°	203.2	3.7
40°-50°	214.8	3.9
50°-60°	202.2	3.7
60°-70°	167.7	3.1
70°-80°	117.7	2.2
80°-90°	69.1	1.3
90°-100°	83.1	1.5
100°-110°	316.4	5.8
110°-120°	568.0	10.4
120°-130°	707.3	12.9
130°-140°	749.6	13.7
140°-150°	697.4	12.8
150°-160°	561.6	10.3
160°-170°	362.2	6.6
170°-180°	124.8	2.3
0°-30°	317.8	5.8
0°-40°	521.0	9.5
0°-60°	938.0	17.2
0°-90°	1292.5	23.7
90°-120°	967.6	17.7
90°-150°	3121.8	57.1
90°-180°	4170.0	76.3
0°-180°	5463.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	410	408	405	409	408	39
15°	393	393	392	396	395	111
25°	359	362	363	368	369	165
35°	314	320	324	331	332	197
45°	262	271	280	287	290	203
55°	205	215	229	238	240	183
65°	142	157	172	184	187	141
75°	79	96	115	128	132	84
85°	24	44	64	78	82	25
90°	10	40	67	86	92	8
95°	60	42	62	80	85	71
105°	300	315	337	357	325	314
115°	555	562	576	588	591	546
125°	778	782	791	803	806	695
135°	964	963	970	979	984	743
145°	1111	1113	1113	1117	1121	694
155°	1218	1218	1216	1219	1216	561
165°	1284	1279	1279	1287	1278	363
175°	1314	1308	1309	1318	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1001120

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.2	409.2	409.2	409.2	409.2
2.5°	411.0	409.6	406.0	409.2	408.7
5°	409.6	408.2	405.0	408.7	408.2
7.5°	406.9	406.0	403.2	407.3	406.9
10°	403.2	402.7	400.5	404.6	404.1
12.5°	398.2	398.2	396.8	400.5	400.5
15°	392.7	393.1	391.8	395.9	395.4
17.5°	385.3	386.7	386.3	390.4	389.9
20°	377.5	378.9	379.4	384.0	384.0
22.5°	368.8	370.7	371.6	376.2	377.1
25°	359.2	362.0	363.3	368.4	368.8
27.5°	348.7	352.8	354.6	359.2	359.7
30°	338.1	341.8	345.0	350.1	351.0
32.5°	326.7	331.3	334.9	340.9	341.8
35°	314.3	319.8	324.4	330.8	332.2
37.5°	301.9	308.4	313.9	320.3	321.6
40°	290.0	296.0	302.4	309.3	311.1
42.5°	276.3	283.2	290.9	298.7	300.1
45°	262.1	270.8	279.5	287.3	289.6
47.5°	248.8	257.5	267.6	275.4	278.1
50°	234.1	244.2	254.3	263.5	266.2
52.5°	219.5	229.6	241.5	250.6	253.4
55°	205.3	214.9	228.6	237.8	240.5
57.5°	189.2	201.1	214.4	225.4	227.7
60°	173.7	185.6	200.7	211.2	214.9
62.5°	158.5	171.8	186.9	197.5	201.1
65°	142.0	156.7	172.3	183.7	187.4
67.5°	126.5	142.0	158.5	170.0	173.7
70°	110.4	126.0	143.4	155.8	159.0
72.5°	94.8	110.9	129.7	141.6	145.2
75°	78.8	95.8	115.0	127.8	132.0
77.5°	63.7	81.6	101.7	114.5	119.1
80°	49.9	68.3	88.4	102.2	105.8
82.5°	36.2	55.4	75.6	89.8	93.9
85°	24.3	43.5	64.1	77.9	82.5
87.5°	15.1	33.9	54.1	67.4	71.5
90°	10.2	39.5	67.0	86.1	91.8
92.5°	21.6	35.7	63.2	81.9	85.6
95°	60.0	41.7	61.5	79.7	84.9
97.5°	108.7	143.6	59.2	76.0	81.1
100°	166.2	195.8	78.0	73.7	77.9
102.5°	231.0	252.9	282.1	72.9	76.6
105°	299.9	315.0	336.8	357.1	325.4
107.5°	363.7	374.5	397.4	413.8	420.9
110°	428.2	437.5	459.4	472.0	478.6

TEST NUMBER: P1001120

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.6	502.0	519.0	528.2	535.8
115°	554.9	562.1	575.7	587.8	591.0
117.5°	612.9	619.6	636.3	645.0	648.6
120°	671.5	676.8	689.1	700.2	701.9
122.5°	726.5	728.5	742.8	752.9	754.1
125°	778.1	781.6	791.0	802.7	806.5
127.5°	828.2	828.8	842.8	850.1	852.3
130°	875.9	876.4	886.7	896.0	898.7
132.5°	920.2	921.6	931.1	939.8	941.7
135°	963.9	962.9	970.0	979.4	984.1
137.5°	1003.2	1002.8	1009.5	1018.4	1019.7
140°	1041.5	1043.1	1045.4	1054.4	1057.7
142.5°	1075.5	1079.4	1079.9	1086.9	1088.8
145°	1110.9	1113.3	1113.3	1117.0	1120.9
147.5°	1138.4	1143.8	1142.8	1144.3	1147.1
150°	1168.8	1172.3	1171.3	1171.3	1172.3
152.5°	1193.9	1196.8	1194.9	1196.8	1195.9
155°	1217.5	1218.5	1215.5	1219.4	1216.5
157.5°	1238.1	1238.1	1234.2	1239.1	1234.2
160°	1255.8	1252.9	1251.9	1257.8	1251.9
162.5°	1271.5	1267.6	1266.6	1272.5	1265.6
165°	1284.3	1279.4	1279.4	1287.2	1278.4
167.5°	1295.1	1290.2	1289.2	1298.1	1288.2
170°	1303.9	1298.1	1299.0	1306.9	1297.1
172.5°	1309.8	1303.9	1304.9	1312.8	1302.0
175°	1313.8	1307.9	1308.9	1317.7	1305.9
177.5°	1316.7	1309.8	1311.8	1319.7	1307.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)