

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001122

Luminaire Tested: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001122
REPORT IS A COMBINATION OF REPORTS P995738 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5519.0 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001122

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001122

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35				27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29				22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24				19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21				16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18				14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16				12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14				10
7	54	43	35	30	48	38	32	27	30	26	22	23	20	17	16	14	12				9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	14	12	11				8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10				7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3879 cd/sqm

TEST NUMBER: P1001122

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.4	2.7
20°-30°	222.8	4.0
30°-40°	258.9	4.7
40°-50°	258.9	4.7
50°-60°	226.5	4.1
60°-70°	168.1	3.0
70°-80°	95.4	1.7
80°-90°	30.0	0.5
90°-100°	43.5	0.8
100°-110°	286.4	5.2
110°-120°	546.8	9.9
120°-130°	694.2	12.6
130°-140°	742.6	13.5
140°-150°	694.4	12.6
150°-160°	560.0	10.1
160°-170°	361.1	6.5
170°-180°	124.5	2.3
0°-30°	427.8	7.8
0°-40°	686.8	12.4
0°-60°	1172.2	21.2
0°-90°	1465.7	26.6
90°-120°	876.6	15.9
90°-150°	3007.8	54.5
90°-180°	4053.0	73.4
0°-180°	5519.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	3	14	22	27	29	4
95°	54	21	22	27	28	66
105°	295	301	306	314	279	309
115°	551	554	553	554	554	542
125°	774	778	776	779	780	691
135°	960	959	963	965	967	740
145°	1107	1110	1110	1111	1113	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1001122

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	2.9	13.7	21.6	27.4	29.4
92.5°	14.7	12.7	20.6	26.5	26.5
95°	53.9	20.6	21.6	27.4	28.4
97.5°	102.9	124.4	21.6	26.5	27.4
100°	160.7	178.3	43.1	26.5	27.4
102.5°	225.3	237.1	248.9	28.4	28.4
105°	294.9	300.8	305.7	314.5	279.2
107.5°	358.6	361.5	368.4	373.3	377.2
110°	423.2	426.2	432.1	434.0	437.0

TEST NUMBER: P1001122

CATALOG NUMBER: SA4XXDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.9	491.8	493.8	492.8	496.7
115°	550.6	553.5	552.6	554.5	554.5
117.5°	608.4	612.3	615.3	614.3	614.3
120°	667.2	671.1	670.1	672.1	670.1
122.5°	722.1	724.0	726.0	727.0	725.0
125°	774.0	777.9	775.9	778.9	779.9
127.5°	824.0	824.9	829.8	828.9	827.9
130°	872.0	872.9	875.9	876.9	876.9
132.5°	916.0	918.0	921.9	922.9	921.9
135°	960.1	959.2	963.1	965.0	967.0
137.5°	999.3	999.3	1004.2	1006.2	1005.2
140°	1037.5	1039.5	1041.5	1044.4	1045.4
142.5°	1071.8	1075.7	1076.7	1078.7	1078.7
145°	1107.1	1110.0	1110.0	1111.0	1113.0
147.5°	1134.5	1140.4	1139.4	1140.4	1141.4
150°	1164.9	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)