

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999940

Luminaire Tested: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999940
REPORT IS A COMBINATION OF REPORTS P988497 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3482.4 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999940

CATALOG NUMBER: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999940

CATALOG NUMBER: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	31
7	62	50	42	36	58	47	40	35	43	37	32	38	34	30	34	30	27
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23
10	51	39	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17256	17256	17256
5°	17284	16417	16295
10°	17114	15571	15057
15°	16879	14572	13645
20°	16568	13435	12168
25°	16249	12269	10817
30°	15820	11133	9342
35°	15400	9988	8075
40°	14975	8863	6769
45°	14480	7703	5632
50°	13965	6584	4585
55°	13432	5464	3640
60°	12811	4370	2754
65°	12101	3332	2239
70°	11238	2416	1780
75°	10153	1843	1359
80°	8583	1249	912
85°	5989	570	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14480 cd/sqm

TEST NUMBER: P999940

CATALOG NUMBER: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	2.9
10°-20°	280.5	8.1
20°-30°	393.8	11.3
30°-40°	429.2	12.3
40°-50°	394.5	11.3
50°-60°	309.8	8.9
60°-70°	201.7	5.8
70°-80°	103.8	3.0
80°-90°	27.6	0.8
90°-100°	72.1	2.1
100°-110°	243.6	7.0
110°-120°	256.1	7.4
120°-130°	210.5	6.0
130°-140°	169.2	4.9
140°-150°	127.8	3.7
150°-160°	89.9	2.6
160°-170°	52.9	1.5
170°-180°	17.2	0.5
0°-30°	776.4	22.3
0°-40°	1205.7	34.6
0°-60°	1910.0	54.8
0°-90°	2243.1	64.4
90°-120°	571.7	16.4
90°-150°	1079.3	31.0
90°-180°	1239.0	35.6
0°-180°	3482.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1090	1085	1072	1081	1078	103
15°	1037	1026	992	974	964	292
25°	941	910	844	804	789	433
35°	811	761	674	612	590	508
45°	663	597	493	423	400	512
55°	504	427	321	261	243	450
65°	340	260	172	138	135	337
75°	182	112	79	72	71	192
85°	42	22	19	19	19	49
90°	0	5	12	11	11	3
95°	12	29	134	51	39	12
105°	42	63	253	453	385	44
115°	74	93	212	437	507	73
125°	102	121	204	354	411	91
135°	120	144	201	298	341	93
145°	137	158	200	249	272	86
155°	156	169	194	220	229	72
165°	170	175	186	198	201	48
175°	177	178	179	181	181	17
180°	178	178	178	178	178	

TEST NUMBER: P999940

CATALOG NUMBER: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.1	1090.1	1090.1	1090.1	1090.1
2.5°	1095.1	1090.1	1079.3	1089.1	1087.2
5°	1090.1	1085.2	1072.4	1081.3	1078.3
7.5°	1081.3	1075.3	1061.5	1065.5	1060.5
10°	1069.4	1062.5	1042.8	1039.8	1033.9
12.5°	1054.6	1045.7	1019.1	1013.2	1002.3
15°	1036.9	1026.0	992.5	973.7	963.9
17.5°	1016.1	1000.4	958.9	937.2	921.4
20°	992.5	972.7	923.4	898.7	877.0
22.5°	966.8	944.1	886.9	853.4	838.6
25°	941.2	909.6	844.5	804.0	789.2
27.5°	910.6	877.0	805.0	758.7	736.0
30°	878.0	840.5	761.6	711.3	684.7
32.5°	846.5	801.1	720.2	661.0	636.3
35°	810.9	760.6	673.8	611.7	590.0
37.5°	776.4	722.2	630.4	562.3	537.7
40°	739.9	680.7	585.0	515.0	489.3
42.5°	702.4	639.3	539.6	466.6	442.0
45°	663.0	596.9	493.3	423.2	399.6
47.5°	625.5	555.4	448.9	378.8	357.1
50°	584.0	514.0	405.5	337.4	316.7
52.5°	543.6	469.6	364.0	298.9	280.2
55°	504.1	427.2	320.6	261.4	242.7
57.5°	463.7	384.8	282.2	226.9	211.1
60°	422.2	343.3	241.7	191.4	175.6
62.5°	381.8	302.9	207.2	159.8	151.9
65°	340.4	260.4	171.7	138.1	135.2
67.5°	300.9	221.0	138.1	121.3	118.4
70°	259.5	182.5	114.4	104.6	100.6
72.5°	220.0	147.0	95.7	87.8	85.8
75°	181.5	112.5	78.9	72.0	71.0
77.5°	143.0	79.9	62.2	58.2	56.2
80°	107.5	57.2	47.4	43.4	43.4
82.5°	75.0	38.5	32.6	30.6	30.6
85°	42.4	21.7	18.7	18.7	18.7
87.5°	15.8	7.9	7.9	6.9	6.9
90°	0.3	4.6	11.6	11.1	11.3
92.5°	5.1	16.2	52.6	24.2	20.9
95°	12.0	29.4	134.0	50.6	39.0
97.5°	17.8	38.8	218.4	101.6	65.3
100°	26.3	47.5	270.0	202.2	122.4
102.5°	34.2	55.4	271.8	341.8	238.6
105°	41.7	62.9	253.3	452.8	385.2
107.5°	49.9	70.4	236.2	493.0	484.0
110°	58.1	78.2	224.6	486.4	524.4



TEST NUMBER: P999940

CATALOG NUMBER: SA2XXRDIP-B675D330UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.6	85.4	217.1	464.4	523.7
115°	73.5	92.8	211.9	437.4	506.9
117.5°	81.7	100.2	209.2	411.6	481.6
120°	89.2	107.3	206.8	388.4	457.4
122.5°	96.4	114.6	205.4	370.5	432.1
125°	102.5	121.4	203.7	354.3	411.2
127.5°	107.7	127.6	202.7	340.4	391.7
130°	112.1	133.3	202.0	326.4	375.7
132.5°	116.2	138.8	201.7	311.9	358.9
135°	120.3	143.6	201.3	297.8	340.8
137.5°	124.1	147.6	201.3	283.4	323.4
140°	128.5	151.4	201.0	270.7	305.3
142.5°	133.0	154.5	201.0	258.6	287.1
145°	137.4	158.0	200.3	248.6	272.1
147.5°	142.2	160.6	199.3	240.0	258.8
150°	147.0	163.4	198.3	232.4	247.1
152.5°	151.8	166.2	196.6	226.2	237.2
155°	156.2	168.7	194.5	220.0	228.7
157.5°	160.0	170.8	192.4	214.2	221.2
160°	163.7	172.8	190.4	208.3	214.0
162.5°	167.5	174.4	188.7	202.8	207.1
165°	170.2	175.4	186.3	197.6	200.7
167.5°	172.6	176.4	184.2	192.8	194.5
170°	175.0	176.9	182.5	188.4	189.0
172.5°	176.4	177.4	180.5	184.4	184.6
175°	177.4	177.6	179.1	181.4	180.8
177.5°	178.1	177.8	177.8	179.1	178.1
180°	177.8	177.8	177.8	177.8	177.8

(END OF REPORT)