

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999961

Luminaire Tested: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999961
REPORT IS A COMBINATION OF REPORTS P988518 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4227.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999961

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P999961

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	52
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P999961

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	2.5
10°-20°	291.7	6.9
20°-30°	409.6	9.7
30°-40°	446.5	10.6
40°-50°	410.3	9.7
50°-60°	322.3	7.6
60°-70°	209.8	5.0
70°-80°	108.0	2.6
80°-90°	29.5	0.7
90°-100°	41.9	1.0
100°-110°	133.2	3.2
110°-120°	227.8	5.4
120°-130°	299.7	7.1
130°-140°	336.4	8.0
140°-150°	329.9	7.8
150°-160°	276.7	6.5
160°-170°	183.5	4.3
170°-180°	64.1	1.5
0°-30°	807.6	19.1
0°-40°	1254.0	29.7
0°-60°	1986.6	47.0
0°-90°	2333.9	55.2
90°-120°	402.9	9.5
90°-150°	1368.8	32.4
90°-180°	1893.0	44.8
0°-180°	4227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	1	7	20	19	19	4
95°	30	35	37	37	35	33
105°	123	125	126	127	127	130
115°	229	232	231	230	229	226
125°	333	338	336	334	334	297
135°	430	437	438	437	435	332
145°	522	526	530	530	528	326
155°	597	599	600	603	602	275
165°	650	649	649	653	650	183
175°	676	674	673	677	674	64
180°	677	677	677	677	677	

TEST NUMBER: P999961

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	0.6	7.4	20.0	18.9	19.4
92.5°	12.6	17.1	17.7	18.3	18.3
95°	29.7	35.4	36.6	36.6	35.4
97.5°	49.7	54.9	57.1	57.1	57.1
100°	72.6	77.1	78.9	78.9	78.3
102.5°	96.6	100.0	102.3	102.9	102.3
105°	122.9	124.6	125.7	126.9	126.9
107.5°	149.1	151.4	151.4	152.0	149.1
110°	174.3	177.7	177.7	177.7	176.0

TEST NUMBER: P999961

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.7	205.1	204.6	202.8	201.7
115°	228.6	232.0	230.8	230.3	228.6
117.5°	255.4	260.0	257.1	255.4	253.7
120°	282.3	286.8	282.3	282.3	280.6
122.5°	306.8	312.6	309.7	308.0	306.8
125°	332.6	337.7	336.0	334.3	333.7
127.5°	357.7	364.0	361.7	359.4	357.7
130°	381.1	388.6	387.4	386.3	384.0
132.5°	407.4	413.1	413.7	410.8	409.1
135°	430.3	436.6	437.7	437.1	435.4
137.5°	455.4	460.5	461.7	461.1	458.8
140°	477.7	482.8	485.7	485.7	483.4
142.5°	500.5	505.7	507.4	508.0	505.7
145°	522.3	526.3	529.7	530.3	528.0
147.5°	541.7	546.8	549.1	550.3	548.0
150°	561.7	565.1	567.4	569.1	567.4
152.5°	579.4	582.8	585.7	588.0	585.7
155°	597.1	598.8	600.5	603.4	601.7
157.5°	612.5	613.7	614.8	618.8	616.0
160°	626.3	627.4	628.0	631.4	629.1
162.5°	638.8	638.8	639.4	643.4	640.5
165°	649.7	649.1	649.1	653.1	650.3
167.5°	659.4	657.7	657.7	661.7	658.8
170°	666.8	665.1	664.5	668.5	665.1
172.5°	672.0	670.3	669.7	673.7	670.3
175°	676.0	674.3	673.1	677.1	673.7
177.5°	678.3	676.5	675.4	678.8	675.4
180°	677.1	677.1	677.1	677.1	677.1

(END OF REPORT)