

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999962

Luminaire Tested: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999962
REPORT IS A COMBINATION OF REPORTS P988519 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4405.3 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999962

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999962

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	59	56	54	51	47	45	43
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P999962

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	2.4
10°-20°	291.7	6.6
20°-30°	409.6	9.3
30°-40°	446.5	10.1
40°-50°	410.3	9.3
50°-60°	322.3	7.3
60°-70°	209.8	4.8
70°-80°	108.0	2.5
80°-90°	29.5	0.7
90°-100°	120.5	2.7
100°-110°	407.2	9.2
110°-120°	428.0	9.7
120°-130°	352.0	8.0
130°-140°	282.8	6.4
140°-150°	213.7	4.8
150°-160°	150.2	3.4
160°-170°	88.4	2.0
170°-180°	28.8	0.7
0°-30°	807.6	18.3
0°-40°	1254.0	28.5
0°-60°	1986.6	45.1
0°-90°	2333.9	53.0
90°-120°	955.6	21.7
90°-150°	1804.1	41.0
90°-180°	2071.0	47.0
0°-180°	4405.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	1	8	19	19	19	4
95°	20	49	224	85	65	21
105°	70	105	423	757	644	74
115°	123	155	354	731	847	122
125°	171	203	340	592	687	152
135°	201	240	336	498	570	155
145°	230	264	335	416	455	144
155°	261	282	325	368	382	120
165°	284	293	311	330	335	80
175°	296	297	299	303	302	28
180°	297	297	297	297	297	

TEST NUMBER: P999962

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	0.6	7.8	19.4	18.6	18.9
92.5°	8.6	27.2	88.0	40.6	34.9
95°	20.0	49.2	224.0	84.6	65.1
97.5°	29.7	64.8	365.1	169.7	109.1
100°	44.0	79.4	451.4	338.0	204.5
102.5°	57.1	92.6	454.2	571.4	398.8
105°	69.7	105.1	423.4	756.8	643.9
107.5°	83.4	117.7	394.8	823.9	809.1
110°	97.1	130.6	375.4	813.0	876.5

TEST NUMBER: P999962

CATALOG NUMBER: SA2XXRDIP-B675D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.7	142.9	362.8	776.2	875.3
115°	122.8	155.1	354.2	731.0	847.3
117.5°	136.6	167.4	349.7	687.9	805.1
120°	149.1	179.4	345.7	649.4	764.5
122.5°	161.1	191.7	343.4	619.4	722.2
125°	171.4	202.8	340.5	592.2	687.4
127.5°	180.0	213.4	338.8	569.1	654.8
130°	187.4	222.8	337.7	545.6	627.9
132.5°	194.3	232.0	337.1	521.3	599.9
135°	201.1	240.0	336.5	497.7	569.7
137.5°	207.4	246.8	336.5	473.6	540.5
140°	214.8	253.1	336.0	452.6	510.2
142.5°	222.3	258.2	336.0	432.2	479.9
145°	229.7	264.0	334.8	415.7	454.8
147.5°	237.7	268.6	333.1	401.1	432.5
150°	245.7	273.2	331.4	388.5	413.1
152.5°	253.7	277.7	328.5	378.0	396.5
155°	261.1	282.0	325.1	367.6	382.2
157.5°	267.4	285.4	321.7	358.0	369.7
160°	273.7	288.8	318.3	348.2	357.7
162.5°	280.0	291.4	315.4	339.1	346.2
165°	284.5	293.1	311.4	330.2	335.4
167.5°	288.5	294.8	308.0	322.2	325.1
170°	292.5	295.6	305.1	314.8	316.0
172.5°	294.8	296.6	301.7	308.2	308.5
175°	296.5	296.8	299.4	303.1	302.3
177.5°	297.7	297.1	297.1	299.4	297.7
180°	297.1	297.1	297.1	297.1	297.1

(END OF REPORT)