

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001185

Luminaire Tested: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001185
REPORT IS A COMBINATION OF REPORTS P995801 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6248.0 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001185

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001185

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24		
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20		
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	24	22	17		
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19	14		
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16	12		
5	64	53	45	39	56	47	40	35	37	32	28	27	24	21	18	16	14	10		
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	13	9		
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11	8		
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7		
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7		
10	43	32	25	20	38	29	22	18	22	18	15	17	14	11	11	9	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3893 cd/sqm

TEST NUMBER: P1001185

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	0.9
10°-20°	151.9	2.4
20°-30°	223.5	3.6
30°-40°	259.8	4.2
40°-50°	259.8	4.2
50°-60°	227.2	3.6
60°-70°	168.7	2.7
70°-80°	95.7	1.5
80°-90°	30.6	0.5
90°-100°	51.2	0.8
100°-110°	337.5	5.4
110°-120°	644.4	10.3
120°-130°	818.1	13.1
130°-140°	875.1	14.0
140°-150°	818.3	13.1
150°-160°	659.9	10.6
160°-170°	425.6	6.8
170°-180°	146.7	2.3
0°-30°	429.3	6.9
0°-40°	689.1	11.0
0°-60°	1176.2	18.8
0°-90°	1471.2	23.5
90°-120°	1033.1	16.5
90°-150°	3544.6	56.7
90°-180°	4777.0	76.5
0°-180°	6248.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	4	16	25	32	35	5
95°	64	24	25	32	34	78
105°	348	354	360	371	329	364
115°	649	652	651	654	654	639
125°	912	917	914	918	919	815
135°	1132	1130	1135	1137	1140	872
145°	1305	1308	1308	1309	1312	815
155°	1431	1432	1428	1433	1429	660
165°	1509	1503	1503	1512	1502	426
175°	1544	1537	1538	1548	1534	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1001185

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	3.5	16.2	25.4	32.3	34.6
92.5°	17.3	15.0	24.2	31.2	31.2
95°	63.5	24.2	25.4	32.3	33.5
97.5°	121.2	146.6	25.4	31.2	32.3
100°	189.4	210.1	50.8	31.2	32.3
102.5°	265.6	279.4	293.3	33.5	33.5
105°	347.5	354.5	360.2	370.6	329.1
107.5°	422.6	426.1	434.1	439.9	444.5
110°	498.8	502.3	509.2	511.5	515.0

TEST NUMBER: P1001185

CATALOG NUMBER: SA4XXDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.7	579.6	581.9	580.8	585.4
115°	648.9	652.4	651.2	653.5	653.5
117.5°	717.0	721.6	725.1	723.9	723.9
120°	786.3	790.9	789.8	792.1	789.8
122.5°	851.0	853.3	855.6	856.7	854.4
125°	912.1	916.8	914.5	917.9	919.1
127.5°	971.0	972.2	978.0	976.8	975.6
130°	1027.6	1028.8	1032.2	1033.4	1033.4
132.5°	1079.6	1081.9	1086.5	1087.6	1086.5
135°	1131.5	1130.4	1135.0	1137.3	1139.6
137.5°	1177.7	1177.7	1183.5	1185.8	1184.6
140°	1222.7	1225.0	1227.4	1230.8	1232.0
142.5°	1263.1	1267.8	1268.9	1271.2	1271.2
145°	1304.7	1308.2	1308.2	1309.3	1311.6
147.5°	1337.0	1344.0	1342.8	1344.0	1345.1
150°	1372.8	1377.5	1376.3	1376.3	1377.5
152.5°	1402.9	1406.3	1404.0	1406.3	1405.2
155°	1430.6	1431.7	1428.3	1432.9	1429.4
157.5°	1454.8	1454.8	1450.2	1456.0	1450.2
160°	1475.6	1472.1	1471.0	1477.9	1471.0
162.5°	1494.1	1489.5	1488.3	1495.2	1487.1
165°	1509.1	1503.3	1503.3	1512.5	1502.2
167.5°	1521.8	1516.0	1514.9	1525.2	1513.7
170°	1532.2	1525.2	1526.4	1535.6	1524.1
172.5°	1539.1	1532.2	1533.3	1542.6	1529.9
175°	1543.7	1536.8	1537.9	1548.3	1534.5
177.5°	1547.2	1539.1	1541.4	1550.6	1536.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)