

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999964

Luminaire Tested: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999964
REPORT IS A COMBINATION OF REPORTS P988521 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4466.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55
2	92	85	79	75	86	80	75	71	70	66	63	60	57	55	51	49	48
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	39	35	33
6	67	55	48	42	62	52	45	40	46	41	37	41	36	33	35	32	30
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27
8	58	46	39	33	54	44	37	32	39	33	30	34	30	27	30	27	24
9	54	42	35	30	51	40	34	29	36	31	27	32	28	25	28	25	22
10	51	39	32	28	48	37	31	26	33	28	24	30	26	22	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23476	23476	23476	23476
5°	23531	24936	23613	19921
10°	23273	26356	23438	16450
15°	22767	26365	23153	12359
20°	22160	21793	22641	10196
25°	21423	13618	21886	8673
30°	20483	8719	21040	7468
35°	19339	6701	19966	6390
40°	18063	5632	18837	5589
45°	16701	4794	17400	4692
50°	15305	4074	16020	4058
55°	13760	3540	14501	3493
60°	12384	2699	13042	2667
65°	11102	2031	11760	2304
70°	9688	1622	10446	1879
75°	8190	1242	8939	1420
80°	6499	845	6994	931
85°	4520	437	4944	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21476 cd/sqm

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.7	3.1
10°-20°	392.7	8.8
20°-30°	505.4	11.3
30°-40°	479.4	10.7
40°-50°	410.9	9.2
50°-60°	312.9	7.0
60°-70°	197.3	4.4
70°-80°	98.4	2.2
80°-90°	27.2	0.6
90°-100°	42.1	0.9
100°-110°	133.7	3.0
110°-120°	228.8	5.1
120°-130°	300.9	6.7
130°-140°	337.8	7.6
140°-150°	331.2	7.4
150°-160°	277.9	6.2
160°-170°	184.3	4.1
170°-180°	64.4	1.4
0°-30°	1038.7	23.3
0°-40°	1518.1	34.0
0°-60°	2241.9	50.2
0°-90°	2564.9	57.4
90°-120°	404.6	9.1
90°-150°	1374.5	30.8
90°-180°	1901.0	42.6
0°-180°	4466.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1483	1483	1483	1483	1483	
5°	1484	1650	1489	1318	1484	141
15°	1399	1862	1422	873	1399	393
25°	1241	994	1268	633	1241	570
35°	1018	490	1051	467	1018	637
45°	765	340	797	333	765	590
55°	516	236	544	233	516	465
65°	312	123	331	139	312	310
75°	146	65	160	74	146	158
85°	32	19	35	20	32	36
90°	1	20	1	20	1	4
95°	30	36	30	36	30	33
105°	123	127	123	127	123	130
115°	230	230	230	230	230	227
125°	334	335	334	335	334	298
135°	432	437	432	437	432	334
145°	524	530	524	530	524	328
155°	600	604	600	604	600	276
165°	652	653	652	653	652	184
175°	679	676	679	676	679	64
180°	680	680	680	680	680	



TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1492.4	1498.6	1501.7	1505.8	1515.1	1521.2	1530.5	1532.6	1531.6	1535.7	1524.3
5°	1484.1	1497.5	1509.9	1520.2	1536.7	1547.0	1558.3	1571.7	1574.8	1590.3	1581.0
7.5°	1472.8	1492.4	1509.9	1530.5	1555.3	1568.7	1586.2	1606.8	1616.1	1634.6	1639.8
10°	1454.3	1482.1	1512.0	1533.6	1567.6	1591.3	1607.8	1640.8	1662.4	1690.3	1686.1
12.5°	1424.4	1460.4	1500.6	1536.7	1581.0	1596.5	1627.4	1661.4	1689.2	1715.0	1737.7
15°	1398.6	1439.8	1484.1	1528.5	1579.0	1607.8	1638.7	1683.1	1712.9	1758.3	1777.9
17.5°	1363.6	1416.1	1468.7	1518.2	1577.9	1610.9	1649.0	1692.3	1736.7	1779.9	1795.4
20°	1327.5	1384.2	1440.9	1507.8	1575.9	1607.8	1647.0	1700.6	1743.9	1777.9	1777.9
22.5°	1284.2	1353.2	1418.2	1482.1	1556.3	1602.7	1642.9	1705.7	1736.7	1743.9	1716.0
25°	1240.9	1310.0	1381.1	1460.4	1545.0	1586.2	1631.5	1690.3	1700.6	1671.7	1599.6
27.5°	1189.4	1266.7	1347.1	1432.6	1521.2	1572.8	1614.0	1653.2	1633.6	1556.3	1443.9
30°	1136.8	1220.3	1311.0	1392.4	1499.6	1547.0	1582.1	1593.4	1531.6	1405.8	1260.5
32.5°	1082.2	1163.6	1259.5	1357.4	1465.6	1510.9	1533.6	1503.7	1390.4	1231.6	1054.4
35°	1018.3	1110.0	1210.0	1312.0	1419.2	1453.2	1466.6	1393.4	1248.1	1043.0	866.8
37.5°	960.6	1052.3	1159.5	1263.6	1367.7	1386.2	1372.8	1258.4	1073.9	870.9	698.8
40°	892.5	990.5	1095.6	1212.0	1297.6	1302.7	1269.8	1121.4	892.5	701.9	595.7
42.5°	829.7	928.6	1033.7	1152.3	1217.2	1199.7	1155.4	960.6	745.2	605.0	519.4
45°	764.7	858.5	971.9	1077.0	1123.4	1082.2	1015.2	808.0	625.6	520.5	454.5
47.5°	701.9	789.5	901.8	1002.8	1011.1	964.7	885.3	677.1	542.1	457.6	404.0
50°	640.0	727.6	832.8	916.3	908.0	844.1	754.4	588.5	471.0	404.0	359.7
52.5°	578.2	657.6	759.6	825.6	790.5	728.7	640.0	498.8	411.2	352.5	318.5
55°	516.4	590.6	678.2	732.8	677.1	606.0	543.2	427.7	356.6	309.2	283.4
57.5°	464.8	523.6	604.0	636.9	570.0	514.3	459.7	367.9	309.2	275.2	245.3
60°	408.1	461.7	527.7	547.3	478.2	432.9	386.5	311.3	264.9	235.0	215.4
62.5°	359.7	404.0	454.5	454.5	393.7	359.7	324.7	260.8	222.6	198.9	189.6
65°	312.3	344.2	380.3	376.2	324.7	294.8	266.9	215.4	186.5	170.1	160.8
67.5°	265.9	290.6	314.3	299.9	262.8	237.1	211.3	174.2	154.6	143.3	130.9
70°	223.7	243.2	255.6	242.2	205.1	183.5	164.9	140.2	124.7	110.3	103.1
72.5°	187.6	195.8	199.9	183.5	152.5	140.2	126.8	109.2	95.9	88.6	86.6
75°	146.4	153.6	150.5	138.1	112.3	103.1	92.8	80.4	77.3	73.2	71.1
77.5°	114.4	114.4	109.2	97.9	80.4	73.2	69.1	62.9	59.8	58.7	56.7
80°	81.4	80.4	77.3	64.9	54.6	50.5	50.5	46.4	45.3	43.3	43.3
82.5°	53.6	53.6	49.5	39.2	36.1	35.0	34.0	32.0	32.0	30.9	30.9
85°	32.0	29.9	24.7	21.6	20.6	20.6	19.6	18.6	19.6	18.6	18.6
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	0.6	2.1	3.7	5.2	6.7	7.5	8.9	11.7	14.5	17.3	20.1
92.5°	12.6	13.6	14.6	15.7	16.7	17.2	17.3	17.4	17.5	17.7	17.8
95°	29.8	31.1	32.4	33.7	35.0	35.6	35.7	36.0	36.2	36.5	36.7
97.5°	49.9	51.1	52.2	53.4	54.5	55.1	55.4	55.9	56.4	56.9	57.4
100°	72.9	73.9	74.9	76.0	77.0	77.5	77.7	78.1	78.4	78.8	79.2
102.5°	97.0	97.8	98.5	99.3	100.0	100.4	100.7	101.2	101.7	102.2	102.7
105°	123.4	123.8	124.2	124.5	124.9	125.1	125.2	125.5	125.7	126.0	126.2
107.5°	149.8	150.3	150.8	151.3	151.8	152.1	152.1	152.1	152.1	152.1	152.1
110°	175.0	175.8	176.6	177.3	178.1	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	202.6	203.4	204.1	204.9	205.6	206.0	205.9	205.8	205.7	205.5	205.4
115°	229.5	230.3	231.1	231.8	232.6	233.0	232.9	232.6	232.3	232.1	231.8
117.5°	256.5	257.5	258.5	259.6	260.6	261.1	260.8	260.1	259.5	258.8	258.2
120°	283.5	284.5	285.5	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5
122.5°	308.1	309.4	310.7	312.0	313.3	313.9	313.6	312.9	312.3	311.6	311.0
125°	334.0	335.1	336.3	337.4	338.5	339.1	338.9	338.5	338.2	337.8	337.4
127.5°	359.2	360.6	362.0	363.4	364.8	365.5	365.2	364.7	364.2	363.7	363.2
130°	382.7	384.4	386.0	387.7	389.4	390.2	390.1	389.8	389.5	389.3	389.0
132.5°	409.1	410.4	411.7	413.0	414.3	414.9	415.0	415.1	415.2	415.3	415.4
135°	432.1	433.5	434.9	436.3	437.7	438.4	438.5	438.8	439.0	439.3	439.5
137.5°	457.3	458.5	459.6	460.8	461.9	462.5	462.6	462.9	463.1	463.4	463.6
140°	479.7	480.9	482.0	483.2	484.3	484.9	485.2	485.8	486.5	487.1	487.7
142.5°	502.7	503.8	505.0	506.1	507.2	507.8	508.0	508.4	508.7	509.1	509.5
145°	524.5	525.4	526.3	527.2	528.1	528.5	528.9	529.6	530.4	531.1	531.9
147.5°	544.0	545.1	546.3	547.4	548.5	549.1	549.4	549.9	550.4	550.9	551.4
150°	564.1	564.9	565.6	566.4	567.1	567.5	567.8	568.3	568.8	569.3	569.8
152.5°	581.8	582.6	583.4	584.1	584.9	585.3	585.6	586.3	586.9	587.6	588.2
155°	599.6	600.0	600.4	600.8	601.2	601.4	601.6	602.0	602.3	602.7	603.1
157.5°	615.1	615.4	615.6	615.9	616.2	616.3	616.4	616.7	616.9	617.2	617.4
160°	628.9	629.1	629.4	629.6	629.9	630.0	630.1	630.2	630.3	630.5	630.6
162.5°	641.5	641.5	641.5	641.5	641.5	641.5	641.6	641.7	641.8	642.0	642.1
165°	652.4	652.3	652.2	652.1	652.0	651.9	651.9	651.9	651.9	651.9	651.9
167.5°	662.2	661.8	661.4	661.1	660.7	660.5	660.5	660.5	660.5	660.5	660.5
170°	669.6	669.2	668.8	668.5	668.1	667.9	667.8	667.7	667.6	667.4	667.3
172.5°	674.8	674.4	674.0	673.7	673.3	673.1	673.0	672.9	672.8	672.6	672.5
175°	678.8	678.4	678.0	677.7	677.3	677.1	677.0	676.7	676.5	676.2	676.0
177.5°	681.1	680.7	680.3	680.0	679.6	679.4	679.3	679.0	678.7	678.5	678.2
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1535.7	1537.7	1540.8	1555.3	1557.3	1561.4	1559.4	1559.4	1560.4	1558.3	1559.4
5°	1601.6	1604.7	1620.2	1637.7	1641.8	1637.7	1642.9	1650.1	1650.1	1650.1	1648.0
7.5°	1663.5	1674.8	1692.3	1718.1	1723.3	1728.4	1737.7	1731.5	1733.6	1742.8	1739.7
10°	1723.3	1739.7	1759.3	1781.0	1792.3	1799.5	1803.6	1812.9	1834.6	1809.8	1819.1
12.5°	1779.9	1803.6	1824.3	1848.0	1856.2	1865.5	1868.6	1876.8	1876.8	1875.8	1883.0
15°	1817.0	1838.7	1857.2	1872.7	1874.8	1872.7	1870.6	1871.7	1874.8	1862.4	1869.6
17.5°	1825.3	1827.3	1833.5	1827.3	1828.4	1806.7	1794.4	1791.3	1762.4	1763.4	1787.2
20°	1785.1	1750.1	1740.8	1706.8	1686.1	1630.5	1628.4	1613.0	1552.2	1570.7	1566.6
22.5°	1674.8	1615.0	1535.7	1496.5	1476.9	1418.2	1372.8	1340.9	1319.2	1297.6	1288.3
25°	1529.5	1432.6	1320.3	1243.0	1231.6	1177.0	1093.5	1054.4	1008.0	993.6	1018.3
27.5°	1341.9	1216.2	1089.4	970.9	949.2	899.8	857.5	829.7	776.1	773.0	775.1
30°	1087.3	960.6	854.4	777.1	723.5	700.8	673.0	652.4	630.8	639.0	641.1
32.5°	893.6	773.0	674.0	632.8	608.1	593.7	570.0	556.6	547.3	544.2	543.2
35°	710.1	629.7	585.4	545.2	530.8	520.5	503.0	496.8	488.5	489.6	489.6
37.5°	608.1	541.1	508.1	487.5	474.1	468.9	457.6	451.4	446.3	444.2	447.3
40°	524.6	478.2	457.6	439.1	427.7	425.7	419.5	412.3	406.1	407.1	410.2
42.5°	463.8	437.0	412.3	397.8	389.6	386.5	381.3	376.2	376.2	373.1	372.1
45°	415.4	393.7	373.1	359.7	354.5	350.4	344.2	343.2	339.1	340.1	341.1
47.5°	372.1	354.5	339.1	325.7	320.5	319.5	313.3	309.2	309.2	308.2	307.1
50°	332.9	315.4	302.0	294.8	287.6	285.5	284.5	283.4	281.4	281.4	282.4
52.5°	301.0	283.4	273.1	266.9	262.8	260.8	260.8	259.7	259.7	259.7	258.7
55°	265.9	251.5	243.2	241.2	239.1	238.1	237.1	235.0	234.0	236.0	234.0
57.5°	232.9	227.8	220.6	218.5	213.3	213.3	210.3	208.2	206.1	208.2	208.2
60°	207.2	199.9	195.8	189.6	185.5	181.4	176.2	175.2	173.1	172.1	171.1
62.5°	180.4	174.2	163.9	154.6	148.4	144.3	142.2	141.2	141.2	140.2	140.2
65°	150.5	136.0	130.9	127.8	126.8	125.7	123.7	122.6	123.7	122.6	123.7
67.5°	117.5	115.4	112.3	110.3	109.2	108.2	108.2	107.2	107.2	107.2	107.2
70°	102.0	96.9	95.9	93.8	93.8	92.8	92.8	92.8	92.8	91.7	93.8
72.5°	84.5	81.4	80.4	79.4	79.4	79.4	78.3	78.3	78.3	77.3	78.3
75°	69.1	68.0	66.0	66.0	64.9	66.0	64.9	64.9	63.9	64.9	64.9
77.5°	55.7	54.6	53.6	53.6	52.6	52.6	52.6	52.6	52.6	52.6	53.6
80°	42.3	41.2	40.2	41.2	40.2	41.2	40.2	40.2	41.2	40.2	40.2
82.5°	30.9	29.9	29.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9	28.9
85°	18.6	17.5	17.5	18.6	17.5	18.6	17.5	17.5	17.5	18.6	18.6
87.5°	8.2	9.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.3
90°	19.8	19.6	19.3	19.0	18.9	19.0	19.1	19.2	19.4	19.5	19.4
92.5°	17.9	18.1	18.2	18.3	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.7	36.7	36.7	36.7	36.6	36.3	36.1	35.8	35.6	35.8
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.2	79.2	79.2	79.2	79.1	79.0	78.9	78.7	78.6	78.7
102.5°	102.8	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.8
105°	126.5	126.7	127.0	127.3	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.2	152.3	152.4	152.5	152.6	152.3	151.7	151.0	150.4	149.8	150.4
110°	178.5	178.5	178.5	178.5	178.5	178.3	177.9	177.5	177.1	176.7	177.1

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	205.0	204.6	204.3	203.9	203.7	203.6	203.3	203.1	202.8	202.6	202.8
115°	231.7	231.5	231.4	231.3	231.2	231.0	230.6	230.3	229.9	229.5	229.9
117.5°	257.8	257.4	257.1	256.7	256.5	256.3	255.9	255.6	255.2	254.8	255.2
120°	283.5	283.5	283.5	283.5	283.5	283.3	282.9	282.5	282.1	281.7	282.1
122.5°	310.6	310.2	309.9	309.5	309.3	309.2	308.9	308.6	308.4	308.1	308.4
125°	337.0	336.6	336.3	335.9	335.7	335.6	335.5	335.4	335.2	335.1	335.2
127.5°	362.7	362.2	361.7	361.2	360.9	360.7	360.3	360.0	359.6	359.2	359.6
130°	388.8	388.5	388.3	388.0	387.9	387.6	387.1	386.6	386.1	385.6	386.1
132.5°	414.8	414.2	413.5	412.9	412.6	412.4	412.0	411.7	411.3	410.9	411.3
135°	439.4	439.3	439.2	439.1	439.0	438.8	438.4	438.0	437.6	437.2	437.6
137.5°	463.5	463.4	463.3	463.2	463.1	462.8	462.3	461.8	461.3	460.8	461.3
140°	487.7	487.7	487.7	487.7	487.7	487.4	486.9	486.4	485.9	485.4	485.9
142.5°	509.6	509.8	509.9	510.0	510.1	509.8	509.3	508.8	508.3	507.8	508.3
145°	532.0	532.2	532.3	532.4	532.5	532.2	531.7	531.2	530.7	530.2	530.7
147.5°	551.7	551.9	552.2	552.5	552.6	552.3	551.8	551.3	550.8	550.3	550.8
150°	570.2	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	570.2
152.5°	588.7	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	588.7
155°	603.7	604.3	605.0	605.6	605.9	605.7	605.3	605.0	604.6	604.2	604.6
157.5°	618.3	619.2	620.1	621.0	621.4	621.1	620.5	619.8	619.2	618.6	619.2
160°	631.4	632.2	632.9	633.7	634.1	633.8	633.3	632.8	632.3	631.8	632.3
162.5°	643.0	643.9	644.8	645.7	646.1	645.8	645.1	644.5	643.8	643.2	643.8
165°	652.8	653.7	654.6	655.5	655.9	655.6	654.9	654.3	653.6	653.0	653.6
167.5°	661.4	662.3	663.2	664.1	664.5	664.2	663.5	662.9	662.2	661.6	662.2
170°	668.2	669.1	670.0	670.9	671.4	671.0	670.2	669.5	668.7	667.9	668.7
172.5°	673.4	674.3	675.2	676.1	676.5	676.1	675.4	674.6	673.9	673.1	673.9
175°	676.9	677.8	678.7	679.6	680.0	679.6	678.8	678.1	677.3	676.5	677.3
177.5°	679.0	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	679.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1563.5	1556.3	1554.2	1556.3	1554.2	1555.3	1548.0	1521.2	1528.5	1517.1	1523.3
5°	1652.1	1646.0	1632.6	1630.5	1628.4	1626.4	1616.1	1592.4	1583.1	1567.6	1566.6
7.5°	1736.7	1736.7	1726.3	1719.1	1709.9	1702.6	1689.2	1654.2	1639.8	1621.2	1610.9
10°	1820.1	1793.3	1804.7	1797.5	1774.8	1770.7	1745.9	1725.3	1697.5	1678.9	1662.4
12.5°	1879.9	1871.7	1861.4	1855.2	1849.0	1835.6	1819.1	1766.5	1752.1	1715.0	1696.5
15°	1877.9	1872.7	1875.8	1875.8	1873.7	1870.6	1857.2	1819.1	1794.4	1758.3	1726.3
17.5°	1776.8	1790.2	1803.6	1812.9	1833.5	1842.8	1855.2	1832.5	1817.0	1786.1	1752.1
20°	1600.6	1633.6	1672.8	1681.0	1699.5	1754.2	1778.9	1798.5	1804.7	1794.4	1766.5
22.5°	1355.3	1383.1	1478.0	1475.9	1502.7	1567.6	1639.8	1698.5	1744.9	1770.7	1760.4
25°	1061.6	1100.7	1151.2	1189.4	1277.0	1373.9	1463.5	1557.3	1637.7	1708.8	1726.3
27.5°	802.9	854.4	894.6	945.1	989.4	1103.8	1219.3	1365.6	1459.4	1594.4	1664.5
30°	649.3	673.0	713.2	736.9	758.6	846.2	977.1	1121.4	1286.3	1441.9	1562.5
32.5°	554.5	571.0	600.9	611.2	633.9	692.6	775.1	907.0	1077.0	1265.6	1424.4
35°	497.8	515.3	521.5	530.8	549.3	586.4	643.1	739.0	892.5	1077.0	1266.7
37.5°	449.4	458.6	476.2	482.3	488.5	516.4	554.5	621.5	723.5	875.0	1085.3
40°	415.4	420.5	429.8	434.9	439.1	458.6	492.7	538.0	613.2	728.7	922.4
42.5°	379.3	385.5	391.6	397.8	403.0	418.4	439.1	482.3	532.8	620.5	760.6
45°	344.2	348.4	355.6	359.7	366.9	379.3	397.8	427.7	473.1	528.7	642.1
47.5°	312.3	317.4	320.5	325.7	330.8	344.2	361.8	381.3	418.4	473.1	555.5
50°	283.4	289.6	293.7	294.8	298.9	311.3	325.7	347.3	371.0	413.3	485.4
52.5°	262.8	263.8	266.9	271.1	270.0	277.2	290.6	307.1	331.9	365.9	418.4
55°	239.1	242.2	244.3	245.3	245.3	251.5	258.7	274.2	293.7	321.6	365.9
57.5°	209.2	212.3	218.5	220.6	223.7	226.7	229.8	240.1	256.6	283.4	319.5
60°	178.3	180.4	186.5	190.7	192.7	201.0	205.1	213.3	222.6	242.2	276.2
62.5°	143.3	145.3	148.4	152.5	156.7	169.0	179.3	187.6	194.8	208.2	236.0
65°	124.7	125.7	127.8	128.8	129.9	135.0	144.3	155.6	169.0	179.3	195.8
67.5°	108.2	109.2	110.3	112.3	113.4	114.4	118.5	121.6	135.0	149.4	161.8
70°	92.8	94.8	95.9	95.9	96.9	98.9	101.0	105.1	109.2	116.5	131.9
72.5°	78.3	79.4	81.4	81.4	81.4	83.5	85.5	87.6	89.7	93.8	100.0
75°	64.9	67.0	67.0	67.0	68.0	68.0	70.1	72.1	74.2	77.3	79.4
77.5°	53.6	53.6	53.6	53.6	54.6	54.6	55.7	57.7	58.7	59.8	61.8
80°	40.2	41.2	41.2	41.2	42.3	42.3	42.3	44.3	45.3	45.3	47.4
82.5°	29.9	29.9	29.9	30.9	29.9	30.9	30.9	32.0	30.9	32.0	33.0
85°	18.6	18.6	18.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.6
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.3	9.3	9.3
90°	19.2	19.1	19.0	18.9	19.0	19.3	19.6	19.8	20.1	17.3	14.5
92.5°	18.4	18.4	18.4	18.4	18.3	18.2	18.1	17.9	17.8	17.7	17.5
95°	36.1	36.3	36.6	36.7	36.7	36.7	36.7	36.7	36.7	36.5	36.2
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	56.9	56.4
100°	78.9	79.0	79.1	79.2	79.2	79.2	79.2	79.2	79.2	78.8	78.4
102.5°	103.0	103.1	103.2	103.3	103.2	103.1	103.0	102.8	102.7	102.2	101.7
105°	127.4	127.4	127.4	127.4	127.3	127.0	126.7	126.5	126.2	126.0	125.7
107.5°	151.0	151.7	152.3	152.6	152.5	152.4	152.3	152.2	152.1	152.1	152.1
110°	177.5	177.9	178.3	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	203.1	203.3	203.6	203.7	203.9	204.3	204.6	205.0	205.4	205.5	205.7
115°	230.3	230.6	231.0	231.2	231.3	231.4	231.5	231.7	231.8	232.1	232.3
117.5°	255.6	255.9	256.3	256.5	256.7	257.1	257.4	257.8	258.2	258.8	259.5
120°	282.5	282.9	283.3	283.5	283.5	283.5	283.5	283.5	283.5	284.5	285.5
122.5°	308.6	308.9	309.2	309.3	309.5	309.9	310.2	310.6	311.0	311.6	312.3
125°	335.4	335.5	335.6	335.7	335.9	336.3	336.6	337.0	337.4	337.8	338.2
127.5°	360.0	360.3	360.7	360.9	361.2	361.7	362.2	362.7	363.2	363.7	364.2
130°	386.6	387.1	387.6	387.9	388.0	388.3	388.5	388.8	389.0	389.3	389.5
132.5°	411.7	412.0	412.4	412.6	412.9	413.5	414.2	414.8	415.4	415.3	415.2
135°	438.0	438.4	438.8	439.0	439.1	439.2	439.3	439.4	439.5	439.3	439.0
137.5°	461.8	462.3	462.8	463.1	463.2	463.3	463.4	463.5	463.6	463.4	463.1
140°	486.4	486.9	487.4	487.7	487.7	487.7	487.7	487.7	487.7	487.1	486.5
142.5°	508.8	509.3	509.8	510.1	510.0	509.9	509.8	509.6	509.5	509.1	508.7
145°	531.2	531.7	532.2	532.5	532.4	532.3	532.2	532.0	531.9	531.1	530.4
147.5°	551.3	551.8	552.3	552.6	552.5	552.2	551.9	551.7	551.4	550.9	550.4
150°	570.6	570.9	571.3	571.5	571.3	570.9	570.6	570.2	569.8	569.3	568.8
152.5°	589.2	589.7	590.2	590.5	590.2	589.7	589.2	588.7	588.2	587.6	586.9
155°	605.0	605.3	605.7	605.9	605.6	605.0	604.3	603.7	603.1	602.7	602.3
157.5°	619.8	620.5	621.1	621.4	621.0	620.1	619.2	618.3	617.4	617.2	616.9
160°	632.8	633.3	633.8	634.1	633.7	632.9	632.2	631.4	630.6	630.5	630.3
162.5°	644.5	645.1	645.8	646.1	645.7	644.8	643.9	643.0	642.1	642.0	641.8
165°	654.3	654.9	655.6	655.9	655.5	654.6	653.7	652.8	651.9	651.9	651.9
167.5°	662.9	663.5	664.2	664.5	664.1	663.2	662.3	661.4	660.5	660.5	660.5
170°	669.5	670.2	671.0	671.4	670.9	670.0	669.1	668.2	667.3	667.4	667.6
172.5°	674.6	675.4	676.1	676.5	676.1	675.2	674.3	673.4	672.5	672.6	672.8
175°	678.1	678.8	679.6	680.0	679.6	678.7	677.8	676.9	676.0	676.2	676.5
177.5°	679.8	680.5	681.3	681.7	681.3	680.5	679.8	679.0	678.2	678.5	678.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1514.0	1508.9	1508.9	1505.8	1505.8	1489.3	1489.3	1494.4	1488.3	1481.0	1470.7
5°	1553.2	1541.9	1538.8	1534.6	1521.2	1500.6	1492.4	1489.3	1476.9	1461.5	1443.9
7.5°	1590.3	1571.7	1562.5	1553.2	1535.7	1506.8	1490.3	1479.0	1460.4	1436.7	1414.1
10°	1626.4	1602.7	1579.0	1567.6	1542.9	1506.8	1483.1	1464.6	1437.8	1405.8	1373.9
12.5°	1659.4	1609.9	1605.8	1583.1	1547.0	1505.8	1469.7	1442.9	1408.9	1371.8	1334.7
15°	1688.2	1637.7	1613.0	1592.4	1545.0	1493.4	1455.3	1422.3	1377.0	1334.7	1289.3
17.5°	1702.6	1648.0	1631.5	1597.5	1549.1	1482.1	1430.5	1390.4	1340.9	1290.4	1238.8
20°	1717.1	1653.2	1626.4	1602.7	1536.7	1460.4	1402.7	1356.3	1301.7	1241.9	1185.3
22.5°	1724.3	1653.2	1621.2	1588.2	1524.3	1436.7	1368.7	1314.1	1250.2	1189.4	1121.4
25°	1711.9	1647.0	1608.9	1574.8	1502.7	1407.9	1329.5	1267.7	1199.7	1130.6	1061.6
27.5°	1681.0	1632.6	1588.2	1553.2	1472.8	1370.8	1288.3	1218.2	1148.1	1070.8	1000.8
30°	1623.3	1601.6	1566.6	1527.4	1439.8	1337.8	1239.9	1167.7	1090.4	1013.1	940.0
32.5°	1533.6	1552.2	1529.5	1495.5	1400.7	1292.4	1188.3	1115.2	1030.7	947.2	880.2
35°	1424.4	1490.3	1478.0	1454.3	1359.4	1244.0	1139.9	1051.3	966.8	882.2	815.2
37.5°	1304.8	1404.8	1415.1	1400.7	1312.0	1194.5	1080.1	993.6	907.0	821.4	753.4
40°	1140.9	1294.5	1327.5	1333.7	1262.6	1134.8	1015.2	930.7	845.1	761.7	679.2
42.5°	990.5	1184.2	1225.4	1251.2	1199.7	1076.0	955.4	861.6	777.1	701.9	619.4
45°	849.3	1051.3	1118.3	1151.2	1128.6	1009.0	884.3	796.7	719.4	650.3	571.0
47.5°	703.9	907.0	1000.8	1053.3	1053.3	941.0	816.3	729.7	655.5	596.7	526.7
50°	607.1	776.1	873.0	942.0	960.6	871.9	754.4	669.9	599.8	535.9	482.3
52.5°	517.4	668.9	749.3	821.4	875.0	797.7	685.4	609.1	540.1	480.3	438.0
55°	447.3	560.7	633.9	713.2	773.0	722.5	618.4	544.2	484.4	434.9	398.9
57.5°	380.3	479.3	539.0	609.1	673.0	634.9	551.4	487.5	434.9	391.6	359.7
60°	323.6	404.0	450.4	505.0	584.4	557.6	488.5	429.8	387.5	348.4	321.6
62.5°	275.2	339.1	378.3	417.4	489.6	477.2	423.6	378.3	342.2	309.2	286.5
65°	225.7	278.3	309.2	343.2	400.9	406.1	362.8	330.8	297.9	269.0	248.4
67.5°	182.4	223.7	251.5	280.3	326.7	341.1	311.3	284.5	256.6	232.9	214.4
70°	147.4	176.2	196.9	219.5	257.7	275.2	259.7	241.2	218.5	198.9	182.4
72.5°	116.5	135.0	147.4	164.9	195.8	213.3	212.3	195.8	179.3	165.9	152.5
75°	85.5	100.0	110.3	121.6	146.4	162.8	167.0	159.8	143.3	133.0	122.6
77.5°	64.9	73.2	78.3	86.6	104.1	118.5	124.7	122.6	111.3	103.1	95.9
80°	49.5	51.5	53.6	56.7	71.1	84.5	88.6	87.6	81.4	78.3	70.1
82.5°	35.0	36.1	37.1	38.1	43.3	54.6	58.7	60.8	55.7	52.6	45.3
85°	20.6	21.6	21.6	23.7	24.7	27.8	35.0	35.0	34.0	29.9	28.9
87.5°	10.3	10.3	9.3	9.3	10.3	11.3	13.4	15.5	13.4	12.4	11.3
90°	11.7	8.9	7.5	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	17.4	17.3	17.2	16.7	15.7	14.6	13.6	12.6	13.6	14.6	15.7
95°	36.0	35.7	35.6	35.0	33.7	32.4	31.1	29.8	31.1	32.4	33.7
97.5°	55.9	55.4	55.1	54.5	53.4	52.2	51.1	49.9	51.1	52.2	53.4
100°	78.1	77.7	77.5	77.0	76.0	74.9	73.9	72.9	73.9	74.9	76.0
102.5°	101.2	100.7	100.4	100.0	99.3	98.5	97.8	97.0	97.8	98.5	99.3
105°	125.5	125.2	125.1	124.9	124.5	124.2	123.8	123.4	123.8	124.2	124.5
107.5°	152.1	152.1	152.1	151.8	151.3	150.8	150.3	149.8	150.3	150.8	151.3
110°	178.5	178.5	178.5	178.1	177.3	176.6	175.8	175.0	175.8	176.6	177.3

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	205.8	205.9	206.0	205.6	204.9	204.1	203.4	202.6	203.4	204.1	204.9
115°	232.6	232.9	233.0	232.6	231.8	231.1	230.3	229.5	230.3	231.1	231.8
117.5°	260.1	260.8	261.1	260.6	259.6	258.5	257.5	256.5	257.5	258.5	259.6
120°	286.6	287.6	288.1	287.6	286.6	285.5	284.5	283.5	284.5	285.5	286.6
122.5°	312.9	313.6	313.9	313.3	312.0	310.7	309.4	308.1	309.4	310.7	312.0
125°	338.5	338.9	339.1	338.5	337.4	336.3	335.1	334.0	335.1	336.3	337.4
127.5°	364.7	365.2	365.5	364.8	363.4	362.0	360.6	359.2	360.6	362.0	363.4
130°	389.8	390.1	390.2	389.4	387.7	386.0	384.4	382.7	384.4	386.0	387.7
132.5°	415.1	415.0	414.9	414.3	413.0	411.7	410.4	409.1	410.4	411.7	413.0
135°	438.8	438.5	438.4	437.7	436.3	434.9	433.5	432.1	433.5	434.9	436.3
137.5°	462.9	462.6	462.5	461.9	460.8	459.6	458.5	457.3	458.5	459.6	460.8
140°	485.8	485.2	484.9	484.3	483.2	482.0	480.9	479.7	480.9	482.0	483.2
142.5°	508.4	508.0	507.8	507.2	506.1	505.0	503.8	502.7	503.8	505.0	506.1
145°	529.6	528.9	528.5	528.1	527.2	526.3	525.4	524.5	525.4	526.3	527.2
147.5°	549.9	549.4	549.1	548.5	547.4	546.3	545.1	544.0	545.1	546.3	547.4
150°	568.3	567.8	567.5	567.1	566.4	565.6	564.9	564.1	564.9	565.6	566.4
152.5°	586.3	585.6	585.3	584.9	584.1	583.4	582.6	581.8	582.6	583.4	584.1
155°	602.0	601.6	601.4	601.2	600.8	600.4	600.0	599.6	600.0	600.4	600.8
157.5°	616.7	616.4	616.3	616.2	615.9	615.6	615.4	615.1	615.4	615.6	615.9
160°	630.2	630.1	630.0	629.9	629.6	629.4	629.1	628.9	629.1	629.4	629.6
162.5°	641.7	641.6	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5	641.5
165°	651.9	651.9	651.9	652.0	652.1	652.2	652.3	652.4	652.3	652.2	652.1
167.5°	660.5	660.5	660.5	660.7	661.1	661.4	661.8	662.2	661.8	661.4	661.1
170°	667.7	667.8	667.9	668.1	668.5	668.8	669.2	669.6	669.2	668.8	668.5
172.5°	672.9	673.0	673.1	673.3	673.7	674.0	674.4	674.8	674.4	674.0	673.7
175°	676.7	677.0	677.1	677.3	677.7	678.0	678.4	678.8	678.4	678.0	677.7
177.5°	679.0	679.3	679.4	679.6	680.0	680.3	680.7	681.1	680.7	680.3	680.0
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1466.6	1467.7	1470.7	1461.5	1447.0	1440.9	1422.3	1419.2	1416.1	1416.1	1419.2
5°	1433.6	1429.5	1430.5	1413.0	1392.4	1380.0	1354.3	1358.4	1345.0	1336.8	1338.8
7.5°	1397.6	1386.2	1385.2	1362.5	1336.8	1314.1	1287.3	1281.1	1268.7	1254.3	1248.1
10°	1352.2	1344.0	1328.5	1302.7	1269.8	1251.2	1215.1	1193.5	1190.4	1168.8	1160.5
12.5°	1305.8	1291.4	1275.9	1239.9	1202.8	1172.9	1146.1	1122.4	1105.9	1087.3	1075.0
15°	1252.2	1234.7	1217.2	1179.1	1135.8	1105.9	1065.7	1030.7	982.2	944.1	922.4
17.5°	1193.5	1173.9	1150.2	1108.0	1065.7	1024.5	950.3	909.0	875.0	852.4	839.0
20°	1132.7	1111.0	1087.3	1045.1	971.9	899.8	858.5	826.6	806.0	783.3	766.8
22.5°	1068.8	1046.1	1020.3	954.4	877.1	826.6	794.6	764.7	734.9	722.5	714.2
25°	1009.0	988.4	955.4	865.7	804.9	758.6	722.5	702.9	687.4	671.0	655.5
27.5°	947.2	909.0	862.7	787.4	749.3	701.9	676.1	661.7	634.9	623.5	616.3
30°	873.0	830.7	786.4	732.8	688.5	655.5	631.8	608.1	592.6	581.3	568.9
32.5°	797.7	757.5	729.7	674.0	641.1	607.1	584.4	570.0	547.3	540.1	534.9
35°	732.8	698.8	674.0	628.7	597.8	566.9	550.4	528.7	514.3	500.9	492.7
37.5°	668.9	650.3	624.6	586.4	553.5	528.7	506.1	498.8	479.3	472.0	463.8
40°	624.6	596.7	575.1	542.1	514.3	487.5	473.1	456.6	443.2	431.8	428.8
42.5°	571.0	550.4	538.0	501.9	473.1	457.6	440.1	421.5	411.2	402.0	390.6
45°	530.8	512.2	494.7	465.9	440.1	420.5	405.0	392.7	375.2	371.0	353.5
47.5°	488.5	470.0	456.6	427.7	404.0	385.5	374.1	357.6	343.2	333.9	325.7
50°	446.3	430.8	418.4	393.7	373.1	353.5	338.1	321.6	315.4	299.9	294.8
52.5°	406.1	395.8	382.4	358.7	338.1	321.6	305.1	291.7	282.4	274.2	268.0
55°	372.1	355.6	349.4	323.6	306.1	288.6	274.2	265.9	254.6	249.4	244.3
57.5°	333.9	324.7	314.3	294.8	275.2	258.7	248.4	236.0	229.8	223.7	219.5
60°	301.0	287.6	279.3	262.8	245.3	229.8	220.6	211.3	203.0	197.9	189.6
62.5°	262.8	252.5	247.4	229.8	215.4	201.0	192.7	183.5	177.3	168.0	157.7
65°	229.8	221.6	215.4	201.0	187.6	174.2	165.9	154.6	146.4	141.2	140.2
67.5°	201.0	194.8	185.5	172.1	158.7	148.4	139.1	129.9	128.8	126.8	126.8
70°	169.0	162.8	157.7	143.3	131.9	120.6	118.5	115.4	112.3	111.3	109.2
72.5°	141.2	136.0	129.9	117.5	106.2	103.1	101.0	98.9	95.9	94.8	93.8
75°	114.4	107.2	103.1	91.7	88.6	86.6	84.5	81.4	79.4	78.3	76.3
77.5°	87.6	80.4	80.4	74.2	72.1	69.1	67.0	64.9	63.9	61.8	61.8
80°	61.8	61.8	59.8	56.7	53.6	52.6	49.5	48.4	47.4	48.4	46.4
82.5°	45.3	41.2	41.2	39.2	37.1	36.1	34.0	34.0	33.0	33.0	33.0
85°	25.8	25.8	24.7	22.7	21.6	21.6	20.6	20.6	19.6	19.6	18.6
87.5°	10.3	9.3	10.3	9.3	9.3	8.2	8.2	8.2	7.2	8.2	7.2
90°	6.7	7.5	8.9	11.7	14.5	17.3	20.1	19.8	19.6	19.3	19.0
92.5°	16.7	17.2	17.3	17.4	17.5	17.7	17.8	17.9	18.1	18.2	18.3
95°	35.0	35.6	35.7	36.0	36.2	36.5	36.7	36.7	36.7	36.7	36.7
97.5°	54.5	55.1	55.4	55.9	56.4	56.9	57.4	57.4	57.4	57.4	57.4
100°	77.0	77.5	77.7	78.1	78.4	78.8	79.2	79.2	79.2	79.2	79.2
102.5°	100.0	100.4	100.7	101.2	101.7	102.2	102.7	102.8	103.0	103.1	103.2
105°	124.9	125.1	125.2	125.5	125.7	126.0	126.2	126.5	126.7	127.0	127.3
107.5°	151.8	152.1	152.1	152.1	152.1	152.1	152.1	152.2	152.3	152.4	152.5
110°	178.1	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	205.6	206.0	205.9	205.8	205.7	205.5	205.4	205.0	204.6	204.3	203.9
115°	232.6	233.0	232.9	232.6	232.3	232.1	231.8	231.7	231.5	231.4	231.3
117.5°	260.6	261.1	260.8	260.1	259.5	258.8	258.2	257.8	257.4	257.1	256.7
120°	287.6	288.1	287.6	286.6	285.5	284.5	283.5	283.5	283.5	283.5	283.5
122.5°	313.3	313.9	313.6	312.9	312.3	311.6	311.0	310.6	310.2	309.9	309.5
125°	338.5	339.1	338.9	338.5	338.2	337.8	337.4	337.0	336.6	336.3	335.9
127.5°	364.8	365.5	365.2	364.7	364.2	363.7	363.2	362.7	362.2	361.7	361.2
130°	389.4	390.2	390.1	389.8	389.5	389.3	389.0	388.8	388.5	388.3	388.0
132.5°	414.3	414.9	415.0	415.1	415.2	415.3	415.4	414.8	414.2	413.5	412.9
135°	437.7	438.4	438.5	438.8	439.0	439.3	439.5	439.4	439.3	439.2	439.1
137.5°	461.9	462.5	462.6	462.9	463.1	463.4	463.6	463.5	463.4	463.3	463.2
140°	484.3	484.9	485.2	485.8	486.5	487.1	487.7	487.7	487.7	487.7	487.7
142.5°	507.2	507.8	508.0	508.4	508.7	509.1	509.5	509.6	509.8	509.9	510.0
145°	528.1	528.5	528.9	529.6	530.4	531.1	531.9	532.0	532.2	532.3	532.4
147.5°	548.5	549.1	549.4	549.9	550.4	550.9	551.4	551.7	551.9	552.2	552.5
150°	567.1	567.5	567.8	568.3	568.8	569.3	569.8	570.2	570.6	570.9	571.3
152.5°	584.9	585.3	585.6	586.3	586.9	587.6	588.2	588.7	589.2	589.7	590.2
155°	601.2	601.4	601.6	602.0	602.3	602.7	603.1	603.7	604.3	605.0	605.6
157.5°	616.2	616.3	616.4	616.7	616.9	617.2	617.4	618.3	619.2	620.1	621.0
160°	629.9	630.0	630.1	630.2	630.3	630.5	630.6	631.4	632.2	632.9	633.7
162.5°	641.5	641.5	641.6	641.7	641.8	642.0	642.1	643.0	643.9	644.8	645.7
165°	652.0	651.9	651.9	651.9	651.9	651.9	651.9	652.8	653.7	654.6	655.5
167.5°	660.7	660.5	660.5	660.5	660.5	660.5	660.5	661.4	662.3	663.2	664.1
170°	668.1	667.9	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.9
172.5°	673.3	673.1	673.0	672.9	672.8	672.6	672.5	673.4	674.3	675.2	676.1
175°	677.3	677.1	677.0	676.7	676.5	676.2	676.0	676.9	677.8	678.7	679.6
177.5°	679.6	679.4	679.3	679.0	678.7	678.5	678.2	679.0	679.8	680.5	681.3
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1419.2	1417.1	1411.0	1413.0	1409.9	1409.9	1407.9	1407.9	1407.9	1413.0	1409.9
5°	1341.9	1334.7	1327.5	1324.4	1321.3	1318.2	1318.2	1317.2	1326.5	1324.4	1332.6
7.5°	1246.1	1244.0	1229.6	1229.6	1224.4	1222.4	1227.5	1228.5	1229.6	1231.6	1236.8
10°	1160.5	1155.4	1134.8	1136.8	1133.7	1129.6	1132.7	1130.6	1137.8	1139.9	1137.8
12.5°	1059.5	1050.2	1027.6	1016.2	1003.9	994.6	1005.9	997.7	1026.5	1034.8	1057.5
15°	925.5	908.0	892.5	892.5	881.2	873.0	878.1	887.4	893.6	902.9	907.0
17.5°	835.9	828.6	816.3	809.1	806.0	802.9	802.9	807.0	820.4	819.4	827.6
20°	759.6	755.5	749.3	740.0	736.9	734.9	734.9	734.9	744.1	752.4	757.5
22.5°	707.0	703.9	699.8	687.4	681.3	679.2	684.4	687.4	694.7	700.8	706.0
25°	654.5	647.3	640.0	635.9	632.8	632.8	634.9	635.9	639.0	642.1	648.3
27.5°	611.2	606.0	595.7	584.4	584.4	581.3	583.4	585.4	592.6	602.9	608.1
30°	562.7	561.7	557.6	553.5	549.3	547.3	551.4	554.5	555.5	560.7	560.7
32.5°	527.7	520.5	513.3	509.1	507.1	506.1	507.1	511.2	511.2	517.4	524.6
35°	492.7	488.5	481.3	474.1	472.0	466.9	471.0	475.1	482.3	485.4	488.5
37.5°	454.5	449.4	446.3	444.2	440.1	441.1	438.0	444.2	450.4	449.4	451.4
40°	425.7	416.4	407.1	406.1	405.0	404.0	404.0	405.0	409.2	413.3	419.5
42.5°	388.6	385.5	377.2	369.0	366.9	364.9	362.8	366.9	375.2	382.4	385.5
45°	350.4	346.3	344.2	338.1	333.9	332.9	330.8	336.0	343.2	346.3	348.4
47.5°	315.4	314.3	308.2	309.2	306.1	307.1	306.1	309.2	309.2	312.3	314.3
50°	291.7	288.6	285.5	283.4	280.3	280.3	279.3	280.3	284.5	288.6	287.6
52.5°	268.0	262.8	261.8	260.8	258.7	260.8	257.7	258.7	262.8	264.9	263.8
55°	240.1	239.1	237.1	235.0	234.0	232.9	232.9	232.9	237.1	240.1	241.2
57.5°	218.5	213.3	209.2	209.2	205.1	204.1	206.1	207.2	210.3	212.3	214.4
60°	188.6	186.5	180.4	177.3	171.1	170.1	170.1	174.2	179.3	186.5	188.6
62.5°	156.7	153.6	152.5	152.5	152.5	152.5	152.5	152.5	152.5	153.6	153.6
65°	139.1	140.2	139.1	138.1	139.1	139.1	138.1	138.1	138.1	139.1	140.2
67.5°	124.7	123.7	124.7	123.7	122.6	122.6	121.6	122.6	123.7	124.7	124.7
70°	108.2	108.2	107.2	108.2	107.2	106.2	105.1	105.1	107.2	108.2	108.2
72.5°	92.8	92.8	91.7	91.7	89.7	89.7	90.7	89.7	89.7	92.8	92.8
75°	77.3	76.3	75.2	75.2	74.2	74.2	74.2	73.2	75.2	75.2	76.3
77.5°	60.8	60.8	60.8	59.8	59.8	58.7	58.7	59.8	59.8	59.8	60.8
80°	46.4	46.4	46.4	45.3	44.3	44.3	44.3	44.3	44.3	45.3	44.3
82.5°	32.0	32.0	32.0	32.0	32.0	30.9	30.9	30.9	32.0	32.0	30.9
85°	19.6	18.6	19.6	19.6	18.6	19.6	18.6	18.6	17.5	17.5	18.6
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	18.9	19.0	19.1	19.2	19.4	19.5	19.4	19.2	19.1	19.0	18.9
92.5°	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4	18.4
95°	36.7	36.6	36.3	36.1	35.8	35.6	35.8	36.1	36.3	36.6	36.7
97.5°	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4	57.4
100°	79.2	79.1	79.0	78.9	78.7	78.6	78.7	78.9	79.0	79.1	79.2
102.5°	103.3	103.2	103.1	103.0	102.8	102.7	102.8	103.0	103.1	103.2	103.3
105°	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4	127.4
107.5°	152.6	152.3	151.7	151.0	150.4	149.8	150.4	151.0	151.7	152.3	152.6
110°	178.5	178.3	177.9	177.5	177.1	176.7	177.1	177.5	177.9	178.3	178.5

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	203.7	203.6	203.3	203.1	202.8	202.6	202.8	203.1	203.3	203.6	203.7
115°	231.2	231.0	230.6	230.3	229.9	229.5	229.9	230.3	230.6	231.0	231.2
117.5°	256.5	256.3	255.9	255.6	255.2	254.8	255.2	255.6	255.9	256.3	256.5
120°	283.5	283.3	282.9	282.5	282.1	281.7	282.1	282.5	282.9	283.3	283.5
122.5°	309.3	309.2	308.9	308.6	308.4	308.1	308.4	308.6	308.9	309.2	309.3
125°	335.7	335.6	335.5	335.4	335.2	335.1	335.2	335.4	335.5	335.6	335.7
127.5°	360.9	360.7	360.3	360.0	359.6	359.2	359.6	360.0	360.3	360.7	360.9
130°	387.9	387.6	387.1	386.6	386.1	385.6	386.1	386.6	387.1	387.6	387.9
132.5°	412.6	412.4	412.0	411.7	411.3	410.9	411.3	411.7	412.0	412.4	412.6
135°	439.0	438.8	438.4	438.0	437.6	437.2	437.6	438.0	438.4	438.8	439.0
137.5°	463.1	462.8	462.3	461.8	461.3	460.8	461.3	461.8	462.3	462.8	463.1
140°	487.7	487.4	486.9	486.4	485.9	485.4	485.9	486.4	486.9	487.4	487.7
142.5°	510.1	509.8	509.3	508.8	508.3	507.8	508.3	508.8	509.3	509.8	510.1
145°	532.5	532.2	531.7	531.2	530.7	530.2	530.7	531.2	531.7	532.2	532.5
147.5°	552.6	552.3	551.8	551.3	550.8	550.3	550.8	551.3	551.8	552.3	552.6
150°	571.5	571.3	570.9	570.6	570.2	569.8	570.2	570.6	570.9	571.3	571.5
152.5°	590.5	590.2	589.7	589.2	588.7	588.2	588.7	589.2	589.7	590.2	590.5
155°	605.9	605.7	605.3	605.0	604.6	604.2	604.6	605.0	605.3	605.7	605.9
157.5°	621.4	621.1	620.5	619.8	619.2	618.6	619.2	619.8	620.5	621.1	621.4
160°	634.1	633.8	633.3	632.8	632.3	631.8	632.3	632.8	633.3	633.8	634.1
162.5°	646.1	645.8	645.1	644.5	643.8	643.2	643.8	644.5	645.1	645.8	646.1
165°	655.9	655.6	654.9	654.3	653.6	653.0	653.6	654.3	654.9	655.6	655.9
167.5°	664.5	664.2	663.5	662.9	662.2	661.6	662.2	662.9	663.5	664.2	664.5
170°	671.4	671.0	670.2	669.5	668.7	667.9	668.7	669.5	670.2	671.0	671.4
172.5°	676.5	676.1	675.4	674.6	673.9	673.1	673.9	674.6	675.4	676.1	676.5
175°	680.0	679.6	678.8	678.1	677.3	676.5	677.3	678.1	678.8	679.6	680.0
177.5°	681.7	681.3	680.5	679.8	679.0	678.2	679.0	679.8	680.5	681.3	681.7
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1	1483.1
2.5°	1413.0	1418.2	1416.1	1404.8	1416.1	1419.2	1425.4	1431.6	1435.7	1441.9	1447.0
5°	1324.4	1334.7	1340.9	1334.7	1355.3	1358.4	1372.8	1381.1	1393.4	1403.8	1412.0
7.5°	1240.9	1249.2	1261.5	1263.6	1275.9	1290.4	1311.0	1331.6	1351.2	1361.5	1370.8
10°	1151.2	1165.7	1184.2	1180.1	1198.7	1221.3	1243.0	1275.9	1292.4	1311.0	1327.5
12.5°	1061.6	1070.8	1095.6	1103.8	1130.6	1148.1	1178.0	1198.7	1239.9	1261.5	1275.9
15°	904.9	943.0	974.0	1011.1	1046.1	1079.1	1105.9	1143.0	1179.1	1195.6	1219.3
17.5°	833.8	851.3	869.9	888.4	933.8	992.5	1039.9	1080.1	1111.0	1132.7	1160.5
20°	759.6	777.1	797.7	815.2	843.1	885.3	944.1	1013.1	1050.2	1072.9	1099.7
22.5°	707.0	723.5	736.9	752.4	774.0	804.9	849.3	934.8	984.3	1012.1	1035.8
25°	650.3	671.0	685.4	696.7	714.2	748.3	784.3	832.8	921.4	943.0	976.0
27.5°	611.2	617.4	633.9	651.4	668.9	687.4	724.5	765.8	825.6	873.0	913.2
30°	564.8	580.3	595.7	602.9	618.4	645.2	667.9	712.2	758.6	795.7	844.1
32.5°	529.8	539.0	549.3	566.9	581.3	599.8	622.5	659.6	698.8	722.5	759.6
35°	490.6	496.8	518.4	525.6	540.1	558.6	581.3	610.1	652.4	671.0	697.8
37.5°	453.5	467.9	474.1	490.6	504.0	522.5	539.0	572.0	599.8	621.5	646.2
40°	424.6	430.8	442.2	456.6	467.9	482.3	503.0	526.7	556.6	574.1	595.7
42.5°	389.6	394.7	409.2	417.4	436.0	449.4	461.7	490.6	517.4	530.8	552.4
45°	351.5	363.8	373.1	389.6	399.9	416.4	431.8	452.5	477.2	492.7	505.0
47.5°	318.5	330.8	340.1	355.6	372.1	379.3	395.8	417.4	440.1	452.5	470.0
50°	291.7	295.8	313.3	320.5	338.1	352.5	363.8	382.4	407.1	414.3	428.8
52.5°	265.9	269.0	280.3	289.6	305.1	317.4	331.9	349.4	370.0	381.3	392.7
55°	243.2	245.3	250.4	260.8	271.1	286.5	299.9	316.4	333.9	346.3	356.6
57.5°	217.5	221.6	225.7	231.9	242.2	256.6	271.1	286.5	301.0	309.2	322.6
60°	187.6	193.8	201.0	208.2	215.4	225.7	242.2	256.6	270.0	277.2	287.6
62.5°	155.6	168.0	174.2	182.4	188.6	197.9	210.3	226.7	236.0	245.3	253.5
65°	140.2	141.2	142.2	150.5	161.8	171.1	182.4	194.8	209.2	215.4	221.6
67.5°	124.7	125.7	127.8	128.8	133.0	143.3	155.6	169.0	180.4	184.5	190.7
70°	109.2	109.2	113.4	114.4	115.4	116.5	126.8	140.2	150.5	155.6	162.8
72.5°	92.8	93.8	95.9	96.9	98.9	101.0	104.1	111.3	123.7	128.8	137.1
75°	76.3	77.3	78.3	79.4	82.5	83.5	86.6	90.7	95.9	102.0	107.2
77.5°	60.8	60.8	61.8	63.9	66.0	67.0	70.1	72.1	74.2	77.3	81.4
80°	45.3	46.4	46.4	48.4	48.4	49.5	50.5	53.6	55.7	57.7	59.8
82.5°	30.9	33.0	33.0	33.0	34.0	35.0	36.1	36.1	38.1	39.2	42.3
85°	18.6	19.6	19.6	19.6	18.6	20.6	20.6	21.6	21.6	21.6	22.7
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.3	9.3
90°	19.0	19.3	19.6	19.8	20.1	17.3	14.5	11.7	8.9	7.5	6.7
92.5°	18.3	18.2	18.1	17.9	17.8	17.7	17.5	17.4	17.3	17.2	16.7
95°	36.7	36.7	36.7	36.7	36.7	36.5	36.2	36.0	35.7	35.6	35.0
97.5°	57.4	57.4	57.4	57.4	57.4	56.9	56.4	55.9	55.4	55.1	54.5
100°	79.2	79.2	79.2	79.2	79.2	78.8	78.4	78.1	77.7	77.5	77.0
102.5°	103.2	103.1	103.0	102.8	102.7	102.2	101.7	101.2	100.7	100.4	100.0
105°	127.3	127.0	126.7	126.5	126.2	126.0	125.7	125.5	125.2	125.1	124.9
107.5°	152.5	152.4	152.3	152.2	152.1	152.1	152.1	152.1	152.1	152.1	151.8
110°	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.5	178.1

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	203.9	204.3	204.6	205.0	205.4	205.5	205.7	205.8	205.9	206.0	205.6
115°	231.3	231.4	231.5	231.7	231.8	232.1	232.3	232.6	232.9	233.0	232.6
117.5°	256.7	257.1	257.4	257.8	258.2	258.8	259.5	260.1	260.8	261.1	260.6
120°	283.5	283.5	283.5	283.5	283.5	284.5	285.5	286.6	287.6	288.1	287.6
122.5°	309.5	309.9	310.2	310.6	311.0	311.6	312.3	312.9	313.6	313.9	313.3
125°	335.9	336.3	336.6	337.0	337.4	337.8	338.2	338.5	338.9	339.1	338.5
127.5°	361.2	361.7	362.2	362.7	363.2	363.7	364.2	364.7	365.2	365.5	364.8
130°	388.0	388.3	388.5	388.8	389.0	389.3	389.5	389.8	390.1	390.2	389.4
132.5°	412.9	413.5	414.2	414.8	415.4	415.3	415.2	415.1	415.0	414.9	414.3
135°	439.1	439.2	439.3	439.4	439.5	439.3	439.0	438.8	438.5	438.4	437.7
137.5°	463.2	463.3	463.4	463.5	463.6	463.4	463.1	462.9	462.6	462.5	461.9
140°	487.7	487.7	487.7	487.7	487.7	487.1	486.5	485.8	485.2	484.9	484.3
142.5°	510.0	509.9	509.8	509.6	509.5	509.1	508.7	508.4	508.0	507.8	507.2
145°	532.4	532.3	532.2	532.0	531.9	531.1	530.4	529.6	528.9	528.5	528.1
147.5°	552.5	552.2	551.9	551.7	551.4	550.9	550.4	549.9	549.4	549.1	548.5
150°	571.3	570.9	570.6	570.2	569.8	569.3	568.8	568.3	567.8	567.5	567.1
152.5°	590.2	589.7	589.2	588.7	588.2	587.6	586.9	586.3	585.6	585.3	584.9
155°	605.6	605.0	604.3	603.7	603.1	602.7	602.3	602.0	601.6	601.4	601.2
157.5°	621.0	620.1	619.2	618.3	617.4	617.2	616.9	616.7	616.4	616.3	616.2
160°	633.7	632.9	632.2	631.4	630.6	630.5	630.3	630.2	630.1	630.0	629.9
162.5°	645.7	644.8	643.9	643.0	642.1	642.0	641.8	641.7	641.6	641.5	641.5
165°	655.5	654.6	653.7	652.8	651.9	651.9	651.9	651.9	651.9	651.9	652.0
167.5°	664.1	663.2	662.3	661.4	660.5	660.5	660.5	660.5	660.5	660.5	660.7
170°	670.9	670.0	669.1	668.2	667.3	667.4	667.6	667.7	667.8	667.9	668.1
172.5°	676.1	675.2	674.3	673.4	672.5	672.6	672.8	672.9	673.0	673.1	673.3
175°	679.6	678.7	677.8	676.9	676.0	676.2	676.5	676.7	677.0	677.1	677.3
177.5°	681.3	680.5	679.8	679.0	678.2	678.5	678.7	679.0	679.3	679.4	679.6
180°	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0	680.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1483.1	1483.1	1483.1	1483.1
2.5°	1456.3	1453.2	1471.8	1492.4
5°	1426.4	1431.6	1455.3	1484.1
7.5°	1395.5	1406.8	1434.7	1472.8
10°	1352.2	1372.8	1415.1	1454.3
12.5°	1310.0	1337.8	1378.0	1424.4
15°	1262.6	1293.5	1342.9	1398.6
17.5°	1210.0	1245.0	1302.7	1363.6
20°	1154.3	1200.7	1261.5	1327.5
22.5°	1092.5	1148.1	1211.0	1284.2
25°	1032.7	1093.5	1156.4	1240.9
27.5°	974.0	1033.7	1103.8	1189.4
30°	915.2	969.8	1045.1	1136.8
32.5°	852.4	909.0	988.4	1082.2
35°	794.6	851.3	925.5	1018.3
37.5°	732.8	793.6	864.7	960.6
40°	660.6	731.8	800.8	892.5
42.5°	600.9	676.1	743.1	829.7
45°	553.5	624.6	680.2	764.7
47.5°	509.1	566.9	623.5	701.9
50°	466.9	511.2	570.0	640.0
52.5°	423.6	461.7	512.2	578.2
55°	384.4	420.5	465.9	516.4
57.5°	348.4	374.1	419.5	464.8
60°	308.2	335.0	370.0	408.1
62.5°	274.2	294.8	327.7	359.7
65°	238.1	257.7	282.4	312.3
67.5°	205.1	222.6	242.2	265.9
70°	175.2	188.6	203.0	223.7
72.5°	143.3	157.7	171.1	187.6
75°	117.5	123.7	135.0	146.4
77.5°	90.7	98.9	105.1	114.4
80°	64.9	72.1	74.2	81.4
82.5°	43.3	47.4	51.5	53.6
85°	24.7	26.8	30.9	32.0
87.5°	9.3	10.3	12.4	14.4
90°	5.2	3.7	2.1	0.6
92.5°	15.7	14.6	13.6	12.6
95°	33.7	32.4	31.1	29.8
97.5°	53.4	52.2	51.1	49.9
100°	76.0	74.9	73.9	72.9
102.5°	99.3	98.5	97.8	97.0
105°	124.5	124.2	123.8	123.4
107.5°	151.3	150.8	150.3	149.8
110°	177.3	176.6	175.8	175.0

TEST NUMBER: P999964

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.9	204.1	203.4	202.6
115°	231.8	231.1	230.3	229.5
117.5°	259.6	258.5	257.5	256.5
120°	286.6	285.5	284.5	283.5
122.5°	312.0	310.7	309.4	308.1
125°	337.4	336.3	335.1	334.0
127.5°	363.4	362.0	360.6	359.2
130°	387.7	386.0	384.4	382.7
132.5°	413.0	411.7	410.4	409.1
135°	436.3	434.9	433.5	432.1
137.5°	460.8	459.6	458.5	457.3
140°	483.2	482.0	480.9	479.7
142.5°	506.1	505.0	503.8	502.7
145°	527.2	526.3	525.4	524.5
147.5°	547.4	546.3	545.1	544.0
150°	566.4	565.6	564.9	564.1
152.5°	584.1	583.4	582.6	581.8
155°	600.8	600.4	600.0	599.6
157.5°	615.9	615.6	615.4	615.1
160°	629.6	629.4	629.1	628.9
162.5°	641.5	641.5	641.5	641.5
165°	652.1	652.2	652.3	652.4
167.5°	661.1	661.4	661.8	662.2
170°	668.5	668.8	669.2	669.6
172.5°	673.7	674.0	674.4	674.8
175°	677.7	678.0	678.4	678.8
177.5°	680.0	680.3	680.7	681.1
180°	680.0	680.0	680.0	680.0

(END OF REPORT)