

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999968

Luminaire Tested: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999968
REPORT IS A COMBINATION OF REPORTS P988525 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4424.4 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999968

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P999968

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51
2	91	83	77	73	84	78	72	68	67	63	59	56	54	51	47	45	43
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P999968

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	2.4
10°-20°	293.0	6.6
20°-30°	411.3	9.3
30°-40°	448.4	10.1
40°-50°	412.1	9.3
50°-60°	323.6	7.3
60°-70°	210.7	4.8
70°-80°	108.4	2.5
80°-90°	29.6	0.7
90°-100°	121.0	2.7
100°-110°	409.0	9.2
110°-120°	429.9	9.7
120°-130°	353.5	8.0
130°-140°	284.1	6.4
140°-150°	214.6	4.9
150°-160°	150.9	3.4
160°-170°	88.8	2.0
170°-180°	28.9	0.7
0°-30°	811.1	18.3
0°-40°	1259.4	28.5
0°-60°	1995.2	45.1
0°-90°	2343.9	53.0
90°-120°	959.8	21.7
90°-150°	1811.9	41.0
90°-180°	2080.0	47.0
0°-180°	4424.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	1	8	20	19	19	4
95°	20	49	225	85	65	21
105°	70	106	425	760	647	74
115°	123	156	356	734	851	122
125°	172	204	342	595	690	153
135°	202	241	338	500	572	156
145°	231	265	336	418	457	145
155°	262	283	326	369	384	121
165°	286	294	313	332	337	81
175°	298	298	301	304	304	28
180°	298	298	298	298	298	

TEST NUMBER: P999968

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	0.6	7.8	19.5	18.6	18.9
92.5°	8.6	27.2	88.4	40.7	35.0
95°	20.1	49.4	224.9	84.9	65.4
97.5°	29.8	65.2	366.7	170.4	109.6
100°	44.2	79.8	453.3	339.4	205.4
102.5°	57.4	93.0	456.2	573.9	400.5
105°	70.0	105.6	425.2	760.0	646.7
107.5°	83.8	118.2	396.5	827.5	812.6
110°	97.6	131.1	377.0	816.6	880.3

TEST NUMBER: P999968

CATALOG NUMBER: SA2XXRDIP-B675D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.2	143.5	364.4	779.6	879.1
115°	123.4	155.8	355.8	734.2	851.0
117.5°	137.2	168.1	351.2	690.9	808.6
120°	149.8	180.2	347.2	652.2	767.8
122.5°	161.8	192.5	344.9	622.0	725.3
125°	172.2	203.8	342.0	594.8	690.3
127.5°	180.8	214.4	340.3	571.6	657.6
130°	188.2	223.8	339.1	548.0	630.7
132.5°	195.1	233.0	338.6	523.6	602.5
135°	202.0	241.0	338.0	499.8	572.1
137.5°	208.3	247.9	338.0	475.8	542.9
140°	215.8	254.2	337.4	454.5	512.4
142.5°	223.2	259.4	337.4	434.2	482.0
145°	230.7	265.1	336.3	417.5	456.8
147.5°	238.7	269.7	334.6	402.8	434.4
150°	246.8	274.3	332.8	390.2	414.9
152.5°	254.8	278.9	330.0	379.6	398.3
155°	262.2	283.2	326.5	369.2	383.9
157.5°	268.6	286.6	323.1	359.5	371.3
160°	274.9	290.0	319.6	349.8	359.2
162.5°	281.2	292.7	316.8	340.6	347.8
165°	285.8	294.4	312.7	331.6	336.9
167.5°	289.8	296.2	309.3	323.6	326.5
170°	293.8	297.0	306.4	316.2	317.3
172.5°	296.1	297.8	303.0	309.6	309.9
175°	297.8	298.1	300.7	304.4	303.6
177.5°	299.0	298.4	298.4	300.7	299.0
180°	298.4	298.4	298.4	298.4	298.4

(END OF REPORT)