

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001299

Luminaire Tested: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001299
REPORT IS A COMBINATION OF REPORTS P995918 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3809.0 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001299

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001299

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46			38
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38			32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32			27
3	79	70	63	57	71	64	57	52	52	47	44	41	38	35	31	29	27			23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24			20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21			17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16			13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14			12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13			11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3879 cd/sqm

TEST NUMBER: P1001299

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.4
10°-20°	151.4	4.0
20°-30°	222.8	5.8
30°-40°	258.9	6.8
40°-50°	258.9	6.8
50°-60°	226.5	5.9
60°-70°	168.1	4.4
70°-80°	95.4	2.5
80°-90°	28.9	0.8
90°-100°	25.2	0.7
100°-110°	165.6	4.3
110°-120°	316.3	8.3
120°-130°	401.5	10.5
130°-140°	429.5	11.3
140°-150°	401.6	10.5
150°-160°	323.9	8.5
160°-170°	208.9	5.5
170°-180°	72.0	1.9
0°-30°	427.8	11.2
0°-40°	686.8	18.0
0°-60°	1172.2	30.8
0°-90°	1464.6	38.5
90°-120°	507.0	13.3
90°-150°	1739.7	45.7
90°-180°	2344.0	61.5
0°-180°	3809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	2	8	12	16	17	3
95°	31	12	12	16	16	38
105°	171	174	177	182	162	179
115°	318	320	320	321	321	313
125°	448	450	449	450	451	400
135°	555	555	557	558	559	428
145°	640	642	642	643	644	400
155°	702	703	701	703	702	324
165°	741	738	738	742	737	209
175°	758	754	755	760	753	72
180°	758	758	758	758	758	

TEST NUMBER: P1001299

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	1.7	7.9	12.5	15.9	17.0
92.5°	8.5	7.4	11.9	15.3	15.3
95°	31.2	11.9	12.5	15.9	16.4
97.5°	59.5	72.0	12.5	15.3	15.9
100°	92.9	103.1	24.9	15.3	15.9
102.5°	130.3	137.1	143.9	16.4	16.4
105°	170.6	174.0	176.8	181.9	161.5
107.5°	207.4	209.1	213.1	215.9	218.2
110°	244.8	246.5	249.9	251.0	252.7

TEST NUMBER: P1001299

CATALOG NUMBER: SA4XXDIP-B350D590UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.1	284.5	285.6	285.0	287.3
115°	318.5	320.2	319.6	320.7	320.7
117.5°	351.9	354.2	355.9	355.3	355.3
120°	385.9	388.2	387.6	388.7	387.6
122.5°	417.6	418.8	419.9	420.5	419.3
125°	447.7	449.9	448.8	450.5	451.1
127.5°	476.6	477.1	480.0	479.4	478.8
130°	504.3	504.9	506.6	507.2	507.2
132.5°	529.8	531.0	533.2	533.8	533.2
135°	555.3	554.8	557.0	558.2	559.3
137.5°	578.0	578.0	580.8	582.0	581.4
140°	600.1	601.2	602.4	604.1	604.6
142.5°	619.9	622.2	622.8	623.9	623.9
145°	640.3	642.0	642.0	642.6	643.7
147.5°	656.2	659.6	659.0	659.6	660.2
150°	673.8	676.0	675.5	675.5	676.0
152.5°	688.5	690.2	689.1	690.2	689.6
155°	702.1	702.7	701.0	703.2	701.5
157.5°	714.0	714.0	711.7	714.6	711.7
160°	724.2	722.5	721.9	725.3	721.9
162.5°	733.3	731.0	730.4	733.8	729.9
165°	740.6	737.8	737.8	742.3	737.2
167.5°	746.9	744.0	743.5	748.6	742.9
170°	752.0	748.6	749.1	753.7	748.0
172.5°	755.4	752.0	752.5	757.1	750.8
175°	757.6	754.2	754.8	759.9	753.1
177.5°	759.3	755.4	756.5	761.0	754.2
180°	757.6	757.6	757.6	757.6	757.6

(END OF REPORT)