

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999982

Luminaire Tested: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999982
REPORT IS A COMBINATION OF REPORTS P988539 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5040.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	99	95	91	88	91	88	84	82	74	72	70	62	61	59	51	50	49	49	49	44
2	90	84	78	73	83	77	73	68	66	62	59	56	53	51	46	44	43	43	43	38
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	41	39	37	37	37	33
4	76	66	59	53	71	62	55	50	53	48	44	45	41	38	38	35	33	33	33	29
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	34	32	29	29	29	26
6	65	54	46	41	60	50	43	39	44	38	34	37	33	30	32	29	26	26	26	23
7	61	49	41	36	56	46	39	34	40	35	31	34	30	27	29	26	24	24	24	21
8	56	45	37	32	52	42	35	31	37	31	28	32	28	25	27	24	22	22	22	19
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	25	22	20	20	20	18
10	49	38	31	26	46	36	29	25	31	26	23	27	23	21	23	20	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23174	23174	23174	23174
5°	23228	24614	23309	19664
10°	22972	26017	23135	16239
15°	22474	26025	22855	12199
20°	21875	21513	22351	10065
25°	21147	13443	21605	8562
30°	20220	8607	20769	7371
35°	19090	6615	19708	6308
40°	17833	5560	18594	5517
45°	16487	4732	17175	4632
50°	15109	4020	15814	4006
55°	13582	3495	14314	3448
60°	12226	2664	12872	2633
65°	10960	2006	11610	2274
70°	9562	1601	10311	1854
75°	8083	1227	8822	1403
80°	6419	835	6906	919
85°	4450	430	4887	454

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21199 cd/sqm

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	2.8
10°-20°	387.6	7.7
20°-30°	498.8	9.9
30°-40°	473.3	9.4
40°-50°	405.6	8.0
50°-60°	308.9	6.1
60°-70°	194.8	3.9
70°-80°	97.2	1.9
80°-90°	27.5	0.5
90°-100°	55.5	1.1
100°-110°	176.4	3.5
110°-120°	301.8	6.0
120°-130°	396.9	7.9
130°-140°	445.5	8.8
140°-150°	436.9	8.7
150°-160°	366.5	7.3
160°-170°	243.1	4.8
170°-180°	84.9	1.7
0°-30°	1025.3	20.3
0°-40°	1498.6	29.7
0°-60°	2213.0	43.9
0°-90°	2532.5	50.2
90°-120°	533.6	10.6
90°-150°	1812.9	36.0
90°-180°	2507.0	49.7
0°-180°	5040.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1464	1464	1464	1464	1464	
5°	1465	1629	1470	1301	1465	139
15°	1381	1838	1404	862	1381	388
25°	1225	981	1251	625	1225	562
35°	1005	483	1038	461	1005	629
45°	755	336	786	329	755	583
55°	510	233	537	230	510	459
65°	308	121	327	137	308	306
75°	144	64	158	73	144	156
85°	32	18	35	19	32	36
90°	1	26	1	26	1	4
95°	39	47	39	47	39	44
105°	163	168	163	168	163	172
115°	303	303	303	303	303	300
125°	440	442	440	442	440	394
135°	570	577	570	577	570	440
145°	692	699	692	699	692	432
155°	791	797	791	797	791	364
165°	860	861	860	861	860	243
175°	895	892	895	892	895	85
180°	897	897	897	897	897	

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1473.2	1479.3	1482.3	1486.4	1495.6	1501.7	1510.8	1512.8	1511.8	1515.9	1504.7
5°	1465.0	1478.3	1490.5	1500.6	1516.9	1527.1	1538.3	1551.5	1554.6	1569.8	1560.7
7.5°	1453.8	1473.2	1490.5	1510.8	1535.2	1548.5	1565.8	1586.1	1595.3	1613.6	1618.7
10°	1435.5	1463.0	1492.5	1513.9	1547.4	1570.8	1587.1	1619.7	1641.0	1668.5	1664.4
12.5°	1406.0	1441.6	1481.3	1516.9	1560.7	1575.9	1606.4	1640.0	1667.5	1692.9	1715.3
15°	1380.6	1421.3	1465.0	1508.8	1558.6	1587.1	1617.6	1661.4	1690.9	1735.7	1755.0
17.5°	1346.0	1397.9	1449.8	1498.6	1557.6	1590.2	1627.8	1670.5	1714.3	1757.0	1772.3
20°	1310.4	1366.3	1422.3	1488.4	1555.6	1587.1	1625.8	1678.7	1721.4	1755.0	1755.0
22.5°	1267.7	1335.8	1399.9	1463.0	1536.2	1582.0	1621.7	1683.8	1714.3	1721.4	1693.9
25°	1224.9	1293.1	1363.3	1441.6	1525.1	1565.8	1610.5	1668.5	1678.7	1650.2	1579.0
27.5°	1174.1	1250.4	1329.7	1414.2	1501.7	1552.5	1593.2	1631.9	1612.6	1536.2	1425.4
30°	1122.2	1204.6	1294.1	1374.5	1480.3	1527.1	1561.7	1572.9	1511.8	1387.7	1244.3
32.5°	1068.3	1148.6	1243.2	1339.9	1446.7	1491.5	1513.9	1484.4	1372.5	1215.8	1040.8
35°	1005.2	1095.7	1194.4	1295.1	1400.9	1434.5	1447.7	1375.5	1232.1	1029.6	855.6
37.5°	948.2	1038.7	1144.6	1247.3	1350.1	1368.4	1355.2	1242.2	1060.1	859.7	689.8
40°	881.1	977.7	1081.5	1196.4	1280.9	1286.0	1253.4	1106.9	881.1	692.8	588.0
42.5°	819.0	916.7	1020.4	1137.4	1201.5	1184.2	1140.5	948.2	735.6	597.2	512.8
45°	754.9	847.5	959.4	1063.2	1108.9	1068.3	1002.1	797.6	617.6	513.8	448.7
47.5°	692.8	779.3	890.2	989.9	998.1	952.3	873.9	668.4	535.1	451.7	398.8
50°	631.8	718.3	822.0	904.5	896.3	833.2	744.7	580.9	464.9	398.8	355.1
52.5°	570.8	649.1	749.8	814.9	780.3	719.3	631.8	492.4	405.9	347.9	314.4
55°	509.7	583.0	669.4	723.4	668.4	598.2	536.2	422.2	352.0	305.2	279.8
57.5°	458.8	516.8	596.2	628.7	562.6	507.7	453.8	363.2	305.2	271.6	242.1
60°	402.9	455.8	520.9	540.2	472.1	427.3	381.5	307.2	261.5	232.0	212.6
62.5°	355.1	398.8	448.7	448.7	388.6	355.1	320.5	257.4	219.8	196.4	187.2
65°	308.3	339.8	375.4	371.3	320.5	291.0	263.5	212.6	184.1	167.9	158.7
67.5°	262.5	286.9	310.3	296.1	259.4	234.0	208.6	171.9	152.6	141.4	129.2
70°	220.8	240.1	252.3	239.1	202.5	181.1	162.8	138.4	123.1	108.9	101.7
72.5°	185.2	193.3	197.4	181.1	150.6	138.4	125.1	107.8	94.6	87.5	85.5
75°	144.5	151.6	148.5	136.3	110.9	101.7	91.6	79.4	76.3	72.2	70.2
77.5°	112.9	112.9	107.8	96.7	79.4	72.2	68.2	62.1	59.0	58.0	56.0
80°	80.4	79.4	76.3	64.1	53.9	49.9	49.9	45.8	44.8	42.7	42.7
82.5°	52.9	52.9	48.8	38.7	35.6	34.6	33.6	31.5	31.5	30.5	30.5
85°	31.5	29.5	24.4	21.4	20.3	20.3	19.3	18.3	19.3	18.3	18.3
87.5°	14.2	11.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.8	2.8	4.8	6.8	8.8	9.8	11.7	15.4	19.1	22.8	26.5
92.5°	16.7	18.0	19.4	20.7	22.0	22.7	22.8	23.0	23.1	23.3	23.5
95°	39.4	41.1	42.7	44.4	46.1	46.9	47.1	47.4	47.7	48.1	48.4
97.5°	65.8	67.3	68.9	70.4	71.9	72.7	73.0	73.7	74.4	75.0	75.7
100°	96.1	97.5	98.8	100.2	101.5	102.2	102.4	102.9	103.4	103.9	104.4
102.5°	127.9	128.9	129.9	130.9	131.9	132.4	132.7	133.4	134.1	134.8	135.5
105°	162.7	163.2	163.7	164.2	164.7	165.0	165.2	165.5	165.8	166.2	166.5
107.5°	197.5	198.2	198.9	199.6	200.3	200.6	200.6	200.6	200.6	200.6	200.6
110°	230.8	231.8	232.8	233.9	234.9	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	267.2	268.2	269.2	270.2	271.2	271.7	271.6	271.4	271.3	271.1	270.9
115°	302.7	303.7	304.7	305.8	306.8	307.3	307.1	306.8	306.5	306.1	305.8
117.5°	338.3	339.7	341.0	342.4	343.7	344.4	344.0	343.1	342.3	341.4	340.6
120°	373.9	375.2	376.6	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9
122.5°	406.4	408.1	409.8	411.5	413.2	414.0	413.6	412.7	411.9	411.0	410.2
125°	440.5	442.0	443.5	445.0	446.5	447.3	447.0	446.5	446.0	445.5	445.0
127.5°	473.8	475.6	477.5	479.3	481.2	482.1	481.8	481.1	480.4	479.8	479.1
130°	504.8	507.0	509.2	511.4	513.6	514.7	514.5	514.2	513.8	513.5	513.1
132.5°	539.6	541.3	543.0	544.7	546.4	547.2	547.3	547.5	547.6	547.8	548.0
135°	569.9	571.7	573.6	575.4	577.3	578.2	578.4	578.7	579.0	579.4	579.7
137.5°	603.2	604.7	606.2	607.7	609.2	610.0	610.2	610.5	610.8	611.2	611.5
140°	632.7	634.2	635.7	637.2	638.7	639.5	639.9	640.8	641.6	642.5	643.3
142.5°	663.0	664.5	666.0	667.5	669.0	669.8	670.1	670.6	671.1	671.6	672.1
145°	691.8	693.0	694.2	695.3	696.5	697.1	697.6	698.6	699.6	700.6	701.6
147.5°	717.5	719.0	720.5	722.0	723.5	724.3	724.6	725.3	726.0	726.6	727.3
150°	744.0	745.0	746.0	747.0	748.0	748.5	748.8	749.5	750.2	750.8	751.5
152.5°	767.4	768.4	769.4	770.5	771.5	772.0	772.4	773.3	774.1	775.0	775.8
155°	790.9	791.4	791.9	792.4	792.9	793.2	793.4	793.9	794.4	794.9	795.4
157.5°	811.3	811.6	812.0	812.3	812.6	812.8	813.0	813.3	813.7	814.0	814.4
160°	829.5	829.8	830.2	830.5	830.8	831.0	831.1	831.3	831.4	831.6	831.8
162.5°	846.2	846.2	846.2	846.2	846.2	846.2	846.3	846.4	846.6	846.7	846.9
165°	860.5	860.3	860.2	860.0	859.9	859.8	859.8	859.8	859.8	859.8	859.8
167.5°	873.4	872.9	872.4	871.9	871.4	871.1	871.1	871.1	871.1	871.1	871.1
170°	883.2	882.7	882.2	881.7	881.2	881.0	880.9	880.7	880.6	880.4	880.2
172.5°	890.0	889.5	889.0	888.5	888.0	887.8	887.7	887.5	887.4	887.2	887.0
175°	895.3	894.8	894.3	893.8	893.3	893.1	892.9	892.6	892.3	891.9	891.6
177.5°	898.4	897.9	897.4	896.9	896.4	896.1	895.9	895.6	895.3	894.9	894.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1515.9	1517.9	1521.0	1535.2	1537.3	1541.3	1539.3	1539.3	1540.3	1538.3	1539.3
5°	1581.0	1584.1	1599.3	1616.6	1620.7	1616.6	1621.7	1628.8	1628.8	1628.8	1626.8
7.5°	1642.1	1653.2	1670.5	1696.0	1701.1	1706.2	1715.3	1709.2	1711.2	1720.4	1717.3
10°	1701.1	1717.3	1736.7	1758.0	1769.2	1776.4	1780.4	1789.6	1810.9	1786.5	1795.7
12.5°	1757.0	1780.4	1800.8	1824.2	1832.3	1841.5	1844.5	1852.7	1852.7	1851.6	1858.8
15°	1793.6	1815.0	1833.3	1848.6	1850.6	1848.6	1846.6	1847.6	1850.6	1838.4	1845.5
17.5°	1801.8	1803.8	1809.9	1803.8	1804.8	1783.5	1771.3	1768.2	1739.7	1740.7	1764.1
20°	1762.1	1727.5	1718.4	1684.8	1664.4	1609.5	1607.5	1592.2	1532.2	1550.5	1546.4
22.5°	1653.2	1594.2	1515.9	1477.2	1457.9	1399.9	1355.2	1323.6	1302.3	1280.9	1271.7
25°	1509.8	1414.2	1303.3	1227.0	1215.8	1161.9	1079.4	1040.8	995.0	980.8	1005.2
27.5°	1324.6	1200.5	1075.4	958.4	937.0	888.2	846.5	819.0	766.1	763.0	765.1
30°	1073.3	948.2	843.4	767.1	714.2	691.8	664.4	644.0	622.6	630.8	632.8
32.5°	882.1	763.0	665.4	624.7	600.3	586.0	562.6	549.4	540.2	537.2	536.2
35°	701.0	621.6	577.9	538.2	524.0	513.8	496.5	490.4	482.2	483.3	483.3
37.5°	600.3	534.1	501.6	481.2	468.0	462.9	451.7	445.6	440.5	438.5	441.5
40°	517.8	472.1	451.7	433.4	422.2	420.2	414.1	407.0	400.8	401.9	404.9
42.5°	457.8	431.4	407.0	392.7	384.6	381.5	376.4	371.3	371.3	368.3	367.3
45°	410.0	388.6	368.3	355.1	350.0	345.9	339.8	338.8	334.7	335.7	336.8
47.5°	367.3	350.0	334.7	321.5	316.4	315.4	309.3	305.2	305.2	304.2	303.2
50°	328.6	311.3	298.1	291.0	283.9	281.8	280.8	279.8	277.7	277.7	278.8
52.5°	297.1	279.8	269.6	263.5	259.4	257.4	257.4	256.4	256.4	256.4	255.4
55°	262.5	248.2	240.1	238.1	236.0	235.0	234.0	232.0	230.9	233.0	230.9
57.5°	229.9	224.8	217.7	215.7	210.6	210.6	207.5	205.5	203.5	205.5	205.5
60°	204.5	197.4	193.3	187.2	183.1	179.1	174.0	173.0	170.9	169.9	168.9
62.5°	178.0	171.9	161.8	152.6	146.5	142.4	140.4	139.4	139.4	138.4	138.4
65°	148.5	134.3	129.2	126.2	125.1	124.1	122.1	121.1	122.1	121.1	122.1
67.5°	116.0	113.9	110.9	108.9	107.8	106.8	106.8	105.8	105.8	105.8	105.8
70°	100.7	95.6	94.6	92.6	92.6	91.6	91.6	91.6	91.6	90.5	92.6
72.5°	83.4	80.4	79.4	78.3	78.3	78.3	77.3	77.3	77.3	76.3	77.3
75°	68.2	67.1	65.1	65.1	64.1	65.1	64.1	64.1	63.1	64.1	64.1
77.5°	54.9	53.9	52.9	52.9	51.9	51.9	51.9	51.9	51.9	51.9	52.9
80°	41.7	40.7	39.7	40.7	39.7	40.7	39.7	39.7	40.7	39.7	39.7
82.5°	30.5	29.5	29.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
85°	18.3	17.3	17.3	18.3	17.3	18.3	17.3	17.3	17.3	18.3	18.3
87.5°	8.1	9.2	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.2
90°	26.2	25.8	25.5	25.2	25.0	25.1	25.2	25.4	25.5	25.7	25.5
92.5°	23.7	23.8	24.0	24.1	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.4	48.4	48.4	48.4	48.2	47.9	47.6	47.2	46.9	47.2
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.4	104.4	104.4	104.4	104.3	104.2	104.0	103.9	103.7	103.9
102.5°	135.7	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	135.7
105°	166.8	167.2	167.5	167.8	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	200.8	200.9	201.1	201.2	201.3	200.9	200.0	199.2	198.3	197.5	198.3
110°	235.4	235.4	235.4	235.4	235.4	235.1	234.6	234.1	233.6	233.1	233.6

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	270.4	269.9	269.4	268.9	268.7	268.5	268.2	267.9	267.5	267.2	267.5
115°	305.6	305.4	305.3	305.1	305.0	304.7	304.2	303.7	303.2	302.7	303.2
117.5°	340.1	339.6	339.1	338.6	338.3	338.0	337.5	337.0	336.5	336.0	336.5
120°	373.9	373.9	373.9	373.9	373.9	373.6	373.1	372.6	372.1	371.6	372.1
122.5°	409.7	409.2	408.7	408.2	407.9	407.7	407.4	407.1	406.7	406.4	406.7
125°	444.5	444.0	443.5	443.0	442.8	442.7	442.5	442.4	442.2	442.0	442.2
127.5°	478.4	477.8	477.1	476.4	476.1	475.8	475.3	474.8	474.3	473.8	474.3
130°	512.8	512.4	512.1	511.8	511.6	511.3	510.6	509.9	509.3	508.6	509.3
132.5°	547.2	546.3	545.5	544.6	544.2	543.9	543.4	542.9	542.4	541.9	542.4
135°	579.5	579.4	579.2	579.1	579.0	578.7	578.2	577.7	577.2	576.7	577.2
137.5°	611.3	611.2	611.0	610.9	610.8	610.5	609.8	609.1	608.4	607.7	608.4
140°	643.3	643.3	643.3	643.3	643.3	643.0	642.3	641.6	641.0	640.3	641.0
142.5°	672.3	672.4	672.6	672.7	672.8	672.5	671.8	671.1	670.5	669.8	670.5
145°	701.8	702.0	702.1	702.3	702.4	702.1	701.4	700.7	700.0	699.3	700.0
147.5°	727.6	728.0	728.3	728.6	728.8	728.5	727.8	727.1	726.5	725.8	726.5
150°	752.0	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	752.0
152.5°	776.5	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	776.5
155°	796.2	797.1	797.9	798.8	799.2	799.0	798.5	798.0	797.5	797.0	797.5
157.5°	815.6	816.8	817.9	819.1	819.7	819.3	818.4	817.6	816.7	815.9	816.7
160°	832.8	833.8	834.8	835.8	836.3	836.0	835.3	834.6	834.0	833.3	834.0
162.5°	848.1	849.3	850.4	851.6	852.2	851.8	850.9	850.1	849.2	848.4	849.2
165°	861.0	862.2	863.3	864.5	865.1	864.7	863.8	863.0	862.1	861.3	862.1
167.5°	872.3	873.5	874.6	875.8	876.4	876.0	875.1	874.3	873.4	872.6	873.4
170°	881.4	882.6	883.7	884.9	885.5	885.0	884.0	883.0	882.0	881.0	882.0
172.5°	888.2	889.4	890.5	891.7	892.3	891.8	890.8	889.8	888.8	887.8	888.8
175°	892.8	894.0	895.1	896.3	896.9	896.4	895.4	894.3	893.3	892.3	893.3
177.5°	895.6	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	895.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1543.4	1536.2	1534.2	1536.2	1534.2	1535.2	1528.1	1501.7	1508.8	1497.6	1503.7
5°	1630.9	1624.8	1611.5	1609.5	1607.5	1605.4	1595.3	1571.9	1562.7	1547.4	1546.4
7.5°	1714.3	1714.3	1704.1	1697.0	1687.8	1680.7	1667.5	1632.9	1618.7	1600.3	1590.2
10°	1796.7	1770.2	1781.4	1774.3	1751.9	1747.9	1723.4	1703.1	1675.6	1657.3	1641.0
12.5°	1855.7	1847.6	1837.4	1831.3	1825.2	1812.0	1795.7	1743.8	1729.6	1692.9	1674.6
15°	1853.7	1848.6	1851.6	1851.6	1849.6	1846.6	1833.3	1795.7	1771.3	1735.7	1704.1
17.5°	1754.0	1767.2	1780.4	1789.6	1809.9	1819.1	1831.3	1808.9	1793.6	1763.1	1729.6
20°	1580.0	1612.6	1651.2	1659.4	1677.7	1731.6	1756.0	1775.3	1781.4	1771.3	1743.8
22.5°	1337.9	1365.3	1458.9	1456.9	1483.3	1547.4	1618.7	1676.6	1722.4	1747.9	1737.7
25°	1047.9	1086.6	1136.4	1174.1	1260.5	1356.2	1444.7	1537.3	1616.6	1686.8	1704.1
27.5°	792.5	843.4	883.1	932.9	976.7	1089.6	1203.6	1348.0	1440.6	1573.9	1643.1
30°	641.0	664.4	704.0	727.4	748.8	835.3	964.5	1106.9	1269.7	1423.3	1542.4
32.5°	547.4	563.6	593.1	603.3	625.7	683.7	765.1	895.3	1063.2	1249.3	1406.0
35°	491.4	508.7	514.8	524.0	542.3	578.9	634.8	729.5	881.1	1063.2	1250.4
37.5°	443.6	452.7	470.0	476.1	482.2	509.7	547.4	613.5	714.2	863.8	1071.3
40°	410.0	415.1	424.2	429.3	433.4	452.7	486.3	531.1	605.3	719.3	910.6
42.5°	374.4	380.5	386.6	392.7	397.8	413.1	433.4	476.1	526.0	612.5	750.8
45°	339.8	343.9	351.0	355.1	362.2	374.4	392.7	422.2	467.0	521.9	633.8
47.5°	308.3	313.4	316.4	321.5	326.6	339.8	357.1	376.4	413.1	467.0	548.4
50°	279.8	285.9	290.0	291.0	295.0	307.2	321.5	342.9	366.3	408.0	479.2
52.5°	259.4	260.5	263.5	267.6	266.6	273.7	286.9	303.2	327.6	361.2	413.1
55°	236.0	239.1	241.1	242.1	242.1	248.2	255.4	270.6	290.0	317.4	361.2
57.5°	206.5	209.6	215.7	217.7	220.8	223.8	226.9	237.1	253.3	279.8	315.4
60°	176.0	178.0	184.1	188.2	190.3	198.4	202.5	210.6	219.8	239.1	272.7
62.5°	141.4	143.5	146.5	150.6	154.6	166.9	177.0	185.2	192.3	205.5	233.0
65°	123.1	124.1	126.2	127.2	128.2	133.3	142.4	153.6	166.9	177.0	193.3
67.5°	106.8	107.8	108.9	110.9	111.9	112.9	117.0	120.1	133.3	147.5	159.7
70°	91.6	93.6	94.6	94.6	95.6	97.7	99.7	103.8	107.8	115.0	130.2
72.5°	77.3	78.3	80.4	80.4	80.4	82.4	84.4	86.5	88.5	92.6	98.7
75°	64.1	66.1	66.1	66.1	67.1	67.1	69.2	71.2	73.3	76.3	78.3
77.5°	52.9	52.9	52.9	52.9	53.9	53.9	54.9	57.0	58.0	59.0	61.0
80°	39.7	40.7	40.7	40.7	41.7	41.7	41.7	43.7	44.8	44.8	46.8
82.5°	29.5	29.5	29.5	30.5	29.5	30.5	30.5	31.5	30.5	31.5	32.6
85°	18.3	18.3	18.3	19.3	19.3	19.3	19.3	19.3	19.3	19.3	20.3
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.2	9.2	9.2
90°	25.4	25.2	25.1	25.0	25.2	25.5	25.8	26.2	26.5	22.8	19.1
92.5°	24.2	24.2	24.2	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
95°	47.6	47.9	48.2	48.4	48.4	48.4	48.4	48.4	48.4	48.1	47.7
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.0	74.4
100°	104.0	104.2	104.3	104.4	104.4	104.4	104.4	104.4	104.4	103.9	103.4
102.5°	135.8	136.0	136.1	136.2	136.1	136.0	135.8	135.7	135.5	134.8	134.1
105°	168.0	168.0	168.0	168.0	167.8	167.5	167.2	166.8	166.5	166.2	165.8
107.5°	199.2	200.0	200.9	201.3	201.2	201.1	200.9	200.8	200.6	200.6	200.6
110°	234.1	234.6	235.1	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	267.9	268.2	268.5	268.7	268.9	269.4	269.9	270.4	270.9	271.1	271.3
115°	303.7	304.2	304.7	305.0	305.1	305.3	305.4	305.6	305.8	306.1	306.5
117.5°	337.0	337.5	338.0	338.3	338.6	339.1	339.6	340.1	340.6	341.4	342.3
120°	372.6	373.1	373.6	373.9	373.9	373.9	373.9	373.9	373.9	375.2	376.6
122.5°	407.1	407.4	407.7	407.9	408.2	408.7	409.2	409.7	410.2	411.0	411.9
125°	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	445.5	446.0
127.5°	474.8	475.3	475.8	476.1	476.4	477.1	477.8	478.4	479.1	479.8	480.4
130°	509.9	510.6	511.3	511.6	511.8	512.1	512.4	512.8	513.1	513.5	513.8
132.5°	542.9	543.4	543.9	544.2	544.6	545.5	546.3	547.2	548.0	547.8	547.6
135°	577.7	578.2	578.7	579.0	579.1	579.2	579.4	579.5	579.7	579.4	579.0
137.5°	609.1	609.8	610.5	610.8	610.9	611.0	611.2	611.3	611.5	611.2	610.8
140°	641.6	642.3	643.0	643.3	643.3	643.3	643.3	643.3	643.3	642.5	641.6
142.5°	671.1	671.8	672.5	672.8	672.7	672.6	672.4	672.3	672.1	671.6	671.1
145°	700.7	701.4	702.1	702.4	702.3	702.1	702.0	701.8	701.6	700.6	699.6
147.5°	727.1	727.8	728.5	728.8	728.6	728.3	728.0	727.6	727.3	726.6	726.0
150°	752.5	753.0	753.5	753.8	753.5	753.0	752.5	752.0	751.5	750.8	750.2
152.5°	777.1	777.8	778.5	778.8	778.5	777.8	777.1	776.5	775.8	775.0	774.1
155°	798.0	798.5	799.0	799.2	798.8	797.9	797.1	796.2	795.4	794.9	794.4
157.5°	817.6	818.4	819.3	819.7	819.1	817.9	816.8	815.6	814.4	814.0	813.7
160°	834.6	835.3	836.0	836.3	835.8	834.8	833.8	832.8	831.8	831.6	831.4
162.5°	850.1	850.9	851.8	852.2	851.6	850.4	849.3	848.1	846.9	846.7	846.6
165°	863.0	863.8	864.7	865.1	864.5	863.3	862.2	861.0	859.8	859.8	859.8
167.5°	874.3	875.1	876.0	876.4	875.8	874.6	873.5	872.3	871.1	871.1	871.1
170°	883.0	884.0	885.0	885.5	884.9	883.7	882.6	881.4	880.2	880.4	880.6
172.5°	889.8	890.8	891.8	892.3	891.7	890.5	889.4	888.2	887.0	887.2	887.4
175°	894.3	895.4	896.4	896.9	896.3	895.1	894.0	892.8	891.6	891.9	892.3
177.5°	896.6	897.6	898.6	899.1	898.6	897.6	896.6	895.6	894.6	894.9	895.3
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1494.5	1489.4	1489.4	1486.4	1486.4	1470.1	1470.1	1475.2	1469.1	1462.0	1451.8
5°	1533.2	1522.0	1519.0	1514.9	1501.7	1481.3	1473.2	1470.1	1457.9	1442.7	1425.4
7.5°	1569.8	1551.5	1542.4	1533.2	1515.9	1487.4	1471.1	1459.9	1441.6	1418.2	1395.9
10°	1605.4	1582.0	1558.6	1547.4	1523.0	1487.4	1464.0	1445.7	1419.3	1387.7	1356.2
12.5°	1638.0	1589.2	1585.1	1562.7	1527.1	1486.4	1450.8	1424.3	1390.8	1354.1	1317.5
15°	1666.5	1616.6	1592.2	1571.9	1525.1	1474.2	1436.5	1404.0	1359.2	1317.5	1272.7
17.5°	1680.7	1626.8	1610.5	1576.9	1529.1	1463.0	1412.1	1372.5	1323.6	1273.8	1222.9
20°	1695.0	1631.9	1605.4	1582.0	1516.9	1441.6	1384.7	1338.9	1285.0	1225.9	1170.0
22.5°	1702.1	1631.9	1600.3	1567.8	1504.7	1418.2	1351.1	1297.2	1234.1	1174.1	1106.9
25°	1689.9	1625.8	1588.1	1554.6	1483.3	1389.7	1312.4	1251.4	1184.2	1116.1	1047.9
27.5°	1659.4	1611.5	1567.8	1533.2	1453.8	1353.1	1271.7	1202.5	1133.4	1057.1	987.9
30°	1602.4	1581.0	1546.4	1507.8	1421.3	1320.6	1223.9	1152.7	1076.4	1000.1	927.9
32.5°	1513.9	1532.2	1509.8	1476.2	1382.6	1275.8	1173.0	1100.8	1017.4	935.0	868.8
35°	1406.0	1471.1	1458.9	1435.5	1341.9	1228.0	1125.2	1037.7	954.3	870.9	804.8
37.5°	1288.0	1386.7	1396.9	1382.6	1295.1	1179.1	1066.2	980.8	895.3	810.9	743.7
40°	1126.2	1277.8	1310.4	1316.5	1246.3	1120.1	1002.1	918.7	834.3	751.8	670.5
42.5°	977.7	1169.0	1209.7	1235.1	1184.2	1062.1	943.1	850.5	767.1	692.8	611.4
45°	838.3	1037.7	1103.9	1136.4	1114.0	996.0	872.9	786.4	710.1	642.0	563.6
47.5°	694.9	895.3	987.9	1039.8	1039.8	928.9	805.8	720.3	647.1	589.1	519.9
50°	599.2	766.1	861.7	929.9	948.2	860.7	744.7	661.3	592.1	529.0	476.1
52.5°	510.7	660.3	739.6	810.9	863.8	787.5	676.6	601.3	533.1	474.1	432.4
55°	441.5	553.5	625.7	704.0	763.0	713.2	610.4	537.2	478.2	429.3	393.7
57.5°	375.4	473.1	532.1	601.3	664.4	626.7	544.3	481.2	429.3	386.6	355.1
60°	319.5	398.8	444.6	498.5	576.9	550.4	482.2	424.2	382.5	343.9	317.4
62.5°	271.6	334.7	373.4	412.0	483.3	471.0	418.1	373.4	337.8	305.2	282.8
65°	222.8	274.7	305.2	338.8	395.8	400.8	358.1	326.6	294.0	265.5	245.2
67.5°	180.1	220.8	248.2	276.7	322.5	336.8	307.2	280.8	253.3	229.9	211.6
70°	145.5	174.0	194.3	216.7	254.3	271.6	256.4	238.1	215.7	196.4	180.1
72.5°	115.0	133.3	145.5	162.8	193.3	210.6	209.6	193.3	177.0	163.8	150.6
75°	84.4	98.7	108.9	120.1	144.5	160.7	164.8	157.7	141.4	131.2	121.1
77.5°	64.1	72.2	77.3	85.5	102.8	117.0	123.1	121.1	109.9	101.7	94.6
80°	48.8	50.9	52.9	56.0	70.2	83.4	87.5	86.5	80.4	77.3	69.2
82.5°	34.6	35.6	36.6	37.6	42.7	53.9	58.0	60.0	54.9	51.9	44.8
85°	20.3	21.4	21.4	23.4	24.4	27.5	34.6	34.6	33.6	29.5	28.5
87.5°	10.2	10.2	9.2	9.2	10.2	11.2	13.2	15.3	13.2	12.2	11.2
90°	15.4	11.7	9.8	8.8	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	23.0	22.8	22.7	22.0	20.7	19.4	18.0	16.7	18.0	19.4	20.7
95°	47.4	47.1	46.9	46.1	44.4	42.7	41.1	39.4	41.1	42.7	44.4
97.5°	73.7	73.0	72.7	71.9	70.4	68.9	67.3	65.8	67.3	68.9	70.4
100°	102.9	102.4	102.2	101.5	100.2	98.8	97.5	96.1	97.5	98.8	100.2
102.5°	133.4	132.7	132.4	131.9	130.9	129.9	128.9	127.9	128.9	129.9	130.9
105°	165.5	165.2	165.0	164.7	164.2	163.7	163.2	162.7	163.2	163.7	164.2
107.5°	200.6	200.6	200.6	200.3	199.6	198.9	198.2	197.5	198.2	198.9	199.6
110°	235.4	235.4	235.4	234.9	233.9	232.8	231.8	230.8	231.8	232.8	233.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	271.4	271.6	271.7	271.2	270.2	269.2	268.2	267.2	268.2	269.2	270.2
115°	306.8	307.1	307.3	306.8	305.8	304.7	303.7	302.7	303.7	304.7	305.8
117.5°	343.1	344.0	344.4	343.7	342.4	341.0	339.7	338.3	339.7	341.0	342.4
120°	377.9	379.2	379.9	379.2	377.9	376.6	375.2	373.9	375.2	376.6	377.9
122.5°	412.7	413.6	414.0	413.2	411.5	409.8	408.1	406.4	408.1	409.8	411.5
125°	446.5	447.0	447.3	446.5	445.0	443.5	442.0	440.5	442.0	443.5	445.0
127.5°	481.1	481.8	482.1	481.2	479.3	477.5	475.6	473.8	475.6	477.5	479.3
130°	514.2	514.5	514.7	513.6	511.4	509.2	507.0	504.8	507.0	509.2	511.4
132.5°	547.5	547.3	547.2	546.4	544.7	543.0	541.3	539.6	541.3	543.0	544.7
135°	578.7	578.4	578.2	577.3	575.4	573.6	571.7	569.9	571.7	573.6	575.4
137.5°	610.5	610.2	610.0	609.2	607.7	606.2	604.7	603.2	604.7	606.2	607.7
140°	640.8	639.9	639.5	638.7	637.2	635.7	634.2	632.7	634.2	635.7	637.2
142.5°	670.6	670.1	669.8	669.0	667.5	666.0	664.5	663.0	664.5	666.0	667.5
145°	698.6	697.6	697.1	696.5	695.3	694.2	693.0	691.8	693.0	694.2	695.3
147.5°	725.3	724.6	724.3	723.5	722.0	720.5	719.0	717.5	719.0	720.5	722.0
150°	749.5	748.8	748.5	748.0	747.0	746.0	745.0	744.0	745.0	746.0	747.0
152.5°	773.3	772.4	772.0	771.5	770.5	769.4	768.4	767.4	768.4	769.4	770.5
155°	793.9	793.4	793.2	792.9	792.4	791.9	791.4	790.9	791.4	791.9	792.4
157.5°	813.3	813.0	812.8	812.6	812.3	812.0	811.6	811.3	811.6	812.0	812.3
160°	831.3	831.1	831.0	830.8	830.5	830.2	829.8	829.5	829.8	830.2	830.5
162.5°	846.4	846.3	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2	846.2
165°	859.8	859.8	859.8	859.9	860.0	860.2	860.3	860.5	860.3	860.2	860.0
167.5°	871.1	871.1	871.1	871.4	871.9	872.4	872.9	873.4	872.9	872.4	871.9
170°	880.7	880.9	881.0	881.2	881.7	882.2	882.7	883.2	882.7	882.2	881.7
172.5°	887.5	887.7	887.8	888.0	888.5	889.0	889.5	890.0	889.5	889.0	888.5
175°	892.6	892.9	893.1	893.3	893.8	894.3	894.8	895.3	894.8	894.3	893.8
177.5°	895.6	895.9	896.1	896.4	896.9	897.4	897.9	898.4	897.9	897.4	896.9
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1447.7	1448.8	1451.8	1442.7	1428.4	1422.3	1404.0	1400.9	1397.9	1397.9	1400.9
5°	1415.2	1411.1	1412.1	1394.8	1374.5	1362.3	1336.8	1340.9	1327.7	1319.5	1321.6
7.5°	1379.6	1368.4	1367.4	1345.0	1319.5	1297.2	1270.7	1264.6	1252.4	1238.2	1232.1
10°	1334.8	1326.7	1311.4	1286.0	1253.4	1235.1	1199.5	1178.1	1175.1	1153.7	1145.6
12.5°	1289.0	1274.8	1259.5	1223.9	1187.3	1157.8	1131.3	1107.9	1091.7	1073.3	1061.1
15°	1236.1	1218.8	1201.5	1163.9	1121.2	1091.7	1052.0	1017.4	969.6	931.9	910.6
17.5°	1178.1	1158.8	1135.4	1093.7	1052.0	1011.3	938.0	897.3	863.8	841.4	828.2
20°	1118.1	1096.7	1073.3	1031.6	959.4	888.2	847.5	815.9	795.6	773.2	756.9
22.5°	1055.0	1032.6	1007.2	942.1	865.8	815.9	784.4	754.9	725.4	713.2	705.0
25°	996.0	975.7	943.1	854.6	794.6	748.8	713.2	693.9	678.6	662.3	647.1
27.5°	935.0	897.3	851.6	777.3	739.6	692.8	667.4	653.2	626.7	615.5	608.4
30°	861.7	820.0	776.3	723.4	679.6	647.1	623.7	600.3	585.0	573.8	561.6
32.5°	787.5	747.8	720.3	665.4	632.8	599.2	576.9	562.6	540.2	533.1	528.0
35°	723.4	689.8	665.4	620.6	590.1	559.6	543.3	521.9	507.7	494.4	486.3
37.5°	660.3	642.0	616.5	578.9	546.3	521.9	499.5	492.4	473.1	466.0	457.8
40°	616.5	589.1	567.7	535.1	507.7	481.2	467.0	450.7	437.5	426.3	423.2
42.5°	563.6	543.3	531.1	495.5	467.0	451.7	434.4	416.1	405.9	396.8	385.6
45°	524.0	505.6	488.3	459.9	434.4	415.1	399.8	387.6	370.3	366.3	349.0
47.5°	482.2	463.9	450.7	422.2	398.8	380.5	369.3	353.0	338.8	329.6	321.5
50°	440.5	425.3	413.1	388.6	368.3	349.0	333.7	317.4	311.3	296.1	291.0
52.5°	400.8	390.7	377.4	354.0	333.7	317.4	301.1	287.9	278.8	270.6	264.5
55°	367.3	351.0	344.9	319.5	302.2	284.9	270.6	262.5	251.3	246.2	241.1
57.5°	329.6	320.5	310.3	291.0	271.6	255.4	245.2	233.0	226.9	220.8	216.7
60°	297.1	283.9	275.7	259.4	242.1	226.9	217.7	208.6	200.4	195.3	187.2
62.5°	259.4	249.3	244.2	226.9	212.6	198.4	190.3	181.1	175.0	165.8	155.7
65°	226.9	218.7	212.6	198.4	185.2	171.9	163.8	152.6	144.5	139.4	138.4
67.5°	198.4	192.3	183.1	169.9	156.7	146.5	137.3	128.2	127.2	125.1	125.1
70°	166.9	160.7	155.7	141.4	130.2	119.0	117.0	113.9	110.9	109.9	107.8
72.5°	139.4	134.3	128.2	116.0	104.8	101.7	99.7	97.7	94.6	93.6	92.6
75°	112.9	105.8	101.7	90.5	87.5	85.5	83.4	80.4	78.3	77.3	75.3
77.5°	86.5	79.4	79.4	73.3	71.2	68.2	66.1	64.1	63.1	61.0	61.0
80°	61.0	61.0	59.0	56.0	52.9	51.9	48.8	47.8	46.8	47.8	45.8
82.5°	44.8	40.7	40.7	38.7	36.6	35.6	33.6	33.6	32.6	32.6	32.6
85°	25.4	25.4	24.4	22.4	21.4	21.4	20.3	20.3	19.3	19.3	18.3
87.5°	10.2	9.2	10.2	9.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1
90°	8.8	9.8	11.7	15.4	19.1	22.8	26.5	26.2	25.8	25.5	25.2
92.5°	22.0	22.7	22.8	23.0	23.1	23.3	23.5	23.7	23.8	24.0	24.1
95°	46.1	46.9	47.1	47.4	47.7	48.1	48.4	48.4	48.4	48.4	48.4
97.5°	71.9	72.7	73.0	73.7	74.4	75.0	75.7	75.7	75.7	75.7	75.7
100°	101.5	102.2	102.4	102.9	103.4	103.9	104.4	104.4	104.4	104.4	104.4
102.5°	131.9	132.4	132.7	133.4	134.1	134.8	135.5	135.7	135.8	136.0	136.1
105°	164.7	165.0	165.2	165.5	165.8	166.2	166.5	166.8	167.2	167.5	167.8
107.5°	200.3	200.6	200.6	200.6	200.6	200.6	200.6	200.8	200.9	201.1	201.2
110°	234.9	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	271.2	271.7	271.6	271.4	271.3	271.1	270.9	270.4	269.9	269.4	268.9
115°	306.8	307.3	307.1	306.8	306.5	306.1	305.8	305.6	305.4	305.3	305.1
117.5°	343.7	344.4	344.0	343.1	342.3	341.4	340.6	340.1	339.6	339.1	338.6
120°	379.2	379.9	379.2	377.9	376.6	375.2	373.9	373.9	373.9	373.9	373.9
122.5°	413.2	414.0	413.6	412.7	411.9	411.0	410.2	409.7	409.2	408.7	408.2
125°	446.5	447.3	447.0	446.5	446.0	445.5	445.0	444.5	444.0	443.5	443.0
127.5°	481.2	482.1	481.8	481.1	480.4	479.8	479.1	478.4	477.8	477.1	476.4
130°	513.6	514.7	514.5	514.2	513.8	513.5	513.1	512.8	512.4	512.1	511.8
132.5°	546.4	547.2	547.3	547.5	547.6	547.8	548.0	547.2	546.3	545.5	544.6
135°	577.3	578.2	578.4	578.7	579.0	579.4	579.7	579.5	579.4	579.2	579.1
137.5°	609.2	610.0	610.2	610.5	610.8	611.2	611.5	611.3	611.2	611.0	610.9
140°	638.7	639.5	639.9	640.8	641.6	642.5	643.3	643.3	643.3	643.3	643.3
142.5°	669.0	669.8	670.1	670.6	671.1	671.6	672.1	672.3	672.4	672.6	672.7
145°	696.5	697.1	697.6	698.6	699.6	700.6	701.6	701.8	702.0	702.1	702.3
147.5°	723.5	724.3	724.6	725.3	726.0	726.6	727.3	727.6	728.0	728.3	728.6
150°	748.0	748.5	748.8	749.5	750.2	750.8	751.5	752.0	752.5	753.0	753.5
152.5°	771.5	772.0	772.4	773.3	774.1	775.0	775.8	776.5	777.1	777.8	778.5
155°	792.9	793.2	793.4	793.9	794.4	794.9	795.4	796.2	797.1	797.9	798.8
157.5°	812.6	812.8	813.0	813.3	813.7	814.0	814.4	815.6	816.8	817.9	819.1
160°	830.8	831.0	831.1	831.3	831.4	831.6	831.8	832.8	833.8	834.8	835.8
162.5°	846.2	846.2	846.3	846.4	846.6	846.7	846.9	848.1	849.3	850.4	851.6
165°	859.9	859.8	859.8	859.8	859.8	859.8	859.8	861.0	862.2	863.3	864.5
167.5°	871.4	871.1	871.1	871.1	871.1	871.1	871.1	872.3	873.5	874.6	875.8
170°	881.2	881.0	880.9	880.7	880.6	880.4	880.2	881.4	882.6	883.7	884.9
172.5°	888.0	887.8	887.7	887.5	887.4	887.2	887.0	888.2	889.4	890.5	891.7
175°	893.3	893.1	892.9	892.6	892.3	891.9	891.6	892.8	894.0	895.1	896.3
177.5°	896.4	896.1	895.9	895.6	895.3	894.9	894.6	895.6	896.6	897.6	898.6
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1400.9	1398.9	1392.8	1394.8	1391.8	1391.8	1389.7	1389.7	1389.7	1394.8	1391.8
5°	1324.6	1317.5	1310.4	1307.3	1304.3	1301.2	1301.2	1300.2	1309.4	1307.3	1315.5
7.5°	1230.0	1228.0	1213.7	1213.7	1208.7	1206.6	1211.7	1212.7	1213.7	1215.8	1220.9
10°	1145.6	1140.5	1120.1	1122.2	1119.1	1115.1	1118.1	1116.1	1123.2	1125.2	1123.2
12.5°	1045.9	1036.7	1014.3	1003.1	990.9	981.8	993.0	984.8	1013.3	1021.5	1043.8
15°	913.6	896.3	881.1	881.1	869.9	861.7	866.8	876.0	882.1	891.2	895.3
17.5°	825.1	818.0	805.8	798.6	795.6	792.5	792.5	796.6	809.8	808.8	817.0
20°	749.8	745.7	739.6	730.5	727.4	725.4	725.4	725.4	734.6	742.7	747.8
22.5°	697.9	694.9	690.8	678.6	672.5	670.5	675.5	678.6	685.7	691.8	696.9
25°	646.0	638.9	631.8	627.7	624.7	624.7	626.7	627.7	630.8	633.8	639.9
27.5°	603.3	598.2	588.0	576.9	576.9	573.8	575.8	577.9	585.0	595.2	600.3
30°	555.5	554.5	550.4	546.3	542.3	540.2	544.3	547.4	548.4	553.5	553.5
32.5°	520.9	513.8	506.7	502.6	500.6	499.5	500.6	504.6	504.6	510.7	517.8
35°	486.3	482.2	475.1	468.0	466.0	460.9	464.9	469.0	476.1	479.2	482.2
37.5°	448.7	443.6	440.5	438.5	434.4	435.4	432.4	438.5	444.6	443.6	445.6
40°	420.2	411.0	401.9	400.8	399.8	398.8	398.8	399.8	403.9	408.0	414.1
42.5°	383.6	380.5	372.4	364.2	362.2	360.2	358.1	362.2	370.3	377.4	380.5
45°	345.9	341.8	339.8	333.7	329.6	328.6	326.6	331.7	338.8	341.8	343.9
47.5°	311.3	310.3	304.2	305.2	302.2	303.2	302.2	305.2	305.2	308.3	310.3
50°	287.9	284.9	281.8	279.8	276.7	276.7	275.7	276.7	280.8	284.9	283.9
52.5°	264.5	259.4	258.4	257.4	255.4	257.4	254.3	255.4	259.4	261.5	260.5
55°	237.1	236.0	234.0	232.0	230.9	229.9	229.9	229.9	234.0	237.1	238.1
57.5°	215.7	210.6	206.5	206.5	202.5	201.4	203.5	204.5	207.5	209.6	211.6
60°	186.2	184.1	178.0	175.0	168.9	167.9	167.9	171.9	177.0	184.1	186.2
62.5°	154.6	151.6	150.6	150.6	150.6	150.6	150.6	150.6	150.6	151.6	151.6
65°	137.3	138.4	137.3	136.3	137.3	137.3	136.3	136.3	136.3	137.3	138.4
67.5°	123.1	122.1	123.1	122.1	121.1	121.1	120.1	121.1	122.1	123.1	123.1
70°	106.8	106.8	105.8	106.8	105.8	104.8	103.8	103.8	105.8	106.8	106.8
72.5°	91.6	91.6	90.5	90.5	88.5	88.5	89.5	88.5	88.5	91.6	91.6
75°	76.3	75.3	74.3	74.3	73.3	73.3	73.3	72.2	74.3	74.3	75.3
77.5°	60.0	60.0	60.0	59.0	59.0	58.0	58.0	59.0	59.0	59.0	60.0
80°	45.8	45.8	45.8	44.8	43.7	43.7	43.7	43.7	43.7	44.8	43.7
82.5°	31.5	31.5	31.5	31.5	31.5	30.5	30.5	30.5	31.5	31.5	30.5
85°	19.3	18.3	19.3	19.3	18.3	19.3	18.3	18.3	17.3	17.3	18.3
87.5°	8.1	7.1	6.1	6.1	7.1	6.1	6.1	6.1	7.1	6.1	6.1
90°	25.0	25.1	25.2	25.4	25.5	25.7	25.5	25.4	25.2	25.1	25.0
92.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.4	48.2	47.9	47.6	47.2	46.9	47.2	47.6	47.9	48.2	48.4
97.5°	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7	75.7
100°	104.4	104.3	104.2	104.0	103.9	103.7	103.9	104.0	104.2	104.3	104.4
102.5°	136.2	136.1	136.0	135.8	135.7	135.5	135.7	135.8	136.0	136.1	136.2
105°	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0
107.5°	201.3	200.9	200.0	199.2	198.3	197.5	198.3	199.2	200.0	200.9	201.3
110°	235.4	235.1	234.6	234.1	233.6	233.1	233.6	234.1	234.6	235.1	235.4

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	268.7	268.5	268.2	267.9	267.5	267.2	267.5	267.9	268.2	268.5	268.7
115°	305.0	304.7	304.2	303.7	303.2	302.7	303.2	303.7	304.2	304.7	305.0
117.5°	338.3	338.0	337.5	337.0	336.5	336.0	336.5	337.0	337.5	338.0	338.3
120°	373.9	373.6	373.1	372.6	372.1	371.6	372.1	372.6	373.1	373.6	373.9
122.5°	407.9	407.7	407.4	407.1	406.7	406.4	406.7	407.1	407.4	407.7	407.9
125°	442.8	442.7	442.5	442.4	442.2	442.0	442.2	442.4	442.5	442.7	442.8
127.5°	476.1	475.8	475.3	474.8	474.3	473.8	474.3	474.8	475.3	475.8	476.1
130°	511.6	511.3	510.6	509.9	509.3	508.6	509.3	509.9	510.6	511.3	511.6
132.5°	544.2	543.9	543.4	542.9	542.4	541.9	542.4	542.9	543.4	543.9	544.2
135°	579.0	578.7	578.2	577.7	577.2	576.7	577.2	577.7	578.2	578.7	579.0
137.5°	610.8	610.5	609.8	609.1	608.4	607.7	608.4	609.1	609.8	610.5	610.8
140°	643.3	643.0	642.3	641.6	641.0	640.3	641.0	641.6	642.3	643.0	643.3
142.5°	672.8	672.5	671.8	671.1	670.5	669.8	670.5	671.1	671.8	672.5	672.8
145°	702.4	702.1	701.4	700.7	700.0	699.3	700.0	700.7	701.4	702.1	702.4
147.5°	728.8	728.5	727.8	727.1	726.5	725.8	726.5	727.1	727.8	728.5	728.8
150°	753.8	753.5	753.0	752.5	752.0	751.5	752.0	752.5	753.0	753.5	753.8
152.5°	778.8	778.5	777.8	777.1	776.5	775.8	776.5	777.1	777.8	778.5	778.8
155°	799.2	799.0	798.5	798.0	797.5	797.0	797.5	798.0	798.5	799.0	799.2
157.5°	819.7	819.3	818.4	817.6	816.7	815.9	816.7	817.6	818.4	819.3	819.7
160°	836.3	836.0	835.3	834.6	834.0	833.3	834.0	834.6	835.3	836.0	836.3
162.5°	852.2	851.8	850.9	850.1	849.2	848.4	849.2	850.1	850.9	851.8	852.2
165°	865.1	864.7	863.8	863.0	862.1	861.3	862.1	863.0	863.8	864.7	865.1
167.5°	876.4	876.0	875.1	874.3	873.4	872.6	873.4	874.3	875.1	876.0	876.4
170°	885.5	885.0	884.0	883.0	882.0	881.0	882.0	883.0	884.0	885.0	885.5
172.5°	892.3	891.8	890.8	889.8	888.8	887.8	888.8	889.8	890.8	891.8	892.3
175°	896.9	896.4	895.4	894.3	893.3	892.3	893.3	894.3	895.4	896.4	896.9
177.5°	899.1	898.6	897.6	896.6	895.6	894.6	895.6	896.6	897.6	898.6	899.1
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0	1464.0
2.5°	1394.8	1399.9	1397.9	1386.7	1397.9	1400.9	1407.0	1413.1	1417.2	1423.3	1428.4
5°	1307.3	1317.5	1323.6	1317.5	1337.9	1340.9	1355.2	1363.3	1375.5	1385.7	1393.8
7.5°	1224.9	1233.1	1245.3	1247.3	1259.5	1273.8	1294.1	1314.5	1333.8	1344.0	1353.1
10°	1136.4	1150.7	1169.0	1164.9	1183.2	1205.6	1227.0	1259.5	1275.8	1294.1	1310.4
12.5°	1047.9	1057.1	1081.5	1089.6	1116.1	1133.4	1162.9	1183.2	1223.9	1245.3	1259.5
15°	893.3	930.9	961.4	998.1	1032.6	1065.2	1091.7	1128.3	1163.9	1180.2	1203.6
17.5°	823.1	840.4	858.7	877.0	921.7	979.7	1026.5	1066.2	1096.7	1118.1	1145.6
20°	749.8	767.1	787.5	804.8	832.2	873.9	931.9	1000.1	1036.7	1059.1	1085.5
22.5°	697.9	714.2	727.4	742.7	764.1	794.6	838.3	922.8	971.6	999.1	1022.5
25°	642.0	662.3	676.6	687.8	705.0	738.6	774.2	822.0	909.5	930.9	963.5
27.5°	603.3	609.4	625.7	643.0	660.3	678.6	715.2	755.9	814.9	861.7	901.4
30°	557.5	572.8	588.0	595.2	610.4	636.9	659.3	703.0	748.8	785.4	833.2
32.5°	522.9	532.1	542.3	559.6	573.8	592.1	614.5	651.1	689.8	713.2	749.8
35°	484.3	490.4	511.7	518.9	533.1	551.4	573.8	602.3	644.0	662.3	688.8
37.5°	447.6	461.9	468.0	484.3	497.5	515.8	532.1	564.6	592.1	613.5	637.9
40°	419.2	425.3	436.5	450.7	461.9	476.1	496.5	519.9	549.4	566.7	588.0
42.5°	384.6	389.7	403.9	412.0	430.4	443.6	455.8	484.3	510.7	524.0	545.3
45°	346.9	359.1	368.3	384.6	394.7	411.0	426.3	446.6	471.0	486.3	498.5
47.5°	314.4	326.6	335.7	351.0	367.3	374.4	390.7	412.0	434.4	446.6	463.9
50°	287.9	292.0	309.3	316.4	333.7	347.9	359.1	377.4	401.9	409.0	423.2
52.5°	262.5	265.5	276.7	285.9	301.1	313.4	327.6	344.9	365.2	376.4	387.6
55°	240.1	242.1	247.2	257.4	267.6	282.8	296.1	312.3	329.6	341.8	352.0
57.5°	214.7	218.7	222.8	228.9	239.1	253.3	267.6	282.8	297.1	305.2	318.4
60°	185.2	191.3	198.4	205.5	212.6	222.8	239.1	253.3	266.6	273.7	283.9
62.5°	153.6	165.8	171.9	180.1	186.2	195.3	207.5	223.8	233.0	242.1	250.3
65°	138.4	139.4	140.4	148.5	159.7	168.9	180.1	192.3	206.5	212.6	218.7
67.5°	123.1	124.1	126.2	127.2	131.2	141.4	153.6	166.9	178.0	182.1	188.2
70°	107.8	107.8	111.9	112.9	113.9	115.0	125.1	138.4	148.5	153.6	160.7
72.5°	91.6	92.6	94.6	95.6	97.7	99.7	102.8	109.9	122.1	127.2	135.3
75°	75.3	76.3	77.3	78.3	81.4	82.4	85.5	89.5	94.6	100.7	105.8
77.5°	60.0	60.0	61.0	63.1	65.1	66.1	69.2	71.2	73.3	76.3	80.4
80°	44.8	45.8	45.8	47.8	47.8	48.8	49.9	52.9	54.9	57.0	59.0
82.5°	30.5	32.6	32.6	32.6	33.6	34.6	35.6	35.6	37.6	38.7	41.7
85°	18.3	19.3	19.3	19.3	18.3	20.3	20.3	21.4	21.4	21.4	22.4
87.5°	7.1	6.1	7.1	7.1	7.1	8.1	7.1	7.1	8.1	9.2	9.2
90°	25.2	25.5	25.8	26.2	26.5	22.8	19.1	15.4	11.7	9.8	8.8
92.5°	24.1	24.0	23.8	23.7	23.5	23.3	23.1	23.0	22.8	22.7	22.0
95°	48.4	48.4	48.4	48.4	48.4	48.1	47.7	47.4	47.1	46.9	46.1
97.5°	75.7	75.7	75.7	75.7	75.7	75.0	74.4	73.7	73.0	72.7	71.9
100°	104.4	104.4	104.4	104.4	104.4	103.9	103.4	102.9	102.4	102.2	101.5
102.5°	136.1	136.0	135.8	135.7	135.5	134.8	134.1	133.4	132.7	132.4	131.9
105°	167.8	167.5	167.2	166.8	166.5	166.2	165.8	165.5	165.2	165.0	164.7
107.5°	201.2	201.1	200.9	200.8	200.6	200.6	200.6	200.6	200.6	200.6	200.3
110°	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	235.4	234.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	268.9	269.4	269.9	270.4	270.9	271.1	271.3	271.4	271.6	271.7	271.2
115°	305.1	305.3	305.4	305.6	305.8	306.1	306.5	306.8	307.1	307.3	306.8
117.5°	338.6	339.1	339.6	340.1	340.6	341.4	342.3	343.1	344.0	344.4	343.7
120°	373.9	373.9	373.9	373.9	373.9	375.2	376.6	377.9	379.2	379.9	379.2
122.5°	408.2	408.7	409.2	409.7	410.2	411.0	411.9	412.7	413.6	414.0	413.2
125°	443.0	443.5	444.0	444.5	445.0	445.5	446.0	446.5	447.0	447.3	446.5
127.5°	476.4	477.1	477.8	478.4	479.1	479.8	480.4	481.1	481.8	482.1	481.2
130°	511.8	512.1	512.4	512.8	513.1	513.5	513.8	514.2	514.5	514.7	513.6
132.5°	544.6	545.5	546.3	547.2	548.0	547.8	547.6	547.5	547.3	547.2	546.4
135°	579.1	579.2	579.4	579.5	579.7	579.4	579.0	578.7	578.4	578.2	577.3
137.5°	610.9	611.0	611.2	611.3	611.5	611.2	610.8	610.5	610.2	610.0	609.2
140°	643.3	643.3	643.3	643.3	643.3	642.5	641.6	640.8	639.9	639.5	638.7
142.5°	672.7	672.6	672.4	672.3	672.1	671.6	671.1	670.6	670.1	669.8	669.0
145°	702.3	702.1	702.0	701.8	701.6	700.6	699.6	698.6	697.6	697.1	696.5
147.5°	728.6	728.3	728.0	727.6	727.3	726.6	726.0	725.3	724.6	724.3	723.5
150°	753.5	753.0	752.5	752.0	751.5	750.8	750.2	749.5	748.8	748.5	748.0
152.5°	778.5	777.8	777.1	776.5	775.8	775.0	774.1	773.3	772.4	772.0	771.5
155°	798.8	797.9	797.1	796.2	795.4	794.9	794.4	793.9	793.4	793.2	792.9
157.5°	819.1	817.9	816.8	815.6	814.4	814.0	813.7	813.3	813.0	812.8	812.6
160°	835.8	834.8	833.8	832.8	831.8	831.6	831.4	831.3	831.1	831.0	830.8
162.5°	851.6	850.4	849.3	848.1	846.9	846.7	846.6	846.4	846.3	846.2	846.2
165°	864.5	863.3	862.2	861.0	859.8	859.8	859.8	859.8	859.8	859.8	859.9
167.5°	875.8	874.6	873.5	872.3	871.1	871.1	871.1	871.1	871.1	871.1	871.4
170°	884.9	883.7	882.6	881.4	880.2	880.4	880.6	880.7	880.9	881.0	881.2
172.5°	891.7	890.5	889.4	888.2	887.0	887.2	887.4	887.5	887.7	887.8	888.0
175°	896.3	895.1	894.0	892.8	891.6	891.9	892.3	892.6	892.9	893.1	893.3
177.5°	898.6	897.6	896.6	895.6	894.6	894.9	895.3	895.6	895.9	896.1	896.4
180°	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9	896.9

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1464.0	1464.0	1464.0	1464.0
2.5°	1437.6	1434.5	1452.8	1473.2
5°	1408.1	1413.1	1436.5	1465.0
7.5°	1377.5	1388.7	1416.2	1453.8
10°	1334.8	1355.2	1396.9	1435.5
12.5°	1293.1	1320.6	1360.2	1406.0
15°	1246.3	1276.8	1325.7	1380.6
17.5°	1194.4	1229.0	1286.0	1346.0
20°	1139.5	1185.3	1245.3	1310.4
22.5°	1078.4	1133.4	1195.4	1267.7
25°	1019.4	1079.4	1141.5	1224.9
27.5°	961.4	1020.4	1089.6	1174.1
30°	903.4	957.4	1031.6	1122.2
32.5°	841.4	897.3	975.7	1068.3
35°	784.4	840.4	913.6	1005.2
37.5°	723.4	783.4	853.6	948.2
40°	652.1	722.3	790.5	881.1
42.5°	593.1	667.4	733.5	819.0
45°	546.3	616.5	671.5	754.9
47.5°	502.6	559.6	615.5	692.8
50°	460.9	504.6	562.6	631.8
52.5°	418.1	455.8	505.6	570.8
55°	379.5	415.1	459.9	509.7
57.5°	343.9	369.3	414.1	458.8
60°	304.2	330.6	365.2	402.9
62.5°	270.6	291.0	323.5	355.1
65°	235.0	254.3	278.8	308.3
67.5°	202.5	219.8	239.1	262.5
70°	173.0	186.2	200.4	220.8
72.5°	141.4	155.7	168.9	185.2
75°	116.0	122.1	133.3	144.5
77.5°	89.5	97.7	103.8	112.9
80°	64.1	71.2	73.3	80.4
82.5°	42.7	46.8	50.9	52.9
85°	24.4	26.5	30.5	31.5
87.5°	9.2	10.2	12.2	14.2
90°	6.8	4.8	2.8	0.8
92.5°	20.7	19.4	18.0	16.7
95°	44.4	42.7	41.1	39.4
97.5°	70.4	68.9	67.3	65.8
100°	100.2	98.8	97.5	96.1
102.5°	130.9	129.9	128.9	127.9
105°	164.2	163.7	163.2	162.7
107.5°	199.6	198.9	198.2	197.5
110°	233.9	232.8	231.8	230.8

TEST NUMBER: P999982

CATALOG NUMBER: SA2XXRDIP-B675D725UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	270.2	269.2	268.2	267.2
115°	305.8	304.7	303.7	302.7
117.5°	342.4	341.0	339.7	338.3
120°	377.9	376.6	375.2	373.9
122.5°	411.5	409.8	408.1	406.4
125°	445.0	443.5	442.0	440.5
127.5°	479.3	477.5	475.6	473.8
130°	511.4	509.2	507.0	504.8
132.5°	544.7	543.0	541.3	539.6
135°	575.4	573.6	571.7	569.9
137.5°	607.7	606.2	604.7	603.2
140°	637.2	635.7	634.2	632.7
142.5°	667.5	666.0	664.5	663.0
145°	695.3	694.2	693.0	691.8
147.5°	722.0	720.5	719.0	717.5
150°	747.0	746.0	745.0	744.0
152.5°	770.5	769.4	768.4	767.4
155°	792.4	791.9	791.4	790.9
157.5°	812.3	812.0	811.6	811.3
160°	830.5	830.2	829.8	829.5
162.5°	846.2	846.2	846.2	846.2
165°	860.0	860.2	860.3	860.5
167.5°	871.9	872.4	872.9	873.4
170°	881.7	882.2	882.7	883.2
172.5°	888.5	889.0	889.5	890.0
175°	893.8	894.3	894.8	895.3
177.5°	896.9	897.4	897.9	898.4
180°	896.9	896.9	896.9	896.9

(END OF REPORT)