

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000002

Luminaire Tested: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000002
REPORT IS A COMBINATION OF REPORTS P988559 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5102.2 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000002

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000002

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P1000002

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	2.1
10°-20°	291.7	5.7
20°-30°	409.6	8.0
30°-40°	446.5	8.8
40°-50°	410.3	8.0
50°-60°	322.3	6.3
60°-70°	209.8	4.1
70°-80°	108.0	2.1
80°-90°	30.1	0.6
90°-100°	160.9	3.2
100°-110°	544.0	10.7
110°-120°	571.8	11.2
120°-130°	470.2	9.2
130°-140°	377.9	7.4
140°-150°	285.5	5.6
150°-160°	200.7	3.9
160°-170°	118.2	2.3
170°-180°	38.4	0.8
0°-30°	807.6	15.8
0°-40°	1254.0	24.6
0°-60°	1986.6	38.9
0°-90°	2334.5	45.8
90°-120°	1276.8	25.0
90°-150°	2410.4	47.2
90°-180°	2768.0	54.3
0°-180°	5102.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	1	10	26	25	25	4
95°	27	66	299	113	87	28
105°	93	140	566	1011	860	99
115°	164	207	473	977	1132	163
125°	229	271	455	791	918	204
135°	269	321	450	665	761	208
145°	307	353	447	555	608	193
155°	349	377	434	491	511	161
165°	380	392	416	441	448	107
175°	396	397	400	405	404	38
180°	397	397	397	397	397	

TEST NUMBER: P1000002

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	0.8	10.4	26.0	24.8	25.2
92.5°	11.5	36.3	117.6	54.2	46.6
95°	26.7	65.6	299.2	113.0	87.0
97.5°	39.7	86.6	487.8	226.7	145.8
100°	58.8	106.1	603.1	451.6	273.3
102.5°	76.3	123.7	606.9	763.4	532.8
105°	93.1	140.5	565.7	1011.1	860.3
107.5°	111.5	157.2	527.5	1100.8	1081.0
110°	129.8	174.4	501.5	1086.3	1171.0

TEST NUMBER: P1000002

CATALOG NUMBER: SA2XXRDIP-B675D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.6	190.9	484.8	1037.0	1169.5
115°	164.1	207.3	473.3	976.8	1132.1
117.5°	182.4	223.7	467.2	919.1	1075.6
120°	199.2	239.7	461.8	867.6	1021.4
122.5°	215.3	256.1	458.8	827.5	964.9
125°	229.0	271.0	455.0	791.2	918.4
127.5°	240.5	285.2	452.7	760.4	874.8
130°	250.4	297.7	451.2	729.0	839.0
132.5°	259.6	309.9	450.4	696.6	801.6
135°	268.7	320.6	449.6	664.9	761.1
137.5°	277.1	329.8	449.6	632.8	722.2
140°	287.0	338.2	448.9	604.6	681.7
142.5°	297.0	345.0	448.9	577.5	641.2
145°	306.9	352.7	447.3	555.3	607.7
147.5°	317.6	358.8	445.1	535.9	577.9
150°	328.3	364.9	442.8	519.1	551.9
152.5°	338.9	371.0	438.9	505.0	529.8
155°	348.9	376.8	434.4	491.2	510.7
157.5°	357.3	381.3	429.8	478.2	493.9
160°	365.7	385.9	425.2	465.3	477.9
162.5°	374.1	389.4	421.4	453.1	462.6
165°	380.2	391.6	416.0	441.2	448.1
167.5°	385.5	393.9	411.5	430.6	434.4
170°	390.9	395.0	407.6	420.6	422.2
172.5°	393.9	396.2	403.1	411.8	412.2
175°	396.2	396.6	400.0	405.0	403.8
177.5°	397.7	397.0	397.0	400.0	397.7
180°	397.0	397.0	397.0	397.0	397.0

(END OF REPORT)