

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001414

Luminaire Tested: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001414
REPORT IS A COMBINATION OF REPORTS P996033 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6395.0 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001414

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001414

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			34
1	93	89	85	81	84	80	77	74	64	62	59	49	48	46	35	34	33			27
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28			22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23			18
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20			16
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17			13
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15			12
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13			10
8	51	38	31	25	45	35	28	23	28	23	19	22	18	16	16	14	12			9
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10			8
10	44	32	25	20	39	29	23	18	24	19	15	19	15	12	14	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 4958 cd/sqm

TEST NUMBER: P1001414

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.0
10°-20°	186.2	2.9
20°-30°	281.6	4.4
30°-40°	340.7	5.3
40°-50°	360.2	5.6
50°-60°	339.0	5.3
60°-70°	281.3	4.4
70°-80°	197.4	3.1
80°-90°	114.0	1.8
90°-100°	109.7	1.7
100°-110°	335.4	5.2
110°-120°	579.7	9.1
120°-130°	712.7	11.1
130°-140°	750.6	11.7
140°-150°	696.0	10.9
150°-160°	560.0	8.8
160°-170°	361.1	5.6
170°-180°	124.5	1.9
0°-30°	532.8	8.3
0°-40°	873.5	13.7
0°-60°	1572.7	24.6
0°-90°	2165.3	33.9
90°-120°	1024.9	16.0
90°-150°	3184.1	49.8
90°-180°	4230.0	66.1
0°-180°	6395.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	15	57	98	126	134	11
95°	64	56	88	115	123	74
105°	302	323	356	384	355	316
115°	555	565	589	608	613	547
125°	777	780	797	815	821	694
135°	962	961	970	984	991	741
145°	1108	1110	1110	1116	1121	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1001414

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	15.2	56.7	97.7	125.7	133.9
92.5°	26.2	51.1	92.0	119.5	125.6
95°	63.9	55.9	88.4	115.0	122.9
97.5°	112.1	155.9	84.6	109.5	117.3
100°	169.2	206.7	101.5	105.6	111.9
102.5°	233.8	262.5	303.4	102.9	109.1
105°	301.8	323.1	356.4	384.4	355.3
107.5°	365.5	381.5	415.3	439.4	448.6
110°	429.3	443.1	475.9	495.5	504.6

TEST NUMBER: P1001414

CATALOG NUMBER: SA4XXDIP-B575D1035UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	491.3	506.4	533.7	549.7	559.7
115°	555.2	565.0	588.7	607.5	612.9
117.5°	613.0	621.5	647.6	662.7	668.8
120°	671.0	677.2	698.5	715.9	720.0
122.5°	725.9	727.8	750.6	766.9	770.3
125°	777.1	780.2	797.4	815.0	820.6
127.5°	827.1	827.2	847.5	860.4	864.8
130°	874.3	874.4	889.7	904.6	909.2
132.5°	918.3	919.5	932.7	946.7	950.3
135°	961.6	960.7	970.0	984.2	990.8
137.5°	1000.8	1000.1	1008.0	1021.6	1024.4
140°	1039.0	1040.3	1043.0	1055.9	1060.8
142.5°	1072.6	1076.5	1076.7	1087.2	1090.2
145°	1107.9	1110.0	1110.0	1115.6	1120.7
147.5°	1135.3	1140.4	1139.4	1141.2	1145.2
150°	1165.7	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)