

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001474

Luminaire Tested: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001474
REPORT IS A COMBINATION OF REPORTS P996093 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7105.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001474

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001474

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	93	88	84	81	83	79	76	73	62	60	58	47	45	44	33	32	31
2	84	77	71	65	75	69	64	59	54	51	47	41	38	36	28	27	26
3	77	67	60	54	68	60	54	49	48	43	40	36	33	30	25	23	21
4	70	59	51	45	62	53	47	41	42	37	33	32	28	26	22	20	18
5	64	52	44	39	57	47	40	35	37	32	29	28	25	22	20	18	16
6	59	47	39	33	52	42	35	30	34	28	25	26	22	19	18	16	14
7	54	42	34	29	48	38	31	26	30	25	22	23	19	17	16	14	12
8	50	38	30	25	45	34	28	23	28	23	19	21	17	15	15	13	11
9	47	35	27	22	42	31	25	20	25	20	17	19	16	13	14	11	10
10	43	32	25	20	39	29	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5154 cd/sqm

TEST NUMBER: P1001474

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	0.9
10°-20°	186.2	2.6
20°-30°	281.6	4.0
30°-40°	340.7	4.8
40°-50°	360.2	5.1
50°-60°	339.0	4.8
60°-70°	281.3	4.0
70°-80°	197.4	2.8
80°-90°	114.5	1.6
90°-100°	117.3	1.7
100°-110°	385.5	5.4
110°-120°	675.4	9.5
120°-130°	834.2	11.7
130°-140°	880.6	12.4
140°-150°	817.5	11.5
150°-160°	658.0	9.3
160°-170°	424.3	6.0
170°-180°	146.2	2.1
0°-30°	532.8	7.5
0°-40°	873.5	12.3
0°-60°	1572.7	22.1
0°-90°	2165.8	30.5
90°-120°	1178.3	16.6
90°-150°	3710.6	52.2
90°-180°	4939.0	69.5
0°-180°	7105.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	16	59	101	130	139	12
95°	73	60	92	120	128	86
105°	353	376	410	439	404	370
115°	652	662	685	705	710	642
125°	913	916	933	951	957	815
135°	1130	1129	1139	1153	1160	871
145°	1302	1304	1304	1310	1316	813
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1001474

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	15.8	59.1	101.4	130.5	139.0
92.5°	28.8	53.4	95.6	124.1	130.2
95°	73.3	59.5	92.1	119.8	127.9
97.5°	130.1	177.7	88.3	114.1	122.1
100°	197.3	237.9	109.1	110.2	116.7
102.5°	273.3	304.0	346.9	107.9	114.1
105°	353.4	375.7	409.9	439.4	404.2
107.5°	428.3	444.8	479.8	504.7	514.6
110°	503.4	517.7	551.5	571.5	581.0

TEST NUMBER: P1001474

CATALOG NUMBER: SA4XXDIP-B575D1205UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.4	592.5	620.1	636.0	646.7
115°	651.6	661.9	685.4	704.6	710.0
117.5°	719.5	728.7	755.3	770.2	776.3
120°	787.8	794.7	815.8	833.5	837.3
122.5°	852.3	854.6	877.7	894.1	897.2
125°	912.6	916.4	933.3	951.3	957.1
127.5°	971.3	971.6	992.8	1005.4	1009.7
130°	1026.9	1027.2	1043.0	1058.1	1062.7
132.5°	1078.7	1080.2	1094.1	1108.3	1111.7
135°	1129.7	1128.6	1138.6	1153.2	1160.1
137.5°	1175.8	1175.1	1183.8	1197.7	1200.4
140°	1220.7	1222.3	1225.3	1238.7	1243.8
142.5°	1260.2	1264.9	1265.2	1276.0	1279.0
145°	1301.7	1304.3	1304.3	1310.1	1315.5
147.5°	1333.9	1340.0	1338.9	1340.8	1345.0
150°	1369.6	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)