

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000020

Luminaire Tested: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000020
REPORT IS A COMBINATION OF REPORTS P988577 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4906.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000020

CATALOG NUMBER: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000020

CATALOG NUMBER: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17256	17256	17256
5°	17284	16417	16295
10°	17114	15571	15057
15°	16879	14572	13645
20°	16568	13435	12168
25°	16249	12269	10817
30°	15820	11133	9342
35°	15400	9988	8075
40°	14975	8863	6769
45°	14480	7703	5632
50°	13965	6584	4585
55°	13432	5464	3640
60°	12811	4370	2754
65°	12101	3332	2239
70°	11238	2416	1780
75°	10153	1843	1359
80°	8583	1249	912
85°	5989	570	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14480 cd/sqm

TEST NUMBER: P1000020

CATALOG NUMBER: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	2.1
10°-20°	280.5	5.7
20°-30°	393.8	8.0
30°-40°	429.2	8.7
40°-50°	394.5	8.0
50°-60°	309.8	6.3
60°-70°	201.7	4.1
70°-80°	103.8	2.1
80°-90°	29.0	0.6
90°-100°	154.7	3.2
100°-110°	523.2	10.7
110°-120°	549.9	11.2
120°-130°	452.2	9.2
130°-140°	363.4	7.4
140°-150°	274.5	5.6
150°-160°	193.0	3.9
160°-170°	113.6	2.3
170°-180°	37.0	0.8
0°-30°	776.4	15.8
0°-40°	1205.7	24.6
0°-60°	1910.0	38.9
0°-90°	2244.4	45.7
90°-120°	1227.9	25.0
90°-150°	2318.0	47.2
90°-180°	2662.0	54.3
0°-180°	4906.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1090	1085	1072	1081	1078	103
15°	1037	1026	992	974	964	292
25°	941	910	844	804	789	433
35°	811	761	674	612	590	508
45°	663	597	493	423	400	512
55°	504	427	321	261	243	450
65°	340	260	172	138	135	337
75°	182	112	79	72	71	192
85°	42	22	19	19	19	49
90°	1	10	25	24	24	4
95°	26	63	288	109	84	27
105°	90	135	544	972	827	95
115°	158	199	455	939	1089	157
125°	220	261	438	761	883	196
135°	258	308	432	639	732	200
145°	295	339	430	534	584	185
155°	336	362	418	472	491	154
165°	366	377	400	424	431	103
175°	381	381	385	390	388	36
180°	382	382	382	382	382	

TEST NUMBER: P1000020

CATALOG NUMBER: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.1	1090.1	1090.1	1090.1	1090.1
2.5°	1095.1	1090.1	1079.3	1089.1	1087.2
5°	1090.1	1085.2	1072.4	1081.3	1078.3
7.5°	1081.3	1075.3	1061.5	1065.5	1060.5
10°	1069.4	1062.5	1042.8	1039.8	1033.9
12.5°	1054.6	1045.7	1019.1	1013.2	1002.3
15°	1036.9	1026.0	992.5	973.7	963.9
17.5°	1016.1	1000.4	958.9	937.2	921.4
20°	992.5	972.7	923.4	898.7	877.0
22.5°	966.8	944.1	886.9	853.4	838.6
25°	941.2	909.6	844.5	804.0	789.2
27.5°	910.6	877.0	805.0	758.7	736.0
30°	878.0	840.5	761.6	711.3	684.7
32.5°	846.5	801.1	720.2	661.0	636.3
35°	810.9	760.6	673.8	611.7	590.0
37.5°	776.4	722.2	630.4	562.3	537.7
40°	739.9	680.7	585.0	515.0	489.3
42.5°	702.4	639.3	539.6	466.6	442.0
45°	663.0	596.9	493.3	423.2	399.6
47.5°	625.5	555.4	448.9	378.8	357.1
50°	584.0	514.0	405.5	337.4	316.7
52.5°	543.6	469.6	364.0	298.9	280.2
55°	504.1	427.2	320.6	261.4	242.7
57.5°	463.7	384.8	282.2	226.9	211.1
60°	422.2	343.3	241.7	191.4	175.6
62.5°	381.8	302.9	207.2	159.8	151.9
65°	340.4	260.4	171.7	138.1	135.2
67.5°	300.9	221.0	138.1	121.3	118.4
70°	259.5	182.5	114.4	104.6	100.6
72.5°	220.0	147.0	95.7	87.8	85.8
75°	181.5	112.5	78.9	72.0	71.0
77.5°	143.0	79.9	62.2	58.2	56.2
80°	107.5	57.2	47.4	43.4	43.4
82.5°	75.0	38.5	32.6	30.6	30.6
85°	42.4	21.7	18.7	18.7	18.7
87.5°	15.8	7.9	7.9	6.9	6.9
90°	0.7	9.9	25.0	23.8	24.2
92.5°	11.0	34.8	113.1	52.2	44.8
95°	25.7	63.1	287.8	108.6	83.7
97.5°	38.2	83.3	469.1	218.0	140.2
100°	56.5	102.0	580.0	434.2	262.8
102.5°	73.4	119.0	583.6	734.2	512.4
105°	89.6	135.1	544.0	972.4	827.4
107.5°	107.2	151.2	507.3	1058.6	1039.5
110°	124.8	167.8	482.3	1044.7	1126.2



TEST NUMBER: P1000020

CATALOG NUMBER: SA2XXRDIP-B675D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.0	183.5	466.2	997.3	1124.7
115°	157.8	199.3	455.2	939.3	1088.7
117.5°	175.5	215.1	449.3	883.9	1034.4
120°	191.6	230.5	444.2	834.4	982.3
122.5°	207.0	246.3	441.2	795.8	928.0
125°	220.2	260.6	437.5	761.0	883.2
127.5°	231.3	274.2	435.3	731.2	841.3
130°	240.8	286.3	433.9	701.1	806.8
132.5°	249.6	298.0	433.1	669.9	770.8
135°	258.4	308.4	432.4	639.4	731.9
137.5°	266.5	317.2	432.4	608.6	694.5
140°	276.0	325.2	431.7	581.4	655.6
142.5°	285.6	331.8	431.7	555.4	616.7
145°	295.1	339.2	430.2	534.0	584.4
147.5°	305.4	345.0	428.0	515.4	555.7
150°	315.7	350.9	425.8	499.2	530.8
152.5°	326.0	356.8	422.1	485.6	509.5
155°	335.5	362.3	417.7	472.4	491.1
157.5°	343.6	366.7	413.3	459.9	475.0
160°	351.7	371.1	408.9	447.4	459.6
162.5°	359.7	374.4	405.2	435.7	444.9
165°	365.6	376.6	400.1	424.4	430.9
167.5°	370.7	378.8	395.7	414.0	417.7
170°	375.9	379.9	392.0	404.5	406.0
172.5°	378.8	381.0	387.6	396.0	396.4
175°	381.0	381.4	384.7	389.5	388.4
177.5°	382.5	381.8	381.8	384.7	382.5
180°	381.8	381.8	381.8	381.8	381.8

(END OF REPORT)