

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000048

Luminaire Tested: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000048
REPORT IS A COMBINATION OF REPORTS P988605 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5943.1 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000048

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000048

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	42	41	40
2	88	80	75	70	79	73	69	64	60	57	54	48	46	44	37	36	34
3	80	71	64	59	73	65	59	54	54	49	46	43	40	37	33	31	30
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	56	47	40	35	39	34	30	31	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	29	25	21	24	21	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P1000048

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	1.8
10°-20°	293.0	4.9
20°-30°	411.3	6.9
30°-40°	448.4	7.5
40°-50°	412.1	6.9
50°-60°	323.6	5.4
60°-70°	210.7	3.5
70°-80°	108.4	1.8
80°-90°	31.0	0.5
90°-100°	209.2	3.5
100°-110°	707.2	11.9
110°-120°	743.4	12.5
120°-130°	611.3	10.3
130°-140°	491.2	8.3
140°-150°	371.1	6.2
150°-160°	260.9	4.4
160°-170°	153.6	2.6
170°-180°	50.0	0.8
0°-30°	811.1	13.6
0°-40°	1259.4	21.2
0°-60°	1995.2	33.6
0°-90°	2345.3	39.5
90°-120°	1659.8	27.9
90°-150°	3133.4	52.7
90°-180°	3598.0	60.5
0°-180°	5943.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	1	13	34	32	33	5
95°	35	85	389	147	113	36
105°	121	183	735	1314	1118	129
115°	213	269	615	1270	1472	212
125°	298	352	592	1029	1194	265
135°	349	417	584	864	989	270
145°	399	458	582	722	790	250
155°	454	490	565	639	664	209
165°	494	509	541	574	582	139
175°	515	516	520	526	525	49
180°	516	516	516	516	516	

TEST NUMBER: P1000048

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	1.0	13.4	33.7	32.2	32.7
92.5°	14.9	47.2	152.8	70.4	60.5
95°	34.7	85.4	389.0	146.9	113.1
97.5°	51.6	112.6	634.1	294.8	189.5
100°	76.4	137.9	784.0	587.0	355.3
102.5°	99.2	160.8	788.9	992.4	692.7
105°	121.1	182.6	735.4	1314.4	1118.4
107.5°	144.9	204.4	685.7	1431.1	1405.2
110°	168.7	226.8	652.0	1412.2	1522.3

TEST NUMBER: P1000048

CATALOG NUMBER: SA2XXRDIP-B675D925UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.5	248.1	630.2	1348.2	1520.3
115°	213.4	269.4	615.3	1269.8	1471.7
117.5°	237.2	290.8	607.3	1194.8	1398.3
120°	259.0	311.6	600.4	1127.8	1327.8
122.5°	279.8	333.0	596.4	1075.7	1254.4
125°	297.7	352.3	591.5	1028.6	1193.8
127.5°	312.6	370.6	588.5	988.4	1137.3
130°	325.5	387.0	586.5	947.8	1090.6
132.5°	337.4	402.9	585.5	905.6	1042.0
135°	349.3	416.8	584.5	864.4	989.4
137.5°	360.2	428.7	584.5	822.7	938.8
140°	373.1	439.6	583.5	786.0	886.2
142.5°	386.0	448.6	583.5	750.8	833.6
145°	398.9	458.5	581.5	722.0	789.9
147.5°	412.8	466.4	578.6	696.7	751.2
150°	426.7	474.4	575.6	674.8	717.5
152.5°	440.6	482.3	570.6	656.4	688.7
155°	453.5	489.8	564.7	638.6	663.9
157.5°	464.4	495.6	558.7	621.8	642.1
160°	475.3	501.6	552.8	604.8	621.2
162.5°	486.3	506.1	547.8	589.0	601.4
165°	494.2	509.1	540.8	573.6	582.5
167.5°	501.1	512.1	534.9	559.7	564.7
170°	508.1	513.6	529.9	546.8	548.8
172.5°	512.1	515.0	524.0	535.4	535.9
175°	515.0	515.5	520.0	526.5	525.0
177.5°	517.0	516.0	516.0	520.0	517.0
180°	516.0	516.0	516.0	516.0	516.0

(END OF REPORT)