

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000062

Luminaire Tested: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000062
REPORT IS A COMBINATION OF REPORTS P988619 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7069.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46		
1	98	94	90	87	90	86	83	80	72	70	68	59	58	57	47	47	46	40		
2	89	83	77	72	82	76	71	67	64	61	58	53	51	48	43	41	40	35		
3	82	73	66	61	75	68	62	57	57	53	49	48	44	42	39	36	35	31		
4	76	65	58	52	69	61	54	49	51	47	43	43	39	37	35	33	31	27		
5	70	59	51	45	64	54	48	43	46	41	37	39	35	32	32	29	27	24		
6	64	53	45	40	59	49	42	38	42	37	33	36	32	29	29	27	24	22		
7	60	48	41	35	55	45	38	33	39	33	30	33	29	26	27	24	22	19		
8	56	44	37	31	51	41	34	30	35	30	27	30	26	23	25	22	20	18		
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	20	18	16		
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29788	29788	29788	29788
5°	29857	31640	29961	25276
10°	29529	33442	29738	20873
15°	28888	33453	29378	15680
20°	28116	27652	28729	12937
25°	27183	17278	27770	11005
30°	25989	11063	26695	9475
35°	24537	8502	25333	8108
40°	22921	7146	23900	7092
45°	21191	6082	22078	5954
50°	19420	5168	20326	5150
55°	17459	4492	18399	4432
60°	15715	3425	16547	3384
65°	14085	2577	14924	2923
70°	12291	2059	13252	2383
75°	10388	1577	11339	1803
80°	8247	1072	8878	1181
85°	5721	553	6286	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27250 cd/sqm

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.5	2.5
10°-20°	498.2	7.0
20°-30°	641.2	9.1
30°-40°	608.3	8.6
40°-50°	521.3	7.4
50°-60°	397.0	5.6
60°-70°	250.4	3.5
70°-80°	124.9	1.8
80°-90°	36.0	0.5
90°-100°	84.4	1.2
100°-110°	268.2	3.8
110°-120°	458.9	6.5
120°-130°	603.6	8.5
130°-140°	677.5	9.6
140°-150°	664.4	9.4
150°-160°	557.3	7.9
160°-170°	369.6	5.2
170°-180°	129.2	1.8
0°-30°	1317.9	18.6
0°-40°	1926.2	27.2
0°-60°	2844.6	40.2
0°-90°	3255.9	46.1
90°-120°	811.5	11.5
90°-150°	2757.0	39.0
90°-180°	3813.0	53.9
0°-180°	7069.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1882	1882	1882	1882	1882	
5°	1883	2094	1890	1673	1883	179
15°	1775	2363	1805	1108	1775	499
25°	1574	1261	1608	803	1574	723
35°	1292	621	1334	592	1292	808
45°	970	432	1011	422	970	749
55°	655	300	690	296	655	590
65°	396	156	420	176	396	393
75°	186	82	203	94	186	201
85°	40	24	44	25	40	46
90°	1	39	1	39	1	6
95°	60	71	60	71	60	67
105°	248	256	248	256	248	261
115°	460	460	460	460	460	455
125°	670	672	670	672	670	599
135°	867	877	867	877	867	670
145°	1052	1064	1052	1064	1052	657
155°	1203	1212	1203	1212	1203	554
165°	1309	1310	1309	1310	1309	369
175°	1362	1357	1362	1357	1362	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1893.6	1901.4	1905.3	1910.6	1922.3	1930.2	1942.0	1944.6	1943.3	1948.5	1934.1
5°	1883.1	1900.1	1915.8	1928.9	1949.8	1962.9	1977.3	1994.3	1998.2	2017.8	2006.0
7.5°	1868.7	1893.6	1915.8	1942.0	1973.3	1990.4	2012.6	2038.7	2050.5	2074.0	2080.6
10°	1845.2	1880.5	1918.4	1945.9	1989.0	2019.1	2040.0	2081.9	2109.4	2144.7	2139.4
12.5°	1807.3	1853.0	1904.0	1949.8	2006.0	2025.7	2064.9	2108.0	2143.4	2176.0	2204.8
15°	1774.6	1826.9	1883.1	1939.3	2003.4	2040.0	2079.3	2135.5	2173.4	2231.0	2255.8
17.5°	1730.1	1796.8	1863.5	1926.3	2002.1	2044.0	2092.4	2147.3	2203.5	2258.4	2278.0
20°	1684.3	1756.3	1828.2	1913.2	1999.5	2040.0	2089.7	2157.7	2212.7	2255.8	2255.8
22.5°	1629.4	1717.0	1799.4	1880.5	1974.7	2033.5	2084.5	2164.3	2203.5	2212.7	2177.4
25°	1574.5	1662.1	1752.3	1853.0	1960.3	2012.6	2070.1	2144.7	2157.7	2121.1	2029.6
27.5°	1509.1	1607.2	1709.2	1817.7	1930.2	1995.6	2047.9	2097.6	2072.7	1974.7	1832.1
30°	1442.4	1548.3	1663.4	1766.7	1902.7	1962.9	2007.4	2021.7	1943.3	1783.7	1599.3
32.5°	1373.1	1476.4	1598.0	1722.3	1859.6	1917.1	1945.9	1908.0	1764.1	1562.7	1337.8
35°	1292.0	1408.4	1535.3	1664.7	1800.7	1843.9	1860.9	1768.0	1583.6	1323.4	1099.8
37.5°	1218.8	1335.2	1471.2	1603.3	1735.3	1758.9	1741.9	1596.7	1362.6	1105.0	886.6
40°	1132.5	1256.7	1390.1	1537.9	1646.4	1653.0	1611.1	1422.8	1132.5	890.6	755.9
42.5°	1052.7	1178.3	1311.6	1462.0	1544.4	1522.2	1466.0	1218.8	945.5	767.6	659.1
45°	970.3	1089.3	1233.2	1366.6	1425.4	1373.1	1288.1	1025.3	793.8	660.4	576.7
47.5°	890.6	1001.7	1144.3	1272.4	1282.9	1224.0	1123.3	859.2	687.9	580.6	512.6
50°	812.1	923.3	1056.6	1162.6	1152.1	1071.0	957.3	746.7	597.6	512.6	456.4
52.5°	733.6	834.3	963.8	1047.5	1003.0	924.6	812.1	632.9	521.8	447.2	404.1
55°	655.2	749.3	860.5	929.8	859.2	768.9	689.2	542.7	452.5	392.3	359.6
57.5°	589.8	664.3	766.3	808.2	723.2	652.6	583.2	466.9	392.3	349.2	311.2
60°	517.9	585.9	669.6	694.4	606.8	549.2	490.4	394.9	336.1	298.2	273.3
62.5°	456.4	512.6	576.7	576.7	499.5	456.4	411.9	330.9	282.5	252.4	240.6
65°	396.2	436.8	482.5	477.3	411.9	374.0	338.7	273.3	236.7	215.8	204.0
67.5°	337.4	368.8	398.9	380.5	333.5	300.8	268.1	221.0	196.2	181.8	166.1
70°	283.8	308.6	324.3	307.3	260.2	232.8	209.2	177.8	158.2	139.9	130.8
72.5°	238.0	248.5	253.7	232.8	193.5	177.8	160.8	138.6	121.6	112.5	109.8
75°	185.7	194.9	190.9	175.2	142.5	130.8	117.7	102.0	98.1	92.8	90.2
77.5°	145.2	145.2	138.6	124.2	102.0	92.8	87.6	79.8	75.8	74.5	71.9
80°	103.3	102.0	98.1	82.4	69.3	64.1	64.1	58.8	57.5	54.9	54.9
82.5°	68.0	68.0	62.8	49.7	45.8	44.5	43.2	40.5	40.5	39.2	39.2
85°	40.5	37.9	31.4	27.5	26.2	26.2	24.8	23.5	24.8	23.5	23.5
87.5°	18.3	14.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
90°	1.2	4.3	7.3	10.4	13.5	15.0	17.8	23.4	29.1	34.7	40.3
92.5°	25.3	27.3	29.4	31.4	33.5	34.5	34.6	34.9	35.2	35.4	35.7
95°	59.8	62.4	65.0	67.5	70.1	71.4	71.7	72.2	72.7	73.2	73.7
97.5°	100.1	102.4	104.7	107.0	109.3	110.5	111.0	112.0	113.1	114.1	115.1
100°	146.2	148.2	150.3	152.3	154.4	155.4	155.8	156.5	157.3	158.0	158.8
102.5°	194.5	196.0	197.6	199.1	200.6	201.4	201.9	202.9	204.0	205.0	206.0
105°	247.5	248.3	249.0	249.8	250.5	250.9	251.2	251.7	252.2	252.7	253.2
107.5°	300.4	301.4	302.4	303.5	304.5	305.0	305.0	305.0	305.0	305.0	305.0
110°	351.0	352.5	354.1	355.6	357.1	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	406.3	407.8	409.4	410.9	412.4	413.2	413.1	412.8	412.5	412.3	412.0
115°	460.4	461.9	463.5	465.0	466.5	467.3	467.0	466.5	466.0	465.5	465.0
117.5°	514.5	516.5	518.6	520.6	522.7	523.7	523.1	521.8	520.5	519.2	517.9
120°	568.6	570.6	572.7	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6
122.5°	618.1	620.7	623.2	625.8	628.3	629.6	629.0	627.7	626.4	625.1	623.8
125°	669.8	672.1	674.4	676.7	679.0	680.2	679.8	679.1	678.3	677.6	676.8
127.5°	720.5	723.3	726.1	729.0	731.8	733.2	732.7	731.6	730.6	729.5	728.5
130°	767.7	771.0	774.3	777.6	780.9	782.6	782.3	781.8	781.3	780.8	780.3
132.5°	820.6	823.2	825.7	828.3	830.8	832.1	832.2	832.5	832.8	833.0	833.3
135°	866.7	869.5	872.3	875.1	877.9	879.3	879.6	880.1	880.6	881.1	881.6
137.5°	917.3	919.6	921.9	924.2	926.5	927.7	928.0	928.5	929.0	929.5	930.0
140°	962.2	964.5	966.8	969.1	971.4	972.5	973.1	974.4	975.7	977.0	978.3
142.5°	1008.2	1010.5	1012.8	1015.1	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0
145°	1052.0	1053.8	1055.6	1057.3	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9
147.5°	1091.1	1093.4	1095.7	1098.0	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1
150°	1131.4	1132.9	1134.5	1136.0	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9
152.5°	1167.1	1168.6	1170.2	1171.7	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7
155°	1202.7	1203.5	1204.3	1205.0	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6
157.5°	1233.8	1234.3	1234.8	1235.3	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4
160°	1261.4	1261.9	1262.4	1262.9	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9
162.5°	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9
165°	1308.6	1308.4	1308.1	1307.9	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
167.5°	1328.2	1327.4	1326.6	1325.9	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7
170°	1343.2	1342.4	1341.6	1340.9	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5
172.5°	1353.5	1352.7	1352.0	1351.2	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9
175°	1361.6	1360.8	1360.0	1359.3	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8
177.5°	1366.2	1365.4	1364.6	1363.9	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1948.5	1951.1	1955.0	1973.3	1976.0	1981.2	1978.6	1978.6	1979.9	1977.3	1978.6
5°	2032.2	2036.1	2055.7	2078.0	2083.2	2078.0	2084.5	2093.7	2093.7	2093.7	2091.0
7.5°	2110.7	2125.0	2147.3	2180.0	2186.5	2193.0	2204.8	2197.0	2199.6	2211.4	2207.4
10°	2186.5	2207.4	2232.3	2259.7	2274.1	2283.3	2288.5	2300.3	2327.7	2296.4	2308.1
12.5°	2258.4	2288.5	2314.7	2344.7	2355.2	2367.0	2370.9	2381.4	2381.4	2380.1	2389.2
15°	2305.5	2333.0	2356.5	2376.1	2378.7	2376.1	2373.5	2374.8	2378.7	2363.1	2372.2
17.5°	2316.0	2318.6	2326.4	2318.6	2319.9	2292.4	2276.7	2272.8	2236.2	2237.5	2267.6
20°	2265.0	2220.5	2208.7	2165.6	2139.4	2068.8	2066.2	2046.6	1969.4	1993.0	1987.7
22.5°	2125.0	2049.2	1948.5	1898.8	1874.0	1799.4	1741.9	1701.3	1673.9	1646.4	1634.7
25°	1940.7	1817.7	1675.2	1577.1	1562.7	1493.4	1387.5	1337.8	1279.0	1260.6	1292.0
27.5°	1702.7	1543.1	1382.3	1231.9	1204.4	1141.6	1088.0	1052.7	984.7	980.8	983.4
30°	1379.6	1218.8	1084.1	986.0	918.0	889.2	853.9	827.8	800.3	810.8	813.4
32.5°	1133.8	980.8	855.2	802.9	771.6	753.2	723.2	706.2	694.4	690.5	689.2
35°	901.0	799.0	742.8	691.8	673.5	660.4	638.2	630.3	619.9	621.2	621.2
37.5°	771.6	686.6	644.7	618.6	601.6	595.0	580.6	572.8	566.2	563.6	567.6
40°	665.6	606.8	580.6	557.1	542.7	540.1	532.2	523.1	515.2	516.5	520.5
42.5°	588.5	554.5	523.1	504.8	494.3	490.4	483.9	477.3	477.3	473.4	472.1
45°	527.0	499.5	473.4	456.4	449.9	444.6	436.8	435.5	430.2	431.5	432.9
47.5°	472.1	449.9	430.2	413.2	406.7	405.4	397.5	392.3	392.3	391.0	389.7
50°	422.4	400.2	383.2	374.0	364.9	362.2	360.9	359.6	357.0	357.0	358.3
52.5°	381.9	359.6	346.5	338.7	333.5	330.9	330.9	329.5	329.5	329.5	328.2
55°	337.4	319.1	308.6	306.0	303.4	302.1	300.8	298.2	296.9	299.5	296.9
57.5°	295.5	289.0	279.9	277.2	270.7	270.7	266.8	264.2	261.5	264.2	264.2
60°	262.9	253.7	248.5	240.6	235.4	230.2	223.6	222.3	219.7	218.4	217.1
62.5°	228.9	221.0	207.9	196.2	188.3	183.1	180.5	179.2	179.2	177.8	177.8
65°	190.9	172.6	166.1	162.2	160.8	159.5	156.9	155.6	156.9	155.6	156.9
67.5°	149.1	146.5	142.5	139.9	138.6	137.3	137.3	136.0	136.0	136.0	136.0
70°	129.5	122.9	121.6	119.0	119.0	117.7	117.7	117.7	117.7	116.4	119.0
72.5°	107.2	103.3	102.0	100.7	100.7	100.7	99.4	99.4	99.4	98.1	99.4
75°	87.6	86.3	83.7	83.7	82.4	83.7	82.4	82.4	81.1	82.4	82.4
77.5°	70.6	69.3	68.0	68.0	66.7	66.7	66.7	66.7	66.7	66.7	68.0
80°	53.6	52.3	51.0	52.3	51.0	52.3	51.0	51.0	52.3	51.0	51.0
82.5°	39.2	37.9	37.9	36.6	36.6	36.6	36.6	36.6	36.6	36.6	36.6
85°	23.5	22.2	22.2	23.5	22.2	23.5	22.2	22.2	22.2	23.5	23.5
87.5°	10.5	11.8	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.8
90°	39.8	39.3	38.8	38.3	38.0	38.1	38.4	38.6	38.9	39.1	38.9
92.5°	35.9	36.2	36.4	36.7	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.7	73.7	73.7	73.7	73.4	72.9	72.4	71.9	71.4	71.9
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.8	158.8	158.8	158.8	158.7	158.4	158.2	157.9	157.7	157.9
102.5°	206.3	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	206.3
105°	253.7	254.2	254.7	255.2	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	305.3	305.5	305.8	306.1	306.2	305.6	304.3	303.0	301.7	300.4	301.7
110°	357.9	357.9	357.9	357.9	357.9	357.5	356.8	356.0	355.3	354.5	355.3

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	411.2	410.5	409.7	409.0	408.6	408.3	407.8	407.3	406.8	406.3	406.8
115°	464.7	464.5	464.2	463.9	463.8	463.4	462.7	461.9	461.2	460.4	461.2
117.5°	517.1	516.4	515.6	514.9	514.5	514.1	513.3	512.6	511.8	511.0	511.8
120°	568.6	568.6	568.6	568.6	568.6	568.2	567.4	566.7	565.9	565.1	565.9
122.5°	623.0	622.3	621.5	620.8	620.4	620.1	619.6	619.1	618.6	618.1	618.6
125°	676.0	675.2	674.5	673.7	673.3	673.2	672.9	672.7	672.4	672.2	672.4
127.5°	727.5	726.5	725.4	724.4	723.9	723.5	722.8	722.0	721.3	720.5	721.3
130°	779.8	779.3	778.8	778.3	778.0	777.5	776.5	775.4	774.4	773.4	774.4
132.5°	832.0	830.7	829.4	828.1	827.5	827.1	826.4	825.6	824.9	824.1	824.9
135°	881.4	881.1	880.9	880.6	880.5	880.1	879.3	878.6	877.8	877.0	877.8
137.5°	929.7	929.5	929.2	928.9	928.8	928.3	927.3	926.2	925.2	924.2	925.2
140°	978.3	978.3	978.3	978.3	978.3	977.8	976.8	975.7	974.7	973.7	974.7
142.5°	1022.3	1022.5	1022.8	1023.1	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6
145°	1067.2	1067.4	1067.7	1068.0	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5
147.5°	1106.6	1107.1	1107.6	1108.1	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8
150°	1143.7	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7
152.5°	1180.7	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7
155°	1210.9	1212.2	1213.5	1214.8	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7
157.5°	1240.2	1242.0	1243.8	1245.6	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0
160°	1266.4	1268.0	1269.5	1271.0	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2
162.5°	1289.7	1291.5	1293.3	1295.1	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5
165°	1309.3	1311.1	1312.8	1314.6	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1
167.5°	1326.5	1328.3	1330.1	1331.9	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3
170°	1340.3	1342.1	1343.9	1345.7	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2
172.5°	1350.7	1352.5	1354.3	1356.1	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6
175°	1357.6	1359.4	1361.2	1363.0	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5
177.5°	1361.9	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1983.8	1974.7	1972.0	1974.7	1972.0	1973.3	1964.2	1930.2	1939.3	1925.0	1932.8
5°	2096.3	2088.4	2071.4	2068.8	2066.2	2063.6	2050.5	2020.4	2008.7	1989.0	1987.7
7.5°	2203.5	2203.5	2190.4	2181.3	2169.5	2160.4	2143.4	2098.9	2080.6	2057.0	2044.0
10°	2309.4	2275.4	2289.8	2280.7	2251.9	2246.7	2215.3	2189.1	2153.8	2130.3	2109.4
12.5°	2385.3	2374.8	2361.7	2353.9	2346.0	2329.0	2308.1	2241.4	2223.1	2176.0	2152.5
15°	2382.7	2376.1	2380.1	2380.1	2377.4	2373.5	2356.5	2308.1	2276.7	2231.0	2190.4
17.5°	2254.5	2271.5	2288.5	2300.3	2326.4	2338.2	2353.9	2325.1	2305.5	2266.3	2223.1
20°	2030.9	2072.7	2122.4	2132.9	2156.4	2225.7	2257.1	2282.0	2289.8	2276.7	2241.4
22.5°	1719.7	1755.0	1875.3	1872.7	1906.7	1989.0	2080.6	2155.1	2214.0	2246.7	2233.6
25°	1347.0	1396.6	1460.7	1509.1	1620.3	1743.2	1857.0	1976.0	2078.0	2168.2	2190.4
27.5°	1018.7	1084.1	1135.1	1199.2	1255.4	1400.6	1547.0	1732.7	1851.7	2023.0	2112.0
30°	823.9	853.9	904.9	935.0	962.5	1073.6	1239.7	1422.8	1632.0	1829.5	1982.5
32.5°	703.6	724.5	762.4	775.5	804.2	878.8	983.4	1150.8	1366.6	1605.9	1807.3
35°	631.6	653.9	661.7	673.5	697.0	744.1	816.0	937.6	1132.5	1366.6	1607.2
37.5°	570.2	581.9	604.2	612.0	619.9	655.2	703.6	788.6	918.0	1110.3	1377.0
40°	527.0	533.5	545.3	551.9	557.1	581.9	625.1	682.6	778.1	924.6	1170.4
42.5°	481.2	489.1	496.9	504.8	511.3	530.9	557.1	612.0	676.1	787.2	965.1
45°	436.8	442.0	451.2	456.4	465.5	481.2	504.8	542.7	600.2	670.9	814.7
47.5°	396.2	402.8	406.7	413.2	419.8	436.8	459.0	483.9	530.9	600.2	704.9
50°	359.6	367.5	372.7	374.0	379.2	394.9	413.2	440.7	470.8	524.4	615.9
52.5°	333.5	334.8	338.7	343.9	342.6	351.8	368.8	389.7	421.1	464.2	530.9
55°	303.4	307.3	309.9	311.2	311.2	319.1	328.2	347.9	372.7	408.0	464.2
57.5°	265.5	269.4	277.2	279.9	283.8	287.7	291.6	304.7	325.6	359.6	405.4
60°	226.2	228.9	236.7	241.9	244.5	255.0	260.2	270.7	282.5	307.3	350.5
62.5°	181.8	184.4	188.3	193.5	198.8	214.5	227.5	238.0	247.2	264.2	299.5
65°	158.2	159.5	162.2	163.5	164.8	171.3	183.1	197.5	214.5	227.5	248.5
67.5°	137.3	138.6	139.9	142.5	143.8	145.2	150.4	154.3	171.3	189.6	205.3
70°	117.7	120.3	121.6	121.6	122.9	125.5	128.2	133.4	138.6	147.8	167.4
72.5°	99.4	100.7	103.3	103.3	103.3	105.9	108.5	111.2	113.8	119.0	126.8
75°	82.4	85.0	85.0	85.0	86.3	86.3	88.9	91.5	94.2	98.1	100.7
77.5°	68.0	68.0	68.0	68.0	69.3	69.3	70.6	73.2	74.5	75.8	78.5
80°	51.0	52.3	52.3	52.3	53.6	53.6	53.6	56.2	57.5	57.5	60.2
82.5°	37.9	37.9	37.9	39.2	37.9	39.2	39.2	40.5	39.2	40.5	41.8
85°	23.5	23.5	23.5	24.8	24.8	24.8	24.8	24.8	24.8	24.8	26.2
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.1	11.8	11.8
90°	38.6	38.4	38.1	38.0	38.3	38.8	39.3	39.8	40.3	34.7	29.1
92.5°	36.8	36.8	36.8	36.8	36.7	36.4	36.2	35.9	35.7	35.4	35.2
95°	72.4	72.9	73.4	73.7	73.7	73.7	73.7	73.7	73.7	73.2	72.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	114.1	113.1
100°	158.2	158.4	158.7	158.8	158.8	158.8	158.8	158.8	158.8	158.0	157.3
102.5°	206.5	206.8	207.1	207.2	207.1	206.8	206.5	206.3	206.0	205.0	204.0
105°	255.5	255.5	255.5	255.5	255.2	254.7	254.2	253.7	253.2	252.7	252.2
107.5°	303.0	304.3	305.6	306.2	306.1	305.8	305.5	305.3	305.0	305.0	305.0
110°	356.0	356.8	357.5	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	407.3	407.8	408.3	408.6	409.0	409.7	410.5	411.2	412.0	412.3	412.5
115°	461.9	462.7	463.4	463.8	463.9	464.2	464.5	464.7	465.0	465.5	466.0
117.5°	512.6	513.3	514.1	514.5	514.9	515.6	516.4	517.1	517.9	519.2	520.5
120°	566.7	567.4	568.2	568.6	568.6	568.6	568.6	568.6	568.6	570.6	572.7
122.5°	619.1	619.6	620.1	620.4	620.8	621.5	622.3	623.0	623.8	625.1	626.4
125°	672.7	672.9	673.2	673.3	673.7	674.5	675.2	676.0	676.8	677.6	678.3
127.5°	722.0	722.8	723.5	723.9	724.4	725.4	726.5	727.5	728.5	729.5	730.6
130°	775.4	776.5	777.5	778.0	778.3	778.8	779.3	779.8	780.3	780.8	781.3
132.5°	825.6	826.4	827.1	827.5	828.1	829.4	830.7	832.0	833.3	833.0	832.8
135°	878.6	879.3	880.1	880.5	880.6	880.9	881.1	881.4	881.6	881.1	880.6
137.5°	926.2	927.3	928.3	928.8	928.9	929.2	929.5	929.7	930.0	929.5	929.0
140°	975.7	976.8	977.8	978.3	978.3	978.3	978.3	978.3	978.3	977.0	975.7
142.5°	1020.6	1021.7	1022.7	1023.2	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5
145°	1065.5	1066.6	1067.6	1068.1	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8
147.5°	1105.8	1106.9	1107.9	1108.4	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1
150°	1144.4	1145.2	1145.9	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9
152.5°	1181.7	1182.8	1183.8	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2
155°	1213.5	1214.2	1215.0	1215.4	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1
157.5°	1243.3	1244.6	1245.9	1246.5	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4
160°	1269.2	1270.3	1271.3	1271.8	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4
162.5°	1292.8	1294.1	1295.4	1296.0	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4
165°	1312.3	1313.6	1314.9	1315.5	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5
167.5°	1329.6	1330.9	1332.2	1332.8	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7
170°	1342.8	1344.3	1345.8	1346.6	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0
172.5°	1353.2	1354.7	1356.2	1357.0	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4
175°	1360.1	1361.6	1363.1	1363.9	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8
177.5°	1363.5	1365.0	1366.5	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1921.0	1914.5	1914.5	1910.6	1910.6	1889.7	1889.7	1896.2	1888.3	1879.2	1866.1
5°	1970.7	1956.3	1952.4	1947.2	1930.2	1904.0	1893.6	1889.7	1874.0	1854.3	1832.1
7.5°	2017.8	1994.3	1982.5	1970.7	1948.5	1911.9	1891.0	1876.6	1853.0	1823.0	1794.2
10°	2063.6	2033.5	2003.4	1989.0	1957.7	1911.9	1881.8	1858.3	1824.3	1783.7	1743.2
12.5°	2105.4	2042.7	2037.4	2008.7	1962.9	1910.6	1864.8	1830.8	1787.7	1740.6	1693.5
15°	2142.0	2078.0	2046.6	2020.4	1960.3	1894.9	1846.5	1804.7	1747.1	1693.5	1636.0
17.5°	2160.4	2091.0	2070.1	2027.0	1965.5	1880.5	1815.1	1764.1	1701.3	1637.3	1571.9
20°	2178.7	2097.6	2063.6	2033.5	1949.8	1853.0	1779.8	1721.0	1651.7	1575.8	1503.9
22.5°	2187.8	2097.6	2057.0	2015.2	1934.1	1823.0	1736.7	1667.3	1586.3	1509.1	1422.8
25°	2172.1	2089.7	2041.4	1998.2	1906.7	1786.3	1687.0	1608.5	1522.2	1434.6	1347.0
27.5°	2132.9	2071.4	2015.2	1970.7	1868.7	1739.3	1634.7	1545.7	1456.8	1358.7	1269.8
30°	2059.7	2032.2	1987.7	1938.0	1826.9	1697.4	1573.2	1481.6	1383.6	1285.5	1192.6
32.5°	1945.9	1969.4	1940.7	1897.5	1777.2	1639.9	1507.8	1415.0	1307.7	1201.8	1116.8
35°	1807.3	1891.0	1875.3	1845.2	1724.9	1578.4	1446.3	1333.9	1226.6	1119.4	1034.4
37.5°	1655.6	1782.4	1795.5	1777.2	1664.7	1515.6	1370.5	1260.6	1150.8	1042.3	955.9
40°	1447.6	1642.5	1684.3	1692.2	1602.0	1439.8	1288.1	1180.9	1072.3	966.4	861.8
42.5°	1256.7	1502.6	1554.9	1587.6	1522.2	1365.3	1212.3	1093.3	986.0	890.6	785.9
45°	1077.6	1333.9	1418.9	1460.7	1432.0	1280.3	1122.0	1010.9	912.8	825.2	724.5
47.5°	893.2	1150.8	1269.8	1336.5	1336.5	1193.9	1035.7	925.9	831.7	757.2	668.2
50°	770.2	984.7	1107.6	1195.3	1218.8	1106.3	957.3	850.0	761.1	680.0	612.0
52.5°	656.5	848.7	950.7	1042.3	1110.3	1012.2	869.6	772.9	685.2	609.4	555.8
55°	567.6	711.4	804.2	904.9	980.8	916.7	784.6	690.5	614.6	551.9	506.1
57.5°	482.5	608.1	683.9	772.9	853.9	805.6	699.6	618.6	551.9	496.9	456.4
60°	410.6	512.6	571.5	640.8	741.5	707.5	619.9	545.3	491.7	442.0	408.0
62.5°	349.2	430.2	479.9	529.6	621.2	605.5	537.5	479.9	434.2	392.3	363.5
65°	286.4	353.1	392.3	435.5	508.7	515.2	460.3	419.8	377.9	341.3	315.2
67.5°	231.5	283.8	319.1	355.7	414.5	432.9	394.9	360.9	325.6	295.5	272.0
70°	187.0	223.6	249.8	278.5	326.9	349.2	329.5	306.0	277.2	252.4	231.5
72.5°	147.8	171.3	187.0	209.2	248.5	270.7	269.4	248.5	227.5	210.5	193.5
75°	108.5	126.8	139.9	154.3	185.7	206.6	211.9	202.7	181.8	168.7	155.6
77.5°	82.4	92.8	99.4	109.8	132.1	150.4	158.2	155.6	141.2	130.8	121.6
80°	62.8	65.4	68.0	71.9	90.2	107.2	112.5	111.2	103.3	99.4	88.9
82.5°	44.5	45.8	47.1	48.4	54.9	69.3	74.5	77.2	70.6	66.7	57.5
85°	26.2	27.5	27.5	30.1	31.4	35.3	44.5	44.5	43.2	37.9	36.6
87.5°	13.1	13.1	11.8	11.8	13.1	14.4	17.0	19.6	17.0	15.7	14.4
90°	23.4	17.8	15.0	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.9	34.6	34.5	33.5	31.4	29.4	27.3	25.3	27.3	29.4	31.4
95°	72.2	71.7	71.4	70.1	67.5	65.0	62.4	59.8	62.4	65.0	67.5
97.5°	112.0	111.0	110.5	109.3	107.0	104.7	102.4	100.1	102.4	104.7	107.0
100°	156.5	155.8	155.4	154.4	152.3	150.3	148.2	146.2	148.2	150.3	152.3
102.5°	202.9	201.9	201.4	200.6	199.1	197.6	196.0	194.5	196.0	197.6	199.1
105°	251.7	251.2	250.9	250.5	249.8	249.0	248.3	247.5	248.3	249.0	249.8
107.5°	305.0	305.0	305.0	304.5	303.5	302.4	301.4	300.4	301.4	302.4	303.5
110°	357.9	357.9	357.9	357.1	355.6	354.1	352.5	351.0	352.5	354.1	355.6

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	412.8	413.1	413.2	412.4	410.9	409.4	407.8	406.3	407.8	409.4	410.9
115°	466.5	467.0	467.3	466.5	465.0	463.5	461.9	460.4	461.9	463.5	465.0
117.5°	521.8	523.1	523.7	522.7	520.6	518.6	516.5	514.5	516.5	518.6	520.6
120°	574.7	576.8	577.8	576.8	574.7	572.7	570.6	568.6	570.6	572.7	574.7
122.5°	627.7	629.0	629.6	628.3	625.8	623.2	620.7	618.1	620.7	623.2	625.8
125°	679.1	679.8	680.2	679.0	676.7	674.4	672.1	669.8	672.1	674.4	676.7
127.5°	731.6	732.7	733.2	731.8	729.0	726.1	723.3	720.5	723.3	726.1	729.0
130°	781.8	782.3	782.6	780.9	777.6	774.3	771.0	767.7	771.0	774.3	777.6
132.5°	832.5	832.2	832.1	830.8	828.3	825.7	823.2	820.6	823.2	825.7	828.3
135°	880.1	879.6	879.3	877.9	875.1	872.3	869.5	866.7	869.5	872.3	875.1
137.5°	928.5	928.0	927.7	926.5	924.2	921.9	919.6	917.3	919.6	921.9	924.2
140°	974.4	973.1	972.5	971.4	969.1	966.8	964.5	962.2	964.5	966.8	969.1
142.5°	1019.7	1019.0	1018.6	1017.4	1015.1	1012.8	1010.5	1008.2	1010.5	1012.8	1015.1
145°	1062.3	1060.8	1060.0	1059.1	1057.3	1055.6	1053.8	1052.0	1053.8	1055.6	1057.3
147.5°	1103.0	1102.0	1101.5	1100.3	1098.0	1095.7	1093.4	1091.1	1093.4	1095.7	1098.0
150°	1139.8	1138.8	1138.3	1137.5	1136.0	1134.5	1132.9	1131.4	1132.9	1134.5	1136.0
152.5°	1175.9	1174.6	1174.0	1173.2	1171.7	1170.2	1168.6	1167.1	1168.6	1170.2	1171.7
155°	1207.3	1206.6	1206.2	1205.8	1205.0	1204.3	1203.5	1202.7	1203.5	1204.3	1205.0
157.5°	1236.9	1236.4	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3	1234.8	1235.3
160°	1264.1	1263.8	1263.7	1263.4	1262.9	1262.4	1261.9	1261.4	1261.9	1262.4	1262.9
162.5°	1287.2	1286.9	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8	1286.8
165°	1307.5	1307.5	1307.5	1307.6	1307.9	1308.1	1308.4	1308.6	1308.4	1308.1	1307.9
167.5°	1324.7	1324.7	1324.7	1325.1	1325.9	1326.6	1327.4	1328.2	1327.4	1326.6	1325.9
170°	1339.3	1339.6	1339.7	1340.1	1340.9	1341.6	1342.4	1343.2	1342.4	1341.6	1340.9
172.5°	1349.7	1350.0	1350.1	1350.5	1351.2	1352.0	1352.7	1353.5	1352.7	1352.0	1351.2
175°	1357.3	1357.8	1358.1	1358.5	1359.3	1360.0	1360.8	1361.6	1360.8	1360.0	1359.3
177.5°	1361.9	1362.4	1362.7	1363.1	1363.9	1364.6	1365.4	1366.2	1365.4	1364.6	1363.9
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1860.9	1862.2	1866.1	1854.3	1836.0	1828.2	1804.7	1800.7	1796.8	1796.8	1800.7
5°	1819.0	1813.8	1815.1	1792.9	1766.7	1751.0	1718.3	1723.6	1706.6	1696.1	1698.7
7.5°	1773.3	1758.9	1757.6	1728.8	1696.1	1667.3	1633.3	1625.5	1609.8	1591.5	1583.6
10°	1715.7	1705.3	1685.7	1653.0	1611.1	1587.6	1541.8	1514.3	1510.4	1483.0	1472.5
12.5°	1656.9	1638.6	1619.0	1573.2	1526.1	1488.2	1454.2	1424.1	1403.2	1379.6	1364.0
15°	1588.9	1566.6	1544.4	1496.0	1441.1	1403.2	1352.2	1307.7	1246.3	1197.9	1170.4
17.5°	1514.3	1489.5	1459.4	1405.8	1352.2	1299.9	1205.7	1153.4	1110.3	1081.5	1064.5
20°	1437.2	1409.7	1379.6	1326.0	1233.2	1141.6	1089.3	1048.8	1022.6	993.9	972.9
22.5°	1356.1	1327.3	1294.6	1210.9	1112.9	1048.8	1008.3	970.3	932.4	916.7	906.3
25°	1280.3	1254.1	1212.3	1098.5	1021.3	962.5	916.7	891.9	872.2	851.3	831.7
27.5°	1201.8	1153.4	1094.6	999.1	950.7	890.6	857.9	839.6	805.6	791.2	782.0
30°	1107.6	1054.0	997.8	929.8	873.6	831.7	801.6	771.6	751.9	737.6	721.9
32.5°	1012.2	961.2	925.9	855.2	813.4	770.2	741.5	723.2	694.4	685.2	678.7
35°	929.8	886.6	855.2	797.7	758.5	719.2	698.3	670.9	652.6	635.6	625.1
37.5°	848.7	825.2	792.5	744.1	702.2	670.9	642.1	632.9	608.1	598.9	588.5
40°	792.5	757.2	729.7	687.9	652.6	618.6	600.2	579.3	562.3	547.9	544.0
42.5°	724.5	698.3	682.6	636.9	600.2	580.6	558.4	534.9	521.8	510.0	495.6
45°	673.5	649.9	627.7	591.1	558.4	533.5	513.9	498.2	476.0	470.8	448.5
47.5°	619.9	596.3	579.3	542.7	512.6	489.1	474.7	453.8	435.5	423.7	413.2
50°	566.2	546.6	530.9	499.5	473.4	448.5	428.9	408.0	400.2	380.5	374.0
52.5°	515.2	502.2	485.2	455.1	428.9	408.0	387.1	370.1	358.3	347.9	340.0
55°	472.1	451.2	443.3	410.6	388.4	366.2	347.9	337.4	323.0	316.5	309.9
57.5°	423.7	411.9	398.9	374.0	349.2	328.2	315.2	299.5	291.6	283.8	278.5
60°	381.9	364.9	354.4	333.5	311.2	291.6	279.9	268.1	257.6	251.1	240.6
62.5°	333.5	320.4	313.9	291.6	273.3	255.0	244.5	232.8	224.9	213.2	200.1
65°	291.6	281.2	273.3	255.0	238.0	221.0	210.5	196.2	185.7	179.2	177.8
67.5°	255.0	247.2	235.4	218.4	201.4	188.3	176.5	164.8	163.5	160.8	160.8
70°	214.5	206.6	200.1	181.8	167.4	153.0	150.4	146.5	142.5	141.2	138.6
72.5°	179.2	172.6	164.8	149.1	134.7	130.8	128.2	125.5	121.6	120.3	119.0
75°	145.2	136.0	130.8	116.4	112.5	109.8	107.2	103.3	100.7	99.4	96.8
77.5°	111.2	102.0	102.0	94.2	91.5	87.6	85.0	82.4	81.1	78.5	78.5
80°	78.5	78.5	75.8	71.9	68.0	66.7	62.8	61.5	60.2	61.5	58.8
82.5°	57.5	52.3	52.3	49.7	47.1	45.8	43.2	43.2	41.8	41.8	41.8
85°	32.7	32.7	31.4	28.8	27.5	27.5	26.2	26.2	24.8	24.8	23.5
87.5°	13.1	11.8	13.1	11.8	11.8	10.5	10.5	10.5	9.2	10.5	9.2
90°	13.5	15.0	17.8	23.4	29.1	34.7	40.3	39.8	39.3	38.8	38.3
92.5°	33.5	34.5	34.6	34.9	35.2	35.4	35.7	35.9	36.2	36.4	36.7
95°	70.1	71.4	71.7	72.2	72.7	73.2	73.7	73.7	73.7	73.7	73.7
97.5°	109.3	110.5	111.0	112.0	113.1	114.1	115.1	115.1	115.1	115.1	115.1
100°	154.4	155.4	155.8	156.5	157.3	158.0	158.8	158.8	158.8	158.8	158.8
102.5°	200.6	201.4	201.9	202.9	204.0	205.0	206.0	206.3	206.5	206.8	207.1
105°	250.5	250.9	251.2	251.7	252.2	252.7	253.2	253.7	254.2	254.7	255.2
107.5°	304.5	305.0	305.0	305.0	305.0	305.0	305.0	305.3	305.5	305.8	306.1
110°	357.1	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	412.4	413.2	413.1	412.8	412.5	412.3	412.0	411.2	410.5	409.7	409.0
115°	466.5	467.3	467.0	466.5	466.0	465.5	465.0	464.7	464.5	464.2	463.9
117.5°	522.7	523.7	523.1	521.8	520.5	519.2	517.9	517.1	516.4	515.6	514.9
120°	576.8	577.8	576.8	574.7	572.7	570.6	568.6	568.6	568.6	568.6	568.6
122.5°	628.3	629.6	629.0	627.7	626.4	625.1	623.8	623.0	622.3	621.5	620.8
125°	679.0	680.2	679.8	679.1	678.3	677.6	676.8	676.0	675.2	674.5	673.7
127.5°	731.8	733.2	732.7	731.6	730.6	729.5	728.5	727.5	726.5	725.4	724.4
130°	780.9	782.6	782.3	781.8	781.3	780.8	780.3	779.8	779.3	778.8	778.3
132.5°	830.8	832.1	832.2	832.5	832.8	833.0	833.3	832.0	830.7	829.4	828.1
135°	877.9	879.3	879.6	880.1	880.6	881.1	881.6	881.4	881.1	880.9	880.6
137.5°	926.5	927.7	928.0	928.5	929.0	929.5	930.0	929.7	929.5	929.2	928.9
140°	971.4	972.5	973.1	974.4	975.7	977.0	978.3	978.3	978.3	978.3	978.3
142.5°	1017.4	1018.6	1019.0	1019.7	1020.5	1021.2	1022.0	1022.3	1022.5	1022.8	1023.1
145°	1059.1	1060.0	1060.8	1062.3	1063.8	1065.4	1066.9	1067.2	1067.4	1067.7	1068.0
147.5°	1100.3	1101.5	1102.0	1103.0	1104.1	1105.1	1106.1	1106.6	1107.1	1107.6	1108.1
150°	1137.5	1138.3	1138.8	1139.8	1140.9	1141.9	1142.9	1143.7	1144.4	1145.2	1145.9
152.5°	1173.2	1174.0	1174.6	1175.9	1177.2	1178.4	1179.7	1180.7	1181.7	1182.8	1183.8
155°	1205.8	1206.2	1206.6	1207.3	1208.1	1208.8	1209.6	1210.9	1212.2	1213.5	1214.8
157.5°	1235.8	1236.1	1236.4	1236.9	1237.4	1237.9	1238.4	1240.2	1242.0	1243.8	1245.6
160°	1263.4	1263.7	1263.8	1264.1	1264.4	1264.6	1264.9	1266.4	1268.0	1269.5	1271.0
162.5°	1286.8	1286.8	1286.9	1287.2	1287.4	1287.7	1287.9	1289.7	1291.5	1293.3	1295.1
165°	1307.6	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1309.3	1311.1	1312.8	1314.6
167.5°	1325.1	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1326.5	1328.3	1330.1	1331.9
170°	1340.1	1339.7	1339.6	1339.3	1339.0	1338.8	1338.5	1340.3	1342.1	1343.9	1345.7
172.5°	1350.5	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9	1350.7	1352.5	1354.3	1356.1
175°	1358.5	1358.1	1357.8	1357.3	1356.8	1356.3	1355.8	1357.6	1359.4	1361.2	1363.0
177.5°	1363.1	1362.7	1362.4	1361.9	1361.4	1360.9	1360.4	1361.9	1363.5	1365.0	1366.5
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1800.7	1798.1	1790.3	1792.9	1789.0	1789.0	1786.3	1786.3	1786.3	1792.9	1789.0
5°	1702.7	1693.5	1684.3	1680.4	1676.5	1672.6	1672.6	1671.3	1683.0	1680.4	1690.9
7.5°	1581.0	1578.4	1560.1	1560.1	1553.6	1551.0	1557.5	1558.8	1560.1	1562.7	1569.3
10°	1472.5	1466.0	1439.8	1442.4	1438.5	1433.3	1437.2	1434.6	1443.7	1446.3	1443.7
12.5°	1344.3	1332.6	1303.8	1289.4	1273.7	1261.9	1276.3	1265.9	1302.5	1313.0	1341.7
15°	1174.3	1152.1	1132.5	1132.5	1118.1	1107.6	1114.2	1125.9	1133.8	1145.6	1150.8
17.5°	1060.6	1051.4	1035.7	1026.6	1022.6	1018.7	1018.7	1023.9	1040.9	1039.6	1050.1
20°	963.8	958.6	950.7	938.9	935.0	932.4	932.4	932.4	944.2	954.6	961.2
22.5°	897.1	893.2	887.9	872.2	864.4	861.8	868.3	872.2	881.4	889.2	895.8
25°	830.4	821.2	812.1	806.9	802.9	802.9	805.6	806.9	810.8	814.7	822.6
27.5°	775.5	768.9	755.9	741.5	741.5	737.6	740.2	742.8	751.9	765.0	771.6
30°	714.0	712.7	707.5	702.2	697.0	694.4	699.6	703.6	704.9	711.4	711.4
32.5°	669.6	660.4	651.2	646.0	643.4	642.1	643.4	648.6	648.6	656.5	665.6
35°	625.1	619.9	610.7	601.6	598.9	592.4	597.6	602.9	612.0	615.9	619.9
37.5°	576.7	570.2	566.2	563.6	558.4	559.7	555.8	563.6	571.5	570.2	572.8
40°	540.1	528.3	516.5	515.2	513.9	512.6	512.6	513.9	519.2	524.4	532.2
42.5°	493.0	489.1	478.6	468.2	465.5	462.9	460.3	465.5	476.0	485.2	489.1
45°	444.6	439.4	436.8	428.9	423.7	422.4	419.8	426.3	435.5	439.4	442.0
47.5°	400.2	398.9	391.0	392.3	388.4	389.7	388.4	392.3	392.3	396.2	398.9
50°	370.1	366.2	362.2	359.6	355.7	355.7	354.4	355.7	360.9	366.2	364.9
52.5°	340.0	333.5	332.2	330.9	328.2	330.9	326.9	328.2	333.5	336.1	334.8
55°	304.7	303.4	300.8	298.2	296.9	295.5	295.5	295.5	300.8	304.7	306.0
57.5°	277.2	270.7	265.5	265.5	260.2	258.9	261.5	262.9	266.8	269.4	272.0
60°	239.3	236.7	228.9	224.9	217.1	215.8	215.8	221.0	227.5	236.7	239.3
62.5°	198.8	194.9	193.5	193.5	193.5	193.5	193.5	193.5	193.5	194.9	194.9
65°	176.5	177.8	176.5	175.2	176.5	176.5	175.2	175.2	175.2	176.5	177.8
67.5°	158.2	156.9	158.2	156.9	155.6	155.6	154.3	155.6	156.9	158.2	158.2
70°	137.3	137.3	136.0	137.3	136.0	134.7	133.4	133.4	136.0	137.3	137.3
72.5°	117.7	117.7	116.4	116.4	113.8	113.8	115.1	113.8	113.8	117.7	117.7
75°	98.1	96.8	95.5	95.5	94.2	94.2	94.2	92.8	95.5	95.5	96.8
77.5°	77.2	77.2	77.2	75.8	75.8	74.5	74.5	75.8	75.8	75.8	77.2
80°	58.8	58.8	58.8	57.5	56.2	56.2	56.2	56.2	56.2	57.5	56.2
82.5°	40.5	40.5	40.5	40.5	40.5	39.2	39.2	39.2	40.5	40.5	39.2
85°	24.8	23.5	24.8	24.8	23.5	24.8	23.5	23.5	22.2	22.2	23.5
87.5°	10.5	9.2	7.8	7.8	9.2	7.8	7.8	7.8	9.2	7.8	7.8
90°	38.0	38.1	38.4	38.6	38.9	39.1	38.9	38.6	38.4	38.1	38.0
92.5°	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8
95°	73.7	73.4	72.9	72.4	71.9	71.4	71.9	72.4	72.9	73.4	73.7
97.5°	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1	115.1
100°	158.8	158.7	158.4	158.2	157.9	157.7	157.9	158.2	158.4	158.7	158.8
102.5°	207.2	207.1	206.8	206.5	206.3	206.0	206.3	206.5	206.8	207.1	207.2
105°	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5	255.5
107.5°	306.2	305.6	304.3	303.0	301.7	300.4	301.7	303.0	304.3	305.6	306.2
110°	357.9	357.5	356.8	356.0	355.3	354.5	355.3	356.0	356.8	357.5	357.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	408.6	408.3	407.8	407.3	406.8	406.3	406.8	407.3	407.8	408.3	408.6
115°	463.8	463.4	462.7	461.9	461.2	460.4	461.2	461.9	462.7	463.4	463.8
117.5°	514.5	514.1	513.3	512.6	511.8	511.0	511.8	512.6	513.3	514.1	514.5
120°	568.6	568.2	567.4	566.7	565.9	565.1	565.9	566.7	567.4	568.2	568.6
122.5°	620.4	620.1	619.6	619.1	618.6	618.1	618.6	619.1	619.6	620.1	620.4
125°	673.3	673.2	672.9	672.7	672.4	672.2	672.4	672.7	672.9	673.2	673.3
127.5°	723.9	723.5	722.8	722.0	721.3	720.5	721.3	722.0	722.8	723.5	723.9
130°	778.0	777.5	776.5	775.4	774.4	773.4	774.4	775.4	776.5	777.5	778.0
132.5°	827.5	827.1	826.4	825.6	824.9	824.1	824.9	825.6	826.4	827.1	827.5
135°	880.5	880.1	879.3	878.6	877.8	877.0	877.8	878.6	879.3	880.1	880.5
137.5°	928.8	928.3	927.3	926.2	925.2	924.2	925.2	926.2	927.3	928.3	928.8
140°	978.3	977.8	976.8	975.7	974.7	973.7	974.7	975.7	976.8	977.8	978.3
142.5°	1023.2	1022.7	1021.7	1020.6	1019.6	1018.6	1019.6	1020.6	1021.7	1022.7	1023.2
145°	1068.1	1067.6	1066.6	1065.5	1064.5	1063.5	1064.5	1065.5	1066.6	1067.6	1068.1
147.5°	1108.4	1107.9	1106.9	1105.8	1104.8	1103.8	1104.8	1105.8	1106.9	1107.9	1108.4
150°	1146.3	1145.9	1145.2	1144.4	1143.7	1142.9	1143.7	1144.4	1145.2	1145.9	1146.3
152.5°	1184.3	1183.8	1182.8	1181.7	1180.7	1179.7	1180.7	1181.7	1182.8	1183.8	1184.3
155°	1215.4	1215.0	1214.2	1213.5	1212.7	1211.9	1212.7	1213.5	1214.2	1215.0	1215.4
157.5°	1246.5	1245.9	1244.6	1243.3	1242.0	1240.7	1242.0	1243.3	1244.6	1245.9	1246.5
160°	1271.8	1271.3	1270.3	1269.2	1268.2	1267.2	1268.2	1269.2	1270.3	1271.3	1271.8
162.5°	1296.0	1295.4	1294.1	1292.8	1291.5	1290.2	1291.5	1292.8	1294.1	1295.4	1296.0
165°	1315.5	1314.9	1313.6	1312.3	1311.1	1309.8	1311.1	1312.3	1313.6	1314.9	1315.5
167.5°	1332.8	1332.2	1330.9	1329.6	1328.3	1327.0	1328.3	1329.6	1330.9	1332.2	1332.8
170°	1346.6	1345.8	1344.3	1342.8	1341.2	1339.7	1341.2	1342.8	1344.3	1345.8	1346.6
172.5°	1357.0	1356.2	1354.7	1353.2	1351.6	1350.1	1351.6	1353.2	1354.7	1356.2	1357.0
175°	1363.9	1363.1	1361.6	1360.1	1358.5	1357.0	1358.5	1360.1	1361.6	1363.1	1363.9
177.5°	1367.3	1366.5	1365.0	1363.5	1361.9	1360.4	1361.9	1363.5	1365.0	1366.5	1367.3
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8	1881.8
2.5°	1792.9	1799.4	1796.8	1782.4	1796.8	1800.7	1808.6	1816.4	1821.7	1829.5	1836.0
5°	1680.4	1693.5	1701.3	1693.5	1719.7	1723.6	1741.9	1752.3	1768.0	1781.1	1791.6
7.5°	1574.5	1585.0	1600.6	1603.3	1619.0	1637.3	1663.4	1689.6	1714.4	1727.5	1739.3
10°	1460.7	1479.0	1502.6	1497.3	1520.9	1549.6	1577.1	1619.0	1639.9	1663.4	1684.3
12.5°	1347.0	1358.7	1390.1	1400.6	1434.6	1456.8	1494.7	1520.9	1573.2	1600.6	1619.0
15°	1148.2	1196.6	1235.8	1282.9	1327.3	1369.2	1403.2	1450.3	1496.0	1517.0	1547.0
17.5°	1057.9	1080.2	1103.7	1127.3	1184.8	1259.3	1319.5	1370.5	1409.7	1437.2	1472.5
20°	963.8	986.0	1012.2	1034.4	1069.7	1123.3	1197.9	1285.5	1332.6	1361.3	1395.3
22.5°	897.1	918.0	935.0	954.6	982.1	1021.3	1077.6	1186.1	1248.9	1284.2	1314.3
25°	825.2	851.3	869.6	884.0	906.3	949.4	995.2	1056.6	1169.1	1196.6	1238.4
27.5°	775.5	783.3	804.2	826.5	848.7	872.2	919.3	971.6	1047.5	1107.6	1158.6
30°	716.6	736.2	755.9	765.0	784.6	818.6	847.4	903.6	962.5	1009.6	1071.0
32.5°	672.2	683.9	697.0	719.2	737.6	761.1	789.9	836.9	886.6	916.7	963.8
35°	622.5	630.3	657.8	666.9	685.2	708.8	737.6	774.2	827.8	851.3	885.3
37.5°	575.4	593.7	601.6	622.5	639.5	663.0	683.9	725.8	761.1	788.6	819.9
40°	538.8	546.6	561.0	579.3	593.7	612.0	638.2	668.2	706.2	728.4	755.9
42.5°	494.3	500.9	519.2	529.6	553.2	570.2	585.9	622.5	656.5	673.5	700.9
45°	445.9	461.6	473.4	494.3	507.4	528.3	547.9	574.1	605.5	625.1	640.8
47.5°	404.1	419.8	431.5	451.2	472.1	481.2	502.2	529.6	558.4	574.1	596.3
50°	370.1	375.3	397.5	406.7	428.9	447.2	461.6	485.2	516.5	525.7	544.0
52.5°	337.4	341.3	355.7	367.5	387.1	402.8	421.1	443.3	469.5	483.9	498.2
55°	308.6	311.2	317.8	330.9	343.9	363.5	380.5	401.5	423.7	439.4	452.5
57.5°	275.9	281.2	286.4	294.2	307.3	325.6	343.9	363.5	381.9	392.3	409.3
60°	238.0	245.9	255.0	264.2	273.3	286.4	307.3	325.6	342.6	351.8	364.9
62.5°	197.5	213.2	221.0	231.5	239.3	251.1	266.8	287.7	299.5	311.2	321.7
65°	177.8	179.2	180.5	190.9	205.3	217.1	231.5	247.2	265.5	273.3	281.2
67.5°	158.2	159.5	162.2	163.5	168.7	181.8	197.5	214.5	228.9	234.1	241.9
70°	138.6	138.6	143.8	145.2	146.5	147.8	160.8	177.8	190.9	197.5	206.6
72.5°	117.7	119.0	121.6	122.9	125.5	128.2	132.1	141.2	156.9	163.5	173.9
75°	96.8	98.1	99.4	100.7	104.6	105.9	109.8	115.1	121.6	129.5	136.0
77.5°	77.2	77.2	78.5	81.1	83.7	85.0	88.9	91.5	94.2	98.1	103.3
80°	57.5	58.8	58.8	61.5	61.5	62.8	64.1	68.0	70.6	73.2	75.8
82.5°	39.2	41.8	41.8	41.8	43.2	44.5	45.8	45.8	48.4	49.7	53.6
85°	23.5	24.8	24.8	24.8	23.5	26.2	26.2	27.5	27.5	27.5	28.8
87.5°	9.2	7.8	9.2	9.2	9.2	10.5	9.2	9.2	10.5	11.8	11.8
90°	38.3	38.8	39.3	39.8	40.3	34.7	29.1	23.4	17.8	15.0	13.5
92.5°	36.7	36.4	36.2	35.9	35.7	35.4	35.2	34.9	34.6	34.5	33.5
95°	73.7	73.7	73.7	73.7	73.7	73.2	72.7	72.2	71.7	71.4	70.1
97.5°	115.1	115.1	115.1	115.1	115.1	114.1	113.1	112.0	111.0	110.5	109.3
100°	158.8	158.8	158.8	158.8	158.8	158.0	157.3	156.5	155.8	155.4	154.4
102.5°	207.1	206.8	206.5	206.3	206.0	205.0	204.0	202.9	201.9	201.4	200.6
105°	255.2	254.7	254.2	253.7	253.2	252.7	252.2	251.7	251.2	250.9	250.5
107.5°	306.1	305.8	305.5	305.3	305.0	305.0	305.0	305.0	305.0	305.0	304.5
110°	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.9	357.1

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	409.0	409.7	410.5	411.2	412.0	412.3	412.5	412.8	413.1	413.2	412.4
115°	463.9	464.2	464.5	464.7	465.0	465.5	466.0	466.5	467.0	467.3	466.5
117.5°	514.9	515.6	516.4	517.1	517.9	519.2	520.5	521.8	523.1	523.7	522.7
120°	568.6	568.6	568.6	568.6	568.6	570.6	572.7	574.7	576.8	577.8	576.8
122.5°	620.8	621.5	622.3	623.0	623.8	625.1	626.4	627.7	629.0	629.6	628.3
125°	673.7	674.5	675.2	676.0	676.8	677.6	678.3	679.1	679.8	680.2	679.0
127.5°	724.4	725.4	726.5	727.5	728.5	729.5	730.6	731.6	732.7	733.2	731.8
130°	778.3	778.8	779.3	779.8	780.3	780.8	781.3	781.8	782.3	782.6	780.9
132.5°	828.1	829.4	830.7	832.0	833.3	833.0	832.8	832.5	832.2	832.1	830.8
135°	880.6	880.9	881.1	881.4	881.6	881.1	880.6	880.1	879.6	879.3	877.9
137.5°	928.9	929.2	929.5	929.7	930.0	929.5	929.0	928.5	928.0	927.7	926.5
140°	978.3	978.3	978.3	978.3	978.3	977.0	975.7	974.4	973.1	972.5	971.4
142.5°	1023.1	1022.8	1022.5	1022.3	1022.0	1021.2	1020.5	1019.7	1019.0	1018.6	1017.4
145°	1068.0	1067.7	1067.4	1067.2	1066.9	1065.4	1063.8	1062.3	1060.8	1060.0	1059.1
147.5°	1108.1	1107.6	1107.1	1106.6	1106.1	1105.1	1104.1	1103.0	1102.0	1101.5	1100.3
150°	1145.9	1145.2	1144.4	1143.7	1142.9	1141.9	1140.9	1139.8	1138.8	1138.3	1137.5
152.5°	1183.8	1182.8	1181.7	1180.7	1179.7	1178.4	1177.2	1175.9	1174.6	1174.0	1173.2
155°	1214.8	1213.5	1212.2	1210.9	1209.6	1208.8	1208.1	1207.3	1206.6	1206.2	1205.8
157.5°	1245.6	1243.8	1242.0	1240.2	1238.4	1237.9	1237.4	1236.9	1236.4	1236.1	1235.8
160°	1271.0	1269.5	1268.0	1266.4	1264.9	1264.6	1264.4	1264.1	1263.8	1263.7	1263.4
162.5°	1295.1	1293.3	1291.5	1289.7	1287.9	1287.7	1287.4	1287.2	1286.9	1286.8	1286.8
165°	1314.6	1312.8	1311.1	1309.3	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.6
167.5°	1331.9	1330.1	1328.3	1326.5	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1325.1
170°	1345.7	1343.9	1342.1	1340.3	1338.5	1338.8	1339.0	1339.3	1339.6	1339.7	1340.1
172.5°	1356.1	1354.3	1352.5	1350.7	1348.9	1349.2	1349.4	1349.7	1350.0	1350.1	1350.5
175°	1363.0	1361.2	1359.4	1357.6	1355.8	1356.3	1356.8	1357.3	1357.8	1358.1	1358.5
177.5°	1366.5	1365.0	1363.5	1361.9	1360.4	1360.9	1361.4	1361.9	1362.4	1362.7	1363.1
180°	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1881.8	1881.8	1881.8	1881.8
2.5°	1847.8	1843.9	1867.4	1893.6
5°	1809.9	1816.4	1846.5	1883.1
7.5°	1770.7	1785.0	1820.3	1868.7
10°	1715.7	1741.9	1795.5	1845.2
12.5°	1662.1	1697.4	1748.4	1807.3
15°	1602.0	1641.2	1704.0	1774.6
17.5°	1535.3	1579.7	1653.0	1730.1
20°	1464.6	1523.5	1600.6	1684.3
22.5°	1386.2	1456.8	1536.6	1629.4
25°	1310.3	1387.5	1467.3	1574.5
27.5°	1235.8	1311.6	1400.6	1509.1
30°	1161.3	1230.6	1326.0	1442.4
32.5°	1081.5	1153.4	1254.1	1373.1
35°	1008.3	1080.2	1174.3	1292.0
37.5°	929.8	1006.9	1097.2	1218.8
40°	838.2	928.5	1016.1	1132.5
42.5°	762.4	857.9	942.9	1052.7
45°	702.2	792.5	863.1	970.3
47.5°	646.0	719.2	791.2	890.6
50°	592.4	648.6	723.2	812.1
52.5°	537.5	585.9	649.9	733.6
55°	487.8	533.5	591.1	655.2
57.5°	442.0	474.7	532.2	589.8
60°	391.0	425.0	469.5	517.9
62.5°	347.9	374.0	415.9	456.4
65°	302.1	326.9	358.3	396.2
67.5°	260.2	282.5	307.3	337.4
70°	222.3	239.3	257.6	283.8
72.5°	181.8	200.1	217.1	238.0
75°	149.1	156.9	171.3	185.7
77.5°	115.1	125.5	133.4	145.2
80°	82.4	91.5	94.2	103.3
82.5°	54.9	60.2	65.4	68.0
85°	31.4	34.0	39.2	40.5
87.5°	11.8	13.1	15.7	18.3
90°	10.4	7.3	4.3	1.2
92.5°	31.4	29.4	27.3	25.3
95°	67.5	65.0	62.4	59.8
97.5°	107.0	104.7	102.4	100.1
100°	152.3	150.3	148.2	146.2
102.5°	199.1	197.6	196.0	194.5
105°	249.8	249.0	248.3	247.5
107.5°	303.5	302.4	301.4	300.4
110°	355.6	354.1	352.5	351.0

TEST NUMBER: P1000062

CATALOG NUMBER: SA2XXRDIP-B865D1080UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	410.9	409.4	407.8	406.3
115°	465.0	463.5	461.9	460.4
117.5°	520.6	518.6	516.5	514.5
120°	574.7	572.7	570.6	568.6
122.5°	625.8	623.2	620.7	618.1
125°	676.7	674.4	672.1	669.8
127.5°	729.0	726.1	723.3	720.5
130°	777.6	774.3	771.0	767.7
132.5°	828.3	825.7	823.2	820.6
135°	875.1	872.3	869.5	866.7
137.5°	924.2	921.9	919.6	917.3
140°	969.1	966.8	964.5	962.2
142.5°	1015.1	1012.8	1010.5	1008.2
145°	1057.3	1055.6	1053.8	1052.0
147.5°	1098.0	1095.7	1093.4	1091.1
150°	1136.0	1134.5	1132.9	1131.4
152.5°	1171.7	1170.2	1168.6	1167.1
155°	1205.0	1204.3	1203.5	1202.7
157.5°	1235.3	1234.8	1234.3	1233.8
160°	1262.9	1262.4	1261.9	1261.4
162.5°	1286.8	1286.8	1286.8	1286.8
165°	1307.9	1308.1	1308.4	1308.6
167.5°	1325.9	1326.6	1327.4	1328.2
170°	1340.9	1341.6	1342.4	1343.2
172.5°	1351.2	1352.0	1352.7	1353.5
175°	1359.3	1360.0	1360.8	1361.6
177.5°	1363.9	1364.6	1365.4	1366.2
180°	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)