

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000084

Luminaire Tested: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000084
REPORT IS A COMBINATION OF REPORTS P988641 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7160.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46		
1	98	94	90	87	90	86	83	80	72	70	68	59	58	57	47	47	46	40		
2	89	83	77	72	82	76	71	67	64	61	58	53	51	48	43	41	40	35		
3	82	73	66	61	75	68	62	57	57	53	49	48	44	42	39	36	35	31		
4	76	65	58	52	69	61	54	49	51	47	43	43	39	37	35	33	31	27		
5	70	59	51	45	64	54	48	43	46	41	37	39	35	32	32	29	27	24		
6	64	53	45	40	59	49	42	38	42	37	33	36	32	29	29	27	24	22		
7	60	48	41	35	55	45	38	33	39	33	30	33	29	26	27	24	22	19		
8	56	44	37	31	51	41	34	30	35	30	27	30	26	23	25	22	20	18		
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	20	18	16		
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30172	30172	30172	30172
5°	30242	32048	30348	25603
10°	29909	33873	30122	21143
15°	29261	33885	29757	15882
20°	28480	28009	29100	13103
25°	27533	17501	28129	11147
30°	26324	11206	27041	9597
35°	24854	8612	25659	8212
40°	23216	7238	24208	7183
45°	21467	6161	22362	6030
50°	19671	5235	20590	5216
55°	17682	4549	18636	4490
60°	15916	3469	16762	3428
65°	14270	2610	15116	2961
70°	12446	2086	13425	2413
75°	10522	1598	11485	1826
80°	8351	1087	8990	1198
85°	5806	560	6357	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27600 cd/sqm

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	2.5
10°-20°	504.7	7.0
20°-30°	649.5	9.1
30°-40°	616.2	8.6
40°-50°	528.1	7.4
50°-60°	402.2	5.6
60°-70°	253.6	3.5
70°-80°	126.5	1.8
80°-90°	36.5	0.5
90°-100°	85.5	1.2
100°-110°	271.7	3.8
110°-120°	464.8	6.5
120°-130°	611.3	8.5
130°-140°	686.2	9.6
140°-150°	672.9	9.4
150°-160°	564.5	7.9
160°-170°	374.4	5.2
170°-180°	130.8	1.8
0°-30°	1334.9	18.6
0°-40°	1951.1	27.2
0°-60°	2881.3	40.2
0°-90°	3297.9	46.1
90°-120°	822.0	11.5
90°-150°	2792.4	39.0
90°-180°	3862.0	53.9
0°-180°	7160.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1906	1906	1906	1906	1906	
5°	1907	2121	1914	1694	1907	181
15°	1798	2394	1828	1122	1798	506
25°	1595	1277	1629	813	1595	732
35°	1309	629	1351	600	1309	819
45°	983	437	1024	428	983	759
55°	664	303	699	299	664	598
65°	401	158	425	179	401	398
75°	188	84	205	95	188	204
85°	41	24	45	25	41	47
90°	1	40	1	40	1	6
95°	61	72	61	72	61	68
105°	251	259	251	259	251	265
115°	466	466	466	466	466	461
125°	678	681	678	681	678	606
135°	878	888	878	888	878	678
145°	1066	1077	1066	1077	1066	666
155°	1218	1228	1218	1228	1218	561
165°	1325	1327	1325	1327	1325	374
175°	1379	1374	1379	1374	1379	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1918.0	1926.0	1930.0	1935.3	1947.2	1955.1	1967.0	1969.7	1968.4	1973.7	1959.1
5°	1907.4	1924.7	1940.6	1953.8	1975.0	1988.2	2002.8	2020.0	2024.0	2043.9	2032.0
7.5°	1892.9	1918.0	1940.6	1967.0	1998.8	2016.1	2038.6	2065.1	2077.0	2100.8	2107.5
10°	1869.0	1904.8	1943.2	1971.0	2014.7	2045.2	2066.4	2108.8	2136.6	2172.4	2167.1
12.5°	1830.6	1877.0	1928.6	1975.0	2032.0	2051.8	2091.6	2135.3	2171.0	2204.2	2233.3
15°	1797.5	1850.5	1907.4	1964.4	2029.3	2066.4	2106.1	2163.1	2201.5	2259.8	2285.0
17.5°	1752.5	1820.0	1887.6	1951.1	2028.0	2070.4	2119.4	2175.0	2232.0	2287.6	2307.5
20°	1706.1	1779.0	1851.8	1937.9	2025.3	2066.4	2116.7	2185.6	2241.2	2285.0	2285.0
22.5°	1650.5	1739.2	1822.7	1904.8	2000.2	2059.8	2111.4	2192.2	2232.0	2241.2	2205.5
25°	1594.8	1683.6	1775.0	1877.0	1985.6	2038.6	2096.9	2172.4	2185.6	2148.5	2055.8
27.5°	1528.6	1627.9	1731.3	1841.2	1955.1	2021.4	2074.3	2124.7	2099.5	2000.2	1855.8
30°	1461.0	1568.3	1684.9	1789.5	1927.3	1988.2	2033.3	2047.8	1968.4	1806.8	1620.0
32.5°	1390.8	1495.5	1618.7	1744.5	1883.6	1941.9	1971.0	1932.6	1786.9	1582.9	1355.1
35°	1308.7	1426.6	1555.1	1686.2	1824.0	1867.7	1884.9	1790.9	1604.1	1340.5	1114.0
37.5°	1234.5	1352.4	1490.2	1624.0	1757.8	1781.6	1764.4	1617.3	1380.2	1119.3	898.1
40°	1147.1	1272.9	1408.1	1557.7	1667.7	1674.3	1631.9	1441.2	1147.1	902.1	765.6
42.5°	1066.3	1193.5	1328.6	1480.9	1564.4	1541.8	1484.9	1234.5	957.7	777.5	667.6
45°	982.9	1103.4	1249.1	1384.2	1443.8	1390.8	1304.7	1038.5	804.0	668.9	584.2
47.5°	902.1	1014.7	1159.0	1288.8	1299.4	1239.8	1137.8	870.3	696.7	588.1	519.2
50°	822.6	935.2	1070.3	1177.6	1167.0	1084.9	969.6	756.4	605.3	519.2	462.3
52.5°	743.1	845.1	976.2	1061.0	1016.0	936.5	822.6	641.1	528.5	453.0	409.3
55°	663.6	759.0	871.6	941.8	870.3	778.9	698.1	549.7	458.3	397.4	364.3
57.5°	597.4	672.9	776.2	818.6	732.5	661.0	590.8	472.9	397.4	353.7	315.3
60°	524.5	593.4	678.2	703.4	614.6	556.3	496.7	400.0	340.4	302.0	276.8
62.5°	462.3	519.2	584.2	584.2	506.0	462.3	417.3	335.1	286.1	255.6	243.7
65°	401.4	442.4	488.8	483.5	417.3	378.8	343.1	276.8	239.8	218.6	206.6
67.5°	341.7	373.5	404.0	385.5	337.8	304.7	271.5	223.9	198.7	184.1	168.2
70°	287.4	312.6	328.5	311.3	263.6	235.8	211.9	180.1	160.3	141.7	132.5
72.5°	241.1	251.7	257.0	235.8	196.0	180.1	162.9	140.4	123.2	113.9	111.3
75°	188.1	197.4	193.4	177.5	144.4	132.5	119.2	103.3	99.3	94.0	91.4
77.5°	147.0	147.0	140.4	125.8	103.3	94.0	88.7	80.8	76.8	75.5	72.9
80°	104.6	103.3	99.3	83.5	70.2	64.9	64.9	59.6	58.3	55.6	55.6
82.5°	68.9	68.9	63.6	50.3	46.4	45.0	43.7	41.1	41.1	39.7	39.7
85°	41.1	38.4	31.8	27.8	26.5	26.5	25.2	23.8	25.2	23.8	23.8
87.5°	18.5	14.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
90°	1.2	4.3	7.4	10.5	13.6	15.2	18.0	23.7	29.4	35.1	40.8
92.5°	25.6	27.7	29.8	31.9	34.0	35.0	35.1	35.4	35.6	35.9	36.1
95°	60.6	63.2	65.8	68.4	71.0	72.3	72.6	73.1	73.6	74.1	74.6
97.5°	101.4	103.7	106.1	108.4	110.7	111.9	112.4	113.5	114.5	115.6	116.6
100°	148.0	150.1	152.2	154.3	156.4	157.4	157.8	158.6	159.3	160.1	160.9
102.5°	197.0	198.6	200.1	201.7	203.2	204.0	204.5	205.6	206.6	207.7	208.7
105°	250.6	251.4	252.2	252.9	253.7	254.1	254.4	254.9	255.4	256.0	256.5
107.5°	304.3	305.3	306.3	307.4	308.4	308.9	308.9	308.9	308.9	308.9	308.9
110°	355.5	357.1	358.6	360.2	361.7	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	411.5	413.1	414.6	416.2	417.7	418.5	418.4	418.1	417.8	417.6	417.3
115°	466.3	467.9	469.4	471.0	472.5	473.3	473.0	472.5	472.0	471.5	471.0
117.5°	521.1	523.2	525.2	527.3	529.4	530.4	529.8	528.5	527.2	525.9	524.6
120°	575.9	578.0	580.0	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9
122.5°	626.0	628.6	631.2	633.7	636.3	637.6	637.0	635.7	634.4	633.1	631.8
125°	678.4	680.7	683.1	685.4	687.7	688.9	688.5	687.7	687.0	686.2	685.4
127.5°	729.7	732.6	735.4	738.3	741.2	742.6	742.1	741.0	740.0	738.9	737.9
130°	777.5	780.9	784.3	787.6	791.0	792.7	792.4	791.9	791.4	790.9	790.4
132.5°	831.2	833.8	836.4	838.9	841.5	842.8	842.9	843.2	843.5	843.7	844.0
135°	877.8	880.6	883.5	886.3	889.2	890.6	890.9	891.4	891.9	892.4	892.9
137.5°	929.1	931.4	933.8	936.1	938.4	939.6	939.9	940.4	940.9	941.4	941.9
140°	974.5	976.8	979.2	981.5	983.8	985.0	985.7	987.0	988.3	989.6	990.9
142.5°	1021.2	1023.5	1025.9	1028.2	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2
145°	1065.5	1067.3	1069.1	1070.9	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6
147.5°	1105.1	1107.4	1109.8	1112.1	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3
150°	1145.9	1147.5	1149.0	1150.6	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6
152.5°	1182.0	1183.6	1185.1	1186.7	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9
155°	1218.2	1219.0	1219.8	1220.5	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2
157.5°	1249.7	1250.2	1250.7	1251.2	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3
160°	1277.6	1278.1	1278.7	1279.2	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1
162.5°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4
165°	1325.4	1325.2	1324.9	1324.7	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3
167.5°	1345.2	1344.4	1343.6	1342.9	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7
170°	1360.4	1359.6	1358.8	1358.1	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7
172.5°	1370.9	1370.1	1369.3	1368.6	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2
175°	1379.0	1378.2	1377.4	1376.7	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2
177.5°	1383.7	1382.9	1382.1	1381.4	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1973.7	1976.3	1980.3	1998.8	2001.5	2006.8	2004.1	2004.1	2005.5	2002.8	2004.1
5°	2058.4	2062.4	2082.3	2104.8	2110.1	2104.8	2111.4	2120.7	2120.7	2120.7	2118.1
7.5°	2137.9	2152.5	2175.0	2208.1	2214.7	2221.4	2233.3	2225.3	2228.0	2239.9	2235.9
10°	2214.7	2235.9	2261.1	2288.9	2303.5	2312.8	2318.1	2330.0	2357.8	2326.0	2337.9
12.5°	2287.6	2318.1	2344.6	2375.0	2385.6	2397.5	2401.5	2412.1	2412.1	2410.8	2420.1
15°	2335.3	2363.1	2386.9	2406.8	2409.5	2406.8	2404.2	2405.5	2409.5	2393.6	2402.8
17.5°	2345.9	2348.5	2356.5	2348.5	2349.9	2322.0	2306.1	2302.2	2265.1	2266.4	2296.9
20°	2294.2	2249.2	2237.3	2193.6	2167.1	2095.5	2092.9	2073.0	1994.9	2018.7	2013.4
22.5°	2152.5	2075.7	1973.7	1923.3	1898.2	1822.7	1764.4	1723.3	1695.5	1667.7	1655.8
25°	1965.7	1841.2	1696.8	1597.5	1582.9	1512.7	1405.4	1355.1	1295.5	1276.9	1308.7
27.5°	1724.6	1563.0	1400.1	1247.8	1220.0	1156.4	1102.1	1066.3	997.4	993.5	996.1
30°	1397.5	1234.5	1098.1	998.8	929.9	900.7	865.0	838.5	810.7	821.3	823.9
32.5°	1148.4	993.5	866.3	813.3	781.5	763.0	732.5	715.3	703.4	699.4	698.1
35°	912.7	809.3	752.4	700.7	682.2	668.9	646.4	638.5	627.9	629.2	629.2
37.5°	781.5	695.4	653.0	626.5	609.3	602.7	588.1	580.2	573.6	570.9	574.9
40°	674.2	614.6	588.1	564.3	549.7	547.1	539.1	529.8	521.9	523.2	527.2
42.5°	596.1	561.6	529.8	511.3	500.7	496.7	490.1	483.5	483.5	479.5	478.2
45°	533.8	506.0	479.5	462.3	455.7	450.4	442.4	441.1	435.8	437.1	438.4
47.5°	478.2	455.7	435.8	418.6	412.0	410.6	402.7	397.4	397.4	396.1	394.7
50°	427.8	405.3	388.1	378.8	369.6	366.9	365.6	364.3	361.6	361.6	362.9
52.5°	386.8	364.3	351.0	343.1	337.8	335.1	335.1	333.8	333.8	333.8	332.5
55°	341.7	323.2	312.6	310.0	307.3	306.0	304.7	302.0	300.7	303.3	300.7
57.5°	299.4	292.7	283.5	280.8	274.2	274.2	270.2	267.6	264.9	267.6	267.6
60°	266.2	257.0	251.7	243.7	238.4	233.1	226.5	225.2	222.5	221.2	219.9
62.5°	231.8	223.9	210.6	198.7	190.7	185.4	182.8	181.5	181.5	180.1	180.1
65°	193.4	174.8	168.2	164.3	162.9	161.6	159.0	157.6	159.0	157.6	159.0
67.5°	151.0	148.4	144.4	141.7	140.4	139.1	139.1	137.8	137.8	137.8	137.8
70°	131.1	124.5	123.2	120.5	120.5	119.2	119.2	119.2	119.2	117.9	120.5
72.5°	108.6	104.6	103.3	102.0	102.0	102.0	100.7	100.7	100.7	99.3	100.7
75°	88.7	87.4	84.8	84.8	83.5	84.8	83.5	83.5	82.1	83.5	83.5
77.5°	71.5	70.2	68.9	68.9	67.6	67.6	67.6	67.6	67.6	67.6	68.9
80°	54.3	53.0	51.7	53.0	51.7	53.0	51.7	51.7	53.0	51.7	51.7
82.5°	39.7	38.4	38.4	37.1	37.1	37.1	37.1	37.1	37.1	37.1	37.1
85°	23.8	22.5	22.5	23.8	22.5	23.8	22.5	22.5	22.5	23.8	23.8
87.5°	10.6	11.9	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	11.9
90°	40.3	39.8	39.3	38.8	38.5	38.6	38.9	39.1	39.4	39.6	39.4
92.5°	36.4	36.6	36.9	37.2	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.6	74.6	74.6	74.6	74.3	73.8	73.3	72.8	72.3	72.8
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.9	160.9	160.9	160.9	160.8	160.5	160.2	160.0	159.7	160.0
102.5°	208.9	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	208.9
105°	257.0	257.5	258.0	258.5	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	309.2	309.4	309.7	310.0	310.1	309.5	308.2	306.9	305.6	304.3	305.6
110°	362.5	362.5	362.5	362.5	362.5	362.1	361.3	360.6	359.8	359.0	359.8

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.5	415.7	415.0	414.2	413.8	413.5	413.0	412.5	412.0	411.5	412.0
115°	470.7	470.5	470.2	469.9	469.8	469.4	468.6	467.9	467.1	466.3	467.1
117.5°	523.8	523.0	522.3	521.5	521.1	520.7	519.9	519.2	518.4	517.6	518.4
120°	575.9	575.9	575.9	575.9	575.9	575.5	574.7	574.0	573.2	572.4	573.2
122.5°	631.0	630.2	629.5	628.7	628.3	628.0	627.5	627.0	626.5	626.0	626.5
125°	684.6	683.8	683.1	682.3	681.9	681.8	681.5	681.3	681.0	680.8	681.0
127.5°	736.9	735.8	734.8	733.7	733.2	732.8	732.0	731.3	730.5	729.7	730.5
130°	789.9	789.3	788.8	788.3	788.0	787.5	786.5	785.4	784.4	783.4	784.4
132.5°	842.7	841.4	840.1	838.8	838.2	837.8	837.0	836.3	835.5	834.7	835.5
135°	892.7	892.4	892.2	891.9	891.8	891.4	890.6	889.9	889.1	888.3	889.1
137.5°	941.6	941.4	941.1	940.8	940.7	940.2	939.2	938.1	937.1	936.1	937.1
140°	990.9	990.9	990.9	990.9	990.9	990.4	989.3	988.3	987.2	986.2	987.2
142.5°	1035.4	1035.7	1035.9	1036.2	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7
145°	1080.9	1081.1	1081.4	1081.7	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1
147.5°	1120.8	1121.3	1121.8	1122.3	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9
150°	1158.4	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4
152.5°	1195.9	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9
155°	1226.5	1227.8	1229.1	1230.4	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3
157.5°	1256.1	1257.9	1259.8	1261.6	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9
160°	1282.7	1284.2	1285.8	1287.3	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5
162.5°	1306.2	1308.0	1309.9	1311.7	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1
165°	1326.1	1327.9	1329.7	1331.5	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9
167.5°	1343.5	1345.3	1347.2	1349.0	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4
170°	1357.5	1359.3	1361.2	1363.0	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5
172.5°	1368.0	1369.8	1371.7	1373.5	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0
175°	1375.0	1376.8	1378.7	1380.5	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0
177.5°	1379.5	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	2009.4	2000.2	1997.5	2000.2	1997.5	1998.8	1989.6	1955.1	1964.4	1949.8	1957.8
5°	2123.3	2115.4	2098.2	2095.5	2092.9	2090.2	2077.0	2046.5	2034.6	2014.7	2013.4
7.5°	2232.0	2232.0	2218.7	2209.4	2197.5	2188.3	2171.0	2126.0	2107.5	2083.6	2070.4
10°	2339.3	2304.8	2319.4	2310.1	2281.0	2275.7	2243.9	2217.4	2181.6	2157.8	2136.6
12.5°	2416.1	2405.5	2392.2	2384.3	2376.3	2359.1	2337.9	2270.4	2251.8	2204.2	2180.3
15°	2413.4	2406.8	2410.8	2410.8	2408.1	2404.2	2386.9	2337.9	2306.1	2259.8	2218.7
17.5°	2283.6	2300.8	2318.1	2330.0	2356.5	2368.4	2384.3	2355.2	2335.3	2295.5	2251.8
20°	2057.1	2099.5	2149.8	2160.4	2184.3	2254.5	2286.3	2311.4	2319.4	2306.1	2270.4
22.5°	1741.9	1777.6	1899.5	1896.8	1931.3	2014.7	2107.5	2183.0	2242.6	2275.7	2262.4
25°	1364.3	1414.7	1479.6	1528.6	1641.2	1765.7	1880.9	2001.5	2104.8	2196.2	2218.7
27.5°	1031.9	1098.1	1149.8	1214.7	1271.6	1418.7	1567.0	1755.1	1875.6	2049.2	2139.2
30°	834.5	865.0	916.6	947.1	974.9	1087.5	1255.7	1441.2	1653.1	1853.1	2008.1
32.5°	712.6	733.8	772.2	785.5	814.6	890.1	996.1	1165.7	1384.2	1626.6	1830.6
35°	639.8	662.3	670.3	682.2	706.0	753.7	826.6	949.7	1147.1	1384.2	1627.9
37.5°	577.5	589.5	612.0	619.9	627.9	663.6	712.6	798.7	929.9	1124.6	1394.8
40°	533.8	540.4	552.4	559.0	564.3	589.5	633.2	691.4	788.1	936.5	1185.5
42.5°	487.5	495.4	503.4	511.3	517.9	537.8	564.3	619.9	684.8	797.4	977.6
45°	442.4	447.7	457.0	462.3	471.6	487.5	511.3	549.7	608.0	679.5	825.2
47.5°	401.4	408.0	412.0	418.6	425.2	442.4	464.9	490.1	537.8	608.0	714.0
50°	364.3	372.2	377.5	378.8	384.1	400.0	418.6	446.4	476.9	531.2	623.9
52.5°	337.8	339.1	343.1	348.4	347.0	356.3	373.5	394.7	426.5	470.2	537.8
55°	307.3	311.3	313.9	315.3	315.3	323.2	332.5	352.3	377.5	413.3	470.2
57.5°	268.9	272.9	280.8	283.5	287.4	291.4	295.4	308.6	329.8	364.3	410.6
60°	229.2	231.8	239.8	245.1	247.7	258.3	263.6	274.2	286.1	311.3	355.0
62.5°	184.1	186.8	190.7	196.0	201.3	217.2	230.5	241.1	250.4	267.6	303.3
65°	160.3	161.6	164.3	165.6	166.9	173.5	185.4	200.0	217.2	230.5	251.7
67.5°	139.1	140.4	141.7	144.4	145.7	147.0	152.3	156.3	173.5	192.1	208.0
70°	119.2	121.9	123.2	123.2	124.5	127.2	129.8	135.1	140.4	149.7	169.6
72.5°	100.7	102.0	104.6	104.6	104.6	107.3	109.9	112.6	115.2	120.5	128.5
75°	83.5	86.1	86.1	86.1	87.4	87.4	90.1	92.7	95.4	99.3	102.0
77.5°	68.9	68.9	68.9	68.9	70.2	70.2	71.5	74.2	75.5	76.8	79.5
80°	51.7	53.0	53.0	53.0	54.3	54.3	54.3	57.0	58.3	58.3	60.9
82.5°	38.4	38.4	38.4	39.7	38.4	39.7	39.7	41.1	39.7	41.1	42.4
85°	23.8	23.8	23.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	26.5
87.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	13.2	11.9	11.9
90°	39.1	38.9	38.6	38.5	38.8	39.3	39.8	40.3	40.8	35.1	29.4
92.5°	37.3	37.3	37.3	37.3	37.2	36.9	36.6	36.4	36.1	35.9	35.6
95°	73.3	73.8	74.3	74.6	74.6	74.6	74.6	74.6	74.6	74.1	73.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	115.6	114.5
100°	160.2	160.5	160.8	160.9	160.9	160.9	160.9	160.9	160.9	160.1	159.3
102.5°	209.2	209.4	209.7	209.8	209.7	209.4	209.2	208.9	208.7	207.7	206.6
105°	258.8	258.8	258.8	258.8	258.5	258.0	257.5	257.0	256.5	256.0	255.4
107.5°	306.9	308.2	309.5	310.1	310.0	309.7	309.4	309.2	308.9	308.9	308.9
110°	360.6	361.3	362.1	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	412.5	413.0	413.5	413.8	414.2	415.0	415.7	416.5	417.3	417.6	417.8
115°	467.9	468.6	469.4	469.8	469.9	470.2	470.5	470.7	471.0	471.5	472.0
117.5°	519.2	519.9	520.7	521.1	521.5	522.3	523.0	523.8	524.6	525.9	527.2
120°	574.0	574.7	575.5	575.9	575.9	575.9	575.9	575.9	575.9	578.0	580.0
122.5°	627.0	627.5	628.0	628.3	628.7	629.5	630.2	631.0	631.8	633.1	634.4
125°	681.3	681.5	681.8	681.9	682.3	683.1	683.8	684.6	685.4	686.2	687.0
127.5°	731.3	732.0	732.8	733.2	733.7	734.8	735.8	736.9	737.9	738.9	740.0
130°	785.4	786.5	787.5	788.0	788.3	788.8	789.3	789.9	790.4	790.9	791.4
132.5°	836.3	837.0	837.8	838.2	838.8	840.1	841.4	842.7	844.0	843.7	843.5
135°	889.9	890.6	891.4	891.8	891.9	892.2	892.4	892.7	892.9	892.4	891.9
137.5°	938.1	939.2	940.2	940.7	940.8	941.1	941.4	941.6	941.9	941.4	940.9
140°	988.3	989.3	990.4	990.9	990.9	990.9	990.9	990.9	990.9	989.6	988.3
142.5°	1033.7	1034.8	1035.8	1036.3	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6
145°	1079.2	1080.2	1081.3	1081.8	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5
147.5°	1120.0	1121.0	1122.1	1122.6	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2
150°	1159.2	1159.9	1160.7	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5
152.5°	1196.9	1198.0	1199.0	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3
155°	1229.1	1229.8	1230.6	1231.0	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6
157.5°	1259.2	1260.5	1261.8	1262.5	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3
160°	1285.5	1286.6	1287.6	1288.1	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6
162.5°	1309.4	1310.7	1312.0	1312.6	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9
165°	1329.2	1330.5	1331.8	1332.4	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3
167.5°	1346.7	1348.0	1349.3	1349.9	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7
170°	1360.0	1361.6	1363.1	1363.9	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2
172.5°	1370.5	1372.1	1373.6	1374.4	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7
175°	1377.5	1379.1	1380.6	1381.4	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2
177.5°	1381.0	1382.6	1384.1	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1945.9	1939.2	1939.2	1935.3	1935.3	1914.1	1914.1	1920.7	1912.7	1903.5	1890.2
5°	1996.2	1981.6	1977.6	1972.3	1955.1	1928.6	1918.0	1914.1	1898.2	1878.3	1855.8
7.5°	2043.9	2020.0	2008.1	1996.2	1973.7	1936.6	1915.4	1900.8	1877.0	1846.5	1817.4
10°	2090.2	2059.8	2029.3	2014.7	1982.9	1936.6	1906.1	1882.3	1847.8	1806.8	1765.7
12.5°	2132.6	2069.0	2063.7	2034.6	1988.2	1935.3	1888.9	1854.5	1810.7	1763.1	1715.4
15°	2169.7	2104.8	2073.0	2046.5	1985.6	1919.4	1870.3	1828.0	1769.7	1715.4	1657.1
17.5°	2188.3	2118.1	2096.9	2053.1	1990.9	1904.8	1838.6	1786.9	1723.3	1658.4	1592.2
20°	2206.8	2124.7	2090.2	2059.8	1975.0	1877.0	1802.8	1743.2	1673.0	1596.2	1523.3
22.5°	2216.1	2124.7	2083.6	2041.2	1959.1	1846.5	1759.1	1688.9	1606.8	1528.6	1441.2
25°	2200.2	2116.7	2067.7	2024.0	1931.3	1809.4	1708.7	1629.3	1541.8	1453.1	1364.3
27.5°	2160.4	2098.2	2041.2	1996.2	1892.9	1761.7	1655.8	1565.7	1475.6	1376.3	1286.2
30°	2086.3	2058.4	2013.4	1963.1	1850.5	1719.3	1593.5	1500.8	1401.4	1302.1	1208.0
32.5°	1971.0	1994.9	1965.7	1922.0	1800.1	1661.1	1527.3	1433.2	1324.6	1217.3	1131.2
35°	1830.6	1915.4	1899.5	1869.0	1747.2	1598.8	1465.0	1351.1	1242.5	1133.9	1047.8
37.5°	1677.0	1805.4	1818.7	1800.1	1686.2	1535.2	1388.2	1276.9	1165.7	1055.7	968.3
40°	1466.3	1663.7	1706.1	1714.0	1622.6	1458.4	1304.7	1196.1	1086.2	978.9	872.9
42.5°	1272.9	1522.0	1575.0	1608.1	1541.8	1382.9	1227.9	1107.4	998.8	902.1	796.1
45°	1091.5	1351.1	1437.2	1479.6	1450.4	1296.8	1136.5	1023.9	924.6	835.8	733.8
47.5°	904.7	1165.7	1286.2	1353.8	1353.8	1209.4	1049.1	937.8	842.5	766.9	676.9
50°	780.2	997.4	1121.9	1210.7	1234.5	1120.6	969.6	861.0	770.9	688.8	619.9
52.5°	665.0	859.7	963.0	1055.7	1124.6	1025.2	880.9	782.8	694.1	617.3	563.0
55°	574.9	720.6	814.6	916.6	993.5	928.6	794.8	699.4	622.6	559.0	512.6
57.5°	488.8	615.9	692.8	782.8	865.0	816.0	708.7	626.5	559.0	503.4	462.3
60°	415.9	519.2	578.9	649.1	751.1	716.6	627.9	552.4	498.1	447.7	413.3
62.5°	353.7	435.8	486.1	536.5	629.2	613.3	544.4	486.1	439.8	397.4	368.2
65°	290.1	357.6	397.4	441.1	515.3	521.9	466.3	425.2	382.8	345.7	319.2
67.5°	234.5	287.4	323.2	360.3	419.9	438.4	400.0	365.6	329.8	299.4	275.5
70°	189.4	226.5	253.0	282.1	331.2	353.7	333.8	310.0	280.8	255.6	234.5
72.5°	149.7	173.5	189.4	211.9	251.7	274.2	272.9	251.7	230.5	213.3	196.0
75°	109.9	128.5	141.7	156.3	188.1	209.3	214.6	205.3	184.1	170.9	157.6
77.5°	83.5	94.0	100.7	111.3	133.8	152.3	160.3	157.6	143.1	132.5	123.2
80°	63.6	66.2	68.9	72.9	91.4	108.6	113.9	112.6	104.6	100.7	90.1
82.5°	45.0	46.4	47.7	49.0	55.6	70.2	75.5	78.2	71.5	67.6	58.3
85°	26.5	27.8	27.8	30.5	31.8	35.8	45.0	45.0	43.7	38.4	37.1
87.5°	13.2	13.2	11.9	11.9	13.2	14.6	17.2	19.9	17.2	15.9	14.6
90°	23.7	18.0	15.2	13.6	10.5	7.4	4.3	1.2	4.3	7.4	10.5
92.5°	35.4	35.1	35.0	34.0	31.9	29.8	27.7	25.6	27.7	29.8	31.9
95°	73.1	72.6	72.3	71.0	68.4	65.8	63.2	60.6	63.2	65.8	68.4
97.5°	113.5	112.4	111.9	110.7	108.4	106.1	103.7	101.4	103.7	106.1	108.4
100°	158.6	157.8	157.4	156.4	154.3	152.2	150.1	148.0	150.1	152.2	154.3
102.5°	205.6	204.5	204.0	203.2	201.7	200.1	198.6	197.0	198.6	200.1	201.7
105°	254.9	254.4	254.1	253.7	252.9	252.2	251.4	250.6	251.4	252.2	252.9
107.5°	308.9	308.9	308.9	308.4	307.4	306.3	305.3	304.3	305.3	306.3	307.4
110°	362.5	362.5	362.5	361.7	360.2	358.6	357.1	355.5	357.1	358.6	360.2

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	418.1	418.4	418.5	417.7	416.2	414.6	413.1	411.5	413.1	414.6	416.2
115°	472.5	473.0	473.3	472.5	471.0	469.4	467.9	466.3	467.9	469.4	471.0
117.5°	528.5	529.8	530.4	529.4	527.3	525.2	523.2	521.1	523.2	525.2	527.3
120°	582.1	584.2	585.2	584.2	582.1	580.0	578.0	575.9	578.0	580.0	582.1
122.5°	635.7	637.0	637.6	636.3	633.7	631.2	628.6	626.0	628.6	631.2	633.7
125°	687.7	688.5	688.9	687.7	685.4	683.1	680.7	678.4	680.7	683.1	685.4
127.5°	741.0	742.1	742.6	741.2	738.3	735.4	732.6	729.7	732.6	735.4	738.3
130°	791.9	792.4	792.7	791.0	787.6	784.3	780.9	777.5	780.9	784.3	787.6
132.5°	843.2	842.9	842.8	841.5	838.9	836.4	833.8	831.2	833.8	836.4	838.9
135°	891.4	890.9	890.6	889.2	886.3	883.5	880.6	877.8	880.6	883.5	886.3
137.5°	940.4	939.9	939.6	938.4	936.1	933.8	931.4	929.1	931.4	933.8	936.1
140°	987.0	985.7	985.0	983.8	981.5	979.2	976.8	974.5	976.8	979.2	981.5
142.5°	1032.9	1032.1	1031.7	1030.5	1028.2	1025.9	1023.5	1021.2	1023.5	1025.9	1028.2
145°	1075.9	1074.4	1073.6	1072.7	1070.9	1069.1	1067.3	1065.5	1067.3	1069.1	1070.9
147.5°	1117.2	1116.1	1115.6	1114.4	1112.1	1109.8	1107.4	1105.1	1107.4	1109.8	1112.1
150°	1154.5	1153.4	1152.9	1152.1	1150.6	1149.0	1147.5	1145.9	1147.5	1149.0	1150.6
152.5°	1191.0	1189.7	1189.0	1188.2	1186.7	1185.1	1183.6	1182.0	1183.6	1185.1	1186.7
155°	1222.9	1222.1	1221.7	1221.3	1220.5	1219.8	1219.0	1218.2	1219.0	1219.8	1220.5
157.5°	1252.8	1252.3	1252.0	1251.7	1251.2	1250.7	1250.2	1249.7	1250.2	1250.7	1251.2
160°	1280.4	1280.1	1280.0	1279.7	1279.2	1278.7	1278.1	1277.6	1278.1	1278.7	1279.2
162.5°	1303.7	1303.4	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3
165°	1324.3	1324.3	1324.3	1324.4	1324.7	1324.9	1325.2	1325.4	1325.2	1324.9	1324.7
167.5°	1341.7	1341.7	1341.7	1342.1	1342.9	1343.6	1344.4	1345.2	1344.4	1343.6	1342.9
170°	1356.5	1356.8	1356.9	1357.3	1358.1	1358.8	1359.6	1360.4	1359.6	1358.8	1358.1
172.5°	1367.0	1367.3	1367.4	1367.8	1368.6	1369.3	1370.1	1370.9	1370.1	1369.3	1368.6
175°	1374.7	1375.2	1375.5	1375.9	1376.7	1377.4	1378.2	1379.0	1378.2	1377.4	1376.7
177.5°	1379.4	1379.9	1380.2	1380.6	1381.4	1382.1	1382.9	1383.7	1382.9	1382.1	1381.4
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1884.9	1886.2	1890.2	1878.3	1859.8	1851.8	1828.0	1824.0	1820.0	1820.0	1824.0
5°	1842.5	1837.2	1838.6	1816.0	1789.5	1773.7	1740.5	1745.8	1728.6	1718.0	1720.7
7.5°	1796.2	1781.6	1780.3	1751.1	1718.0	1688.9	1654.4	1646.5	1630.6	1612.0	1604.1
10°	1737.9	1727.3	1707.4	1674.3	1631.9	1608.1	1561.7	1533.9	1529.9	1502.1	1491.5
12.5°	1678.3	1659.7	1639.9	1593.5	1545.8	1507.4	1473.0	1442.5	1421.3	1397.5	1381.6
15°	1609.4	1586.9	1564.4	1515.4	1459.7	1421.3	1369.6	1324.6	1262.4	1213.3	1185.5
17.5°	1533.9	1508.7	1478.3	1424.0	1369.6	1316.7	1221.3	1168.3	1124.6	1095.5	1078.2
20°	1455.7	1427.9	1397.5	1343.2	1249.1	1156.4	1103.4	1062.3	1035.8	1006.7	985.5
22.5°	1373.6	1344.5	1311.4	1226.6	1127.2	1062.3	1021.3	982.9	944.4	928.6	918.0
25°	1296.8	1270.3	1227.9	1112.7	1034.5	974.9	928.6	903.4	883.5	862.3	842.5
27.5°	1217.3	1168.3	1108.7	1012.0	963.0	902.1	868.9	850.4	816.0	801.4	792.1
30°	1121.9	1067.6	1010.7	941.8	884.8	842.5	812.0	781.5	761.7	747.1	731.2
32.5°	1025.2	973.6	937.8	866.3	823.9	780.2	751.1	732.5	703.4	694.1	687.5
35°	941.8	898.1	866.3	808.0	768.3	728.5	707.3	679.5	661.0	643.8	633.2
37.5°	859.7	835.8	802.7	753.7	711.3	679.5	650.4	641.1	615.9	606.7	596.1
40°	802.7	766.9	739.1	696.7	661.0	626.5	608.0	586.8	569.6	555.0	551.0
42.5°	733.8	707.3	691.4	645.1	608.0	588.1	565.6	541.8	528.5	516.6	502.0
45°	682.2	658.3	635.8	598.7	565.6	540.4	520.6	504.7	482.2	476.9	454.3
47.5°	627.9	604.0	586.8	549.7	519.2	495.4	480.8	459.6	441.1	429.2	418.6
50°	573.6	553.7	537.8	506.0	479.5	454.3	434.5	413.3	405.3	385.5	378.8
52.5°	521.9	508.7	491.4	461.0	434.5	413.3	392.1	374.9	362.9	352.3	344.4
55°	478.2	457.0	449.0	415.9	393.4	370.9	352.3	341.7	327.2	320.6	313.9
57.5°	429.2	417.3	404.0	378.8	353.7	332.5	319.2	303.3	295.4	287.4	282.1
60°	386.8	369.6	359.0	337.8	315.3	295.4	283.5	271.5	260.9	254.3	243.7
62.5°	337.8	324.5	317.9	295.4	276.8	258.3	247.7	235.8	227.8	215.9	202.7
65°	295.4	284.8	276.8	258.3	241.1	223.9	213.3	198.7	188.1	181.5	180.1
67.5°	258.3	250.4	238.4	221.2	204.0	190.7	178.8	166.9	165.6	162.9	162.9
70°	217.2	209.3	202.7	184.1	169.6	155.0	152.3	148.4	144.4	143.1	140.4
72.5°	181.5	174.8	166.9	151.0	136.4	132.5	129.8	127.2	123.2	121.9	120.5
75°	147.0	137.8	132.5	117.9	113.9	111.3	108.6	104.6	102.0	100.7	98.0
77.5°	112.6	103.3	103.3	95.4	92.7	88.7	86.1	83.5	82.1	79.5	79.5
80°	79.5	79.5	76.8	72.9	68.9	67.6	63.6	62.3	60.9	62.3	59.6
82.5°	58.3	53.0	53.0	50.3	47.7	46.4	43.7	43.7	42.4	42.4	42.4
85°	33.1	33.1	31.8	29.1	27.8	27.8	26.5	26.5	25.2	25.2	23.8
87.5°	13.2	11.9	13.2	11.9	11.9	10.6	10.6	10.6	9.3	10.6	9.3
90°	13.6	15.2	18.0	23.7	29.4	35.1	40.8	40.3	39.8	39.3	38.8
92.5°	34.0	35.0	35.1	35.4	35.6	35.9	36.1	36.4	36.6	36.9	37.2
95°	71.0	72.3	72.6	73.1	73.6	74.1	74.6	74.6	74.6	74.6	74.6
97.5°	110.7	111.9	112.4	113.5	114.5	115.6	116.6	116.6	116.6	116.6	116.6
100°	156.4	157.4	157.8	158.6	159.3	160.1	160.9	160.9	160.9	160.9	160.9
102.5°	203.2	204.0	204.5	205.6	206.6	207.7	208.7	208.9	209.2	209.4	209.7
105°	253.7	254.1	254.4	254.9	255.4	256.0	256.5	257.0	257.5	258.0	258.5
107.5°	308.4	308.9	308.9	308.9	308.9	308.9	308.9	309.2	309.4	309.7	310.0
110°	361.7	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	417.7	418.5	418.4	418.1	417.8	417.6	417.3	416.5	415.7	415.0	414.2
115°	472.5	473.3	473.0	472.5	472.0	471.5	471.0	470.7	470.5	470.2	469.9
117.5°	529.4	530.4	529.8	528.5	527.2	525.9	524.6	523.8	523.0	522.3	521.5
120°	584.2	585.2	584.2	582.1	580.0	578.0	575.9	575.9	575.9	575.9	575.9
122.5°	636.3	637.6	637.0	635.7	634.4	633.1	631.8	631.0	630.2	629.5	628.7
125°	687.7	688.9	688.5	687.7	687.0	686.2	685.4	684.6	683.8	683.1	682.3
127.5°	741.2	742.6	742.1	741.0	740.0	738.9	737.9	736.9	735.8	734.8	733.7
130°	791.0	792.7	792.4	791.9	791.4	790.9	790.4	789.9	789.3	788.8	788.3
132.5°	841.5	842.8	842.9	843.2	843.5	843.7	844.0	842.7	841.4	840.1	838.8
135°	889.2	890.6	890.9	891.4	891.9	892.4	892.9	892.7	892.4	892.2	891.9
137.5°	938.4	939.6	939.9	940.4	940.9	941.4	941.9	941.6	941.4	941.1	940.8
140°	983.8	985.0	985.7	987.0	988.3	989.6	990.9	990.9	990.9	990.9	990.9
142.5°	1030.5	1031.7	1032.1	1032.9	1033.6	1034.4	1035.2	1035.4	1035.7	1035.9	1036.2
145°	1072.7	1073.6	1074.4	1075.9	1077.5	1079.0	1080.6	1080.9	1081.1	1081.4	1081.7
147.5°	1114.4	1115.6	1116.1	1117.2	1118.2	1119.3	1120.3	1120.8	1121.3	1121.8	1122.3
150°	1152.1	1152.9	1153.4	1154.5	1155.5	1156.6	1157.6	1158.4	1159.2	1159.9	1160.7
152.5°	1188.2	1189.0	1189.7	1191.0	1192.3	1193.6	1194.9	1195.9	1196.9	1198.0	1199.0
155°	1221.3	1221.7	1222.1	1222.9	1223.6	1224.4	1225.2	1226.5	1227.8	1229.1	1230.4
157.5°	1251.7	1252.0	1252.3	1252.8	1253.3	1253.8	1254.3	1256.1	1257.9	1259.8	1261.6
160°	1279.7	1280.0	1280.1	1280.4	1280.6	1280.9	1281.1	1282.7	1284.2	1285.8	1287.3
162.5°	1303.3	1303.3	1303.4	1303.7	1303.9	1304.2	1304.4	1306.2	1308.0	1309.9	1311.7
165°	1324.4	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1326.1	1327.9	1329.7	1331.5
167.5°	1342.1	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1343.5	1345.3	1347.2	1349.0
170°	1357.3	1356.9	1356.8	1356.5	1356.2	1356.0	1355.7	1357.5	1359.3	1361.2	1363.0
172.5°	1367.8	1367.4	1367.3	1367.0	1366.7	1366.5	1366.2	1368.0	1369.8	1371.7	1373.5
175°	1375.9	1375.5	1375.2	1374.7	1374.2	1373.7	1373.2	1375.0	1376.8	1378.7	1380.5
177.5°	1380.6	1380.2	1379.9	1379.4	1378.9	1378.4	1377.9	1379.5	1381.0	1382.6	1384.1
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1824.0	1821.3	1813.4	1816.0	1812.1	1812.1	1809.4	1809.4	1809.4	1816.0	1812.1
5°	1724.6	1715.4	1706.1	1702.1	1698.1	1694.2	1694.2	1692.9	1704.8	1702.1	1712.7
7.5°	1601.5	1598.8	1580.3	1580.3	1573.6	1571.0	1577.6	1578.9	1580.3	1582.9	1589.5
10°	1491.5	1484.9	1458.4	1461.0	1457.1	1451.8	1455.7	1453.1	1462.4	1465.0	1462.4
12.5°	1361.7	1349.8	1320.6	1306.1	1290.2	1278.2	1292.8	1282.2	1319.3	1329.9	1359.0
15°	1189.5	1167.0	1147.1	1147.1	1132.5	1121.9	1128.6	1140.5	1148.4	1160.4	1165.7
17.5°	1074.3	1065.0	1049.1	1039.8	1035.8	1031.9	1031.9	1037.2	1054.4	1053.1	1063.7
20°	976.2	970.9	963.0	951.1	947.1	944.4	944.4	944.4	956.4	967.0	973.6
22.5°	908.7	904.7	899.4	883.5	875.6	872.9	879.5	883.5	892.8	900.7	907.4
25°	841.1	831.9	822.6	817.3	813.3	813.3	816.0	817.3	821.3	825.2	833.2
27.5°	785.5	778.9	765.6	751.1	751.1	747.1	749.7	752.4	761.7	774.9	781.5
30°	723.2	721.9	716.6	711.3	706.0	703.4	708.7	712.6	714.0	720.6	720.6
32.5°	678.2	668.9	659.7	654.4	651.7	650.4	651.7	657.0	657.0	665.0	674.2
35°	633.2	627.9	618.6	609.3	606.7	600.0	605.3	610.6	619.9	623.9	627.9
37.5°	584.2	577.5	573.6	570.9	565.6	566.9	563.0	570.9	578.9	577.5	580.2
40°	547.1	535.1	523.2	521.9	520.6	519.2	519.2	520.6	525.9	531.2	539.1
42.5°	499.4	495.4	484.8	474.2	471.6	468.9	466.3	471.6	482.2	491.4	495.4
45°	450.4	445.1	442.4	434.5	429.2	427.8	425.2	431.8	441.1	445.1	447.7
47.5°	405.3	404.0	396.1	397.4	393.4	394.7	393.4	397.4	397.4	401.4	404.0
50°	374.9	370.9	366.9	364.3	360.3	360.3	359.0	360.3	365.6	370.9	369.6
52.5°	344.4	337.8	336.5	335.1	332.5	335.1	331.2	332.5	337.8	340.4	339.1
55°	308.6	307.3	304.7	302.0	300.7	299.4	299.4	299.4	304.7	308.6	310.0
57.5°	280.8	274.2	268.9	268.9	263.6	262.3	264.9	266.2	270.2	272.9	275.5
60°	242.4	239.8	231.8	227.8	219.9	218.6	218.6	223.9	230.5	239.8	242.4
62.5°	201.3	197.4	196.0	196.0	196.0	196.0	196.0	196.0	196.0	197.4	197.4
65°	178.8	180.1	178.8	177.5	178.8	178.8	177.5	177.5	177.5	178.8	180.1
67.5°	160.3	159.0	160.3	159.0	157.6	157.6	156.3	157.6	159.0	160.3	160.3
70°	139.1	139.1	137.8	139.1	137.8	136.4	135.1	135.1	137.8	139.1	139.1
72.5°	119.2	119.2	117.9	117.9	115.2	115.2	116.6	115.2	115.2	119.2	119.2
75°	99.3	98.0	96.7	96.7	95.4	95.4	95.4	94.0	96.7	96.7	98.0
77.5°	78.2	78.2	78.2	76.8	76.8	75.5	75.5	76.8	76.8	76.8	78.2
80°	59.6	59.6	59.6	58.3	57.0	57.0	57.0	57.0	57.0	58.3	57.0
82.5°	41.1	41.1	41.1	41.1	41.1	39.7	39.7	39.7	41.1	41.1	39.7
85°	25.2	23.8	25.2	25.2	23.8	25.2	23.8	23.8	22.5	22.5	23.8
87.5°	10.6	9.3	7.9	7.9	9.3	7.9	7.9	7.9	9.3	7.9	7.9
90°	38.5	38.6	38.9	39.1	39.4	39.6	39.4	39.1	38.9	38.6	38.5
92.5°	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3
95°	74.6	74.3	73.8	73.3	72.8	72.3	72.8	73.3	73.8	74.3	74.6
97.5°	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6	116.6
100°	160.9	160.8	160.5	160.2	160.0	159.7	160.0	160.2	160.5	160.8	160.9
102.5°	209.8	209.7	209.4	209.2	208.9	208.7	208.9	209.2	209.4	209.7	209.8
105°	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8	258.8
107.5°	310.1	309.5	308.2	306.9	305.6	304.3	305.6	306.9	308.2	309.5	310.1
110°	362.5	362.1	361.3	360.6	359.8	359.0	359.8	360.6	361.3	362.1	362.5

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	413.8	413.5	413.0	412.5	412.0	411.5	412.0	412.5	413.0	413.5	413.8
115°	469.8	469.4	468.6	467.9	467.1	466.3	467.1	467.9	468.6	469.4	469.8
117.5°	521.1	520.7	519.9	519.2	518.4	517.6	518.4	519.2	519.9	520.7	521.1
120°	575.9	575.5	574.7	574.0	573.2	572.4	573.2	574.0	574.7	575.5	575.9
122.5°	628.3	628.0	627.5	627.0	626.5	626.0	626.5	627.0	627.5	628.0	628.3
125°	681.9	681.8	681.5	681.3	681.0	680.8	681.0	681.3	681.5	681.8	681.9
127.5°	733.2	732.8	732.0	731.3	730.5	729.7	730.5	731.3	732.0	732.8	733.2
130°	788.0	787.5	786.5	785.4	784.4	783.4	784.4	785.4	786.5	787.5	788.0
132.5°	838.2	837.8	837.0	836.3	835.5	834.7	835.5	836.3	837.0	837.8	838.2
135°	891.8	891.4	890.6	889.9	889.1	888.3	889.1	889.9	890.6	891.4	891.8
137.5°	940.7	940.2	939.2	938.1	937.1	936.1	937.1	938.1	939.2	940.2	940.7
140°	990.9	990.4	989.3	988.3	987.2	986.2	987.2	988.3	989.3	990.4	990.9
142.5°	1036.3	1035.8	1034.8	1033.7	1032.7	1031.7	1032.7	1033.7	1034.8	1035.8	1036.3
145°	1081.8	1081.3	1080.2	1079.2	1078.1	1077.1	1078.1	1079.2	1080.2	1081.3	1081.8
147.5°	1122.6	1122.1	1121.0	1120.0	1118.9	1117.9	1118.9	1120.0	1121.0	1122.1	1122.6
150°	1161.1	1160.7	1159.9	1159.2	1158.4	1157.6	1158.4	1159.2	1159.9	1160.7	1161.1
152.5°	1199.5	1199.0	1198.0	1196.9	1195.9	1194.9	1195.9	1196.9	1198.0	1199.0	1199.5
155°	1231.0	1230.6	1229.8	1229.1	1228.3	1227.5	1228.3	1229.1	1229.8	1230.6	1231.0
157.5°	1262.5	1261.8	1260.5	1259.2	1257.9	1256.6	1257.9	1259.2	1260.5	1261.8	1262.5
160°	1288.1	1287.6	1286.6	1285.5	1284.5	1283.5	1284.5	1285.5	1286.6	1287.6	1288.1
162.5°	1312.6	1312.0	1310.7	1309.4	1308.1	1306.8	1308.1	1309.4	1310.7	1312.0	1312.6
165°	1332.4	1331.8	1330.5	1329.2	1327.9	1326.6	1327.9	1329.2	1330.5	1331.8	1332.4
167.5°	1349.9	1349.3	1348.0	1346.7	1345.4	1344.1	1345.4	1346.7	1348.0	1349.3	1349.9
170°	1363.9	1363.1	1361.6	1360.0	1358.5	1356.9	1358.5	1360.0	1361.6	1363.1	1363.9
172.5°	1374.4	1373.6	1372.1	1370.5	1369.0	1367.4	1369.0	1370.5	1372.1	1373.6	1374.4
175°	1381.4	1380.6	1379.1	1377.5	1376.0	1374.4	1376.0	1377.5	1379.1	1380.6	1381.4
177.5°	1384.9	1384.1	1382.6	1381.0	1379.5	1377.9	1379.5	1381.0	1382.6	1384.1	1384.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1	1906.1
2.5°	1816.0	1822.7	1820.0	1805.4	1820.0	1824.0	1831.9	1839.9	1845.2	1853.1	1859.8
5°	1702.1	1715.4	1723.3	1715.4	1741.9	1745.8	1764.4	1775.0	1790.9	1804.1	1814.7
7.5°	1594.8	1605.4	1621.3	1624.0	1639.9	1658.4	1684.9	1711.4	1736.6	1749.8	1761.7
10°	1479.6	1498.1	1522.0	1516.7	1540.5	1569.7	1597.5	1639.9	1661.1	1684.9	1706.1
12.5°	1364.3	1376.3	1408.1	1418.7	1453.1	1475.6	1514.0	1540.5	1593.5	1621.3	1639.9
15°	1163.0	1212.0	1251.8	1299.4	1344.5	1386.9	1421.3	1469.0	1515.4	1536.5	1567.0
17.5°	1071.6	1094.1	1118.0	1141.8	1200.1	1275.6	1336.5	1388.2	1427.9	1455.7	1491.5
20°	976.2	998.8	1025.2	1047.8	1083.5	1137.8	1213.3	1302.1	1349.8	1378.9	1413.4
22.5°	908.7	929.9	947.1	967.0	994.8	1034.5	1091.5	1201.4	1265.0	1300.8	1331.2
25°	835.8	862.3	880.9	895.4	918.0	961.7	1008.0	1070.3	1184.2	1212.0	1254.4
27.5°	785.5	793.4	814.6	837.2	859.7	883.5	931.2	984.2	1061.0	1121.9	1173.6
30°	725.9	745.8	765.6	774.9	794.8	829.2	858.3	915.3	974.9	1022.6	1084.9
32.5°	680.8	692.8	706.0	728.5	747.1	770.9	800.1	847.8	898.1	928.6	976.2
35°	630.5	638.5	666.3	675.6	694.1	717.9	747.1	784.2	838.5	862.3	896.8
37.5°	582.8	601.4	609.3	630.5	647.7	671.6	692.8	735.2	770.9	798.7	830.5
40°	545.7	553.7	568.3	586.8	601.4	619.9	646.4	676.9	715.3	737.8	765.6
42.5°	500.7	507.3	525.9	536.5	560.3	577.5	593.4	630.5	665.0	682.2	710.0
45°	451.7	467.6	479.5	500.7	513.9	535.1	555.0	581.5	613.3	633.2	649.1
47.5°	409.3	425.2	437.1	457.0	478.2	487.5	508.7	536.5	565.6	581.5	604.0
50°	374.9	380.2	402.7	412.0	434.5	453.0	467.6	491.4	523.2	532.5	551.0
52.5°	341.7	345.7	360.3	372.2	392.1	408.0	426.5	449.0	475.5	490.1	504.7
55°	312.6	315.3	321.9	335.1	348.4	368.2	385.5	406.7	429.2	445.1	458.3
57.5°	279.5	284.8	290.1	298.0	311.3	329.8	348.4	368.2	386.8	397.4	414.6
60°	241.1	249.0	258.3	267.6	276.8	290.1	311.3	329.8	347.0	356.3	369.6
62.5°	200.0	215.9	223.9	234.5	242.4	254.3	270.2	291.4	303.3	315.3	325.9
65°	180.1	181.5	182.8	193.4	208.0	219.9	234.5	250.4	268.9	276.8	284.8
67.5°	160.3	161.6	164.3	165.6	170.9	184.1	200.0	217.2	231.8	237.1	245.1
70°	140.4	140.4	145.7	147.0	148.4	149.7	162.9	180.1	193.4	200.0	209.3
72.5°	119.2	120.5	123.2	124.5	127.2	129.8	133.8	143.1	159.0	165.6	176.2
75°	98.0	99.3	100.7	102.0	106.0	107.3	111.3	116.6	123.2	131.1	137.8
77.5°	78.2	78.2	79.5	82.1	84.8	86.1	90.1	92.7	95.4	99.3	104.6
80°	58.3	59.6	59.6	62.3	62.3	63.6	64.9	68.9	71.5	74.2	76.8
82.5°	39.7	42.4	42.4	42.4	43.7	45.0	46.4	46.4	49.0	50.3	54.3
85°	23.8	25.2	25.2	25.2	23.8	26.5	26.5	27.8	27.8	27.8	29.1
87.5°	9.3	7.9	9.3	9.3	9.3	10.6	9.3	9.3	10.6	11.9	11.9
90°	38.8	39.3	39.8	40.3	40.8	35.1	29.4	23.7	18.0	15.2	13.6
92.5°	37.2	36.9	36.6	36.4	36.1	35.9	35.6	35.4	35.1	35.0	34.0
95°	74.6	74.6	74.6	74.6	74.6	74.1	73.6	73.1	72.6	72.3	71.0
97.5°	116.6	116.6	116.6	116.6	116.6	115.6	114.5	113.5	112.4	111.9	110.7
100°	160.9	160.9	160.9	160.9	160.9	160.1	159.3	158.6	157.8	157.4	156.4
102.5°	209.7	209.4	209.2	208.9	208.7	207.7	206.6	205.6	204.5	204.0	203.2
105°	258.5	258.0	257.5	257.0	256.5	256.0	255.4	254.9	254.4	254.1	253.7
107.5°	310.0	309.7	309.4	309.2	308.9	308.9	308.9	308.9	308.9	308.9	308.4
110°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	361.7

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	414.2	415.0	415.7	416.5	417.3	417.6	417.8	418.1	418.4	418.5	417.7
115°	469.9	470.2	470.5	470.7	471.0	471.5	472.0	472.5	473.0	473.3	472.5
117.5°	521.5	522.3	523.0	523.8	524.6	525.9	527.2	528.5	529.8	530.4	529.4
120°	575.9	575.9	575.9	575.9	575.9	578.0	580.0	582.1	584.2	585.2	584.2
122.5°	628.7	629.5	630.2	631.0	631.8	633.1	634.4	635.7	637.0	637.6	636.3
125°	682.3	683.1	683.8	684.6	685.4	686.2	687.0	687.7	688.5	688.9	687.7
127.5°	733.7	734.8	735.8	736.9	737.9	738.9	740.0	741.0	742.1	742.6	741.2
130°	788.3	788.8	789.3	789.9	790.4	790.9	791.4	791.9	792.4	792.7	791.0
132.5°	838.8	840.1	841.4	842.7	844.0	843.7	843.5	843.2	842.9	842.8	841.5
135°	891.9	892.2	892.4	892.7	892.9	892.4	891.9	891.4	890.9	890.6	889.2
137.5°	940.8	941.1	941.4	941.6	941.9	941.4	940.9	940.4	939.9	939.6	938.4
140°	990.9	990.9	990.9	990.9	990.9	989.6	988.3	987.0	985.7	985.0	983.8
142.5°	1036.2	1035.9	1035.7	1035.4	1035.2	1034.4	1033.6	1032.9	1032.1	1031.7	1030.5
145°	1081.7	1081.4	1081.1	1080.9	1080.6	1079.0	1077.5	1075.9	1074.4	1073.6	1072.7
147.5°	1122.3	1121.8	1121.3	1120.8	1120.3	1119.3	1118.2	1117.2	1116.1	1115.6	1114.4
150°	1160.7	1159.9	1159.2	1158.4	1157.6	1156.6	1155.5	1154.5	1153.4	1152.9	1152.1
152.5°	1199.0	1198.0	1196.9	1195.9	1194.9	1193.6	1192.3	1191.0	1189.7	1189.0	1188.2
155°	1230.4	1229.1	1227.8	1226.5	1225.2	1224.4	1223.6	1222.9	1222.1	1221.7	1221.3
157.5°	1261.6	1259.8	1257.9	1256.1	1254.3	1253.8	1253.3	1252.8	1252.3	1252.0	1251.7
160°	1287.3	1285.8	1284.2	1282.7	1281.1	1280.9	1280.6	1280.4	1280.1	1280.0	1279.7
162.5°	1311.7	1309.9	1308.0	1306.2	1304.4	1304.2	1303.9	1303.7	1303.4	1303.3	1303.3
165°	1331.5	1329.7	1327.9	1326.1	1324.3	1324.3	1324.3	1324.3	1324.3	1324.3	1324.4
167.5°	1349.0	1347.2	1345.3	1343.5	1341.7	1341.7	1341.7	1341.7	1341.7	1341.7	1342.1
170°	1363.0	1361.2	1359.3	1357.5	1355.7	1356.0	1356.2	1356.5	1356.8	1356.9	1357.3
172.5°	1373.5	1371.7	1369.8	1368.0	1366.2	1366.5	1366.7	1367.0	1367.3	1367.4	1367.8
175°	1380.5	1378.7	1376.8	1375.0	1373.2	1373.7	1374.2	1374.7	1375.2	1375.5	1375.9
177.5°	1384.1	1382.6	1381.0	1379.5	1377.9	1378.4	1378.9	1379.4	1379.9	1380.2	1380.6
180°	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4	1381.4

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1906.1	1906.1	1906.1	1906.1
2.5°	1871.7	1867.7	1891.5	1918.0
5°	1833.3	1839.9	1870.3	1907.4
7.5°	1793.5	1808.1	1843.9	1892.9
10°	1737.9	1764.4	1818.7	1869.0
12.5°	1683.6	1719.3	1771.0	1830.6
15°	1622.6	1662.4	1726.0	1797.5
17.5°	1555.1	1600.1	1674.3	1752.5
20°	1483.6	1543.2	1621.3	1706.1
22.5°	1404.1	1475.6	1556.4	1650.5
25°	1327.3	1405.4	1486.2	1594.8
27.5°	1251.8	1328.6	1418.7	1528.6
30°	1176.3	1246.5	1343.2	1461.0
32.5°	1095.5	1168.3	1270.3	1390.8
35°	1021.3	1094.1	1189.5	1308.7
37.5°	941.8	1019.9	1111.3	1234.5
40°	849.1	940.5	1029.2	1147.1
42.5°	772.2	868.9	955.0	1066.3
45°	711.3	802.7	874.2	982.9
47.5°	654.4	728.5	801.4	902.1
50°	600.0	657.0	732.5	822.6
52.5°	544.4	593.4	658.3	743.1
55°	494.1	540.4	598.7	663.6
57.5°	447.7	480.8	539.1	597.4
60°	396.1	430.5	475.5	524.5
62.5°	352.3	378.8	421.2	462.3
65°	306.0	331.2	362.9	401.4
67.5°	263.6	286.1	311.3	341.7
70°	225.2	242.4	260.9	287.4
72.5°	184.1	202.7	219.9	241.1
75°	151.0	159.0	173.5	188.1
77.5°	116.6	127.2	135.1	147.0
80°	83.5	92.7	95.4	104.6
82.5°	55.6	60.9	66.2	68.9
85°	31.8	34.4	39.7	41.1
87.5°	11.9	13.2	15.9	18.5
90°	10.5	7.4	4.3	1.2
92.5°	31.9	29.8	27.7	25.6
95°	68.4	65.8	63.2	60.6
97.5°	108.4	106.1	103.7	101.4
100°	154.3	152.2	150.1	148.0
102.5°	201.7	200.1	198.6	197.0
105°	252.9	252.2	251.4	250.6
107.5°	307.4	306.3	305.3	304.3
110°	360.2	358.6	357.1	355.5

TEST NUMBER: P1000084

CATALOG NUMBER: SA2XXRDIP-B865D1080UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	416.2	414.6	413.1	411.5
115°	471.0	469.4	467.9	466.3
117.5°	527.3	525.2	523.2	521.1
120°	582.1	580.0	578.0	575.9
122.5°	633.7	631.2	628.6	626.0
125°	685.4	683.1	680.7	678.4
127.5°	738.3	735.4	732.6	729.7
130°	787.6	784.3	780.9	777.5
132.5°	838.9	836.4	833.8	831.2
135°	886.3	883.5	880.6	877.8
137.5°	936.1	933.8	931.4	929.1
140°	981.5	979.2	976.8	974.5
142.5°	1028.2	1025.9	1023.5	1021.2
145°	1070.9	1069.1	1067.3	1065.5
147.5°	1112.1	1109.8	1107.4	1105.1
150°	1150.6	1149.0	1147.5	1145.9
152.5°	1186.7	1185.1	1183.6	1182.0
155°	1220.5	1219.8	1219.0	1218.2
157.5°	1251.2	1250.7	1250.2	1249.7
160°	1279.2	1278.7	1278.1	1277.6
162.5°	1303.3	1303.3	1303.3	1303.3
165°	1324.7	1324.9	1325.2	1325.4
167.5°	1342.9	1343.6	1344.4	1345.2
170°	1358.1	1358.8	1359.6	1360.4
172.5°	1368.6	1369.3	1370.1	1370.9
175°	1376.7	1377.4	1378.2	1379.0
177.5°	1381.4	1382.1	1382.9	1383.7
180°	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)