

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001594

Luminaire Tested: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001594
REPORT IS A COMBINATION OF REPORTS P996216 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4699.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001594

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001594

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43			37
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35			30
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	29			25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25			21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22			18
6	61	48	40	34	55	45	37	32	38	32	28	31	27	23	25	21	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15			12
9	48	36	28	23	44	33	27	22	28	23	19	23	19	16	19	16	13			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5611	5611	5611
5°	5627	5465	5475
10°	5590	5358	5342
15°	5538	5236	5192
20°	5460	5105	5047
25°	5373	4961	4890
30°	5279	4818	4730
35°	5172	4672	4587
40°	5086	4532	4440
45°	4959	4400	4310
50°	4850	4251	4173
55°	4738	4106	4014
60°	4565	3927	3865
65°	4375	3733	3686
70°	4143	3512	3479
75°	3818	3266	3281
80°	3455	3016	3075
85°	2969	2765	2907

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4959 cd/sqm

TEST NUMBER: P1001594

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	1.4
10°-20°	186.8	4.0
20°-30°	282.4	6.0
30°-40°	341.7	7.3
40°-50°	361.2	7.7
50°-60°	340.0	7.2
60°-70°	282.1	6.0
70°-80°	198.0	4.2
80°-90°	113.2	2.4
90°-100°	91.7	2.0
100°-110°	215.3	4.6
110°-120°	350.2	7.5
120°-130°	421.3	9.0
130°-140°	438.8	9.3
140°-150°	404.4	8.6
150°-160°	324.9	6.9
160°-170°	209.5	4.5
170°-180°	72.2	1.5
0°-30°	534.4	11.4
0°-40°	876.2	18.6
0°-60°	1577.4	33.6
0°-90°	2170.7	46.2
90°-120°	657.2	14.0
90°-150°	1921.8	40.9
90°-180°	2528.0	53.8
0°-180°	4699.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	688	688	688	688	688	
5°	689	687	681	687	687	65
15°	660	661	659	666	665	186
25°	604	609	611	620	620	278
35°	529	538	546	556	559	331
45°	441	455	470	483	487	341
55°	345	361	384	400	404	308
65°	239	264	290	309	315	237
75°	132	161	193	215	222	141
85°	41	73	108	131	139	43
90°	14	51	89	114	122	10
95°	41	47	80	104	111	47
105°	178	197	228	252	238	187
115°	324	333	357	375	380	319
125°	452	454	472	488	493	404
135°	558	558	566	579	585	431
145°	643	644	644	649	653	402
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1001594

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	688.1	688.1	688.1	688.1	688.1
2.5°	691.2	688.9	682.7	688.1	687.3
5°	688.9	686.6	681.2	687.3	686.6
7.5°	684.2	682.7	678.1	685.0	684.2
10°	678.1	677.3	673.5	680.4	679.6
12.5°	669.6	669.6	667.3	673.5	673.5
15°	660.4	661.1	658.8	665.7	665.0
17.5°	648.0	650.3	649.6	656.5	655.7
20°	634.9	637.2	638.0	645.7	645.7
22.5°	620.3	623.4	624.9	632.6	634.2
25°	604.1	608.7	611.0	619.5	620.3
27.5°	586.4	593.3	596.4	604.1	604.9
30°	568.7	574.8	580.2	588.7	590.2
32.5°	549.4	557.1	563.3	573.3	574.8
35°	528.6	537.8	545.5	556.3	558.6
37.5°	507.8	518.6	527.8	538.6	540.9
40°	487.8	497.8	508.6	520.1	523.2
42.5°	464.6	476.2	489.3	502.4	504.7
45°	440.8	455.4	470.0	483.1	487.0
47.5°	418.4	433.0	450.0	463.1	467.7
50°	393.7	410.7	427.7	443.1	447.7
52.5°	369.1	386.0	406.1	421.5	426.1
55°	345.2	361.4	384.5	399.9	404.5
57.5°	318.2	338.3	360.6	379.1	383.0
60°	292.0	312.1	337.5	355.2	361.4
62.5°	266.6	289.0	314.4	332.1	338.3
65°	238.9	263.5	289.7	309.0	315.2
67.5°	212.7	238.9	266.6	285.9	292.0
70°	185.7	211.9	241.2	262.0	267.4
72.5°	159.5	186.5	218.1	238.1	244.3
75°	132.5	161.0	193.4	215.0	221.9
77.5°	107.1	137.2	171.1	192.6	200.3
80°	84.0	114.8	148.7	171.8	178.0
82.5°	60.9	93.2	127.1	151.0	158.0
85°	40.8	73.2	107.9	131.0	138.7
87.5°	25.4	57.0	90.9	113.3	120.2
90°	14.0	51.2	88.8	114.5	121.9
92.5°	20.1	45.9	83.6	108.5	114.7
95°	41.3	47.3	79.5	103.7	111.3
97.5°	68.9	103.8	75.7	98.5	106.1
100°	101.7	131.9	83.6	94.7	100.7
102.5°	139.2	162.9	199.1	91.2	97.4
105°	178.0	196.8	228.2	252.5	238.3
107.5°	214.9	229.7	260.7	282.8	290.5
110°	251.7	264.2	294.6	313.4	321.3

TEST NUMBER: P1001594

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.3	299.9	326.6	342.9	351.4
115°	324.0	332.7	356.8	374.9	380.3
117.5°	357.6	364.4	389.3	404.9	411.1
120°	391.0	395.5	417.3	433.8	438.9
122.5°	422.8	423.9	445.9	461.8	466.1
125°	452.1	453.6	471.7	488.1	493.2
127.5°	481.1	480.9	499.1	512.4	517.3
130°	508.1	507.9	522.0	536.4	541.1
132.5°	533.7	534.1	545.6	559.3	563.3
135°	558.5	557.9	565.6	579.1	584.9
137.5°	581.2	580.5	586.5	599.1	602.4
140°	603.4	603.8	605.7	617.5	621.9
142.5°	622.6	624.9	624.6	634.3	637.4
145°	643.1	644.0	644.0	649.1	653.4
147.5°	659.0	661.6	661.0	662.4	666.1
150°	676.6	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)