

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001597

Luminaire Tested: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001597
REPORT IS A COMBINATION OF REPORTS P996219 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4848.0 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001597

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001597

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	48	48	43
2	89	82	76	70	82	76	70	66	64	61	57	54	51	49	44	42	41	41	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	35	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	30	30	26
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	20	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1001597

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.9
10°-20°	256.8	5.3
20°-30°	377.9	7.8
30°-40°	439.3	9.1
40°-50°	439.3	9.1
50°-60°	384.2	7.9
60°-70°	285.2	5.9
70°-80°	161.8	3.3
80°-90°	47.9	1.0
90°-100°	25.4	0.5
100°-110°	167.0	3.4
110°-120°	319.0	6.6
120°-130°	404.9	8.4
130°-140°	433.2	8.9
140°-150°	405.0	8.4
150°-160°	326.6	6.7
160°-170°	210.7	4.3
170°-180°	72.6	1.5
0°-30°	725.8	15.0
0°-40°	1165.1	24.0
0°-60°	1988.6	41.0
0°-90°	2483.6	51.2
90°-120°	511.4	10.5
90°-150°	1754.5	36.2
90°-180°	2364.0	48.8
0°-180°	4848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	2	8	13	16	17	4
95°	31	12	13	16	17	39
105°	172	176	178	184	163	180
115°	321	323	322	324	324	316
125°	452	454	453	454	455	403
135°	560	560	562	563	564	432
145°	646	648	648	648	649	404
155°	708	709	707	709	708	327
165°	747	744	744	749	744	211
175°	764	761	761	766	760	73
180°	764	764	764	764	764	

TEST NUMBER: P1001597

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	1.7	8.0	12.6	16.0	17.1
92.5°	8.6	7.4	12.0	15.4	15.4
95°	31.4	12.0	12.6	16.0	16.6
97.5°	60.0	72.6	12.6	15.4	16.0
100°	93.7	104.0	25.1	15.4	16.0
102.5°	131.4	138.3	145.2	16.6	16.6
105°	172.0	175.5	178.3	183.5	162.9
107.5°	209.2	210.9	214.9	217.7	220.0
110°	246.9	248.6	252.0	253.2	254.9

TEST NUMBER: P1001597

CATALOG NUMBER: SA4XXDIP-B575D590UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	286.9	288.0	287.5	289.8
115°	321.2	322.9	322.3	323.5	323.5
117.5°	354.9	357.2	358.9	358.3	358.3
120°	389.2	391.5	390.9	392.1	390.9
122.5°	421.2	422.3	423.5	424.1	422.9
125°	451.5	453.8	452.6	454.4	454.9
127.5°	480.6	481.2	484.1	483.5	482.9
130°	508.6	509.2	510.9	511.5	511.5
132.5°	534.4	535.5	537.8	538.4	537.8
135°	560.1	559.5	561.8	562.9	564.1
137.5°	582.9	582.9	585.8	586.9	586.4
140°	605.2	606.4	607.5	609.2	609.8
142.5°	625.2	627.5	628.1	629.2	629.2
145°	645.8	647.5	647.5	648.1	649.2
147.5°	661.8	665.2	664.7	665.2	665.8
150°	679.5	681.8	681.2	681.2	681.8
152.5°	694.4	696.1	695.0	696.1	695.5
155°	708.1	708.7	707.0	709.2	707.5
157.5°	720.1	720.1	717.8	720.7	717.8
160°	730.4	728.7	728.1	731.5	728.1
162.5°	739.5	737.2	736.7	740.1	736.1
165°	747.0	744.1	744.1	748.7	743.5
167.5°	753.3	750.4	749.8	755.0	749.2
170°	758.4	755.0	755.5	760.1	754.4
172.5°	761.8	758.4	759.0	763.5	757.3
175°	764.1	760.7	761.3	766.4	759.5
177.5°	765.8	761.8	763.0	767.5	760.7
180°	764.1	764.1	764.1	764.1	764.1

(END OF REPORT)