

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000094

Luminaire Tested: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000094
REPORT IS A COMBINATION OF REPORTS P988653 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6856.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	98	94	90	87	90	86	83	80	72	70	68	59	58	57	47	47	46
2	89	83	77	72	82	76	71	67	64	61	58	53	51	48	43	41	40
3	82	73	66	61	75	68	62	57	57	53	49	48	44	42	39	36	35
4	76	65	58	52	69	61	54	49	51	47	43	43	39	37	35	33	31
5	70	59	51	45	64	54	48	43	46	41	37	39	35	32	32	29	27
6	64	53	45	40	59	49	42	38	42	37	33	36	32	29	29	27	24
7	60	48	41	35	55	45	38	33	39	33	30	33	29	26	27	24	22
8	56	44	37	31	51	41	34	30	35	30	27	30	26	23	25	22	20
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	20	18
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28890	28890	28890	28890
5°	28958	30686	29058	24515
10°	28639	32435	28842	20244
15°	28017	32444	28492	15208
20°	27270	26818	27863	12547
25°	26363	16758	26932	10673
30°	25205	10730	25892	9189
35°	23798	8245	24569	7863
40°	22231	6931	23180	6879
45°	20554	5899	21412	5775
50°	18834	5012	19714	4995
55°	16931	4355	17845	4298
60°	15242	3321	16049	3282
65°	13662	2499	14472	2835
70°	11918	1997	12854	2310
75°	10075	1529	10998	1748
80°	8000	1041	8607	1146
85°	5551	536	6088	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 26428 cd/sqm

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	2.5
10°-20°	483.2	7.0
20°-30°	621.9	9.1
30°-40°	590.0	8.6
40°-50°	505.6	7.4
50°-60°	385.1	5.6
60°-70°	242.8	3.5
70°-80°	121.1	1.8
80°-90°	34.9	0.5
90°-100°	81.8	1.2
100°-110°	260.1	3.8
110°-120°	445.1	6.5
120°-130°	585.4	8.5
130°-140°	657.1	9.6
140°-150°	644.4	9.4
150°-160°	540.5	7.9
160°-170°	358.5	5.2
170°-180°	125.3	1.8
0°-30°	1278.2	18.6
0°-40°	1868.2	27.2
0°-60°	2758.9	40.2
0°-90°	3157.8	46.1
90°-120°	787.1	11.5
90°-150°	2673.9	39.0
90°-180°	3698.0	53.9
0°-180°	6856.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1825	1825	1825	1825	1825	
5°	1826	2031	1833	1622	1826	173
15°	1721	2292	1750	1074	1721	484
25°	1527	1223	1560	779	1527	701
35°	1253	602	1294	574	1253	784
45°	941	418	980	410	941	726
55°	635	290	670	287	635	573
65°	384	151	407	171	384	381
75°	180	80	197	91	180	195
85°	39	23	43	24	39	45
90°	1	38	1	38	1	6
95°	58	69	58	69	58	65
105°	240	248	240	248	240	253
115°	446	446	446	446	446	442
125°	650	652	650	652	650	581
135°	840	851	840	851	840	650
145°	1020	1031	1020	1031	1020	637
155°	1166	1175	1166	1175	1166	537
165°	1269	1270	1269	1270	1269	358
175°	1320	1316	1320	1316	1320	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1836.5	1844.1	1847.9	1853.0	1864.4	1872.0	1883.4	1886.0	1884.7	1889.8	1875.8
5°	1826.4	1842.9	1858.1	1870.8	1891.1	1903.7	1917.7	1934.2	1938.0	1957.0	1945.6
7.5°	1812.4	1836.5	1858.1	1883.4	1913.9	1930.4	1951.9	1977.3	1988.7	2011.5	2017.9
10°	1789.6	1823.8	1860.6	1887.2	1929.1	1958.3	1978.6	2019.2	2045.8	2080.0	2075.0
12.5°	1752.8	1797.2	1846.7	1891.1	1945.6	1964.6	2002.7	2044.5	2078.8	2110.5	2138.4
15°	1721.1	1771.8	1826.4	1880.9	1943.1	1978.6	2016.6	2071.2	2107.9	2163.7	2187.8
17.5°	1678.0	1742.7	1807.3	1868.2	1941.8	1982.4	2029.3	2082.6	2137.1	2190.4	2209.4
20°	1633.6	1703.3	1773.1	1855.5	1939.2	1978.6	2026.8	2092.7	2146.0	2187.8	2187.8
22.5°	1580.3	1665.3	1745.2	1823.8	1915.2	1972.2	2021.7	2099.1	2137.1	2146.0	2111.7
25°	1527.0	1612.0	1699.5	1797.2	1901.2	1951.9	2007.7	2080.0	2092.7	2057.2	1968.4
27.5°	1463.6	1558.8	1657.7	1763.0	1872.0	1935.4	1986.2	2034.4	2010.3	1915.2	1776.9
30°	1398.9	1501.7	1613.3	1713.5	1845.4	1903.7	1946.9	1960.8	1884.7	1730.0	1551.1
32.5°	1331.7	1431.9	1549.9	1670.4	1803.5	1859.3	1887.2	1850.5	1711.0	1515.6	1297.5
35°	1253.1	1366.0	1489.0	1614.6	1746.5	1788.3	1804.8	1714.8	1535.9	1283.5	1066.7
37.5°	1182.1	1294.9	1426.9	1555.0	1683.0	1705.9	1689.4	1548.6	1321.6	1071.7	859.9
40°	1098.4	1218.8	1348.2	1491.5	1596.8	1603.1	1562.6	1379.9	1098.4	863.7	733.1
42.5°	1021.0	1142.7	1272.1	1418.0	1497.9	1476.3	1421.8	1182.1	917.0	744.5	639.2
45°	941.1	1056.5	1196.0	1325.4	1382.5	1331.7	1249.3	994.4	769.9	640.5	559.3
47.5°	863.7	971.5	1109.8	1234.1	1244.2	1187.1	1089.5	833.3	667.1	563.1	497.2
50°	787.6	895.4	1024.8	1127.5	1117.4	1038.7	928.4	724.2	579.6	497.2	442.6
52.5°	711.5	809.2	934.7	1015.9	972.8	896.7	787.6	613.9	506.1	433.8	391.9
55°	635.4	726.7	834.5	901.8	833.3	745.8	668.4	526.3	438.8	380.5	348.8
57.5°	572.0	644.3	743.2	783.8	701.4	632.9	565.7	452.8	380.5	338.6	301.9
60°	502.3	568.2	649.4	673.5	588.5	532.7	475.6	383.0	326.0	289.2	265.1
62.5°	442.6	497.2	559.3	559.3	484.5	442.6	399.5	320.9	274.0	244.8	233.4
65°	384.3	423.6	468.0	462.9	399.5	362.7	328.5	265.1	229.6	209.3	197.9
67.5°	327.2	357.7	386.8	369.1	323.4	291.7	260.0	214.3	190.2	176.3	161.1
70°	275.2	299.3	314.5	298.1	252.4	225.8	202.9	172.5	153.5	135.7	126.8
72.5°	230.8	241.0	246.1	225.8	187.7	172.5	156.0	134.4	118.0	109.1	106.5
75°	180.1	189.0	185.2	170.0	138.2	126.8	114.1	98.9	95.1	90.1	87.5
77.5°	140.8	140.8	134.4	120.5	98.9	90.1	85.0	77.4	73.6	72.3	69.8
80°	100.2	98.9	95.1	79.9	67.2	62.1	62.1	57.1	55.8	53.3	53.3
82.5°	66.0	66.0	60.9	48.2	44.4	43.1	41.9	39.3	39.3	38.0	38.0
85°	39.3	36.8	30.4	26.6	25.4	25.4	24.1	22.8	24.1	22.8	22.8
87.5°	17.8	14.0	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
90°	1.1	4.1	7.1	10.0	13.0	14.5	17.2	22.7	28.2	33.6	39.1
92.5°	24.6	26.6	28.6	30.5	32.5	33.5	33.6	33.9	34.1	34.4	34.6
95°	58.0	60.5	63.0	65.5	68.0	69.2	69.4	69.9	70.4	70.9	71.4
97.5°	97.1	99.3	101.6	103.8	106.1	107.2	107.7	108.7	109.6	110.6	111.6
100°	141.8	143.8	145.8	147.7	149.7	150.7	151.1	151.8	152.5	153.3	154.0
102.5°	188.6	190.1	191.6	193.1	194.6	195.3	195.8	196.8	197.8	198.8	199.8
105°	240.0	240.7	241.5	242.2	242.9	243.3	243.6	244.1	244.6	245.1	245.6
107.5°	291.3	292.3	293.3	294.3	295.3	295.8	295.8	295.8	295.8	295.8	295.8
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	394.0	395.5	397.0	398.5	400.0	400.7	400.6	400.3	400.1	399.8	399.6
115°	446.5	448.0	449.5	451.0	452.5	453.2	453.0	452.5	452.0	451.5	451.0
117.5°	499.0	501.0	503.0	504.9	506.9	507.9	507.3	506.0	504.8	503.5	502.3
120°	551.4	553.4	555.4	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4
122.5°	599.4	601.9	604.4	606.9	609.4	610.6	610.0	608.7	607.5	606.2	605.0
125°	649.7	651.9	654.1	656.4	658.6	659.7	659.3	658.6	657.9	657.1	656.4
127.5°	698.8	701.5	704.3	707.0	709.7	711.1	710.6	709.6	708.6	707.6	706.6
130°	744.6	747.8	751.0	754.3	757.5	759.1	758.8	758.3	757.8	757.3	756.8
132.5°	795.9	798.4	800.9	803.4	805.9	807.1	807.2	807.5	807.7	808.0	808.2
135°	840.5	843.2	846.0	848.7	851.4	852.8	853.1	853.6	854.1	854.6	855.1
137.5°	889.7	891.9	894.1	896.4	898.6	899.7	899.9	900.4	900.9	901.4	901.9
140°	933.2	935.4	937.6	939.9	942.1	943.2	943.8	945.1	946.3	947.6	948.8
142.5°	977.9	980.1	982.3	984.6	986.8	987.9	988.3	989.0	989.7	990.5	991.2
145°	1020.3	1022.0	1023.8	1025.5	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8
147.5°	1058.2	1060.4	1062.7	1064.9	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7
150°	1097.3	1098.8	1100.3	1101.8	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5
152.5°	1131.9	1133.4	1134.9	1136.4	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2
155°	1166.5	1167.2	1168.0	1168.7	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2
157.5°	1196.6	1197.1	1197.6	1198.1	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1
160°	1223.4	1223.9	1224.4	1224.9	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8
162.5°	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1
165°	1269.2	1269.0	1268.7	1268.5	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1
167.5°	1288.2	1287.4	1286.7	1285.9	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8
170°	1302.7	1301.9	1301.2	1300.4	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2
172.5°	1312.7	1312.0	1311.2	1310.5	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3
175°	1320.5	1319.8	1319.0	1318.3	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0
177.5°	1325.0	1324.3	1323.5	1322.8	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1889.8	1892.3	1896.1	1913.9	1916.4	1921.5	1919.0	1919.0	1920.2	1917.7	1919.0
5°	1971.0	1974.8	1993.8	2015.3	2020.4	2015.3	2021.7	2030.6	2030.6	2030.6	2028.0
7.5°	2047.1	2061.0	2082.6	2114.3	2120.6	2127.0	2138.4	2130.8	2133.3	2144.7	2140.9
10°	2120.6	2140.9	2165.0	2191.6	2205.6	2214.5	2219.5	2231.0	2257.6	2227.2	2238.6
12.5°	2190.4	2219.5	2244.9	2274.1	2284.2	2295.6	2299.4	2309.6	2309.6	2308.3	2317.2
15°	2236.0	2262.7	2285.5	2304.5	2307.1	2304.5	2302.0	2303.3	2307.1	2291.8	2300.7
17.5°	2246.2	2248.7	2256.3	2248.7	2250.0	2223.4	2208.1	2204.3	2168.8	2170.1	2199.3
20°	2196.7	2153.6	2142.2	2100.3	2075.0	2006.5	2003.9	1984.9	1910.1	1932.9	1927.8
22.5°	2061.0	1987.4	1889.8	1841.6	1817.5	1745.2	1689.4	1650.1	1623.4	1596.8	1585.4
25°	1882.2	1763.0	1624.7	1529.6	1515.6	1448.4	1345.7	1297.5	1240.4	1222.7	1253.1
27.5°	1651.3	1496.6	1340.6	1194.7	1168.1	1107.2	1055.2	1021.0	955.0	951.2	953.8
30°	1338.1	1182.1	1051.4	956.3	890.4	862.5	828.2	802.8	776.2	786.4	788.9
32.5°	1099.6	951.2	829.5	778.7	748.3	730.5	701.4	684.9	673.5	669.7	668.4
35°	873.9	774.9	720.4	670.9	653.2	640.5	618.9	611.3	601.2	602.4	602.4
37.5°	748.3	665.9	625.3	599.9	583.4	577.1	563.1	555.5	549.2	546.6	550.4
40°	645.6	588.5	563.1	540.3	526.3	523.8	516.2	507.3	499.7	501.0	504.8
42.5°	570.7	537.8	507.3	489.6	479.4	475.6	469.3	462.9	462.9	459.1	457.9
45°	511.1	484.5	459.1	442.6	436.3	431.2	423.6	422.3	417.3	418.5	419.8
47.5°	457.9	436.3	417.3	400.8	394.4	393.2	385.6	380.5	380.5	379.2	378.0
50°	409.7	388.1	371.6	362.7	353.9	351.3	350.1	348.8	346.2	346.2	347.5
52.5°	370.3	348.8	336.1	328.5	323.4	320.9	320.9	319.6	319.6	319.6	318.3
55°	327.2	309.5	299.3	296.8	294.2	293.0	291.7	289.2	287.9	290.4	287.9
57.5°	286.6	280.3	271.4	268.9	262.5	262.5	258.7	256.2	253.7	256.2	256.2
60°	254.9	246.1	241.0	233.4	228.3	223.2	216.9	215.6	213.1	211.8	210.5
62.5°	222.0	214.3	201.7	190.2	182.6	177.6	175.0	173.8	173.8	172.5	172.5
65°	185.2	167.4	161.1	157.3	156.0	154.7	152.2	150.9	152.2	150.9	152.2
67.5°	144.6	142.1	138.2	135.7	134.4	133.2	133.2	131.9	131.9	131.9	131.9
70°	125.6	119.2	118.0	115.4	115.4	114.1	114.1	114.1	114.1	112.9	115.4
72.5°	104.0	100.2	98.9	97.7	97.7	97.7	96.4	96.4	96.4	95.1	96.4
75°	85.0	83.7	81.2	81.2	79.9	81.2	79.9	79.9	78.6	79.9	79.9
77.5°	68.5	67.2	66.0	66.0	64.7	64.7	64.7	64.7	64.7	64.7	66.0
80°	52.0	50.7	49.5	50.7	49.5	50.7	49.5	49.5	50.7	49.5	49.5
82.5°	38.0	36.8	36.8	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5
85°	22.8	21.6	21.6	22.8	21.6	22.8	21.6	21.6	21.6	22.8	22.8
87.5°	10.1	11.4	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	11.4
90°	38.6	38.1	37.6	37.1	36.8	36.9	37.2	37.5	37.7	38.0	37.7
92.5°	34.8	35.1	35.3	35.6	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.4	71.4	71.4	71.4	71.2	70.7	70.2	69.7	69.2	69.7
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	154.0	154.0	154.0	154.0	153.9	153.6	153.4	153.1	152.9	153.1
102.5°	200.0	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	200.0
105°	246.1	246.6	247.1	247.6	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.0	296.3	296.5	296.8	296.9	296.3	295.0	293.8	292.5	291.3	292.5
110°	347.2	347.2	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.8	344.6

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	398.9	398.1	397.4	396.7	396.3	396.0	395.5	395.0	394.5	394.0	394.5
115°	450.8	450.5	450.3	450.0	449.9	449.5	448.8	448.0	447.3	446.5	447.3
117.5°	501.6	500.8	500.1	499.4	499.0	498.6	497.9	497.1	496.4	495.6	496.4
120°	551.4	551.4	551.4	551.4	551.4	551.0	550.3	549.6	548.8	548.1	548.8
122.5°	604.3	603.5	602.8	602.1	601.7	601.4	600.9	600.4	599.9	599.4	599.9
125°	655.6	654.9	654.1	653.4	653.0	652.9	652.6	652.4	652.1	651.9	652.1
127.5°	705.6	704.6	703.6	702.6	702.1	701.7	701.0	700.3	699.5	698.8	699.5
130°	756.3	755.8	755.3	754.8	754.6	754.1	753.1	752.1	751.1	750.1	751.1
132.5°	807.0	805.7	804.5	803.2	802.6	802.2	801.5	800.7	800.0	799.2	800.0
135°	854.8	854.6	854.3	854.0	853.9	853.5	852.8	852.1	851.3	850.6	851.3
137.5°	901.7	901.4	901.2	900.9	900.8	900.3	899.3	898.4	897.4	896.4	897.4
140°	948.8	948.8	948.8	948.8	948.8	948.3	947.3	946.4	945.4	944.4	945.4
142.5°	991.5	991.7	992.0	992.3	992.4	991.9	990.9	989.9	988.9	987.9	988.9
145°	1035.0	1035.3	1035.5	1035.8	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4
147.5°	1073.2	1073.7	1074.2	1074.7	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5
150°	1109.2	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2
152.5°	1145.2	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2
155°	1174.4	1175.7	1176.9	1178.2	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2
157.5°	1202.8	1204.6	1206.3	1208.0	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5
160°	1228.3	1229.8	1231.3	1232.8	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0
162.5°	1250.8	1252.6	1254.3	1256.0	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5
165°	1269.8	1271.6	1273.3	1275.0	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5
167.5°	1286.5	1288.3	1290.0	1291.7	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3
170°	1299.9	1301.7	1303.4	1305.1	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8
172.5°	1310.0	1311.8	1313.5	1315.2	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9
175°	1316.7	1318.5	1320.2	1321.9	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6
177.5°	1320.9	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1924.0	1915.2	1912.6	1915.2	1912.6	1913.9	1905.0	1872.0	1880.9	1867.0	1874.6
5°	2033.1	2025.5	2009.0	2006.5	2003.9	2001.4	1988.7	1959.5	1948.1	1929.1	1927.8
7.5°	2137.1	2137.1	2124.4	2115.5	2104.1	2095.3	2078.8	2035.6	2017.9	1995.1	1982.4
10°	2239.8	2206.9	2220.8	2211.9	2184.0	2179.0	2148.5	2123.2	2088.9	2066.1	2045.8
12.5°	2313.4	2303.3	2290.6	2283.0	2275.4	2258.9	2238.6	2173.9	2156.1	2110.5	2087.6
15°	2310.9	2304.5	2308.3	2308.3	2305.8	2302.0	2285.5	2238.6	2208.1	2163.7	2124.4
17.5°	2186.6	2203.1	2219.5	2231.0	2256.3	2267.7	2283.0	2255.1	2236.0	2198.0	2156.1
20°	1969.7	2010.3	2058.5	2068.6	2091.4	2158.7	2189.1	2213.2	2220.8	2208.1	2173.9
22.5°	1667.8	1702.1	1818.8	1816.2	1849.2	1929.1	2017.9	2090.2	2147.3	2179.0	2166.3
25°	1306.4	1354.6	1416.7	1463.6	1571.4	1690.7	1801.0	1916.4	2015.3	2102.9	2124.4
27.5°	988.0	1051.4	1100.9	1163.0	1217.6	1358.4	1500.4	1680.5	1795.9	1962.1	2048.3
30°	799.0	828.2	877.7	906.8	933.5	1041.3	1202.4	1379.9	1582.9	1774.4	1922.8
32.5°	682.4	702.6	739.4	752.1	780.0	852.3	953.8	1116.1	1325.4	1557.5	1752.8
35°	612.6	634.2	641.8	653.2	676.0	721.7	791.4	909.4	1098.4	1325.4	1558.8
37.5°	553.0	564.4	586.0	593.6	601.2	635.4	682.4	764.8	890.4	1076.8	1335.5
40°	511.1	517.5	528.9	535.2	540.3	564.4	606.3	662.1	754.6	896.7	1135.1
42.5°	466.7	474.3	482.0	489.6	495.9	514.9	540.3	593.6	655.7	763.5	936.0
45°	423.6	428.7	437.6	442.6	451.5	466.7	489.6	526.3	582.2	650.6	790.2
47.5°	384.3	390.6	394.4	400.8	407.1	423.6	445.2	469.3	514.9	582.2	683.6
50°	348.8	356.4	361.5	362.7	367.8	383.0	400.8	427.4	456.6	508.6	597.4
52.5°	323.4	324.7	328.5	333.6	332.3	341.2	357.7	378.0	408.4	450.3	514.9
55°	294.2	298.1	300.6	301.9	301.9	309.5	318.3	337.4	361.5	395.7	450.3
57.5°	257.5	261.3	268.9	271.4	275.2	279.0	282.8	295.5	315.8	348.8	393.2
60°	219.4	222.0	229.6	234.6	237.2	247.3	252.4	262.5	274.0	298.1	339.9
62.5°	176.3	178.8	182.6	187.7	192.8	208.0	220.7	230.8	239.7	256.2	290.4
65°	153.5	154.7	157.3	158.5	159.8	166.1	177.6	191.5	208.0	220.7	241.0
67.5°	133.2	134.4	135.7	138.2	139.5	140.8	145.9	149.7	166.1	183.9	199.1
70°	114.1	116.7	118.0	118.0	119.2	121.8	124.3	129.4	134.4	143.3	162.3
72.5°	96.4	97.7	100.2	100.2	100.2	102.7	105.3	107.8	110.3	115.4	123.0
75°	79.9	82.4	82.4	82.4	83.7	83.7	86.2	88.8	91.3	95.1	97.7
77.5°	66.0	66.0	66.0	66.0	67.2	67.2	68.5	71.0	72.3	73.6	76.1
80°	49.5	50.7	50.7	50.7	52.0	52.0	52.0	54.5	55.8	55.8	58.3
82.5°	36.8	36.8	36.8	38.0	36.8	38.0	38.0	39.3	38.0	39.3	40.6
85°	22.8	22.8	22.8	24.1	24.1	24.1	24.1	24.1	24.1	24.1	25.4
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	12.7	11.4	11.4
90°	37.5	37.2	36.9	36.8	37.1	37.6	38.1	38.6	39.1	33.6	28.2
92.5°	35.7	35.7	35.7	35.7	35.6	35.3	35.1	34.8	34.6	34.4	34.1
95°	70.2	70.7	71.2	71.4	71.4	71.4	71.4	71.4	71.4	70.9	70.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	110.6	109.6
100°	153.4	153.6	153.9	154.0	154.0	154.0	154.0	154.0	154.0	153.3	152.5
102.5°	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	198.8	197.8
105°	247.8	247.8	247.8	247.8	247.6	247.1	246.6	246.1	245.6	245.1	244.6
107.5°	293.8	295.0	296.3	296.9	296.8	296.5	296.3	296.0	295.8	295.8	295.8
110°	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.0	395.5	396.0	396.3	396.7	397.4	398.1	398.9	399.6	399.8	400.1
115°	448.0	448.8	449.5	449.9	450.0	450.3	450.5	450.8	451.0	451.5	452.0
117.5°	497.1	497.9	498.6	499.0	499.4	500.1	500.8	501.6	502.3	503.5	504.8
120°	549.6	550.3	551.0	551.4	551.4	551.4	551.4	551.4	551.4	553.4	555.4
122.5°	600.4	600.9	601.4	601.7	602.1	602.8	603.5	604.3	605.0	606.2	607.5
125°	652.4	652.6	652.9	653.0	653.4	654.1	654.9	655.6	656.4	657.1	657.9
127.5°	700.3	701.0	701.7	702.1	702.6	703.6	704.6	705.6	706.6	707.6	708.6
130°	752.1	753.1	754.1	754.6	754.8	755.3	755.8	756.3	756.8	757.3	757.8
132.5°	800.7	801.5	802.2	802.6	803.2	804.5	805.7	807.0	808.2	808.0	807.7
135°	852.1	852.8	853.5	853.9	854.0	854.3	854.6	854.8	855.1	854.6	854.1
137.5°	898.4	899.3	900.3	900.8	900.9	901.2	901.4	901.7	901.9	901.4	900.9
140°	946.4	947.3	948.3	948.8	948.8	948.8	948.8	948.8	948.8	947.6	946.3
142.5°	989.9	990.9	991.9	992.4	992.3	992.0	991.7	991.5	991.2	990.5	989.7
145°	1033.4	1034.4	1035.4	1035.9	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8
147.5°	1072.5	1073.5	1074.5	1075.0	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7
150°	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5
152.5°	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7
155°	1176.9	1177.7	1178.4	1178.8	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7
157.5°	1205.8	1207.0	1208.3	1208.9	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1
160°	1231.0	1232.0	1233.0	1233.5	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3
162.5°	1253.8	1255.0	1256.3	1256.9	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6
165°	1272.8	1274.0	1275.3	1275.9	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1
167.5°	1289.5	1290.8	1292.0	1292.6	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8
170°	1302.3	1303.8	1305.3	1306.0	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7
172.5°	1312.4	1313.9	1315.4	1316.1	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8
175°	1319.1	1320.6	1322.1	1322.8	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0
177.5°	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1863.1	1856.8	1856.8	1853.0	1853.0	1832.7	1832.7	1839.1	1831.4	1822.6	1809.9
5°	1911.3	1897.4	1893.6	1888.5	1872.0	1846.7	1836.5	1832.7	1817.5	1798.5	1776.9
7.5°	1957.0	1934.2	1922.8	1911.3	1889.8	1854.3	1834.0	1820.0	1797.2	1768.0	1740.1
10°	2001.4	1972.2	1943.1	1929.1	1898.7	1854.3	1825.1	1802.3	1769.3	1730.0	1690.7
12.5°	2042.0	1981.1	1976.0	1948.1	1903.7	1853.0	1808.6	1775.6	1733.8	1688.1	1642.5
15°	2077.5	2015.3	1984.9	1959.5	1901.2	1837.8	1790.9	1750.3	1694.5	1642.5	1586.7
17.5°	2095.3	2028.0	2007.7	1965.9	1906.3	1823.8	1760.4	1711.0	1650.1	1587.9	1524.5
20°	2113.0	2034.4	2001.4	1972.2	1891.1	1797.2	1726.2	1669.1	1601.9	1528.3	1458.6
22.5°	2121.9	2034.4	1995.1	1954.5	1875.8	1768.0	1684.3	1617.1	1538.5	1463.6	1379.9
25°	2106.7	2026.8	1979.8	1938.0	1849.2	1732.5	1636.1	1560.0	1476.3	1391.3	1306.4
27.5°	2068.6	2009.0	1954.5	1911.3	1812.4	1686.9	1585.4	1499.1	1412.9	1317.8	1231.5
30°	1997.6	1971.0	1927.8	1879.6	1771.8	1646.3	1525.8	1437.0	1341.9	1246.8	1156.7
32.5°	1887.2	1910.1	1882.2	1840.3	1723.6	1590.5	1462.4	1372.3	1268.3	1165.6	1083.1
35°	1752.8	1834.0	1818.8	1789.6	1672.9	1530.9	1402.8	1293.7	1189.7	1085.7	1003.2
37.5°	1605.7	1728.7	1741.4	1723.6	1614.6	1470.0	1329.2	1222.7	1116.1	1010.8	927.1
40°	1404.0	1593.0	1633.6	1641.2	1553.7	1396.4	1249.3	1145.3	1040.0	937.3	835.8
42.5°	1218.8	1457.3	1508.0	1539.7	1476.3	1324.1	1175.7	1060.3	956.3	863.7	762.3
45°	1045.1	1293.7	1376.1	1416.7	1388.8	1241.7	1088.2	980.4	885.3	800.3	702.6
47.5°	866.3	1116.1	1231.5	1296.2	1296.2	1158.0	1004.5	898.0	806.6	734.4	648.1
50°	747.0	955.0	1074.3	1159.2	1182.1	1073.0	928.4	824.4	738.2	659.5	593.6
52.5°	636.7	823.1	922.1	1010.8	1076.8	981.7	843.4	749.6	664.6	591.0	539.0
55°	550.4	690.0	780.0	877.7	951.2	889.1	761.0	669.7	596.1	535.2	490.8
57.5°	468.0	589.8	663.3	749.6	828.2	781.3	678.5	599.9	535.2	482.0	442.6
60°	398.2	497.2	554.3	621.5	719.1	686.2	601.2	528.9	476.9	428.7	395.7
62.5°	338.6	417.3	465.5	513.7	602.4	587.2	521.3	465.5	421.1	380.5	352.6
65°	277.8	342.4	380.5	422.3	493.4	499.7	446.4	407.1	366.5	331.0	305.7
67.5°	224.5	275.2	309.5	345.0	402.1	419.8	383.0	350.1	315.8	286.6	263.8
70°	181.4	216.9	242.2	270.2	317.1	338.6	319.6	296.8	268.9	244.8	224.5
72.5°	143.3	166.1	181.4	202.9	241.0	262.5	261.3	241.0	220.7	204.2	187.7
75°	105.3	123.0	135.7	149.7	180.1	200.4	205.5	196.6	176.3	163.6	150.9
77.5°	79.9	90.1	96.4	106.5	128.1	145.9	153.5	150.9	137.0	126.8	118.0
80°	60.9	63.4	66.0	69.8	87.5	104.0	109.1	107.8	100.2	96.4	86.2
82.5°	43.1	44.4	45.7	46.9	53.3	67.2	72.3	74.8	68.5	64.7	55.8
85°	25.4	26.6	26.6	29.2	30.4	34.2	43.1	43.1	41.9	36.8	35.5
87.5°	12.7	12.7	11.4	11.4	12.7	14.0	16.5	19.0	16.5	15.2	14.0
90°	22.7	17.2	14.5	13.0	10.0	7.1	4.1	1.1	4.1	7.1	10.0
92.5°	33.9	33.6	33.5	32.5	30.5	28.6	26.6	24.6	26.6	28.6	30.5
95°	69.9	69.4	69.2	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	108.7	107.7	107.2	106.1	103.8	101.6	99.3	97.1	99.3	101.6	103.8
100°	151.8	151.1	150.7	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	196.8	195.8	195.3	194.6	193.1	191.6	190.1	188.6	190.1	191.6	193.1
105°	244.1	243.6	243.3	242.9	242.2	241.5	240.7	240.0	240.7	241.5	242.2
107.5°	295.8	295.8	295.8	295.3	294.3	293.3	292.3	291.3	292.3	293.3	294.3
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	400.3	400.6	400.7	400.0	398.5	397.0	395.5	394.0	395.5	397.0	398.5
115°	452.5	453.0	453.2	452.5	451.0	449.5	448.0	446.5	448.0	449.5	451.0
117.5°	506.0	507.3	507.9	506.9	504.9	503.0	501.0	499.0	501.0	503.0	504.9
120°	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4	553.4	555.4	557.4
122.5°	608.7	610.0	610.6	609.4	606.9	604.4	601.9	599.4	601.9	604.4	606.9
125°	658.6	659.3	659.7	658.6	656.4	654.1	651.9	649.7	651.9	654.1	656.4
127.5°	709.6	710.6	711.1	709.7	707.0	704.3	701.5	698.8	701.5	704.3	707.0
130°	758.3	758.8	759.1	757.5	754.3	751.0	747.8	744.6	747.8	751.0	754.3
132.5°	807.5	807.2	807.1	805.9	803.4	800.9	798.4	795.9	798.4	800.9	803.4
135°	853.6	853.1	852.8	851.4	848.7	846.0	843.2	840.5	843.2	846.0	848.7
137.5°	900.4	899.9	899.7	898.6	896.4	894.1	891.9	889.7	891.9	894.1	896.4
140°	945.1	943.8	943.2	942.1	939.9	937.6	935.4	933.2	935.4	937.6	939.9
142.5°	989.0	988.3	987.9	986.8	984.6	982.3	980.1	977.9	980.1	982.3	984.6
145°	1030.3	1028.8	1028.1	1027.2	1025.5	1023.8	1022.0	1020.3	1022.0	1023.8	1025.5
147.5°	1069.8	1068.8	1068.3	1067.2	1064.9	1062.7	1060.4	1058.2	1060.4	1062.7	1064.9
150°	1105.5	1104.5	1104.0	1103.3	1101.8	1100.3	1098.8	1097.3	1098.8	1100.3	1101.8
152.5°	1140.5	1139.2	1138.6	1137.9	1136.4	1134.9	1133.4	1131.9	1133.4	1134.9	1136.4
155°	1170.9	1170.2	1169.8	1169.4	1168.7	1168.0	1167.2	1166.5	1167.2	1168.0	1168.7
157.5°	1199.6	1199.1	1198.9	1198.6	1198.1	1197.6	1197.1	1196.6	1197.1	1197.6	1198.1
160°	1226.1	1225.8	1225.7	1225.4	1224.9	1224.4	1223.9	1223.4	1223.9	1224.4	1224.9
162.5°	1248.4	1248.1	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0
165°	1268.1	1268.1	1268.1	1268.2	1268.5	1268.7	1269.0	1269.2	1269.0	1268.7	1268.5
167.5°	1284.8	1284.8	1284.8	1285.2	1285.9	1286.7	1287.4	1288.2	1287.4	1286.7	1285.9
170°	1298.9	1299.2	1299.3	1299.7	1300.4	1301.2	1301.9	1302.7	1301.9	1301.2	1300.4
172.5°	1309.0	1309.3	1309.4	1309.8	1310.5	1311.2	1312.0	1312.7	1312.0	1311.2	1310.5
175°	1316.5	1317.0	1317.2	1317.6	1318.3	1319.0	1319.8	1320.5	1319.8	1319.0	1318.3
177.5°	1320.9	1321.4	1321.7	1322.1	1322.8	1323.5	1324.3	1325.0	1324.3	1323.5	1322.8
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1804.8	1806.1	1809.9	1798.5	1780.7	1773.1	1750.3	1746.5	1742.7	1742.7	1746.5
5°	1764.2	1759.1	1760.4	1738.9	1713.5	1698.3	1666.6	1671.6	1655.1	1645.0	1647.5
7.5°	1719.8	1705.9	1704.6	1676.7	1645.0	1617.1	1584.1	1576.5	1561.3	1543.5	1535.9
10°	1664.0	1653.9	1634.9	1603.1	1562.6	1539.7	1495.3	1468.7	1464.9	1438.3	1428.1
12.5°	1607.0	1589.2	1570.2	1525.8	1480.1	1443.3	1410.4	1381.2	1360.9	1338.1	1322.8
15°	1541.0	1519.4	1497.9	1450.9	1397.7	1360.9	1311.4	1268.3	1208.7	1161.8	1135.1
17.5°	1468.7	1444.6	1415.4	1363.4	1311.4	1260.7	1169.4	1118.7	1076.8	1048.9	1032.4
20°	1393.9	1367.2	1338.1	1286.1	1196.0	1107.2	1056.5	1017.2	991.8	963.9	943.6
22.5°	1315.2	1287.3	1255.6	1174.5	1079.3	1017.2	977.9	941.1	904.3	889.1	878.9
25°	1241.7	1216.3	1175.7	1065.4	990.6	933.5	889.1	865.0	846.0	825.7	806.6
27.5°	1165.6	1118.7	1061.6	969.0	922.1	863.7	832.0	814.3	781.3	767.3	758.5
30°	1074.3	1022.3	967.7	901.8	847.2	806.6	777.5	748.3	729.3	715.3	700.1
32.5°	981.7	932.2	898.0	829.5	788.9	747.0	719.1	701.4	673.5	664.6	658.3
35°	901.8	859.9	829.5	773.7	735.6	697.6	677.3	650.6	632.9	616.4	606.3
37.5°	823.1	800.3	768.6	721.7	681.1	650.6	622.7	613.9	589.8	580.9	570.7
40°	768.6	734.4	707.7	667.1	632.9	599.9	582.2	561.9	545.4	531.4	527.6
42.5°	702.6	677.3	662.1	617.7	582.2	563.1	541.6	518.7	506.1	494.6	480.7
45°	653.2	630.4	608.8	573.3	541.6	517.5	498.4	483.2	461.7	456.6	435.0
47.5°	601.2	578.4	561.9	526.3	497.2	474.3	460.4	440.1	422.3	410.9	400.8
50°	549.2	530.2	514.9	484.5	459.1	435.0	416.0	395.7	388.1	369.1	362.7
52.5°	499.7	487.0	470.5	441.4	416.0	395.7	375.4	358.9	347.5	337.4	329.8
55°	457.9	437.6	430.0	398.2	376.7	355.1	337.4	327.2	313.3	306.9	300.6
57.5°	410.9	399.5	386.8	362.7	338.6	318.3	305.7	290.4	282.8	275.2	270.2
60°	370.3	353.9	343.7	323.4	301.9	282.8	271.4	260.0	249.9	243.5	233.4
62.5°	323.4	310.7	304.4	282.8	265.1	247.3	237.2	225.8	218.1	206.7	194.1
65°	282.8	272.7	265.1	247.3	230.8	214.3	204.2	190.2	180.1	173.8	172.5
67.5°	247.3	239.7	228.3	211.8	195.3	182.6	171.2	159.8	158.5	156.0	156.0
70°	208.0	200.4	194.1	176.3	162.3	148.4	145.9	142.1	138.2	137.0	134.4
72.5°	173.8	167.4	159.8	144.6	130.6	126.8	124.3	121.8	118.0	116.7	115.4
75°	140.8	131.9	126.8	112.9	109.1	106.5	104.0	100.2	97.7	96.4	93.9
77.5°	107.8	98.9	98.9	91.3	88.8	85.0	82.4	79.9	78.6	76.1	76.1
80°	76.1	76.1	73.6	69.8	66.0	64.7	60.9	59.6	58.3	59.6	57.1
82.5°	55.8	50.7	50.7	48.2	45.7	44.4	41.9	41.9	40.6	40.6	40.6
85°	31.7	31.7	30.4	27.9	26.6	26.6	25.4	25.4	24.1	24.1	22.8
87.5°	12.7	11.4	12.7	11.4	11.4	10.1	10.1	10.1	8.9	10.1	8.9
90°	13.0	14.5	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1
92.5°	32.5	33.5	33.6	33.9	34.1	34.4	34.6	34.8	35.1	35.3	35.6
95°	68.0	69.2	69.4	69.9	70.4	70.9	71.4	71.4	71.4	71.4	71.4
97.5°	106.1	107.2	107.7	108.7	109.6	110.6	111.6	111.6	111.6	111.6	111.6
100°	149.7	150.7	151.1	151.8	152.5	153.3	154.0	154.0	154.0	154.0	154.0
102.5°	194.6	195.3	195.8	196.8	197.8	198.8	199.8	200.0	200.3	200.5	200.8
105°	242.9	243.3	243.6	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6
107.5°	295.3	295.8	295.8	295.8	295.8	295.8	295.8	296.0	296.3	296.5	296.8
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	400.0	400.7	400.6	400.3	400.1	399.8	399.6	398.9	398.1	397.4	396.7
115°	452.5	453.2	453.0	452.5	452.0	451.5	451.0	450.8	450.5	450.3	450.0
117.5°	506.9	507.9	507.3	506.0	504.8	503.5	502.3	501.6	500.8	500.1	499.4
120°	559.4	560.4	559.4	557.4	555.4	553.4	551.4	551.4	551.4	551.4	551.4
122.5°	609.4	610.6	610.0	608.7	607.5	606.2	605.0	604.3	603.5	602.8	602.1
125°	658.6	659.7	659.3	658.6	657.9	657.1	656.4	655.6	654.9	654.1	653.4
127.5°	709.7	711.1	710.6	709.6	708.6	707.6	706.6	705.6	704.6	703.6	702.6
130°	757.5	759.1	758.8	758.3	757.8	757.3	756.8	756.3	755.8	755.3	754.8
132.5°	805.9	807.1	807.2	807.5	807.7	808.0	808.2	807.0	805.7	804.5	803.2
135°	851.4	852.8	853.1	853.6	854.1	854.6	855.1	854.8	854.6	854.3	854.0
137.5°	898.6	899.7	899.9	900.4	900.9	901.4	901.9	901.7	901.4	901.2	900.9
140°	942.1	943.2	943.8	945.1	946.3	947.6	948.8	948.8	948.8	948.8	948.8
142.5°	986.8	987.9	988.3	989.0	989.7	990.5	991.2	991.5	991.7	992.0	992.3
145°	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8	1035.0	1035.3	1035.5	1035.8
147.5°	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7	1073.2	1073.7	1074.2	1074.7
150°	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5	1109.2	1110.0	1110.7	1111.4
152.5°	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2	1145.2	1146.2	1147.1	1148.1
155°	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2	1174.4	1175.7	1176.9	1178.2
157.5°	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1	1202.8	1204.6	1206.3	1208.0
160°	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8	1228.3	1229.8	1231.3	1232.8
162.5°	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1	1250.8	1252.6	1254.3	1256.0
165°	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1269.8	1271.6	1273.3	1275.0
167.5°	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1286.5	1288.3	1290.0	1291.7
170°	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2	1299.9	1301.7	1303.4	1305.1
172.5°	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3	1310.0	1311.8	1313.5	1315.2
175°	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0	1316.7	1318.5	1320.2	1321.9
177.5°	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4	1320.9	1322.4	1323.9	1325.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1746.5	1743.9	1736.3	1738.9	1735.1	1735.1	1732.5	1732.5	1732.5	1738.9	1735.1
5°	1651.3	1642.5	1633.6	1629.8	1626.0	1622.2	1622.2	1620.9	1632.3	1629.8	1639.9
7.5°	1533.4	1530.9	1513.1	1513.1	1506.8	1504.2	1510.6	1511.8	1513.1	1515.6	1522.0
10°	1428.1	1421.8	1396.4	1398.9	1395.1	1390.1	1393.9	1391.3	1400.2	1402.8	1400.2
12.5°	1303.8	1292.4	1264.5	1250.6	1235.3	1223.9	1237.9	1227.7	1263.2	1273.4	1301.3
15°	1138.9	1117.4	1098.4	1098.4	1084.4	1074.3	1080.6	1092.0	1099.6	1111.0	1116.1
17.5°	1028.6	1019.7	1004.5	995.6	991.8	988.0	988.0	993.1	1009.6	1008.3	1018.5
20°	934.7	929.7	922.1	910.6	906.8	904.3	904.3	904.3	915.7	925.9	932.2
22.5°	870.1	866.3	861.2	846.0	838.4	835.8	842.2	846.0	854.8	862.5	868.8
25°	805.4	796.5	787.6	782.5	778.7	778.7	781.3	782.5	786.4	790.2	797.8
27.5°	752.1	745.8	733.1	719.1	719.1	715.3	717.9	720.4	729.3	742.0	748.3
30°	692.5	691.2	686.2	681.1	676.0	673.5	678.5	682.4	683.6	690.0	690.0
32.5°	649.4	640.5	631.6	626.5	624.0	622.7	624.0	629.1	629.1	636.7	645.6
35°	606.3	601.2	592.3	583.4	580.9	574.5	579.6	584.7	593.6	597.4	601.2
37.5°	559.3	553.0	549.2	546.6	541.6	542.8	539.0	546.6	554.3	553.0	555.5
40°	523.8	512.4	501.0	499.7	498.4	497.2	497.2	498.4	503.5	508.6	516.2
42.5°	478.2	474.3	464.2	454.1	451.5	449.0	446.4	451.5	461.7	470.5	474.3
45°	431.2	426.2	423.6	416.0	410.9	409.7	407.1	413.5	422.3	426.2	428.7
47.5°	388.1	386.8	379.2	380.5	376.7	378.0	376.7	380.5	380.5	384.3	386.8
50°	358.9	355.1	351.3	348.8	345.0	345.0	343.7	345.0	350.1	355.1	353.9
52.5°	329.8	323.4	322.2	320.9	318.3	320.9	317.1	318.3	323.4	326.0	324.7
55°	295.5	294.2	291.7	289.2	287.9	286.6	286.6	286.6	291.7	295.5	296.8
57.5°	268.9	262.5	257.5	257.5	252.4	251.1	253.7	254.9	258.7	261.3	263.8
60°	232.1	229.6	222.0	218.1	210.5	209.3	209.3	214.3	220.7	229.6	232.1
62.5°	192.8	189.0	187.7	187.7	187.7	187.7	187.7	187.7	187.7	189.0	189.0
65°	171.2	172.5	171.2	170.0	171.2	171.2	170.0	170.0	170.0	171.2	172.5
67.5°	153.5	152.2	153.5	152.2	150.9	150.9	149.7	150.9	152.2	153.5	153.5
70°	133.2	133.2	131.9	133.2	131.9	130.6	129.4	129.4	131.9	133.2	133.2
72.5°	114.1	114.1	112.9	112.9	110.3	110.3	111.6	110.3	110.3	114.1	114.1
75°	95.1	93.9	92.6	92.6	91.3	91.3	91.3	90.1	92.6	92.6	93.9
77.5°	74.8	74.8	74.8	73.6	73.6	72.3	72.3	73.6	73.6	73.6	74.8
80°	57.1	57.1	57.1	55.8	54.5	54.5	54.5	54.5	54.5	55.8	54.5
82.5°	39.3	39.3	39.3	39.3	39.3	38.0	38.0	38.0	39.3	39.3	38.0
85°	24.1	22.8	24.1	24.1	22.8	24.1	22.8	22.8	21.6	21.6	22.8
87.5°	10.1	8.9	7.6	7.6	8.9	7.6	7.6	7.6	8.9	7.6	7.6
90°	36.8	36.9	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	36.8
92.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.2	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	153.9	153.6	153.4	153.1	152.9	153.1	153.4	153.6	153.9	154.0
102.5°	200.9	200.8	200.5	200.3	200.0	199.8	200.0	200.3	200.5	200.8	200.9
105°	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.9	296.3	295.0	293.8	292.5	291.3	292.5	293.8	295.0	296.3	296.9
110°	347.2	346.8	346.1	345.3	344.6	343.8	344.6	345.3	346.1	346.8	347.2

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	396.3	396.0	395.5	395.0	394.5	394.0	394.5	395.0	395.5	396.0	396.3
115°	449.9	449.5	448.8	448.0	447.3	446.5	447.3	448.0	448.8	449.5	449.9
117.5°	499.0	498.6	497.9	497.1	496.4	495.6	496.4	497.1	497.9	498.6	499.0
120°	551.4	551.0	550.3	549.6	548.8	548.1	548.8	549.6	550.3	551.0	551.4
122.5°	601.7	601.4	600.9	600.4	599.9	599.4	599.9	600.4	600.9	601.4	601.7
125°	653.0	652.9	652.6	652.4	652.1	651.9	652.1	652.4	652.6	652.9	653.0
127.5°	702.1	701.7	701.0	700.3	699.5	698.8	699.5	700.3	701.0	701.7	702.1
130°	754.6	754.1	753.1	752.1	751.1	750.1	751.1	752.1	753.1	754.1	754.6
132.5°	802.6	802.2	801.5	800.7	800.0	799.2	800.0	800.7	801.5	802.2	802.6
135°	853.9	853.5	852.8	852.1	851.3	850.6	851.3	852.1	852.8	853.5	853.9
137.5°	900.8	900.3	899.3	898.4	897.4	896.4	897.4	898.4	899.3	900.3	900.8
140°	948.8	948.3	947.3	946.4	945.4	944.4	945.4	946.4	947.3	948.3	948.8
142.5°	992.4	991.9	990.9	989.9	988.9	987.9	988.9	989.9	990.9	991.9	992.4
145°	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4	1033.4	1034.4	1035.4	1035.9
147.5°	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5	1072.5	1073.5	1074.5	1075.0
150°	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2	1110.0	1110.7	1111.4	1111.8
152.5°	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2	1146.2	1147.1	1148.1	1148.6
155°	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2	1176.9	1177.7	1178.4	1178.8
157.5°	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5	1205.8	1207.0	1208.3	1208.9
160°	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0	1231.0	1232.0	1233.0	1233.5
162.5°	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5	1253.8	1255.0	1256.3	1256.9
165°	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5	1272.8	1274.0	1275.3	1275.9
167.5°	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3	1289.5	1290.8	1292.0	1292.6
170°	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8	1302.3	1303.8	1305.3	1306.0
172.5°	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9	1312.4	1313.9	1315.4	1316.1
175°	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6	1319.1	1320.6	1322.1	1322.8
177.5°	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9	1322.4	1323.9	1325.4	1326.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1	1825.1
2.5°	1738.9	1745.2	1742.7	1728.7	1742.7	1746.5	1754.1	1761.7	1766.8	1774.4	1780.7
5°	1629.8	1642.5	1650.1	1642.5	1667.8	1671.6	1689.4	1699.5	1714.8	1727.4	1737.6
7.5°	1527.0	1537.2	1552.4	1555.0	1570.2	1587.9	1613.3	1638.7	1662.8	1675.4	1686.9
10°	1416.7	1434.5	1457.3	1452.2	1475.0	1502.9	1529.6	1570.2	1590.5	1613.3	1633.6
12.5°	1306.4	1317.8	1348.2	1358.4	1391.3	1412.9	1449.7	1475.0	1525.8	1552.4	1570.2
15°	1113.6	1160.5	1198.6	1244.2	1287.3	1327.9	1360.9	1406.6	1450.9	1471.2	1500.4
17.5°	1026.1	1047.6	1070.5	1093.3	1149.1	1221.4	1279.7	1329.2	1367.2	1393.9	1428.1
20°	934.7	956.3	981.7	1003.2	1037.5	1089.5	1161.8	1246.8	1292.4	1320.3	1353.3
22.5°	870.1	890.4	906.8	925.9	952.5	990.6	1045.1	1150.4	1211.2	1245.5	1274.7
25°	800.3	825.7	843.4	857.4	878.9	920.8	965.2	1024.8	1133.9	1160.5	1201.1
27.5°	752.1	759.7	780.0	801.6	823.1	846.0	891.6	942.4	1015.9	1074.3	1123.7
30°	695.0	714.1	733.1	742.0	761.0	794.0	821.9	876.4	933.5	979.1	1038.7
32.5°	651.9	663.3	676.0	697.6	715.3	738.2	766.1	811.7	859.9	889.1	934.7
35°	603.7	611.3	638.0	646.8	664.6	687.4	715.3	750.8	802.8	825.7	858.6
37.5°	558.1	575.8	583.4	603.7	620.2	643.0	663.3	703.9	738.2	764.8	795.2
40°	522.5	530.2	544.1	561.9	575.8	593.6	618.9	648.1	684.9	706.4	733.1
42.5°	479.4	485.8	503.5	513.7	536.5	553.0	568.2	603.7	636.7	653.2	679.8
45°	432.5	447.7	459.1	479.4	492.1	512.4	531.4	556.8	587.2	606.3	621.5
47.5°	391.9	407.1	418.5	437.6	457.9	466.7	487.0	513.7	541.6	556.8	578.4
50°	358.9	364.0	385.6	394.4	416.0	433.8	447.7	470.5	501.0	509.9	527.6
52.5°	327.2	331.0	345.0	356.4	375.4	390.6	408.4	430.0	455.3	469.3	483.2
55°	299.3	301.9	308.2	320.9	333.6	352.6	369.1	389.4	410.9	426.2	438.8
57.5°	267.6	272.7	277.8	285.4	298.1	315.8	333.6	352.6	370.3	380.5	397.0
60°	230.8	238.4	247.3	256.2	265.1	277.8	298.1	315.8	332.3	341.2	353.9
62.5°	191.5	206.7	214.3	224.5	232.1	243.5	258.7	279.0	290.4	301.9	312.0
65°	172.5	173.8	175.0	185.2	199.1	210.5	224.5	239.7	257.5	265.1	272.7
67.5°	153.5	154.7	157.3	158.5	163.6	176.3	191.5	208.0	222.0	227.0	234.6
70°	134.4	134.4	139.5	140.8	142.1	143.3	156.0	172.5	185.2	191.5	200.4
72.5°	114.1	115.4	118.0	119.2	121.8	124.3	128.1	137.0	152.2	158.5	168.7
75°	93.9	95.1	96.4	97.7	101.5	102.7	106.5	111.6	118.0	125.6	131.9
77.5°	74.8	74.8	76.1	78.6	81.2	82.4	86.2	88.8	91.3	95.1	100.2
80°	55.8	57.1	57.1	59.6	59.6	60.9	62.1	66.0	68.5	71.0	73.6
82.5°	38.0	40.6	40.6	40.6	41.9	43.1	44.4	44.4	46.9	48.2	52.0
85°	22.8	24.1	24.1	24.1	22.8	25.4	25.4	26.6	26.6	26.6	27.9
87.5°	8.9	7.6	8.9	8.9	8.9	10.1	8.9	8.9	10.1	11.4	11.4
90°	37.1	37.6	38.1	38.6	39.1	33.6	28.2	22.7	17.2	14.5	13.0
92.5°	35.6	35.3	35.1	34.8	34.6	34.4	34.1	33.9	33.6	33.5	32.5
95°	71.4	71.4	71.4	71.4	71.4	70.9	70.4	69.9	69.4	69.2	68.0
97.5°	111.6	111.6	111.6	111.6	111.6	110.6	109.6	108.7	107.7	107.2	106.1
100°	154.0	154.0	154.0	154.0	154.0	153.3	152.5	151.8	151.1	150.7	149.7
102.5°	200.8	200.5	200.3	200.0	199.8	198.8	197.8	196.8	195.8	195.3	194.6
105°	247.6	247.1	246.6	246.1	245.6	245.1	244.6	244.1	243.6	243.3	242.9
107.5°	296.8	296.5	296.3	296.0	295.8	295.8	295.8	295.8	295.8	295.8	295.3
110°	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.5

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	396.7	397.4	398.1	398.9	399.6	399.8	400.1	400.3	400.6	400.7	400.0
115°	450.0	450.3	450.5	450.8	451.0	451.5	452.0	452.5	453.0	453.2	452.5
117.5°	499.4	500.1	500.8	501.6	502.3	503.5	504.8	506.0	507.3	507.9	506.9
120°	551.4	551.4	551.4	551.4	551.4	553.4	555.4	557.4	559.4	560.4	559.4
122.5°	602.1	602.8	603.5	604.3	605.0	606.2	607.5	608.7	610.0	610.6	609.4
125°	653.4	654.1	654.9	655.6	656.4	657.1	657.9	658.6	659.3	659.7	658.6
127.5°	702.6	703.6	704.6	705.6	706.6	707.6	708.6	709.6	710.6	711.1	709.7
130°	754.8	755.3	755.8	756.3	756.8	757.3	757.8	758.3	758.8	759.1	757.5
132.5°	803.2	804.5	805.7	807.0	808.2	808.0	807.7	807.5	807.2	807.1	805.9
135°	854.0	854.3	854.6	854.8	855.1	854.6	854.1	853.6	853.1	852.8	851.4
137.5°	900.9	901.2	901.4	901.7	901.9	901.4	900.9	900.4	899.9	899.7	898.6
140°	948.8	948.8	948.8	948.8	948.8	947.6	946.3	945.1	943.8	943.2	942.1
142.5°	992.3	992.0	991.7	991.5	991.2	990.5	989.7	989.0	988.3	987.9	986.8
145°	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8	1030.3	1028.8	1028.1	1027.2
147.5°	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7	1069.8	1068.8	1068.3	1067.2
150°	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5	1105.5	1104.5	1104.0	1103.3
152.5°	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7	1140.5	1139.2	1138.6	1137.9
155°	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7	1170.9	1170.2	1169.8	1169.4
157.5°	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1	1199.6	1199.1	1198.9	1198.6
160°	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3	1226.1	1225.8	1225.7	1225.4
162.5°	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6	1248.4	1248.1	1248.0	1248.0
165°	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1268.2
167.5°	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1285.2
170°	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7	1298.9	1299.2	1299.3	1299.7
172.5°	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8	1309.0	1309.3	1309.4	1309.8
175°	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0	1316.5	1317.0	1317.2	1317.6
177.5°	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4	1320.9	1321.4	1321.7	1322.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1825.1	1825.1	1825.1	1825.1
2.5°	1792.1	1788.3	1811.1	1836.5
5°	1755.3	1761.7	1790.9	1826.4
7.5°	1717.3	1731.2	1765.5	1812.4
10°	1664.0	1689.4	1741.4	1789.6
12.5°	1612.0	1646.3	1695.7	1752.8
15°	1553.7	1591.7	1652.6	1721.1
17.5°	1489.0	1532.1	1603.1	1678.0
20°	1420.5	1477.6	1552.4	1633.6
22.5°	1344.4	1412.9	1490.3	1580.3
25°	1270.8	1345.7	1423.0	1527.0
27.5°	1198.6	1272.1	1358.4	1463.6
30°	1126.3	1193.5	1286.1	1398.9
32.5°	1048.9	1118.7	1216.3	1331.7
35°	977.9	1047.6	1138.9	1253.1
37.5°	901.8	976.6	1064.1	1182.1
40°	813.0	900.5	985.5	1098.4
42.5°	739.4	832.0	914.5	1021.0
45°	681.1	768.6	837.1	941.1
47.5°	626.5	697.6	767.3	863.7
50°	574.5	629.1	701.4	787.6
52.5°	521.3	568.2	630.4	711.5
55°	473.1	517.5	573.3	635.4
57.5°	428.7	460.4	516.2	572.0
60°	379.2	412.2	455.3	502.3
62.5°	337.4	362.7	403.3	442.6
65°	293.0	317.1	347.5	384.3
67.5°	252.4	274.0	298.1	327.2
70°	215.6	232.1	249.9	275.2
72.5°	176.3	194.1	210.5	230.8
75°	144.6	152.2	166.1	180.1
77.5°	111.6	121.8	129.4	140.8
80°	79.9	88.8	91.3	100.2
82.5°	53.3	58.3	63.4	66.0
85°	30.4	33.0	38.0	39.3
87.5°	11.4	12.7	15.2	17.8
90°	10.0	7.1	4.1	1.1
92.5°	30.5	28.6	26.6	24.6
95°	65.5	63.0	60.5	58.0
97.5°	103.8	101.6	99.3	97.1
100°	147.7	145.8	143.8	141.8
102.5°	193.1	191.6	190.1	188.6
105°	242.2	241.5	240.7	240.0
107.5°	294.3	293.3	292.3	291.3
110°	345.0	343.5	342.0	340.5

TEST NUMBER: P1000094

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	398.5	397.0	395.5	394.0
115°	451.0	449.5	448.0	446.5
117.5°	504.9	503.0	501.0	499.0
120°	557.4	555.4	553.4	551.4
122.5°	606.9	604.4	601.9	599.4
125°	656.4	654.1	651.9	649.7
127.5°	707.0	704.3	701.5	698.8
130°	754.3	751.0	747.8	744.6
132.5°	803.4	800.9	798.4	795.9
135°	848.7	846.0	843.2	840.5
137.5°	896.4	894.1	891.9	889.7
140°	939.9	937.6	935.4	933.2
142.5°	984.6	982.3	980.1	977.9
145°	1025.5	1023.8	1022.0	1020.3
147.5°	1064.9	1062.7	1060.4	1058.2
150°	1101.8	1100.3	1098.8	1097.3
152.5°	1136.4	1134.9	1133.4	1131.9
155°	1168.7	1168.0	1167.2	1166.5
157.5°	1198.1	1197.6	1197.1	1196.6
160°	1224.9	1224.4	1223.9	1223.4
162.5°	1248.0	1248.0	1248.0	1248.0
165°	1268.5	1268.7	1269.0	1269.2
167.5°	1285.9	1286.7	1287.4	1288.2
170°	1300.4	1301.2	1301.9	1302.7
172.5°	1310.5	1311.2	1312.0	1312.7
175°	1318.3	1319.0	1319.8	1320.5
177.5°	1322.8	1323.5	1324.3	1325.0
180°	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)