

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001652

Luminaire Tested: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001652
REPORT IS A COMBINATION OF REPORTS P996274 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5520.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001652

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001652

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19
6	60	48	40	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	26	46	36	29	24	29	24	20	24	20	17	18	15	13
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1001652

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.2
10°-20°	187.8	3.4
20°-30°	284.0	5.1
30°-40°	343.6	6.2
40°-50°	363.2	6.6
50°-60°	341.9	6.2
60°-70°	283.7	5.1
70°-80°	199.1	3.6
80°-90°	114.3	2.1
90°-100°	100.7	1.8
100°-110°	272.6	4.9
110°-120°	459.3	8.3
120°-130°	559.7	10.1
130°-140°	586.8	10.6
140°-150°	542.8	9.8
150°-160°	436.4	7.9
160°-170°	281.4	5.1
170°-180°	97.0	1.8
0°-30°	537.4	9.7
0°-40°	881.0	16.0
0°-60°	1586.1	28.7
0°-90°	2183.2	39.6
90°-120°	832.7	15.1
90°-150°	2521.9	45.7
90°-180°	3337.0	60.5
0°-180°	5520.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	15	54	94	121	128	11
95°	52	52	84	110	117	60
105°	237	257	289	316	294	248
115°	434	443	467	486	491	427
125°	606	609	626	643	649	542
135°	750	749	758	772	778	578
145°	864	865	865	870	875	540
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1001652

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	14.7	54.1	93.5	120.6	128.3
92.5°	23.1	48.6	88.1	114.4	120.6
95°	52.1	51.6	84.2	109.7	117.4
97.5°	89.5	128.8	80.3	104.3	112.1
100°	133.7	167.7	92.5	100.4	106.6
102.5°	184.1	210.4	248.9	97.3	103.5
105°	236.8	256.9	289.3	315.6	294.3
107.5°	286.5	301.8	334.4	357.5	366.1
110°	336.1	349.1	380.9	400.2	408.7



TEST NUMBER: P1001652

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.1	398.0	425.1	441.4	450.6
115°	433.7	443.0	467.0	485.7	491.1
117.5°	478.8	486.5	512.0	527.5	533.7
120°	523.9	529.2	551.0	568.0	572.7
122.5°	566.6	568.2	590.6	606.8	610.7
125°	606.3	608.6	626.4	643.4	648.9
127.5°	645.2	645.2	664.5	677.8	682.4
130°	681.9	681.8	696.5	711.3	715.9
132.5°	716.2	716.9	729.3	743.3	747.2
135°	749.8	749.0	757.6	771.5	777.6
137.5°	780.3	779.6	786.5	799.7	802.8
140°	810.1	810.9	813.1	825.5	830.2
142.5°	836.1	839.2	839.1	849.2	852.3
145°	863.6	865.1	865.1	870.5	875.1
147.5°	885.0	888.8	888.0	889.6	893.4
150°	908.7	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)