

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000098

Luminaire Tested: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000098
REPORT IS A COMBINATION OF REPORTS P988657 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6932.6 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000098

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1000098

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	71	64	59	73	66	60	55	54	50	46	44	41	38	35	33	31
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22182	22182	22182
5°	22218	21103	20947
10°	21999	20016	19354
15°	21696	18731	17540
20°	21297	17270	15642
25°	20886	15770	13905
30°	20337	14311	12008
35°	19797	12840	10380
40°	19249	11394	8702
45°	18612	9901	7239
50°	17954	8462	5894
55°	17267	7025	4679
60°	16471	5617	3539
65°	15553	4283	2877
70°	14443	3107	2289
75°	13051	2371	1748
80°	11034	1605	1173
85°	7698	735	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18612 cd/sqm

TEST NUMBER: P1000098

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	1.9
10°-20°	360.5	5.2
20°-30°	506.2	7.3
30°-40°	551.8	8.0
40°-50°	507.1	7.3
50°-60°	398.3	5.7
60°-70°	259.2	3.7
70°-80°	133.5	1.9
80°-90°	37.8	0.5
90°-100°	235.3	3.4
100°-110°	795.5	11.5
110°-120°	836.1	12.1
120°-130°	687.6	9.9
130°-140°	552.5	8.0
140°-150°	417.4	6.0
150°-160°	293.4	4.2
160°-170°	172.8	2.5
170°-180°	56.2	0.8
0°-30°	998.1	14.4
0°-40°	1549.8	22.4
0°-60°	2455.2	35.4
0°-90°	2885.7	41.6
90°-120°	1866.9	26.9
90°-150°	3524.5	50.8
90°-180°	4047.0	58.4
0°-180°	6932.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1401	1401	1401	1401	1401	
5°	1401	1395	1378	1390	1386	133
15°	1333	1319	1276	1252	1239	376
25°	1210	1169	1086	1034	1014	556
35°	1042	978	866	786	758	652
45°	852	767	634	544	514	658
55°	648	549	412	336	312	579
65°	438	335	221	178	174	434
75°	233	145	102	93	91	247
85°	54	28	24	24	24	63
90°	1	15	38	36	37	5
95°	39	96	438	165	127	40
105°	136	205	827	1478	1258	145
115°	240	303	692	1428	1655	238
125°	335	396	665	1157	1343	298
135°	393	469	658	972	1113	304
145°	449	516	654	812	888	282
155°	510	551	635	718	747	235
165°	556	573	608	645	655	157
175°	579	580	585	592	590	55
180°	580	580	580	580	580	

TEST NUMBER: P1000098

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1401.3	1401.3	1401.3	1401.3	1401.3
2.5°	1407.7	1401.3	1387.4	1400.1	1397.5
5°	1401.3	1395.0	1378.5	1389.9	1386.1
7.5°	1389.9	1382.3	1364.5	1369.6	1363.3
10°	1374.7	1365.8	1340.5	1336.6	1329.0
12.5°	1355.7	1344.3	1310.0	1302.4	1288.5
15°	1332.8	1318.9	1275.8	1251.7	1239.0
17.5°	1306.2	1285.9	1232.7	1204.8	1184.5
20°	1275.8	1250.4	1187.0	1155.3	1127.4
22.5°	1242.8	1213.6	1140.1	1097.0	1077.9
25°	1209.8	1169.2	1085.5	1033.6	1014.5
27.5°	1170.5	1127.4	1034.8	975.2	946.1
30°	1128.7	1080.5	979.0	914.3	880.1
32.5°	1088.1	1029.8	925.8	849.7	818.0
35°	1042.4	977.8	866.2	786.3	758.4
37.5°	998.0	928.3	810.4	722.9	691.2
40°	951.1	875.0	752.0	662.0	629.0
42.5°	902.9	821.8	693.7	599.8	568.1
45°	852.2	767.2	634.1	544.0	513.6
47.5°	804.0	714.0	577.0	487.0	459.1
50°	750.8	660.7	521.2	433.7	407.1
52.5°	698.8	603.6	468.0	384.3	360.2
55°	648.0	549.1	412.2	336.1	312.0
57.5°	596.0	494.6	362.7	291.7	271.4
60°	542.8	441.3	310.7	246.0	225.7
62.5°	490.8	389.3	266.3	205.4	195.3
65°	437.5	334.8	220.7	177.5	173.7
67.5°	386.8	284.1	177.5	156.0	152.2
70°	333.5	234.6	147.1	134.4	129.4
72.5°	282.8	189.0	123.0	112.9	110.3
75°	233.3	144.6	101.5	92.6	91.3
77.5°	183.9	102.7	79.9	74.8	72.3
80°	138.2	73.6	60.9	55.8	55.8
82.5°	96.4	49.5	41.8	39.3	39.3
85°	54.5	27.9	24.1	24.1	24.1
87.5°	20.3	10.1	10.1	8.9	8.9
90°	1.1	15.0	38.0	36.2	36.8
92.5°	16.7	53.0	171.9	79.2	68.1
95°	39.1	96.0	437.6	165.2	127.3
97.5°	58.0	126.7	713.3	331.5	213.2
100°	86.0	155.2	881.8	660.2	399.6
102.5°	111.6	180.8	887.4	1116.2	779.1
105°	136.2	205.4	827.1	1478.5	1258.0
107.5°	163.0	230.0	771.3	1609.6	1580.6
110°	189.8	255.0	733.4	1588.4	1712.3

TEST NUMBER: P1000098

CATALOG NUMBER: SA2XXRDIP-B865D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.3	279.0	708.8	1516.4	1710.1
115°	240.0	303.0	692.1	1428.2	1655.4
117.5°	266.8	327.0	683.1	1344.0	1572.8
120°	291.3	350.5	675.3	1268.6	1493.5
122.5°	314.8	374.5	670.9	1210.1	1410.9
125°	334.9	396.2	665.3	1157.0	1342.8
127.5°	351.6	416.9	661.9	1111.8	1279.2
130°	366.1	435.4	659.7	1066.1	1226.8
132.5°	379.5	453.2	658.6	1018.6	1172.1
135°	392.9	468.8	657.5	972.2	1112.9
137.5°	405.2	482.2	657.5	925.4	1056.0
140°	419.7	494.5	656.4	884.0	996.8
142.5°	434.2	504.6	656.4	844.4	937.7
145°	448.7	515.7	654.1	812.1	888.5
147.5°	464.4	524.6	650.8	783.6	845.0
150°	480.0	533.6	647.4	759.0	807.0
152.5°	495.6	542.5	641.8	738.4	774.7
155°	510.1	550.8	635.1	718.3	746.8
157.5°	522.4	557.6	628.4	699.3	722.2
160°	534.7	564.2	621.8	680.3	698.8
162.5°	547.0	569.3	616.2	662.5	676.4
165°	555.9	572.6	608.4	645.2	655.2
167.5°	563.7	576.0	601.7	629.6	635.1
170°	571.5	577.6	596.1	615.0	617.3
172.5°	576.0	579.4	589.4	602.2	602.8
175°	579.3	579.9	584.9	592.2	590.5
177.5°	581.6	580.5	580.5	584.9	581.6
180°	580.5	580.5	580.5	580.5	580.5

(END OF REPORT)