

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001659

Luminaire Tested: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001659
REPORT IS A COMBINATION OF REPORTS P996281 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5611.0 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001659

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1001659

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31
4	73	62	55	49	67	57	51	45	48	43	39	39	36	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1001659

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.6
10°-20°	255.3	4.6
20°-30°	375.8	6.7
30°-40°	436.8	7.8
40°-50°	436.8	7.8
50°-60°	382.0	6.8
60°-70°	283.6	5.1
70°-80°	160.9	2.9
80°-90°	48.2	0.9
90°-100°	33.7	0.6
100°-110°	221.9	4.0
110°-120°	423.7	7.6
120°-130°	537.9	9.6
130°-140°	575.4	10.3
140°-150°	538.1	9.6
150°-160°	433.9	7.7
160°-170°	279.8	5.0
170°-180°	96.4	1.7
0°-30°	721.7	12.9
0°-40°	1158.6	20.6
0°-60°	1977.4	35.2
0°-90°	2470.1	44.0
90°-120°	679.3	12.1
90°-150°	2330.7	41.5
90°-180°	3141.0	56.0
0°-180°	5611.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	2	11	17	21	23	5
95°	42	16	17	21	22	51
105°	228	233	237	244	216	239
115°	427	429	428	430	430	420
125°	600	603	601	604	604	536
135°	744	743	746	748	749	573
145°	858	860	860	861	862	536
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1001659

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	2.3	10.6	16.7	21.3	22.8
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.8	15.9	16.7	21.3	22.0
97.5°	79.7	96.4	16.7	20.5	21.3
100°	124.5	138.2	33.4	20.5	21.3
102.5°	174.6	183.7	192.8	22.0	22.0
105°	228.5	233.1	236.9	243.7	216.4
107.5°	277.9	280.1	285.5	289.3	292.3
110°	328.0	330.2	334.8	336.3	338.6

TEST NUMBER: P1001659

CATALOG NUMBER: SA4XXDIP-B575D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.6	381.1	382.6	381.9	384.9
115°	426.7	428.9	428.2	429.7	429.7
117.5°	471.5	474.5	476.8	476.0	476.0
120°	517.0	520.0	519.3	520.8	519.3
122.5°	559.5	561.0	562.6	563.3	561.8
125°	599.8	602.8	601.3	603.6	604.3
127.5°	638.5	639.2	643.0	642.3	641.5
130°	675.7	676.4	678.7	679.5	679.5
132.5°	709.8	711.4	714.4	715.2	714.4
135°	744.0	743.3	746.3	747.8	749.3
137.5°	774.4	774.4	778.2	779.7	778.9
140°	804.0	805.5	807.0	809.3	810.1
142.5°	830.6	833.6	834.4	835.9	835.9
145°	857.9	860.2	860.2	860.9	862.4
147.5°	879.1	883.7	882.9	883.7	884.5
150°	902.7	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)